

ASK-400

With many great features, this printer is the key to success for your on-site photo business.



Compact Size

170mm high, foot print 0.1m²

High Speed

8.4 sec (Standard 4"× 6")

High Durability

200,000 prints (Standard 4"× 6")

Sticker Printing

Standard Print



Sticker Print



Value-added Sticker printing is suitable for images shot by smartphone.



*Paper tray optional

Sticker printing

Put stickers on any suitable surface after peeling off the backing.

A variety of functions for smooth operation




Compact Size

This compactly 170 mm-high printer can be installed in an area equivalent 0.1 m² with minimal interference.



Easy Operation

Easily replace paper and ink ribbon by pulling out printer front panel.



Dust-Free Design

A separator creates different passages of air for the thermal head and power supply. The high air pressure in the printer prevents dust from entering.



Energy Saving Design

Consuming only 0.5W or less in sleep mode, the ASK-400 saves energy and lowers your costs.

ASK-400 Specifications

Printing method	Dye-sublimation thermal transfer (D2T2)
Foot print	0.10 m ²
Line-up of consumables (*1)	Standard Print : 5"×7", 6"×8" Sticker Print : 6"×8"
Print size (*2)	Standard Print : 3.5"×5", 5"×5", 5"×7", 4"×6", 6"×6", 6"×8" Sticker Print : 4"×6", 6"×8"
Surface finish (*3)	Glossy type, Matte type
Ribbon finish	Yellow, Magenta, Cyan and Overcoat
Printing resolution (*4)	300 × 300 dpi (Standard mode), 300 × 600 dpi (High Quality mode)
Operation for paper exchange	Semi-Auto Loading
Printer life	200,000 prints (Standard 4" × 6")
Number of prints	Standard 3.5" × 5": 460 sheets, 5" × 7": 230 sheets in 1 roll Standard 4" × 6": 400 sheets, 6" × 8": 200 sheets in 1 roll Sticker 4" × 6": 400 sheets, 6" × 8": 200 sheets in 1 roll

Print speed (*5)	Standard 3.5"×5": approx. 7.6 sec (Glossy type, Standard mode) Standard 4"×6": approx. 8.4 sec (Glossy type, Standard mode) Sticker 4"×6": approx. 13.0 sec (Glossy type, High Quality mode)
Dimensions (W×D×H)	10.8"×14.4"×6.7" (275 mm × 366 mm × 170 mm)
Weight	approx. 12 kg (26.4 lb)
Interface	USB 2.0 Type B connector
Power supply	100V-240 V 50 / 60 Hz
Driver software (*6)	Windows 7 / Windows 10 (32 bit / 64 bit)

*1 printer memorizes the consumable type (sticker or standard) which is first loaded into the printer and then the printer accepts only the same type of consumables.

*2 Sticker/Standard can use 6"×8" ribbon and divide it to 4"×6"×2 prints. Standard can use 5"×7" ribbon and divide it to 3.5"×5"×2 prints.

*3 Both are available with one media. Sticker media is limited to Glossy type.

*4 Stickers can be printed in High Quality mode only.

*5 Does not including data processing/transferring time and paper initialization/paper feed times.


In case of using the function of ribbon rewind.

*6 Windows 7 is only guaranteed to work(not be subject to future version upgrades or quality assurance) because Windows 7 is not supported by Microsoft Corporation.

Windows 7, Windows 10 are registered trademarks of Microsoft Corporation in the United States and other countries.

Specifications are subject to change without notice.

Dimensions (Installation space)



Specifications are subject to change without notice.

FUJIFILM

FUJIFILM Corporation

7-3, AKASAKA 9-CHOME, MINATO-KU, TOKYO 107-0052, JAPAN

Ref. No. PB-2201E (SK-22-04-F5BK5) ©2020 FUJIFILM Corporation