

FA-2 N3S NEG Fixer Start Up Kit

For Processing C-41 and Compatible Color Negative Films Through Process C-41SM



Catalog Number: 60005423 (2 x 3.9 L)

DESCRIPTION

This product is designed for mixing fresh N3 fixer working tank solution for all Noritsu C-41SM minilab processors' FIX tanks.

SAFE HANDLING INSTRUCTIONS

Please refer to Material Safety Data Sheets (MSDS) for specific chemical details. For emergencies, please contact CHEMTREC at 1-800-424-9300. You can obtain an MSDS by calling the Fujifilm Technical Hotline at 1-800-526-0851 Ext. 10.

HMIS INFORMATION

Hazardous Materials Identification System. Please refer to Section 3 in the MSDS for further information.

	Concentrate	Working Tank
Health	1	1
Flammability	0	0
Reactivity	0	0
Personal Protection	C	C

SPECS & RECOMMENDATIONS

Temperature	35 - 41° C 95 - 106° F
Processing Time	N3 = 2'00"
Starting Replenishment Rate	135-24
	15.3 ml/m

Refer to bulletin FA-2 Neg for additional specifications and replenishment pump setting recommendations.

SPECIFIC GRAVITY & pH

	pH @ 25° C	SpG @ 20° C	SpG @ 38° C
Replenisher Tank	Concentrates – Specifications Not Published		
Fresh Tank	7.40 ± 0.20	1.123 ± 0.020	1.115 ± 0.20

MIXING INSTRUCTIONS

N3 (FIX) Fresh Fixer Working Tank

3.9 Liters

To Fill Processor Fixer Working Tank . . .

- Mix fresh N3 fixer using above instructions.
- NOTE:** Repeat steps 2 through 5 for each FIX tank (there are 2 FIX tanks total)
- Remove the FIX filter from the FIX filter housing.
- Pour mixed fixer tank solution into the FIX circulation filter port.
- Fill to the designated fill line in tank.
- Reinstall the FIX filter.
- Remaining solution should be disposed of properly.

SHELF LIFE

	Concentrate	Working Tank
Time	U = 24 Months O = 2 Weeks	2 Weeks
Color	Clear, Pale Yellow	Clear, Pale Yellow
Odor	Slight Vinegar Odor	Slight Ammonia Odor

U = Unopened, O = Opened

The data contained in this photographic bulletin is believed to be true and accurate, but is offered solely for your consideration, investigation, and verification. Nothing herein shall be construed to be a warranty or guarantee by either FUJIFILM Hunt Chemicals or any of its affiliates, and all such warranties, implied or otherwise, including any implied warranty of merchantability, are hereby expressly disclaimed. You, of course, are fully responsible for any use and / or domestic or foreign sale of the product(s) described, and nothing in this photographic bulletin shall be construed to constitute permission or a recommendation to practice any invention covered by patent or patent application or know-how owned by FUJIFILM, its affiliates, or others.