



For the Processing of Color Paper compatible with RA-4 HR Process


PROCESS PARAMETERS

Process	Product Name	Cat. No.	To Make	Parts	Timing	Temp. (°C)	Repl. Rate	ml/m
CD P1	SP 161 P1R	822564	4x10L	2L Single	45"	35.0 ± 0.3	161ml/m ²	20.45
BF P2	CP RA B/F/R	830045	2x10L	A=1.44L B=2L	45"	35.0 ± 3.0	215ml/m ²	27.31
STB P3	CP 3R	822524	4x100L	1L Single	90"	35.0 ± 3.0	250ml/m ²	31.75

P1S Developer Starter = Universal Print Starter 6 x 1L 830070


REPLENISHER

P1R




WORKING TANK


P1




P2R



P2



P3R



P3

