

**FUJIFILM**

QUALITY  
FINISHES

CREATIVE  
EXPRESSION

ENDLESS  
POSSIBILITIES



**PURPOSE BUILT  
TO BRING QUALITY  
DUPLEX PHOTO  
PRODUCTS TO  
ON-SITE RETAIL**

.....  
**FUJIFILM CX 3240**  
CREATIVE DUPLEX PRINTER



0  
2  
4  
3  
2  
4  
0  
CX  
3  
2  
4  
0

# THE FUJIFILM CX 3240 CREATIVE DUPLEX PRINTER EASILY PRODUCES QUALITY, ON-SITE CREATIVE PRODUCTS THAT CONSUMERS LOVE TO PURCHASE.

## IT'S SMART + VERSATILE

Auto duplex printing on flat paper and scored paper for simple folded card products

Borderless printing with rounded corners or scalloped edge finishes

Handles paper of greater weight + thickness up to 120 lb cover (324 gsm)

Prints on paper from as small as 3.5" x 5" to as large as 8.5" x 14"

Up to a 5 tray configuration (including bypass), allows for extreme versatility in size and substrate preference

## PURPOSE-BUILT PRINTER AND QUALIFIED PAPERS MAKE THE MOST OF THESE CUSTOMER FAVORITES

Greeting cards, photo cards and invitations

Photobooks and calendars

Counter cards and so much more

## SMALL FOOTPRINT

Small footprint with big-time production

## EASY + EFFICIENT

No post cutting or finishing required

**CALL 877.845.1608  
TO LEARN MORE ABOUT  
THE FUJIFILM CX 3240  
CREATIVE DUPLEX PRINTER.**

<b>PRINT TECHNOLOGY</b>	LED Printhead
<b>PRINT RESOLUTION</b>	1200 x 2400 dpi
<b>PAPER SIZES</b>	Minimum: 3.5 x 5 in (88.9 x 127 mm) Maximum: 8.5 x 14 in (215.9 x 355.6 mm)
<b>DIMENSIONS (W X D X H); WEIGHT*</b>	18.5 x 21.1 x 17.5 in; (470 x 536 x 444 mm); Approximately 86 lb/39 kg (with toner cartridges)
<b>POWER REQUIREMENTS</b>	AC100-127V ±10%; 12 A; 50/60Hz ±3%
<b>ENVIRONMENT (WHEN PRINTING)</b>	Temperature: 41°F-90°F (5°C-32°C) Humidity: 15%-85%
<b>CONNECTIVITY</b>	Device Port x1 (USB 3.0) / Host Port x2 (USB 2.0) Ethernet 10/100/1000 Base-T
<b>CONSUMABLES**</b>	FUJIFILM Toner Cartridges: C, M, Y, K FUJIFILM Drum Cartridges: C, M, Y, K FUJIFILM Waste Toner Cartridge
<b>ROUTINE MAINTENANCE ITEMS**</b>	Fusing Unit, Transfer Roller, Maintenance Kit, Paper Roller Kit

\*Dimensions are for printer with 1 tray and no caster. Up to 3 additional trays may be purchased separately. \*\*Use of non FUJIFILM approved consumables, paper and routine maintenance items may affect performance, warranty and service contract availability. Descriptions and/or printer and paper specifications in this material are subject to change.

