Time is a series of moments. Now you can crop and shape your favorite ones.

instax SQUARE SQ20 captures the best moment of moving subjects and expresses it to the maximum possible effect in a single photo. The instax SQUARE SQ20 allows you to enjoy photography and prints like never before with speed, liveliness and a mysterious world view.







FRAME GRAB

Shoot a video up to 15 seconds long, use the dial on the back of the camera to select the frame that captures the moment best and print the photo.

TIMESHIFT COLLAGE

Four images can be taken with a time difference at one time.

"SEQUENCE"

Expresses the motion of the subject with a sequence filter to create a sense of action or whimsy.

SELFIE MIRROR

A mirror is included next to the lens to ensure the perfect selfie every time.





ZOOM

The SQ20 is the first camera in the instax series to include a zoom function. The digital zoom enables you to zoom in up to 4x and adjust the view angle however you want.





OTHER FEATURES

- \bullet Internal memory holds around 50 still pictures, and more can be saved by using a Micro SD card.
- \bullet Reprinting (the latest 50 photos are saved in the print history.)
- Index prints can be created with a four-frame or nine-frame layout.
- Comes with a built-in rechargeable battery.

SPECIFICATIONS

Image sensor	1/5-in., CMOS with primary color filter
Effective pixels	1920 x 1920
Storage media	Built-in memory, microSD/microSDHC memory card
Recording capacity (still picture)	Built-in memory: Approx. 50 files (still picture), Approx. 30 seconds (movie) microSD/microSDHC memory card: Approx. 1000 files per 1 gigabyte
Recording capacity (movie)	microSD/microSDHC memory card: Approx. 3 minutes (total) per 1 gigabyte
File system	Still picture: Compliant with Design Rule for Camera File System (DCF), Exif Ver.2.3, Compliant with JPEG and PIM Movie: $800 \times 800 \times 15$ fps, H.264 (No sound can be recorded.)
Focal length	Fixed as 33.4 mm (35-mm format equivalent)
Aperture	F2.4
Auto focus system	Single AF (Contrast-detect TTL, equipped with AF illuminator) Continuous AF (Only for movie shooting)
Focus range	10 cm/3.9 in. to ∞
Shutter speed	1/7500 sec. to 1/2 sec. (Auto), maximum 10 sec. in Bulb mode
Sensitivity	ISO 100 to 1600 (Auto)
Exposure control	Programmed AE
Exposure compensation	-2.0 EV to +2.0 EV in increments of 1/3 EV
Metering	256-segment through the lens (TTL) metering, Multi metering
White balance	Auto
Flash	Auto/Compulsory flash/Suppressed flash Effective range: Approx. 50 cm to 8 m/1.6 ft. to 26.2 ft.
Shooting mode	Standard, Double exposure, Bulb mode, Split, Collage, Time Shift Collage
Self-timer	Approx. 10 sec./Approx. 2 sec.
Image effect	21 Filters (18 for still picture, 3 for movie shooting only), Brightness adjustment, Vignette
Playback function	Trimming, Multi image playback

Film	FUJIFILM Instant Film "instax SQUARE" (Purchased separately)
Photo capacity	10 prints/pack
Film size	86 mm x 72 mm/3.4 in. x 2.8 in.
Image size	62 mm x 62 mm/2.4 in. x 2.4 in.
Supported image size	800 x 800 dots
Printing solution	12.5 dots/mm (318 dpi, 80 µm dot pitch)
Printing levels	256 levels per color (RGB)
Supported image format	JPEG (Some images saved with a photo editing/processing software may not be displayed or printed.) JPEG files captured from a movie file can be printed.
Printing time	Approx. 12 seconds
Print timing	Printing shortly after shooting/Printing after selecting image
Printing function	Images on built-in memory/micro SD card
Reprint	Printable up to the past 50 prints (Up to 50 images stored in print history)
Digital zoom	Up to 4 X in shooting/printing
LCD monitor	2.7-in. (6.9 cm) TFT color LCD monitor, Pixels: Approx. 230k-dots
External interface	Micro USB Micro-B (For charging/file copying)
Power supply	Li-ion battery (Built-in, Cannot be removed.)
Charging function	Built-in
Printing capacity	Approx. 100 prints (From when the battery is charged fully) * Varies depending on the conditions of use.
Charging time	Approx. 2 to 3 hours (Using 0.5 A USB port) * Varies depending on air temperature.
Dimension	119 mm x 50 mm x 127 mm/4.7 in. x 2 in. x 5 in. (W x D x H)
Weight	390 g/13.8 oz. (excluding film pack and memory card) 440 g/15.5 oz. (including film pack and memory card)
Operating environment	Temperature: 5 °C (41 °F) to 40 °C (104 °F) Humidity: 20% to 80% (no condensation)
	* Specifications above are subject to change for improvent

* Specifications above are subject to change for improvent.

instant film instax SQUARE

Film size: 86 mm x 72 mm Image size: 62 mm x 62 mm WHITE Frame

•10Sheets x 1Pack •10Sheets x 2Packs



BLACK Frame

•10Sheets x 1Pack



instax.com



FUJIFILM Corporation



SHOOT, REWIND, PRINT

instax square 5020

HYBRID INSTANT CAMERA



HYBRID INSTANT CAMERA

- For square format film
- Select and print your favorite photos after shooting
- Enjoy editing photos with a variety of filters

instax square 5020

HYBRID INSTANT CAMERA
[INSTANT PRINT + DIGITAL TECHNOLOGIES]



MATTE BLACK JAN 4547410351156



BEIGE JAN 4547410351156













FRAME GRAB

Shoot a video up to 15 seconds long, use the dial on the back of the camera to select the frame that captures the moment best and print the photo.




SHOOTING MODE

A variety of modes to broaden the range of expression in your photos.

TIMESHIFT COLLAGE

Four images can be taken with a time difference at one time. Press the shutter button to shoot when four images appear on the monitor. The time difference between frames can be adjusted within 0.2 to 2.0 seconds.





Two shutters go off and the two pictures are combined into one image.



SPLIT

Multiple images can be captured on one images. Select four segmentation options: vertically halved, horizontally divided in three, divided in quarters and divided in nine.



BULB MODE

The shutter opens while it is being pressed.



COLLAGE

You can create a collage style image where one image is divided up at random or you can take photos for each segment.



ADJUSTING / PROCESSING IMAGES (EFFECT)

Enjoy editing and processing with a variety of filters that can be applied while shooting or viewing photos.



