

Barcode Labels: Library Compatibility List

LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #
DLT							
ADIC AML/2 DLT	1704-99	Breece Hill 30/50-PAK SDLT	1705-BH6C	Dell PowerVault 128T DLT	1701-01	HP StorageWorks MSL5052 SDLT	1707-DGS
ADIC AML/2 DLT	1704-99V	Breece Hill 30/50-PAK SDLT	1705-BH8C	Dell PowerVault 128T SDLT	1707-OS	HP StorageWorks SSL1016 DLT1	1701-01
ADIC AML/2 DLT	1704-28	Breece Hill 6.210/9.140 DLT	1705-BH5C	Dell PowerVault 128T SDLT	1707-DGS	HP StorageWorks SSL1016 SDLT	1707-OS
ADIC AML/2 DLT	1703-AD	Breece Hill 6.210/9.140 DLT	1705-BH6C	Dell PowerVault 128T SDLT	1707-CNS	HP StorageWorks SSL1016 SDLT	1707-CNS
ADIC AML/2 DLT	1703-GR	Breece Hill 6.210/9.140 DLT	1705-BH8C	Dell Powervault 130T DLT	1703-DG	HP SureStore 1/20 to 8/80 DLT	1701-01
ADIC AML/E DLT	1704-99	Breece Hill 6.210/9.140 SDLT	1705-BH5C	Dell Powervault 130T DLT	1703-OD	HP SureStore 1/20 to 8/80 SDLT	1707-OS
ADIC AML/E DLT	1704-99V	Breece Hill 6.210/9.140 SDLT	1705-BH6C	Dell Powervault 130T DLT	1703-OC	HP SureStore 1/20 to 8/80 SDLT	1707-CNS
ADIC AML/E DLT	1704-28	Breece Hill 6.210/9.140 SDLT	1705-BH8C	Dell Powervault 130T DLT	1703-0E	HP SureStore 1/20 to 8/80 SDLT	1707-DGS
ADIC AML/E DLT	1703-AD	Breece Hill B2.15	1705-BH5C	Dell Powervault 130T DLT	1703-CN	HP SureStore 1/8 Autoloader VS80	1707-OB
ADIC AML/E DLT	1703-GR	Breece Hill B2.15	1705-BH6C	Dell Powervault 130T DLT	1703-CNB	HP SureStore 1/9 DLT	1701-01
ADIC AML/E DLT	1707-OSH	Breece Hill B2.15	1705-BH8C	Dell Powervault 130T SDLT	1703-OS	HP SureStore 1/9 DLT1	1707-OB
ADIC AML/J DLT	1704-99	Breece Hill Q12.420	1705-BH5C	Dell Powervault 130T SDLT	1703-CNS	HP SureStore 1/9 SDLT	1707-CNS
ADIC AML/J DLT	1704-99V	Breece Hill Q12.420	1705-BH6C	Dell PowerVault 132T SDLT	1707-OSH	HP SureStore 1/9 SDLT	1707-OS
ADIC AML/J DLT	1704-28	Breece Hill Q12.420	1705-BH8C	Dell PowerVault 136T DLT	1704-28	HP SureStore 1/9 SDLT	1707-DGS
ADIC AML/J DLT	1703-AD	Breece Hill Q140	1705-BH6C	Dell PowerVault 136T DLT	1704-99V	HP SureStore 10/100-120-140 DLT	1701-01
ADIC AML/J DLT	1703-GR	Breece Hill Q140	1705-BH5C	Dell PowerVault 136T DLT	1704-99	HP SureStore 10/100-120-140 SDLT	1707-DGS
ADIC Fastor 2 SDLT	1707-OSH	Breece Hill Q140	1705-BH8C	Dell PowerVault 136T SDLT	1707-OSH	HP SureStore 10/100-120-140 SDLT	1707-OS
ADIC FastStor 22 DLT	1704-28	Breece Hill Q15.350	1705-BH6C	Exabyte 18D/230D/690D	1701-01	HP SureStore 10/100-120-140 SDLT	1707-CNS
ADIC FastStor 7 DLT	1704-28	Breece Hill Q15.350	1705-BH5C	Exabyte 18D/230D/690D	1705-BH6C	HP SureStore 10/180 DLT	1703-DG
ADIC FastStor 7 DLT	1703-AD	Breece Hill Q15.350	1705-BH8C	Exabyte 18D/230D/690D	1702-01	HP SureStore 10/180 DLT	1703-OD
ADIC Scalar 100 DLT	1704-99V	Breece Hill Q18.280	1705-BH6C	Exabyte 18D/230D/690D	1705-BH5C	HP SureStore 10/180 DLT	1703-OC
ADIC Scalar 100 DLT	1704-28	Breece Hill Q18.280	1705-BH5C	Exabyte 18D/230D/690D	1705-BH8C	HP SureStore 10/180 DLT	1703-0E
ADIC Scalar 100 DLT	1704-99	Breece Hill Q18.280	1705-BH8C	HP 4228/4248/4448 DLT	1701-01	HP SureStore 10/180 DLT	1703-CN
ADIC Scalar 100 DLT	1703-AD	Breece Hill Q210	1705-BH6C	HP 7215 DLT	1701-01	HP SureStore 10/180 SDLT	1703-OS
ADIC Scalar 100 SDLT	1707-OSH	Breece Hill Q210	1705-BH5C	HP 7228/7248/7448 DLT	1701-01	HP SureStore 10/180 SDLT	1703-CNS
ADIC Scalar 100 SDLT	1707-OS2H	Breece Hill Q210	1705-BH8C	HP A4845-252/420/588 DLT	1703-DG	HP SureStore 10/180 SDLT	1703-DGS
ADIC Scalar 1000 DLT	1704-99V	Breece Hill Q4.30/50 DLT	1705-BH6C	HP A4845-252/420/588 DLT	1703-OD	HP SureStore 2/40 - 4/40 DLT	1701-01
ADIC Scalar 1000 DLT	1704-28	Breece Hill Q4.30/50 DLT	1705-BH5C	HP A4845-252/420/588 DLT	1703-OC	HP SureStore 2/40 - 4/40 SDLT	1707-CNS
ADIC Scalar 1000 DLT	1703-AD	Breece Hill Q4.30/50 DLT	1705-BH8C	HP A4845-252/420/588 DLT	1703-0E	HP SureStore 2/40 - 4/40 SDLT	1707-OS
ADIC Scalar 1000 DLT	1704-99	Breece Hill Q4.30/50 SDLT	1705-BH6C	HP A4845-252/420/588 DLT	1703-CN	HP SureStore 2/40 - 4/40 SDLT	1707-DGS
ADIC Scalar 1000 SDLT	1707-OSH	Breece Hill Q4.30/50 SDLT	1705-BH5C	HP A4845-252/420/588 DLT	1703-CNS	HP SureStore 20/700 DLT	1703-DG
ADIC Scalar 10K DLT	1704-28	Breece Hill Q4.30/50 SDLT	1705-BH8C	HP A4846-100 DLT	1703-DG	HP SureStore 20/700 DLT	1703-OD
ADIC Scalar 10K SDLT	1707-OSH	Breece Hill Q6.100 DLT	1705-BH6C	HP A4846-100 DLT	1703-OD	HP SureStore 20/700 DLT	1703-OC
ADIC Scalar 218M	1704-99V	Breece Hill Q6.100 DLT	1705-BH8C	HP A4846-100 DLT	1703-OC	HP SureStore 20/700 DLT	1703-0E
ADIC Scalar 218M	1704-99	Breece Hill Q6.100 DLT	1705-BH5C	HP A4846-100 DLT	1703-0E	HP SureStore 20/700 DLT	1703-CN
ADIC Scalar 224	1704-99V	Breece Hill Q6.100 SDLT	1705-BH6C	HP A4846-100 DLT	1703-CN	HP SureStore 20/700 SDLT	1703-OS
ADIC Scalar 234	1704-99V	Breece Hill Q6.100 SDLT	1705-BH8C	HP A4846-100 DLT	1703-CNS	HP SureStore 20/700 SDLT	1703-CNS
ADIC Scalar 24 SDLT	1707-OSH	Breece Hill Q6.210/9.140 DLT	1705-BH5C	HP StorageWorks		HP SureStore 20/700 SDLT	1703-DGS
ADIC Scalar 448	1704-99V	Breece Hill Q6.210/9.140 DLT	1705-BH6C	1/8 Autoloader VS80	1704-28	HP SureStore 4/30 DLT	1703-DG
ADIC Scalar 458	1704-99V	Breece Hill Q6.210/9.140 DLT	1705-BH8C	HP StorageWorks ESL 9198 DLT	1701-01	HP SureStore 4/30 DLT	1703-OD
ADIC Scalar i2000 SDLT	1707-OSH	Breece Hill Q6.210/9.140 DLT	1705-BH5C	HP StorageWorks ESL 9198 SDLT	1707-OS	HP SureStore 4/30 DLT	1703-OC
ADIC Tape Array 5	1704-99V	Breece Hill Q6.210/9.140 SDLT	1705-BH6C	HP StorageWorks ESL 9198 SDLT	1707-DGS	HP SureStore 4/30 DLT	1703-0E
ADIC Tape Array 5	1704-99	Breece Hill Q6.210/9.140 SDLT	1705-BH8C	HP StorageWorks ESL 9198 SDLT	1707-CNS	HP SureStore 4/30 DLT	1703-CN
ADIC VLS DLT	1704-28	Breece Hill Q6.210/9.140 SDLT	1705-BH5C	HP StorageWorks ESL 9322 DLT	1701-01	HP SureStore 4/30 SDLT	1703-OS
ADIC VLS DLT	1707-OSH	Breece Hill Q70	1705-BH6C	HP StorageWorks ESL 9322 DLT	1707-OS	HP SureStore 4/30 SDLT	1703-CNS
ADIC VLS DLT	1703-AD	Breece Hill Q70	1705-BH8C	HP StorageWorks ESL 9322 SDLT	1707-DGS	HP SureStore 4/30 SDLT	1703-DGS
ADIC VLS DLT	1704-99	Breece Hill Q70	1705-BH5C	HP StorageWorks ESL 9322 SDLT	1707-CNS	HP SureStore 4/60 - 6/60 DLT	1701-01
Breece Hill 100-PAK DLT	1705-BH5C	Compaq TL 881	1701-01	HP StorageWorks ESL 9595 DLT	1701-01	HP SureStore 4/60 - 6/60 SDLT	1707-DGS
Breece Hill 100-PAK DLT	1705-BH6C	Compaq TL 881	1702-01	HP StorageWorks ESL 9595 SDLT	1707-OS	HP SureStore 4/60 - 6/60 SDLT	1707-OS
Breece Hill 100-PAK DLT	1705-BH8C	Compaq TL 890	1701-01	HP StorageWorks ESL 9595 SDLT	1707-OSH	HP SureStore 4/60 - 6/60 SDLT	1707-CNS
Breece Hill 100-PAK SDLT	1705-BH5C	Compaq TL 890	1702-01	HP StorageWorks ESL 9595 SDLT	1707-CNS	HP SureStore 4215 DLT	1701-01
Breece Hill 100-PAK SDLT	1705-BH6C	Compaq TL 891/892	1701-01	HP StorageWorks ESL 9595 SDLT	1707-DGS	IBM 4560SLX SDLT	1701-01
Breece Hill 100-PAK SDLT	1705-BH8C	Compaq TL 891/892	1702-01	HP StorageWorks MSL5026 DLT	1701-01	IBM 7337/3447 DLT	1705-BH6C
Breece Hill 10-PAK SDLT	1705-BH6C	Compaq TL 891DLX	1701-01	HP StorageWorks MSL5026 SDLT	1707-OS	IBM 7337/3447 DLT	1705-BH8C
Breece Hill 10-PAK SDLT	1705-BH5C	Compaq TL 891DLX	1702-01	HP StorageWorks MSL5026 SDLT	1707-CNS	IBM 7337/3447 DLT	1705-BH5C
Breece Hill 10-PAK SDLT	1705-BH8C	Compaq TL 894	1701-01	HP StorageWorks MSL5026 SDLT	1707-DGS	Overland DLT LibraryXpress LXB	1701-01
Breece Hill 30/50-PAK DLT	1705-BH5C	Compaq TL895 DLT	1701-01	HP StorageWorks MSL5026 SDLT	1707-OSH	Overland DLT LibraryXpress LXB	1702-01
Breece Hill 30/50-PAK DLT	1705-BH6C	Dell PowerVault 120T DLT	1704-28	HP StorageWorks MSL5052 DLT	1701-01	Overland LoaderXpress DLT, SDLT	1701-01
Breece Hill 30/50-PAK DLT	1705-BH8C	Dell PowerVault 120T SDLT	1707-OSH	HP StorageWorks MSL5052 SDLT	1707-OS	Overland LXB	
Breece Hill 30/50-PAK SDLT	1705-BH5C	Dell PowerVault 122T VS80	1704-28	HP StorageWorks MSL5052 SDLT	1707-CNS	4110/7110/4210/7210 DLT	1701-01

LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #
Overland LXB		Quantum/ATL P7000 SDLT	1707-CNS	STK L700 DLT	1703-0C	Sun StorEdge L100 SDLT	1701-01S
4110/7110/4210/7210 DLT	1702-01	Quantum/ATL P7000 SDLT	1707-DGS	STK L700 DLT	1703-0E	Sun StorEdge L11000 DLT	1701-01
Overland Neo 2000 DLT, SDLT	1701-01	Quantum/ATL P7000 SDLT	1707-OS	STK L700 DLT	1703-CN	Sun StorEdge L11000 DLT	1702-01
Overland Neo 4100 DLT, SDLT	1701-01	Quantum/ATL PX720 SDLT	1707-CNS	STK L700 SDLT	1703-0S	Sun StorEdge L180 DLT	1703-0D
Overland Neo 4200 DLT, SDLT	1701-01	Quantum/ATL PX720 SDLT	1707-OS	STK L700 SDLT	1703-DGS	Sun StorEdge L180 DLT	1703-DG
Overland Neo 4300 DLT, SDLT	1701-01	Quantum/ATL PX720 SDLT	1707-DGS	STK L700 SDLT	1703-CNS	Sun StorEdge L180 DLT	1703-0C
Overland Neo 4400 DLT, SDLT	1701-01	Quantum/ATL PX720 SDLT	1707-OSH	STK Timberwolf 7430 DLT	1703-0D	Sun StorEdge L180 DLT	1703-0E
Overland PowerLoader DLT, SDLT	1701-01	Silicon Graphics L180 DLT	1703-DG	STK Timberwolf 7430 DLT	1703-DG	Sun StorEdge L180 DLT	1703-CN
Qualstar RLS Series DLT	1705-06	Silicon Graphics L180 DLT	1703-0D	STK Timberwolf 7430 DLT	1703-CNB	Sun StorEdge L180 SDLT	1703-CNS
Qualstar RLS Series SDLT	1705-06	Silicon Graphics L180 DLT	1703-0C	STK Timberwolf 7430 DLT	1703-0S	Sun StorEdge L180 SDLT	1703-0S
Qualstar TLS 6000 Series DLT	1705-BH6C	Silicon Graphics L180 DLT	1703-0E	STK Timberwolf 7430 DLT	1703-CN	Sun StorEdge L20/L40/L60 DLT	1701-01
Qualstar TLS 6000 Series SDLT	1705-BH6C	Silicon Graphics L180 DLT	1703-0S	STK Timberwolf 7430 DLT	1703-0C	Sun StorEdge L20/L40/L60 SDLT	1707-CNS
Qualstar TLS 8000 Series DLT	1705-BH6C	Silicon Graphics L180 DLT	1703-CN	STK Timberwolf 7430 DLT	1703-0E	Sun StorEdge L20/L40/L60 SDLT	1707-OS
Qualstar TLS 8000 Series SDLT	1705-BH6C	Silicon Graphics L180 DLT	1703-CNB	STK Timberwolf 7430 DLT	1703-0D	Sun StorEdge L20/L40/L60 SDLT	1707-DGS
Quantum/ATL 520 Series DLT	1701-01	Silicon Graphics L180 DLT	1703-CNS	STK Timberwolf 7430 DLT	1703-DG	Sun StorEdge L25 DLT	1701-01
Quantum/ATL 7100 Series DLT	1701-01	STK L180 DLT	1703-DG	STK Timberwolf 9710 DLT	1703-CN	Sun StorEdge L25 SDLT	1701-01S
Quantum/ATL M1500 DLT	1701-01	STK L180 DLT	1703-0D	STK Timberwolf 9710 DLT	1703-0E	Sun StorEdge L3500 DLT	1701-01
Quantum/ATL M1500 SDLT	1707-OSH	STK L180 DLT	1703-0C	STK Timberwolf 9710 DLT	1703-0C	Sun StorEdge L7 DLT	1704-28
Quantum/ATL M1500 SDLT	1707-CNS	STK L180 DLT	1703-0E	STK Timberwolf 9710 SDLT	1703-0S	Sun StorEdge L700 DLT	1703-0D
Quantum/ATL M1500 SDLT	1707-0S	STK L180 DLT	1703-CN	STK Timberwolf 9710 SDLT	1703-CNS	Sun StorEdge L700 DLT	1703-DG
Quantum/ATL M1500 SDLT	1707-DGS	STK L180 DLT	1703-CNB	STK Timberwolf 9710 SDLT	1703-DGS	Sun StorEdge L700 DLT	1703-CN
Quantum/ATL M1800 DLT	1701-01	STK L180 SDLT	1703-0S	STK Timberwolf 9714 DLT	1703-0D	Sun StorEdge L700 DLT	1703-0E
Quantum/ATL M1800 SDLT	1707-0S	STK L180 SDLT	1703-CNS	STK Timberwolf 9714 DLT	1703-DG	Sun StorEdge L700 DLT	1703-0C
Quantum/ATL M1800 SDLT	1707-CNS	STK L180 SDLT	1703-DGS	STK Timberwolf 9714 DLT	1703-CN	Sun StorEdge L700 SDLT	1703-0S
Quantum/ATL M1800 SDLT	1707-DGS	STK L20/40/80 DLT	1703-0D	STK Timberwolf 9714 DLT	1703-0C	Sun StorEdge L700 SDLT	1703-CNS
Quantum/ATL M1800 SDLT	1707-OSH	STK L20/40/80 DLT	1703-DG	STK Timberwolf 9714 DLT	1703-0E	Sun StorEdge L8 Autoloader SDLT	1707-OSH
Quantum/ATL M2500 DLT	1701-01	STK L20/40/80 DLT	1703-0C	STK Timberwolf 9730 DLT	1703-0D	Sun StorEdge L9 DLT	1701-01
Quantum/ATL M2500 SDLT	1707-OSH	STK L20/40/80 DLT	1703-0E	STK Timberwolf 9730 DLT	1703-CNB	Sun StorEdge L9 DLT1	1707-0B
Quantum/ATL M2500 SDLT	1707-CNS	STK L20/40/80 DLT	1703-CN	STK Timberwolf 9730 DLT	1703-DG	Sun StorEdge L9 SDLT	1707-DGS
Quantum/ATL M2500 SDLT	1707-DGS	STK L20/40/80 DLT1	1703-0D	STK Timberwolf 9730 DLT	1703-0E	Sun StorEdge L9 SDLT	1707-CNS
Quantum/ATL M2500 SDLT	1707-0S	STK L20/40/80 DLT1	1703-DG	STK Timberwolf 9730 DLT	1703-0C	Sun StorEdge L9 SDLT	1707-0S
Quantum/ATL P4000 DLT	1701-01	STK L20/40/80 DLT1	1703-CNB	STK Timberwolf 9730 DLT	1703-CN	Tandberg DLT Autoloader	1701-01
Quantum/ATL P4000 SDLT	1707-0S	STK L20/40/80 SDLT	1703-0S	STK Timberwolf 9740 DLT	1703-0D	Tandberg DLT1280L	1701-01
Quantum/ATL P4000 SDLT	1707-CNS	STK L20/40/80 SDLT	1703-CNS	STK Timberwolf 9740 DLT	1703-CNB	Tandberg SDLT220 Autoloader	1701-01
Quantum/ATL P4000 SDLT	1707-DGS	STK L20/40/80 SDLT	1703-DGS	STK Timberwolf 9740 DLT	1703-DG	Tandberg SDLT320 Autoloader	1701-01
Quantum/ATL P4000 SDLT	1707-OSH	STK L700 DLT	1703-0D	STK Timberwolf 9740 DLT	1703-CN	Tandberg SDLT3520L	1701-01
Quantum/ATL P7000 DLT	1701-01	STK L700 DLT	1703-DG	STK Timberwolf 9740 DLT	1703-0C	Tandem ACL5158 DLT	1701-01
Quantum/ATL P7000 SDLT	1707-OSH	STK L700 DLT	1703-CNB	Sun StorEdge L100 DLT	1701-01		

4mm

Breece Hill A2.15	1699-4M	Breece Hill A2.15	1699-4MB
-------------------	---------	-------------------	----------

LTO

ADIC AML/2 LTO	1700-DG	ADIC Scalar 100 LTO	1700-CNHU	Breece Hill Q4.30/50 LTO	1700-00	Exabyte 221L LTO	1700-00
ADIC AML/2 LTO	1700-00	ADIC Scalar 100 LTO	1700-002	Breece Hill Q6.100 LTO	1700-00	Exabyte Magnum20 LTO	1700-DG
ADIC AML/2 LTO	1700-CNI	ADIC Scalar 100 LTO	1700-CNI	Breece Hill Q6.100 LTO	1700-CNHU	Exabyte Magnum20 LTO	1700-00
ADIC AML/2 LTO	1700-002	ADIC Scalar 100 LTO	1700-CNH	Dell PowerVault 122T LTO	1700-CNHU	Exabyte Magnum20 LTO	1700-CNHU
ADIC AML/2 LTO	1700-CNHU	ADIC Scalar 100 LTO	1700-00	Dell PowerVault 122T LTO	1700-00	Exabyte Magnum20 LTO	1700-002
ADIC AML/2 LTO	1700-CNH	ADIC Scalar 100 LTO	1700-003	Dell PowerVault 128T LTO	1700-LD	HP StorageWorks 1/8 Autoloader LTO	1700-CNHU
ADIC AML/2 LTO	1700-CNS	ADIC Scalar 1000 LTO	1700-CNI	Dell PowerVault 128T LTO	1700-DGDH	HP StorageWorks 1/8 Autoloader LTO	1700-DG
ADIC AML/E LTO	1700-DG	ADIC Scalar 1000 LTO	1700-CNS	Dell PowerVault 128T LTO	1700-LD2	HP StorageWorks 1/8 Autoloader LTO	1700-00
ADIC AML/E LTO	1700-CNI	ADIC Scalar 1000 LTO	1700-CNHU	Dell PowerVault 128T LTO	1700-CNDU	HP StorageWorks EML 103e LTO	1700-003
ADIC AML/E LTO	1700-CNHU	ADIC Scalar 1000 LTO	1700-00	Dell PowerVault 128T LTO	1700-CNDH	HP StorageWorks EML 245e LTO	1700-003
ADIC AML/E LTO	1700-CNH	ADIC Scalar 1000 LTO	1700-DG	Dell PowerVault 132T LTO	1700-00	HP StorageWorks ESL 322e LTO	1700-003
ADIC AML/E LTO	1700-CNS	ADIC Scalar 1000 LTO	1700-CNH	Dell PowerVault 132T LTO	1700-CNHU	HP StorageWorks ESL 712e LTO	1700-003
ADIC AML/E LTO	1700-00	ADIC Scalar 1000 LTO	1700-002	Dell PowerVault 132T LTO	1700-03	HP StorageWorks ESL 9198 LTO	1700-LD
ADIC AML/E LTO	1700-002	ADIC Scalar 10K LTO	1700-CNHU	Dell PowerVault 136T LTO	1700-CNI	HP StorageWorks ESL 9198 LTO	1700-LD2
ADIC AML/J LTO	1700-DG	ADIC Scalar 10K LTO	1700-002	Dell PowerVault 136T LTO	1700-CNS	HP StorageWorks ESL 9198 LTO	1700-CNDU
ADIC AML/J LTO	1700-CNI	ADIC Scalar 10K LTO	1700-00	Dell PowerVault 136T LTO	1700-DG	HP StorageWorks ESL 9322 LTO	1700-LD
ADIC AML/J LTO	1700-CNHU	ADIC Scalar 10K LTO	1700-003	Dell PowerVault 136T LTO	1700-002	HP StorageWorks ESL 9322 LTO	1700-LD2
ADIC AML/J LTO	1700-CNH	ADIC Scalar 24 LTO	1700-00	Dell PowerVault 136T LTO	1700-CNH	HP StorageWorks ESL 9322 LTO	1700-CNDU
ADIC AML/J LTO	1700-CNS	ADIC Scalar 24 LTO	1700-DG	Dell PowerVault 136T LTO	1700-CNHU	HP StorageWorks ESL 9595 LTO	1700-LD
ADIC AML/J LTO	1700-002	ADIC Scalar 24 LTO	1700-CNHU	Dell PowerVault 136T LTO	1700-003	HP StorageWorks ESL 9595 LTO	1700-LD2
ADIC AML/J LTO	1700-00	ADIC Scalar 24 LTO	1700-002	Dell PowerVault 136T LTO	1700-00	HP StorageWorks ESL 9595 LTO	1700-CNDU
ADIC FastStor 2 LTO	1700-DG	ADIC Scalar 24 LTO	1700-003	Dell PowerVault 136T LTO	1700-00	HP StorageWorks MSL 5030 LTO	1700-LD
ADIC FastStor 2 LTO	1700-CNI	ADIC Scalar i2000 LTO	1700-002	Exabyte 110L LTO	1700-CNI	HP StorageWorks MSL 5030 LTO	1700-CNDU
ADIC FastStor 2 LTO	1700-CNHU	ADIC Scalar i2000 LTO	1700-CNHU	Exabyte 110L LTO	1700-CNS	HP StorageWorks MSL 5030 LTO	1700-LD2
ADIC FastStor 2 LTO	1700-CNH	ADIC Scalar i2000 LTO	1700-00	Exabyte 110L LTO	1700-DG	HP StorageWorks MSL5060 LTO	1700-LD
ADIC FastStor 2 LTO	1700-CNS	ADIC Scalar i2000 LTO	1700-003	Exabyte 110L LTO	1700-CNH	HP StorageWorks MSL5060 LTO	1700-LD2
ADIC FastStor 2 LTO	1700-00	Breece Hill 100-PAK LTO	1700-CNHU	Exabyte 110L LTO	1700-CNHU	HP StorageWorks MSL5060 LTO	1700-CNDU
ADIC FastStor 2 LTO	1700-002	Breece Hill 100-PAK LTO	1700-00	Exabyte 110L LTO	1700-002	HP StorageWorks	
ADIC FastStor 2 LTO	1700-003	Breece Hill 10-PAK LTO	1700-00	Exabyte 221L LTO	1700-CNI	MSL6000 Series LTO2	1700-CNDU
ADIC FastStor 7 LTO	1700-DG	Breece Hill 10-PAK LTO	1700-CNHU	Exabyte 221L LTO	1700-CNS	HP StorageWorks	
ADIC FastStor 7 LTO	1700-CNHU	Breece Hill 10-PAK LTO	1700-002	Exabyte 221L LTO	1700-002	MSL6000 Series LTO2	1700-LD2
ADIC FastStor 7 LTO	1700-00	Breece Hill 30/50-PAK LTO	1700-00	Exabyte 221L LTO	1700-CNH	HP StorageWorks MSL6030 LTO	1700-003
ADIC Scalar 100 LTO	1700-CNS	Breece Hill 30/50-PAK LTO	1700-CNHU	Exabyte 221L LTO	1700-CNHU	HP StorageWorks MSL6060 LTO	1700-003
ADIC Scalar 100 LTO	1700-DG	Breece Hill Q4.30/50 LTO	1700-CNHU	Exabyte 221L LTO	1700-DG	HP StorageWorks SSL1016 LTO2	1700-LD2

LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #
HP StorageWorks SSL1016 LTO2	1700-CNDU	IBM 3584 Ultrium Ultrascalable	1700-CNNU	Overland PowerLoader LTO	1700-0V2	STK L700 LTO	1700-CNVI
HP SureStore 1/20 to 8/80 LTO	1700-DGD	IBM 3584 Ultrium Ultrascalable	1700-002	Plasmon V Series LTO	1700-CNHU	STK L700 LTO	1700-CNVS
HP SureStore 1/20 to 8/80 LTO	1700-LD	IBM 3584 Ultrium Ultrascalable	1700-003	Plasmon V Series LTO	1700-CNI	STK L700 LTO	1700-0V
HP SureStore 1/20 to 8/80 LTO	1700-CNDU	IBM 3600-109 LTO	1700-CNHU	Plasmon V Series LTO	1700-002	STK L700 LTO	1700-0V2
HP SureStore 1/8 Autoloader LTO	1700-LD	IBM 3600-109 LTO	1700-CNI	Plasmon V Series LTO	1700-00	STK L700 LTO	1700-DGV
HP SureStore 1/8 Autoloader LTO	1700-CNDU	IBM 3600-109 LTO	1700-CNS	Qualstar TLS 8000 Series LTO	1700-08	STK L700e LTO	1700-0V3
HP SureStore 1/9 LTO	1700-DGD	IBM 3600-109 LTO	1700-002	Quantum/ATL M1500 LTO	1700-CNHU	STK SL500 LTO	1700-0V3
HP SureStore 1/9 LTO	1700-LD	IBM 3600-109 LTO	1700-CNH	Quantum/ATL M1500 LTO	1700-00	STK SL8500 LTO	1700-0V3
HP SureStore 1/9 LTO	1700-CNDU	IBM 3600-109 LTO	1700-00	Quantum/ATL M1500 LTO	1700-002	Sun StorEdge	1700-CNHU
HP SureStore 10/100-120-140 LTO	1700-DGD	IBM 3600-220 LTO	1700-CNHU	Quantum/ATL M1500 LTO	1700-003	Sun StorEdge	1700-002
HP SureStore 10/100-120-140 LTO	1700-LD	IBM 3600-220 LTO	1700-CNI	Quantum/ATL M1800 LTO	1700-CNHU	Sun StorEdge	1700-00
HP SureStore 10/100-120-140 LTO	1700-CNDU	IBM 3600-220 LTO	1700-CNS	Quantum/ATL M1800 LTO	1700-002	Sun StorEdge	1700-003
HP SureStore 10/180 LTO	1700-DGD	IBM 3600-220 LTO	1700-00	Quantum/ATL M1800 LTO	1700-00	Sun StorEdge L100 LTO	1700-CNHU
HP SureStore 10/180 LTO	1700-LD	IBM 3600-220 LTO	1700-CNH	Quantum/ATL M1800 LTO	1700-003	Sun StorEdge L100 LTO	1700-00
HP SureStore 10/180 LTO	1700-CNDCU	IBM 3600-220 LTO	1700-002	Quantum/ATL M2500 LTO	1700-CNHU	Sun StorEdge L100 LTO	1700-002
HP SureStore 2/40 - 4/40 LTO	1700-DGD	IBM 3600-440 LTO	1700-CNHU	Quantum/ATL M2500 LTO	1700-00	Sun StorEdge L100 LTO	1700-003
HP SureStore 2/40 - 4/40 LTO	1700-LD	IBM 3600-440 LTO	1700-CNI	Quantum/ATL M2500 LTO	1700-002	Sun StorEdge L180 LTO	1700-CNVS
HP SureStore 2/40 - 4/40 LTO	1700-CNDU	IBM 3600-440 LTO	1700-002	Quantum/ATL M2500 LTO	1700-003	Sun StorEdge L180 LTO	1700-DGV
HP SureStore 20/700 LTO	1700-DGD	IBM 3600-440 LTO	1700-CNH	Quantum/ATL P4000 LTO	1700-CNHU	Sun StorEdge L180 LTO	1700-DGV2
HP SureStore 20/700 LTO	1700-CNDCU	IBM 3600-440 LTO	1700-CNS	Quantum/ATL P4000 LTO	1700-002	Sun StorEdge L180 LTO	1700-CNVI
HP SureStore 20/700 LTO	1700-LD	IBM 3600-440 LTO	1700-00	Quantum/ATL P4000 LTO	1700-00	Sun StorEdge L180 LTO	1700-0V
HP SureStore 4/30 LTO	1700-DGD	IBM 3600-660 LTO	1700-CNHU	Quantum/ATL P7000 LTO	1700-CNHU	Sun StorEdge L180 LTO	1700-0V2
HP SureStore 4/30 LTO	1700-LD	IBM 3600-660 LTO	1700-CNI	Quantum/ATL P7000 LTO	1700-00	Sun StorEdge L180 LTO	1700-CNVH
HP SureStore 4/30 LTO	1700-CNDU	IBM 3600-660 LTO	1700-CNS	Quantum/ATL P7000 LTO	1700-002	Sun StorEdge L180 LTO	1700-CNVU
HP SureStore 4/60 - 6/60 LTO	1700-DGD	IBM 3600-660 LTO	1700-00	Quantum/ATL PX720 LTO	1700-CNHU	Sun StorEdge L20/L40/L60 LTO	1700-LD
HP SureStore 4/60 - 6/60 LTO	1700-CNDU	IBM 3600-660 LTO	1700-002	Quantum/ATL PX720 LTO	1700-002	Sun StorEdge L20/L40/L60 LTO	1700-DGDH
HP SureStore 4/60 - 6/60 LTO	1700-LD	IBM 3600-660 LTO	1700-CNH	Quantum/ATL PX720 LTO	1700-003	Sun StorEdge L20/L40/L60 LTO	1700-CNDH
HP SureStore 4/60 - 6/60 LTO	1700-CNI	IBM 4560SLX LTO	1700-CNVU	STK L1400M LTO	1700-0V3	Sun StorEdge L20/L40/L60 LTO	1700-CNDU
IBM 3581 LTO Ultrium Autoloader	1700-CNI	IBM 4560SLX LTO	1700-0V	STK L180 LTO	1700-CNVH	Sun StorEdge L20/L40/L60 LTO	1700-LD2
IBM 3581 LTO Ultrium Autoloader	1700-CNS	IBM 4560SLX LTO	1700-0V2	STK L180 LTO	1700-CNVI	Sun StorEdge L25 LTO	1700-CNHU
IBM 3581 LTO Ultrium Autoloader	1700-DGI	Overland LoaderXpress LTO	1700-CNVU	STK L180 LTO	1700-CNVS	Sun StorEdge L25 LTO	1700-002
IBM 3581 LTO Ultrium Autoloader	1700-DG	Overland LoaderXpress LTO	1700-0V	STK L180 LTO	1700-DGV	Sun StorEdge L25 LTO	1700-00
IBM 3581 LTO Ultrium Autoloader	1700-00	Overland LoaderXpress LTO	1700-0V2	STK L180 LTO	1700-0V	Sun StorEdge L25 LTO	1700-003
IBM 3581 LTO Ultrium Autoloader	1700-002	Overland Neo 2000 LTO	1700-CNVU	STK L180 LTO	1700-0V2	Sun StorEdge L700 LTO	1700-CNVH
IBM 3581 LTO Ultrium Autoloader	1700-CNH	Overland Neo 2000 LTO	1700-0V	STK L180 LTO	1700-CNVU	Sun StorEdge L700 LTO	1700-CNVU
IBM 3581 LTO Ultrium Autoloader	1700-CNHU	Overland Neo 2000 LTO	1700-0V2	STK L180 LTO	1700-0V3	Sun StorEdge L700 LTO	1700-DGV2
IBM 3581 LTO Ultrium Autoloader	1700-003	Overland Neo 2000 LTO	1700-0V3	STK L20/40/80 LTO	1700-CNVH	Sun StorEdge L700 LTO	1700-0V
IBM 3582 Ultrium Scalable	1700-CNHU	Overland Neo 4100 LTO	1700-CNVU	STK L20/40/80 LTO	1700-CNVI	Sun StorEdge L700 LTO	1700-0V2
IBM 3582 Ultrium Scalable	1700-002	Overland Neo 4100 LTO	1700-0V	STK L20/40/80 LTO	1700-CNVS	Sun StorEdge L700 LTO	1700-CNVI
IBM 3582 Ultrium Scalable	1700-003	Overland Neo 4100 LTO	1700-0V2	STK L20/40/80 LTO	1700-CNVU	Sun StorEdge L700 LTO	1700-CNVS
IBM 3582 Ultrium Scalable	1700-003	Overland Neo 4100 LTO	1700-0V3	STK L20/40/80 LTO	1700-DGV	Sun StorEdge L700 LTO	1700-DGV
IBM 3583 Ultrium Scalable	1700-CNI	Overland Neo 4100 LTO	1700-0V3	STK L20/40/80 LTO	1700-0V	Sun StorEdge L8 Autoloader LTO	1700-CNHU
IBM 3583 Ultrium Scalable	1700-CNS	Overland Neo 4200 LTO	1700-CNVU	STK L20/40/80 LTO	1700-0V2	Sun StorEdge L8 Autoloader LTO	1700-00
IBM 3583 Ultrium Scalable	1700-002	Overland Neo 4200 LTO	1700-0V	STK L20/40/80 LTO	1700-0V3	Sun StorEdge L8 Autoloader LTO	1700-002
IBM 3583 Ultrium Scalable	1700-002	Overland Neo 4200 LTO	1700-0V2	STK L5500 LTO	1700-CNVI	Sun StorEdge L8 LTO	1700-CNHU
IBM 3583 Ultrium Scalable	1700-CNH	Overland Neo 4200 LTO	1700-0V	STK L5500 LTO	1700-CNVH	Sun StorEdge L8 LTO	1700-DG
IBM 3583 Ultrium Scalable	1700-CNHU	Overland Neo 4200 LTO	1700-0V3	STK L5500 LTO	1700-CNVS	Sun StorEdge L8 LTO	1700-00
IBM 3583 Ultrium Scalable	1700-DG	Overland Neo 4200 LTO	1700-0V2	STK L5500 LTO	1700-DGV	Sun StorEdge L9 LTO	1700-DGD
IBM 3583 Ultrium Scalable	1700-DGI	Overland Neo 4200 LTO	1700-0V3	STK L5500 LTO	1700-0V	Sun StorEdge L9 LTO	1700-LD2
IBM 3583 Ultrium Scalable	1700-00	Overland Neo 4300 LTO	1700-CNVU	STK L5500 LTO	1700-0V2	Sun StorEdge L9 LTO	1700-DGDH
IBM 3583 Ultrium Scalable	1700-00	Overland Neo 4300 LTO	1700-0V	STK L5500 LTO	1700-CNVU	Sun StorEdge L9 LTO	1700-CNDH
IBM 3583 Ultrium Scalable	1700-003	Overland Neo 4300 LTO	1700-0V2	STK L5500 LTO	1700-0V3	Sun StorEdge L9 LTO	1700-CNDU
IBM 3584 Ultrium Ultrascalable	1700-CNI	Overland Neo 4400 LTO	1700-CNVU	STK L700 LTO	1700-CNVU	Sun StorEdge L9 LTO	1700-LD
IBM 3584 Ultrium Ultrascalable	1700-CNS	Overland Neo 4400 LTO	1700-0V	STK L700 LTO	1700-CNVH		
IBM 3584 Ultrium Ultrascalable	1700-DGI	Overland Neo 4400 LTO	1700-0V2				
IBM 3584 Ultrium Ultrascalable	1700-DG	Overland Neo 8000 LTO	1700-0V3				
IBM 3584 Ultrium Ultrascalable	1700-00	Overland PowerLoader LTO	1700-CNVU				
IBM 3584 Ultrium Ultrascalable	1700-CNH	Overland PowerLoader LTO	1700-0V				

1/2" MTC (Media Tape Cartridge)

ADIC AML/2 1/2" MTC	1687-BW	ADIC AML/E 1/2" MTC	1687-VC	ADIC AML/J 1/2" MTC	1688-GR	ADIC Scalar 1000 3590	1684-TB
ADIC AML/2 1/2" MTC	1687-CN	ADIC AML/E 1/2" MTC	1687-VCW	ADIC AML/J 1/2" MTC	1682-06	ADIC Scalar 1000 3590	1684-06
ADIC AML/2 1/2" MTC	1687-VC	ADIC AML/E 1/2" MTC	1684-06	ADIC AML/J 1/2" MTC	1684-WL	ADIC Scalar 1000 3590	1683-06
ADIC AML/2 1/2" MTC	1687-VCW	ADIC AML/E 1/2" MTC	1682-BWO	ADIC AML/J 1/2" MTC	1682-BWL	ADIC Scalar 1000 3590	1682-BWL
ADIC AML/2 1/2" MTC	1688-GR	ADIC AML/E 1/2" MTC	1682-BWL	ADIC AML/J 1/2" MTC	1684-DW	ADIC Scalar 1000 3590	1687-MI
ADIC AML/2 1/2" MTC	1682-06	ADIC AML/E 1/2" MTC	1684-DW	ADIC AML/J 1/2" MTC	1684-TB	ADIC Scalar 1000 3590	1682-06
ADIC AML/2 1/2" MTC	1684-WL	ADIC AML/E 1/2" MTC	1684-TB	ADIC AML/J 1/2" MTC	1684-06	ADIC Scalar 1000 3590	1687-WL
ADIC AML/2 1/2" MTC	1682-BWL	ADIC AML/E 1/2" MTC	1688-GR	ADIC AML/J 1/2" MTC	1687-06	ADIC Scalar 1000 3590	1687-06
ADIC AML/2 1/2" MTC	1682-BWO	ADIC AML/E 1/2" MTC	1683-06	ADIC AML/J 1/2" MTC	1687-WL	ADIC Scalar 1000 3590	1687-06W
ADIC AML/2 1/2" MTC	1684-DW	ADIC AML/E 1/2" MTC	1687-MI	ADIC AML/J 1/2" MTC	1683-06	ADIC Scalar 1000 3590	1684-WL
ADIC AML/2 1/2" MTC	1684-TB	ADIC AML/E 1/2" MTC	1682-06	ADIC AML/J 1/2" MTC	1687-06W	ADIC Scalar 1000 3590	1685-06
ADIC AML/2 1/2" MTC	1684-06	ADIC AML/E 1/2" MTC	1687-06	ADIC AML/J 1/2" MTC	1682-BWO	ADIC Scalar 1000 3590	1685-DW
ADIC AML/2 1/2" MTC	1685-06	ADIC AML/E 1/2" MTC	1687-WL	ADIC AML/J 1/2" MTC	1685-06	ADIC Scalar 1000 3590	1685-WL
ADIC AML/2 1/2" MTC	1685-DW	ADIC AML/E 1/2" MTC	1687-06W	ADIC AML/J 1/2" MTC	1685-DW	ADIC Scalar 10K 3590	1687-06
ADIC AML/2 1/2" MTC	1683-06	ADIC AML/E 1/2" MTC	1684-WL	ADIC AML/J 1/2" MTC	1685-WL	ADIC Scalar 10K 3590	1687-VC
ADIC AML/2 1/2" MTC	1687-06	ADIC AML/E 1/2" MTC	1685-06	ADIC AML/J 1/2" MTC	1687-MI	HP SureStore 10/180 9840	1687-BW
ADIC AML/2 1/2" MTC	1687-WL	ADIC AML/E 1/2" MTC	1685-DW	ADIC AML/J 1/2" MTC	1687-BW	HP SureStore 10/180 9840	1687-CN
ADIC AML/2 1/2" MTC	1687-06W	ADIC AML/E 1/2" MTC	1685-WL	ADIC AML/J 1/2" MTC	1687-CN	HP SureStore 10/180 9840	1687-VC
ADIC AML/2 1/2" MTC	1685-WL	ADIC AML/J 1/2" MTC	1687-BW	ADIC Scalar 1000 3590	1687-VC	HP SureStore 10/180 9840	1687-VCW
ADIC AML/2 1/2" MTC	1687-MI	ADIC AML/J 1/2" MTC	1687-CN	ADIC Scalar 1000 3590	1687-VCW	HP SureStore 10/180 9840	1682-06
ADIC AML/E 1/2" MTC	1687-BW	ADIC AML/J 1/2" MTC	1687-VC	ADIC Scalar 1000 3590	1682-BWO	HP SureStore 10/180 9840	1684-WL
ADIC AML/E 1/2" MTC	1687-CN	ADIC AML/J 1/2" MTC	1687-VCW	ADIC Scalar 1000 3590	1684-DW	HP SureStore 10/180 9840	1684-DW

Please check www.fujifilmusa.com/datacenterservices for updates to the Library Compatibility List.

LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #	LIBRARY NAME	PART #
HP SureStore 10/180 9840	1684-06	Overland TapeXpress L60E	1687-06	STK L5500 9840/9940	1687-BW	STK Timberwolf 9740 9840/9940	1687-BW
HP SureStore 10/180 9840	1687-WL	Quantum/ATL PowerStor L200	1701-01	STK L5500 9840/9940	1687-VCW	STK Timberwolf 9740 9840/9940	1687-CN
HP SureStore 10/180 9840	1687-06	Quantum/ATL PowerStor L200	1702-01	STK L5500 9840/9940	1684-DW	STK Timberwolf 9740 9840/9940	1687-VC
HP SureStore 10/180 9840	1683-06	Quantum/ATL PowerStor L500	1701-01	STK L5500 9840/9940	1684-WL	STK Timberwolf 9740 9840/9940	1687-VCW
HP SureStore 10/180 9840	1687-06W	Quantum/ATL PowerStor L500	1702-01	STK L5500 9840/9940	1685-WL	STK Timberwolf 9740 9840/9940	1687-WL
HP SureStore 10/180 9840	1682-BWL	Silicon Graphics L180 9840	1687-BW	STK L5500 9840/9940	1687-WL	STK Timberwolf 9740 9840/9940	1687-06W
HP SureStore 10/180 9840	1682-BWO	Silicon Graphics L180 9840	1687-VC	STK L5500 9840/9940	1687-06	STK Timberwolf 9740 9840/9940	1684-TB
HP SureStore 10/180 9840	1685-06	Silicon Graphics L180 9840	1687-VCW	STK L5500 9840/9940	1682-06	STK Timberwolf 9740 9840/9940	1682-06
HP SureStore 10/180 9840	1685-DW	Silicon Graphics L180 9840	1682-06	STK L5500 9840/9940	1685-06	STK Timberwolf 9740 9840/9940	1684-DW
HP SureStore 10/180 9840	1685-WL	Silicon Graphics L180 9840	1684-TB	STK L5500 9840/9940	1687-06W	STK Timberwolf 9740 9840/9940	1684-06
HP SureStore 10/180 9840	1687-MI	Silicon Graphics L180 9840	1684-06	STK L5500 9840/9940	1684-TB	STK Timberwolf 9740 9840/9940	1683-06
HP SureStore 20/700 9840	1687-BW	Silicon Graphics L180 9840	1687-WL	STK L5500 9840/9940	1685-DW	STK Timberwolf 9740 9840/9940	1682-BWL
HP SureStore 20/700 9840	1687-CN	Silicon Graphics L180 9840	1683-06	STK L5500 9840/9940	1687-MI	STK Timberwolf 9740 9840/9940	1682-BWO
HP SureStore 20/700 9840	1687-VC	Silicon Graphics L180 9840	1687-06W	STK L700 9840/9940	1687-BW	STK Timberwolf 9740 9840/9940	1684-WL
HP SureStore 20/700 9840	1687-VCW	Silicon Graphics L180 9840	1682-BWL	STK L700 9840/9940	1687-CN	STK Timberwolf 9740 9840/9940	1685-06
HP SureStore 20/700 9840	1682-BWO	Silicon Graphics L180 9840	1682-BWO	STK L700 9840/9940	1687-VC	STK Timberwolf 9740 9840/9940	1685-DW
HP SureStore 20/700 9840	1684-DW	Silicon Graphics L180 9840	1685-06	STK L700 9840/9940	1687-VCW	STK Timberwolf 9740 9840/9940	1685-WL
HP SureStore 20/700 9840	1684-06	Silicon Graphics L180 9840	1685-DW	STK L700 9840/9940	1687-WL	STK Timberwolf 9740 9840/9940	1687-MI
HP SureStore 20/700 9840	1683-06	Silicon Graphics L180 9840	1685-WL	STK L700 9840/9940	1687-06W	STK Wolfcreek 9360 9840/9940	1687-BW
HP SureStore 20/700 9840	1682-BWL	Silicon Graphics L180 9840	1687-06	STK L700 9840/9940	1684-DW	STK Wolfcreek 9360 9840/9940	1687-CN
HP SureStore 20/700 9840	1687-MI	Silicon Graphics L180 9840	1687-MI	STK L700 9840/9940	1684-WL	STK Wolfcreek 9360 9840/9940	1687-VC
HP SureStore 20/700 9840	1682-06	Silicon Graphics L700 9840	1687-BW	STK L700 9840/9940	1687-MI	STK Wolfcreek 9360 9840/9940	1687-VCW
HP SureStore 20/700 9840	1684-TB	Silicon Graphics L700 9840	1687-VC	STK L700 9840/9940	1682-06	STK Wolfcreek 9360 9840/9940	1687-WL
HP SureStore 20/700 9840	1687-WL	Silicon Graphics L700 9840	1687-VCW	STK L700 9840/9940	1684-TB	STK Wolfcreek 9360 9840/9940	1684-WL
HP SureStore 20/700 9840	1687-06	Silicon Graphics L700 9840	1687-WL	STK L700 9840/9940	1684-06	STK Wolfcreek 9360 9840/9940	1682-BWO
HP SureStore 20/700 9840	1687-06W	Silicon Graphics L700 9840	1682-06	STK L700 9840/9940	1683-06	STK Wolfcreek 9360 9840/9940	1685-06
HP SureStore 20/700 9840	1684-WL	Silicon Graphics L700 9840	1684-TB	STK L700 9840/9940	1685-06	STK Wolfcreek 9360 9840/9940	1685-WL
HP SureStore 20/700 9840	1685-06	Silicon Graphics L700 9840	1684-06	STK L700 9840/9940	1685-DW	STK Wolfcreek 9360 9840/9940	1687-06W
HP SureStore 20/700 9840	1685-DW	Silicon Graphics L700 9840	1683-06	STK L700 9840/9940	1685-WL	STK Wolfcreek 9360 9840/9940	1687-MI
HP SureStore 20/700 9840	1685-WL	Silicon Graphics L700 9840	1682-BWL	STK L700 9840/9940	1687-06	STK Wolfcreek 9360 9840/9940	1682-06
HP SureStore 4/30 9840	1687-BW	Silicon Graphics L700 9840	1682-BWO	STK Powderhorn 9310	1687-BW	STK Wolfcreek 9360 9840/9940	1684-DW
HP SureStore 4/30 9840	1687-CN	Silicon Graphics L700 9840	1687-MI	STK Powderhorn 9310	1687-CN	STK Wolfcreek 9360 9840/9940	1684-06
HP SureStore 4/30 9840	1687-VC	Silicon Graphics L700 9840	1687-06W	STK Powderhorn 9310	1687-VC	STK Wolfcreek 9360 9840/9940	1683-06
HP SureStore 4/30 9840	1687-VCW	Silicon Graphics L700 9840	1685-06	STK Powderhorn 9310	1687-VCW	STK Wolfcreek 9360 9840/9940	1682-BWL
HP SureStore 4/30 9840	1682-06	Silicon Graphics L700 9840	1685-DW	STK Powderhorn 9310	1688-EZ	STK Wolfcreek 9360 9840/9940	1684-TB
HP SureStore 4/30 9840	1684-TB	Silicon Graphics L700 9840	1685-WL	STK Powderhorn 9310	1688-V6	STK Wolfcreek 9360 9840/9940	1685-DW
HP SureStore 4/30 9840	1684-DW	Silicon Graphics L700 9840	1687-06	STK Powderhorn 9310	1682-06	STK Wolfcreek 9360 9840/9940	1687-06
HP SureStore 4/30 9840	1684-06	STK 4400/4410 ACS	1687-BW	STK Powderhorn 9310	1683-06	Sun StorEdge L180 9840	1687-06W
HP SureStore 4/30 9840	1687-WL	STK 4400/4410 ACS	1687-CN	STK Powderhorn 9310	1682-BWO	Sun StorEdge L180 9840	1687-BW
HP SureStore 4/30 9840	1683-06	STK 4400/4410 ACS	1687-VC	STK Powderhorn 9310	1687-06	Sun StorEdge L180 9840	1687-CN
HP SureStore 4/30 9840	1687-06	STK 4400/4410 ACS	1687-VCW	STK Powderhorn 9310	1684-06	Sun StorEdge L180 9840	1687-VC
HP SureStore 4/30 9840	1687-06W	STK 4400/4410 ACS	1687-WL	STK Powderhorn 9310	1682-BWL	Sun StorEdge L180 9840	1687-VCW
HP SureStore 4/30 9840	1682-BWL	STK 4400/4410 ACS	1688-EZ	STK Powderhorn 9310	1685-06	Sun StorEdge L180 9840	1687-WL
HP SureStore 4/30 9840	1682-BWO	STK 4400/4410 ACS	1688-V6	STK Powderhorn 9310	1687-06W	Sun StorEdge L180 9840	1688-EZ
HP SureStore 4/30 9840	1685-06	STK 4400/4410 ACS	1684-DW	STK Timberwolf 9710 9840	1687-BW	Sun StorEdge L180 9840	1688-V6
HP SureStore 4/30 9840	1685-WL	STK 4400/4410 ACS	1682-06	STK Timberwolf 9710 9840	1687-CN	Sun StorEdge L180 9840	1684-TB
IBM MagStar 3494	1687-BW	STK 4400/4410 ACS	1684-06	STK Timberwolf 9710 9840	1687-VC	Sun StorEdge L180 9840	1684-DW
IBM MagStar 3494	1687-CN	STK 4400/4410 ACS	1682-BWL	STK Timberwolf 9710 9840	1687-VCW	Sun StorEdge L180 9840	1684-06
IBM MagStar 3494	1687-VC	STK 4400/4410 ACS	1685-06	STK Timberwolf 9710 9840	1687-WL	Sun StorEdge L180 9840	1682-06
IBM MagStar 3494	1687-VCW	STK 4400/4410 ACS	1685-WL	STK Timberwolf 9710 9840	1684-TB	Sun StorEdge L180 9840	1683-06
IBM MagStar 3494	1696-B07	STK 4400/4410 ACS	1687-06W	STK Timberwolf 9710 9840	1682-06	Sun StorEdge L180 9840	1682-BWL
IBM MagStar 3494	1688-3592	STK 4400/4410 ACS	1684-WL	STK Timberwolf 9710 9840	1684-DW	Sun StorEdge L180 9840	1682-BWO
IBM MagStar 3494	1688-3592CN	STK 4400/4410 ACS	1684-TB	STK Timberwolf 9710 9840	1684-06	Sun StorEdge L180 9840	1684-WL
IBM MagStar 3494	1688-3592D6	STK 4400/4410 ACS	1683-06	STK Timberwolf 9710 9840	1683-06	Sun StorEdge L180 9840	1685-06
IBM MagStar 3494	1682-BWL	STK 4400/4410 ACS	1682-BWO	STK Timberwolf 9710 9840	1682-BWL	Sun StorEdge L180 9840	1685-DW
IBM MagStar 3494	1682-BWO	STK 4400/4410 ACS	1685-DW	STK Timberwolf 9710 9840	1682-BWO	Sun StorEdge L180 9840	1685-WL
IBM MagStar 3494	1682-06	STK 4400/4410 ACS	1687-06	STK Timberwolf 9710 9840	1684-WL	Sun StorEdge L180 9840	1687-06
IBM MagStar 3494	1687-06	STK 4400/4410 ACS	1687-MI	STK Timberwolf 9710 9840	1685-06	Sun StorEdge L180 9840	1687-MI
IBM MagStar 3494	1696-S07	STK L180 9840	1687-BW	STK Timberwolf 9710 9840	1685-DW	Sun StorEdge L700 9840	1687-BW
IBM MagStar 3494	1687-06W	STK L180 9840	1687-CN	STK Timberwolf 9710 9840	1685-WL	Sun StorEdge L700 9840	1687-VC
IBM MagStar 3494	1685-06	STK L180 9840	1687-VC	STK Timberwolf 9710 9840	1687-06W	Sun StorEdge L700 9840	1687-VCW
Memorex/Telex -		STK L180 9840	1687-VCW	STK Timberwolf 9710 9840	1687-MI	Sun StorEdge L700 9840	1687-WL
Sutmyn 5600 ATL Sultan	1687-VC	STK L180 9840	1687-WL	STK Timberwolf 9738 9840	1687-CN	Sun StorEdge L700 9840	1688-EZ
Memorex/Telex -		STK L180 9840	1682-06	STK Timberwolf 9738 9840	1687-VC	Sun StorEdge L700 9840	1688-V6
Sutmyn 5600 ATL Sultan	1687-06	STK L180 9840	1684-TB	STK Timberwolf 9738 9840	1687-VCW	Sun StorEdge L700 9840	1687-06W
Memorex/Telex -		STK L180 9840	1684-06	STK Timberwolf 9738 9840	1687-WL	Sun StorEdge L700 9840	1683-06
Sutmyn 5600 ATL Sultan	1682-BWL	STK L180 9840	1683-06	STK Timberwolf 9738 9840	1682-06	Sun StorEdge L700 9840	1684-06
Memorex/Telex -		STK L180 9840	1682-BWL	STK Timberwolf 9738 9840	1684-DW	Sun StorEdge L700 9840	1682-06
Sutmyn 5600 ATL Sultan	1682-BWO	STK L180 9840	1682-BWO	STK Timberwolf 9738 9840	1684-06	Sun StorEdge L700 9840	1682-BWL
Overland TapeXpress L60E	1687-BW	STK L180 9840	1684-DW	STK Timberwolf 9738 9840	1683-06	Sun StorEdge L700 9840	1682-BWO
Overland TapeXpress L60E	1687-CN	STK L180 9840	1687-MI	STK Timberwolf 9738 9840	1684-WL	Sun StorEdge L700 9840	1684-DW
Overland TapeXpress L60E	1688-EZ	STK L180 9840	1684-WL	STK Timberwolf 9738 9840	1682-BWL	Sun StorEdge L700 9840	1684-TB
Overland TapeXpress L60E	1687-VC	STK L180 9840	1685-06	STK Timberwolf 9738 9840	1682-BWO	Sun StorEdge L700 9840	1687-MI
Overland TapeXpress L60E	1688-V6	STK L180 9840	1685-DW	STK Timberwolf 9738 9840	1684-TB	Sun StorEdge L700 9840	1684-WL
Overland TapeXpress L60E	1682-06	STK L180 9840	1685-WL	STK Timberwolf 9738 9840	1687-MI	Sun StorEdge L700 9840	1685-06
Overland TapeXpress L60E	1684-06	STK L180 9840	1687-06W	STK Timberwolf 9738 9840	1685-06	Sun StorEdge L700 9840	1685-DW
Overland TapeXpress L60E	1683-06	STK L5500 9840/9940	1687-CN	STK Timberwolf 9738 9840	1685-DW	Sun StorEdge L700 9840	1685-WL
Overland TapeXpress L60E	1682-BWL	STK L5500 9840/9940	1687-VC	STK Timberwolf 9738 9840	1685-WL	Sun StorEdge L700 9840	1687-06
Overland TapeXpress L60E	1682-BWO	STK L5500 9840/9940	1684-06	STK Timberwolf 9738 9840	1687-06	Sun StorEdge L700 9840	1687-CN
Overland TapeXpress L60E	1685-06	STK L5500 9840/9940	1683-06	STK Timberwolf 9738 9840	1687-06W		

Please check www.fujifilmusa.com/datacenterservices for updates to the Library Compatibility List.