

POLYPLAST PY

**Fujifilm PANTONE®
Matching System**

**Version 2.0
SMS Base Colors**

Polyplast PY Seritone Matching System

PANTONE® Shades Simulated From Seritone Base Colors

This booklet furnishes the necessary formulas to simulate all the "C" colors of the PANTONE Color Formula Guide, except Double print, Fluorescent, and Metallic Colors.

Each formula was printed through a 280 (110/cm) monofilament screen with a 75 durometer sharp edge squeegee, on white rigid vinyl, and the ink was thinned 10% with PY-TH. All formulas are presented by weight. However, due to variations in ink film thickness, screen mesh, and other variables, some formulas may need adjustments.

The Seritone Matching System (SMS) has been designed to enable screen printers to simulate almost any shade from nine SMS Base Colors plus Shading Black, Tinting White, and Mixing Clear.

Each SMS Base Color has been carefully selected for its cleanliness of tone, resistance to fading, and suitability for intermixing. In addition, each ink has been formulated to be free of lead and other heavy metals.

Although every care is taken in producing these formulations, variations in substrates and printing conditions will affect color achieved. Fujifilm assumes no responsibility for actual color achieved. For this reason, all formulations must be proofed, prior to production run, to ensure color accuracy.

In some cases, to accurately simulate a PANTONE shade, considerable amounts of Mixing Clear and/or Tinting White are in the formulation. The exterior durability of color mixes with high percentages of Mixing Clear and/or Tinting White will be reduced. The Technical Services Department, in many cases, can provide an alternate PANTONE simulation formula yielding improved exterior durability.

The SMS Base Colors are listed below and are available in single gallon containers:

DESCRIPTION	
PY-064 SMS Yellow GS (Green Shade)	PY-165 SMS Magenta
PY-066 SMS Yellow RS (Red Shade)	PY-230 SMS Blue
PY-114 SMS Orange	PY-325 SMS Green
PY-121 SMS Red YS (Yellow Shade)	PY-TW SMS Tinting White
PY-127 SMS Violet	PY-SB Shading Black
PY-164 SMS Red BS (Blue Shade)	PY-MX Mixing Clear

Fujifilm's color mixing ink formulations for screen process printing produce only simulations of PANTONE Colors in this color reproduction method due to differences in ink film, opacity and pigment selection. The pigment selection used in blending screen process inks may cause metamerism. Pantone, Inc. assumes no responsibility for formula accuracy. PANTONE® is Pantone, Inc.'s checkstandard trademark for color. Portions© Pantone, Inc., 1963,1991.C=Coated Paper

Polyplast PY

PANTONE Yellow 012 C PY-064 90.00 PY-066 10.00	Formula	PANTONE Process Yellow C PY-MX 67.50 PY-064 30.00 PY-066 2.50	Formula	PANTONE Process Magenta C PY-165 48.00 PY-MX 43.00 PY-TW 7.00 PY-066 2.00	Formula	PANTONE Process Cyan C PY-MX 45.50 PY-TW 45.50 PY-230 8.50 PY-064 0.50	Formula
PANTONE Process Black C PY-MX 73.90 PY-SB 24.60 PY-230 1.50	Formula	PANTONE 100 C PY-TW 85.90 PY-064 12.70 PY-066 1.40	Formula	PANTONE 711 C PY-121 68.10 PY-TW 22.70 PY-164 9.10 PY-SB 0.10	Formula	PANTONE 712 C PY-TW 98.00 PY-114 1.10 PY-066 0.90	Formula
PANTONE 713 C PY-TW 96.42 PY-066 2.07 PY-114 1.51	Formula	PANTONE 714 C PY-TW 89.63 PY-066 6.60 PY-114 3.77	Formula	PANTONE 715 C PY-TW 76.92 PY-066 15.39 PY-114 7.69	Formula	PANTONE 716 C PY-TW 48.90 PY-066 37.60 PY-114 13.20 PY-SB 0.30	Formula
PANTONE 717 C PY-066 80.92 PY-114 18.50 PY-SB 0.58	Formula	PANTONE 718 C PY-066 72.37 PY-114 26.31 PY-SB 1.32	Formula	PANTONE 719 C PY-TW 97.80 PY-066 1.10 PY-121 1.00 PY-SB 0.10	Formula	PANTONE 720 C PY-TW 96.90 PY-066 1.80 PY-121 1.20 PY-SB 0.10	Formula

Polyplast PY

PANTONE 721 C PY-TW 93.30 PY-066 4.10 PY-121 2.10 PY-SB 0.50	Formula	PANTONE 722 C PY-TW 62.30 PY-066 28.70 PY-121 7.20 PY-SB 1.80	Formula	PANTONE 723 C PY-TW 52.60 PY-066 36.00 PY-121 9.10 PY-SB 2.30	Formula	PANTONE 724 C PY-066 78.60 PY-121 16.00 PY-SB 4.60 PY-164 0.80	Formula
PANTONE 725 C PY-066 54.80 PY-MX 32.40 PY-164 6.90 PY-SB 5.90	Formula	PANTONE 726 C PY-TW 97.40 PY-066 1.50 PY-121 1.00 PY-SB 0.10	Formula	PANTONE 727 C PY-TW 95.70 PY-066 2.30 PY-121 1.60 PY-SB 0.40	Formula	PANTONE 728 C PY-TW 92.20 PY-066 4.40 PY-121 2.30 PY-SB 1.10	Formula
PANTONE 729 C PY-TW 85.70 PY-066 8.10 PY-121 4.30 PY-SB 1.90	Formula	PANTONE 730 C PY-TW 67.30 PY-066 22.60 PY-121 7.50 PY-SB 2.60	Formula	PANTONE 731 C PY-066 56.40 PY-114 34.60 PY-SB 9.00	Formula	PANTONE 732 C PY-066 43.50 PY-114 21.70 PY-MX 21.70 PY-SB 10.80 PY-164 2.30	Formula
PANTONE 689 C PY-165 44.60 PY-TW 38.40 PY-MX 11.00 PY-SB 4.00 PY-066 2.00	Formula	PANTONE 690 C PY-165 74.00 PY-SB 10.00 PY-MX 10.00 PY-TW 4.00 PY-066 2.00	Formula	PANTONE 691 C PY-TW 98.89 PY-121 1.01 PY-SB 0.10	Formula	PANTONE 692 C PY-TW 98.00 PY-121 1.73 PY-SB 0.27	Formula

Polyplast PY

PANTONE 693 C PY-TW 96.39 PY-121 3.01 PY-SB 0.60	Formula	PANTONE 694 C PY-TW 92.16 PY-121 6.80 PY-SB 1.04	Formula	PANTONE 695 C PY-TW 77.22 PY-121 20.75 PY-SB 2.03	Formula	PANTONE 696 C PY-TW 47.35 PY-121 45.10 PY-SB 4.17 PY-164 3.38	Formula
PANTONE 697 C PY-121 58.65 PY-TW 32.26 PY-SB 4.69 PY-164 4.40	Formula	PANTONE 698 C PY-TW 98.90 PY-121 1.00 PY-164 0.10	Formula	PANTONE 699 C PY-TW 98.00 PY-121 1.80 PY-164 0.20	Formula	PANTONE 700 C PY-TW 96.10 PY-121 3.40 PY-164 0.50	Formula
PANTONE 701 C PY-TW 90.00 PY-121 8.00 PY-164 1.60 PY-SB 0.40	Formula	PANTONE 702 C PY-TW 56.80 PY-MX 24.60 PY-121 14.30 PY-164 3.30 PY-SB 1.00	Formula	PANTONE 703 C PY-TW 32.30 PY-MX 30.30 PY-121 25.90 PY-164 9.80 PY-SB 1.70	Formula	PANTONE 704 C PY-121 46.10 PY-TW 19.20 PY-MX 19.20 PY-164 11.50 PY-SB 4.00	Formula
PANTONE 705 C PY-TW 99.50 PY-121 0.40 PY-164 0.10	Formula	PANTONE 706 C PY-TW 98.40 PY-121 1.50 PY-164 0.10	Formula	PANTONE 707 C PY-TW 95.60 PY-121 4.00 PY-164 0.40	Formula	PANTONE 708 C PY-TW 91.00 PY-121 7.00 PY-164 2.00	Formula

Polyplast PY

PANTONE 709 C PY-TW 82.50 PY-121 14.00 PY-164 3.50	Formula	PANTONE 710 C PY-TW 51.20 PY-121 42.20 PY-164 6.50 PY-SB 0.10	Formula	PANTONE 667 C PY-TW 79.06 PY-165 9.55 PY-127 6.33 PY-SB 5.06	Formula	PANTONE 668 C PY-TW 61.73 PY-165 16.05 PY-127 16.05 PY-SB 6.17	Formula
PANTONE 669 C PY-165 37.50 PY-TW 29.17 PY-127 27.08 PY-SB 6.25	Formula	PANTONE 670 C PY-TW 98.69 PY-165 1.11 PY-066 0.20	Formula	PANTONE 671 C PY-TW 97.77 PY-165 1.95 PY-066 0.28	Formula	PANTONE 672 C PY-TW 94.45 PY-165 5.00 PY-066 0.45 PY-SB 0.10	Formula
PANTONE 673 C PY-TW 87.21 PY-165 11.63 PY-066 0.97 PY-SB 0.19	Formula	PANTONE 674 C PY-TW 73.63 PY-165 24.55 PY-066 1.40 PY-SB 0.42	Formula	PANTONE 675 C PY-165 53.24 PY-TW 44.37 PY-066 1.77 PY-SB 0.62	Formula	PANTONE 676 C PY-165 72.47 PY-TW 24.15 PY-066 2.41 PY-SB 0.97	Formula
PANTONE 677 C PY-TW 98.30 PY-165 1.20 PY-066 0.40 PY-SB 0.10	Formula	PANTONE 678 C PY-TW 98.40 PY-165 1.30 PY-SB 0.20 PY-066 0.10	Formula	PANTONE 679 C PY-TW 96.90 PY-165 2.60 PY-066 0.30 PY-SB 0.20	Formula	PANTONE 680 C PY-TW 91.80 PY-165 6.60 PY-SB 1.00 PY-066 0.60	Formula

Polyplast PY

PANTONE 681 C PY-TW 78.50 PY-165 17.70 PY-066 1.90 PY-SB 1.90	Formula	PANTONE 682 C PY-TW 47.10 PY-165 45.60 PY-066 4.40 PY-SB 2.90	Formula	PANTONE 683 C PY-165 73.20 PY-TW 19.20 PY-SB 4.80 PY-066 2.80	Formula	PANTONE 684 C PY-TW 96.60 PY-165 2.80 PY-066 0.30 PY-SB 0.30	Formula
PANTONE 685 C PY-TW 96.50 PY-165 3.00 PY-066 0.30 PY-SB 0.20	Formula	PANTONE 686 C PY-TW 94.00 PY-165 5.00 PY-066 0.50 PY-SB 0.50	Formula	PANTONE 687 C PY-TW 87.80 PY-165 10.00 PY-SB 1.20 PY-066 1.00	Formula	PANTONE 688 C PY-TW 64.00 PY-165 22.00 PY-MX 10.00 PY-066 2.00 PY-SB 2.00	Formula
PANTONE 645 C PY-TW 92.30 PY-165 3.85 PY-230 2.31 PY-SB 1.54	Formula	PANTONE 646 C PY-TW 87.21 PY-165 5.96 PY-230 4.36 PY-SB 2.47	Formula	PANTONE 647 C PY-TW 60.87 PY-165 18.26 PY-230 16.96 PY-SB 3.91	Formula	PANTONE 648 C PY-230 57.97 PY-165 20.29 PY-TW 13.04 PY-SB 8.70	Formula
PANTONE 649 C PY-TW 99.50 PY-165 0.20 PY-230 0.20 PY-SB 0.10	Formula	PANTONE 650 C PY-TW 99.30 PY-230 0.30 PY-165 0.20 PY-SB 0.20	Formula	PANTONE 651 C PY-TW 95.80 PY-SB 1.50 PY-127 1.50 PY-230 1.20	Formula	PANTONE 652 C PY-TW 89.00 PY-127 4.20 PY-230 3.70 PY-SB 3.10	Formula

Polyplast PY

PANTONE 653 C	Formula
PY-TW	68.80
PY-127	12.90
PY-230	11.90
PY-SB	6.40

PANTONE 654 C	Formula
PY-230	43.40
PY-MX	34.60
PY-127	13.00
PY-SB	8.60
PY-325	0.40

PANTONE 655 C	Formula
PY-230	57.80
PY-127	17.34
PY-SB	12.14
PY-MX	11.56
PY-325	1.16

PANTONE 656 C	Formula
PY-TW	99.01
PY-165	0.55
PY-230	0.28
PY-SB	0.16

PANTONE 657 C	Formula
PY-TW	97.82
PY-165	1.26
PY-230	0.69
PY-SB	0.23

PANTONE 658 C	Formula
PY-TW	94.94
PY-165	3.31
PY-230	1.65
PY-SB	0.10

PANTONE 659 C	Formula
PY-TW	87.61
PY-165	7.76
PY-230	4.13
PY-SB	0.50

PANTONE 660 C	Formula
PY-TW	69.32
PY-165	17.33
PY-230	13.00
PY-SB	0.35

PANTONE 661 C	Formula
PY-230	56.18
PY-TW	33.15
PY-127	10.67

PANTONE 662 C	Formula
PY-230	76.19
PY-127	21.90
PY-SB	1.91

PANTONE 663 C	Formula
PY-TW	99.39
PY-127	0.28
PY-SB	0.23
PY-165	0.10

PANTONE 664 C	Formula
PY-TW	98.84
PY-127	0.58
PY-SB	0.58

PANTONE 665 C	Formula
PY-TW	98.04
PY-127	1.09
PY-SB	0.87

PANTONE 666 C	Formula
PY-TW	94.12
PY-127	2.35
PY-SB	1.77
PY-165	1.76

PANTONE 625 C	Formula
PY-TW	81.70
PY-325	6.00
PY-066	5.60
PY-SB	5.50
PY-114	1.20

PANTONE 626 C	Formula
PY-325	49.40
PY-066	24.20
PY-TW	16.50
PY-SB	9.90

Polyplast PY

PANTONE 627 C		Formula
PY-325	60.00	
PY-066	20.00	
PY-SB	20.00	

PANTONE 628 C		Formula
PY-MX	85.00	
PY-TW	14.40	
PY-230	0.30	
PY-325	0.20	
PY-SB	0.10	

PANTONE 629 C		Formula
PY-MX	75.10	
PY-TW	24.00	
PY-230	0.50	
PY-325	0.30	
PY-SB	0.10	

PANTONE 630 C		Formula
PY-MX	74.50	
PY-TW	24.00	
PY-230	1.10	
PY-325	0.20	
PY-SB	0.20	

PANTONE 631 C		Formula
PY-MX	61.00	
PY-TW	35.90	
PY-230	2.30	
PY-SB	0.50	
PY-325	0.30	

PANTONE 632 C		Formula
PY-TW	57.70	
PY-MX	35.30	
PY-230	5.30	
PY-325	0.90	
PY-SB	0.80	

PANTONE 633 C		Formula
PY-MX	62.60	
PY-TW	27.40	
PY-230	7.70	
PY-SB	1.70	
PY-325	0.60	

PANTONE 634 C		Formula
PY-MX	80.00	
PY-230	16.00	
PY-SB	3.50	
PY-325	0.50	

PANTONE 635 C		Formula
PY-TW	99.17	
PY-230	0.48	
PY-325	0.25	
PY-SB	0.10	

PANTONE 636 C		Formula
PY-TW	98.75	
PY-230	1.00	
PY-325	0.25	

PANTONE 637 C		Formula
PY-TW	97.65	
PY-230	1.81	
PY-325	0.36	
PY-SB	0.18	

PANTONE 638 C		Formula
PY-TW	93.69	
PY-230	5.25	
PY-325	0.96	
PY-SB	0.10	

PANTONE 639 C		Formula
PY-TW	84.94	
PY-230	12.55	
PY-325	2.41	
PY-SB	0.10	

PANTONE 640 C		Formula
PY-TW	73.10	
PY-230	23.25	
PY-325	3.65	

PANTONE 641 C		Formula
PY-MX	55.74	
PY-230	33.45	
PY-TW	8.36	
PY-325	2.23	
PY-SB	0.22	

PANTONE 642 C		Formula
PY-TW	99.25	
PY-230	0.25	
PY-165	0.25	
PY-SB	0.25	

Polyplast PY

PANTONE 643 C PY-TW 98.86 PY-165 0.52 PY-230 0.31 PY-SB 0.31	Formula	PANTONE 644 C PY-TW 96.67 PY-165 1.61 PY-230 0.97 PY-SB 0.75	Formula	PANTONE 603 C PY-TW 83.30 PY-064 15.00 PY-066 1.70	Formula	PANTONE 604 C PY-TW 59.40 PY-064 37.90 PY-066 2.60 PY-SB 0.10	Formula
PANTONE 605 C PY-064 66.50 PY-TW 28.70 PY-066 4.50 PY-SB 0.30	Formula	PANTONE 606 C PY-064 81.60 PY-TW 12.90 PY-066 4.90 PY-SB 0.60	Formula	PANTONE 607 C PY-TW 98.50 PY-064 1.20 PY-066 0.30	Formula	PANTONE 608 C PY-TW 96.77 PY-064 2.42 PY-066 0.81	Formula
PANTONE 609 C PY-TW 95.12 PY-064 3.19 PY-066 1.59 PY-SB 0.10	Formula	PANTONE 610 C PY-TW 82.10 PY-064 15.30 PY-066 2.19 PY-SB 0.41	Formula	PANTONE 611 C PY-TW 74.27 PY-066 25.15 PY-325 0.39 PY-SB 0.19	Formula	PANTONE 612 C PY-TW 50.83 PY-066 48.28 PY-325 0.64 PY-SB 0.25	Formula
PANTONE 613 C PY-066 61.43 PY-TW 36.85 PY-SB 0.98 PY-325 0.74	Formula	PANTONE 614 C PY-TW 98.60 PY-066 1.10 PY-SB 0.30	Formula	PANTONE 615 C PY-TW 97.90 PY-066 1.70 PY-SB 0.40	Formula	PANTONE 616 C PY-TW 95.30 PY-066 2.50 PY-064 1.60 PY-SB 0.60	Formula

Polyplast PY

PANTONE 617 C	Formula
PY-TW 92.60	
PY-066 4.60	
PY-064 1.80	
PY-SB 1.00	

PANTONE 618 C	Formula
PY-TW 85.50	
PY-066 11.80	
PY-SB 1.30	
PY-064 1.30	
PY-230 0.10	

PANTONE 619 C	Formula
PY-TW 66.90	
PY-066 28.60	
PY-SB 3.30	
PY-064 1.00	
PY-230 0.20	

PANTONE 620 C	Formula
PY-TW 47.80	
PY-066 47.80	
PY-SB 4.20	
PY-230 0.20	

PANTONE 621 C	Formula
PY-TW 99.10	
PY-SB 0.40	
PY-066 0.30	
PY-325 0.20	

PANTONE 622 C	Formula
PY-TW 98.40	
PY-SB 0.70	
PY-325 0.50	
PY-066 0.40	

PANTONE 623 C	Formula
PY-TW 95.20	
PY-066 1.80	
PY-SB 1.60	
PY-325 1.40	

PANTONE 624 C	Formula
PY-TW 91.90	
PY-SB 3.00	
PY-066 2.90	
PY-325 2.20	

PANTONE 5767 C	Formula
PY-TW 66.30	
PY-066 26.50	
PY-114 2.90	
PY-SB 2.20	
PY-325 2.10	

PANTONE 5777 C	Formula
PY-TW 87.70	
PY-066 7.70	
PY-114 2.70	
PY-325 1.30	
PY-SB 0.60	

PANTONE 5787 C	Formula
PY-TW 94.50	
PY-066 3.90	
PY-SB 0.80	
PY-325 0.40	
PY-114 0.40	

PANTONE 5797 C	Formula
PY-TW 98.40	
PY-066 1.00	
PY-SB 0.30	
PY-114 0.20	
PY-325 0.10	

PANTONE 5807 C	Formula
PY-TW 98.50	
PY-066 0.80	
PY-114 0.30	
PY-325 0.20	
PY-SB 0.20	

PANTONE 581 C	Formula
PY-064 89.00	
PY-SB 7.50	
PY-114 2.50	
PY-230 1.00	

PANTONE 582 C	Formula
PY-064 79.20	
PY-TW 15.80	
PY-114 2.30	
PY-SB 2.00	
PY-230 0.70	

PANTONE 583 C	Formula
PY-064 79.80	
PY-TW 18.50	
PY-114 1.20	
PY-230 0.50	

Polyplast PY

PANTONE 584 C	Formula
PY-TW	55.20
PY-064	44.20
PY-114	0.40
PY-230	0.20

PANTONE 585 C	Formula
PY-TW	70.50
PY-064	29.00
PY-114	0.30
PY-230	0.20

PANTONE 586 C	Formula
PY-TW	81.50
PY-064	18.00
PY-114	0.30
PY-230	0.20

PANTONE 587 C	Formula
PY-TW	92.00
PY-064	7.00
PY-066	0.90
PY-230	0.10

PANTONE 5815 C	Formula
PY-066	54.80
PY-114	32.30
PY-325	12.90

PANTONE 5825 C	Formula
PY-066	60.00
PY-TW	18.50
PY-114	15.40
PY-325	6.10

PANTONE 5835 C	Formula
PY-TW	72.10
PY-066	18.90
PY-114	6.10
PY-325	2.40
PY-SB	0.50

PANTONE 5845 C	Formula
PY-TW	85.00
PY-066	10.60
PY-114	2.40
PY-325	1.20
PY-SB	0.80

PANTONE 5855 C	Formula
PY-TW	94.10
PY-066	3.90
PY-114	0.90
PY-SB	0.60
PY-325	0.50

PANTONE 5865 C	Formula
PY-TW	97.00
PY-066	2.00
PY-SB	0.40
PY-114	0.40
PY-325	0.20

PANTONE 5875 C	Formula
PY-TW	98.30
PY-066	1.00
PY-SB	0.30
PY-114	0.20
PY-325	0.20

PANTONE 600 C	Formula
PY-TW	97.00
PY-064	1.80
PY-066	1.10
PY-SB	0.10

PANTONE 601 C	Formula
PY-TW	97.00
PY-064	1.60
PY-066	1.30
PY-SB	0.10

PANTONE 602 C	Formula
PY-TW	93.20
PY-064	5.80
PY-066	1.00

PANTONE 568 C	Formula
PY-TW	57.90
PY-325	28.10
PY-066	8.40
PY-SB	5.60

PANTONE 569 C	Formula
PY-TW	71.41
PY-325	25.54
PY-SB	1.74
PY-066	1.31

Polyplast PY

PANTONE 570 C PY-TW 96.00 PY-325 2.70 PY-SB 1.00 PY-066 0.30	Formula	PANTONE 571 C PY-TW 98.80 PY-325 1.00 PY-066 0.10 PY-SB 0.10	Formula	PANTONE 572 C PY-TW 99.20 PY-325 0.60 PY-066 0.10 PY-SB 0.10	Formula	PANTONE 573 C PY-TW 99.60 PY-325 0.30 PY-066 0.10	Formula
PANTONE 574 C PY-066 70.57 PY-325 15.26 PY-114 9.14 PY-SB 5.03	Formula	PANTONE 575 C PY-066 73.50 PY-325 15.90 PY-114 7.90 PY-SB 2.70	Formula	PANTONE 576 C PY-064 82.60 PY-TW 6.72 PY-MX 4.80 PY-230 3.00 PY-SB 2.88	Formula	PANTONE 577 C PY-TW 59.31 PY-064 23.25 PY-MX 15.79 PY-SB 0.97 PY-230 0.68	Formula
PANTONE 578 C PY-TW 87.85 PY-064 11.22 PY-SB 0.54 PY-230 0.39	Formula	PANTONE 579 C PY-TW 91.90 PY-064 7.48 PY-SB 0.36 PY-230 0.26	Formula	PANTONE 580 C PY-TW 94.60 PY-064 5.00 PY-230 0.20 PY-SB 0.20	Formula	PANTONE 5743 C PY-066 41.40 PY-114 27.60 PY-325 17.20 PY-TW 13.80	Formula
PANTONE 5753 C PY-066 42.30 PY-TW 30.80 PY-114 19.20 PY-325 7.70	Formula	PANTONE 5763 C PY-TW 59.00 PY-066 22.50 PY-114 11.80 PY-325 6.70	Formula	PANTONE 5773 C PY-TW 86.65 PY-066 6.94 PY-114 4.16 PY-325 2.25	Formula	PANTONE 5783 C PY-TW 92.76 PY-066 3.25 PY-114 2.60 PY-325 1.39	Formula

Polyplast PY

PANTONE 5793 C	Formula
PY-TW	96.83
PY-066	1.29
PY-114	1.28
PY-325	0.60

PANTONE 5803 C	Formula
PY-TW	98.56
PY-114	0.65
PY-066	0.50
PY-325	0.29

PANTONE 5747 C	Formula
PY-066	52.60
PY-114	23.50
PY-325	14.20
PY-TW	6.40
PY-SB	3.30

PANTONE 5757 C	Formula
PY-066	64.20
PY-TW	18.00
PY-114	10.40
PY-325	6.30
PY-SB	1.10

PANTONE 5535 C	Formula
PY-325	40.00
PY-114	15.00
PY-TW	15.00
PY-066	15.00
PY-SB	15.00

PANTONE 5545 C	Formula
PY-TW	73.30
PY-SB	10.10
PY-066	9.70
PY-325	6.90

PANTONE 5555 C	Formula
PY-TW	88.50
PY-SB	5.00
PY-066	3.60
PY-325	2.90

PANTONE 5565 C	Formula
PY-TW	95.10
PY-SB	2.30
PY-066	1.30
PY-325	1.30

PANTONE 5575 C	Formula
PY-TW	97.60
PY-SB	1.30
PY-066	0.60
PY-325	0.50

PANTONE 5585 C	Formula
PY-TW	98.70
PY-SB	0.70
PY-066	0.30
PY-325	0.30

PANTONE 5595 C	Formula
PY-TW	99.10
PY-SB	0.50
PY-066	0.30
PY-325	0.10

PANTONE 560 C	Formula
PY-325	36.50
PY-TW	32.00
PY-114	23.00
PY-SB	5.50
PY-066	3.00

PANTONE 561 C	Formula
PY-TW	45.00
PY-325	40.00
PY-114	13.00
PY-230	2.00

PANTONE 562 C	Formula
PY-TW	65.00
PY-325	25.00
PY-114	10.00

PANTONE 563 C	Formula
PY-TW	95.90
PY-325	2.70
PY-114	0.80
PY-SB	0.60

PANTONE 564 C	Formula
PY-TW	96.70
PY-325	1.70
PY-121	1.20
PY-066	0.40

Polyplast PY

PANTONE 565 C	Formula
PY-TW 97.90	
PY-325 1.10	
PY-121 0.70	
PY-066 0.30	

PANTONE 566 C	Formula
PY-TW 99.00	
PY-325 0.50	
PY-121 0.30	
PY-066 0.20	

PANTONE 5605 C	Formula
PY-066 39.10	
PY-325 21.20	
PY-SB 19.10	
PY-TW 14.20	
PY-164 6.40	

PANTONE 5615 C	Formula
PY-TW 60.30	
PY-066 21.60	
PY-SB 13.80	
PY-325 4.30	

PANTONE 5625 C	Formula
PY-TW 83.10	
PY-066 8.90	
PY-SB 6.40	
PY-325 1.60	

PANTONE 5635 C	Formula
PY-TW 94.00	
PY-SB 2.80	
PY-066 2.70	
PY-325 0.50	

PANTONE 5645 C	Formula
PY-TW 95.60	
PY-064 2.40	
PY-SB 1.60	
PY-325 0.40	

PANTONE 5655 C	Formula
PY-TW 98.70	
PY-SB 0.70	
PY-066 0.40	
PY-325 0.20	

PANTONE 5665 C	Formula
PY-TW 99.10	
PY-SB 0.50	
PY-066 0.30	
PY-325 0.10	

PANTONE 567 C	Formula
PY-325 45.70	
PY-TW 29.60	
PY-114 14.00	
PY-066 7.30	
PY-SB 3.40	

PANTONE 552 C	Formula
PY-TW 99.20	
PY-SB 0.40	
PY-230 0.30	
PY-165 0.10	

PANTONE 5463 C	Formula
PY-MX 28.74	
PY-TW 24.07	
PY-SB 17.37	
PY-325 15.05	
PY-230 14.77	

PANTONE 5473 C	Formula
PY-TW 60.10	
PY-064 15.90	
PY-230 12.50	
PY-SB 8.70	
PY-325 2.80	

PANTONE 5483 C	Formula
PY-TW 84.00	
PY-064 7.60	
PY-230 4.60	
PY-SB 3.80	

PANTONE 5493 C	Formula
PY-TW 94.80	
PY-064 2.60	
PY-230 1.30	
PY-SB 1.30	

PANTONE 5503 C	Formula
PY-TW 96.70	
PY-064 1.50	
PY-SB 1.00	
PY-230 0.80	

Polyplast PY

PANTONE 5513 C	Formula
PY-TW 99.10	
PY-SB 0.40	
PY-066 0.20	
PY-230 0.20	
PY-066 0.10	

PANTONE 5523 C	Formula
PY-TW 99.60	
PY-SB 0.20	
PY-066 0.10	
PY-230 0.10	

PANTONE 5467 C	Formula
PY-MX 40.20	
PY-066 23.00	
PY-230 23.00	
PY-SB 11.50	
PY-TW 2.30	

PANTONE 5477 C	Formula
PY-TW 54.80	
PY-066 16.10	
PY-230 12.90	
PY-114 9.60	
PY-SB 6.60	

PANTONE 5487 C	Formula
PY-TW 77.80	
PY-114 7.00	
PY-066 6.60	
PY-230 6.10	
PY-SB 2.50	

PANTONE 5497 C	Formula
PY-TW 92.50	
PY-SB 3.00	
PY-066 1.50	
PY-114 1.50	
PY-230 1.50	

PANTONE 5507 C	Formula
PY-TW 97.70	
PY-SB 0.80	
PY-066 0.50	
PY-114 0.50	
PY-230 0.50	

PANTONE 5517 C	Formula
PY-TW 98.60	
PY-SB 0.40	
PY-230 0.40	
PY-066 0.30	
PY-114 0.30	

PANTONE 5527 C	Formula
PY-TW 99.21	
PY-SB 0.34	
PY-066 0.15	
PY-114 0.15	
PY-230 0.15	

PANTONE 553 C	Formula
PY-325 34.00	
PY-TW 22.00	
PY-066 22.00	
PY-114 11.00	
PY-SB 11.00	

PANTONE 554 C	Formula
PY-325 42.00	
PY-TW 28.00	
PY-066 20.00	
PY-114 5.00	
PY-SB 5.00	

PANTONE 555 C	Formula
PY-325 39.40	
PY-TW 39.40	
PY-066 15.20	
PY-114 3.00	
PY-SB 3.00	

PANTONE 556 C	Formula
PY-TW 90.50	
PY-325 4.00	
PY-066 3.00	
PY-SB 2.00	
PY-114 0.50	

PANTONE 557 C	Formula
PY-TW 95.70	
PY-325 1.80	
PY-066 1.20	
PY-SB 1.00	
PY-114 0.30	

PANTONE 558 C	Formula
PY-TW 98.00	
PY-325 0.80	
PY-114 0.40	
PY-066 0.40	
PY-SB 0.40	

PANTONE 559 C	Formula
PY-TW 99.00	
PY-325 0.40	
PY-114 0.20	
PY-066 0.20	
PY-SB 0.20	

Polyplast PY

PANTONE 537 C		Formula
PY-TW	67.00	
PY-MX	31.70	
PY-165	0.80	
PY-230	0.30	
PY-SB	0.20	

PANTONE 538 C		Formula
PY-TW	99.09	
PY-SB	0.39	
PY-165	0.37	
PY-230	0.15	

PANTONE 539 C		Formula
PY-230	68.57	
PY-TW	17.14	
PY-SB	14.29	

PANTONE 540 C		Formula
PY-230	79.70	
PY-TW	14.70	
PY-SB	3.00	
PY-064	2.60	

PANTONE 541 C		Formula
PY-230	75.40	
PY-TW	19.84	
PY-SB	3.57	
PY-127	1.19	

PANTONE 542 C		Formula
PY-TW	66.90	
PY-MX	24.10	
PY-230	4.80	
PY-165	3.40	
PY-SB	0.80	

PANTONE 543 C		Formula
PY-TW	75.80	
PY-MX	20.40	
PY-127	1.70	
PY-230	1.70	
PY-SB	0.40	

PANTONE 544 C		Formula
PY-TW	69.80	
PY-MX	28.50	
PY-165	0.80	
PY-230	0.60	
PY-SB	0.30	

PANTONE 545 C		Formula
PY-TW	99.00	
PY-230	0.50	
PY-SB	0.30	
PY-127	0.20	

PANTONE 5395 C		Formula
PY-230	49.52	
PY-TW	24.76	
PY-SB	20.00	
PY-127	4.29	
PY-325	1.43	

PANTONE 5405 C		Formula
PY-TW	39.90	
PY-MX	34.70	
PY-127	9.80	
PY-066	8.60	
PY-230	7.00	

PANTONE 5415 C		Formula
PY-TW	47.60	
PY-MX	36.20	
PY-127	6.60	
PY-066	5.70	
PY-230	3.90	

PANTONE 5425 C		Formula
PY-TW	92.20	
PY-165	2.80	
PY-SB	2.00	
PY-230	2.00	
PY-066	1.00	

PANTONE 5435 C		Formula
PY-TW	97.80	
PY-SB	0.80	
PY-230	0.60	
PY-127	0.50	
PY-066	0.30	

PANTONE 5445 C		Formula
PY-TW	99.12	
PY-SB	0.54	
PY-230	0.14	
PY-066	0.10	
PY-164	0.10	

PANTONE 5455 C		Formula
PY-TW	99.15	
PY-SB	0.50	
PY-230	0.21	
PY-165	0.14	

Polyplast PY

PANTONE 546 C PY-TW 26.00 PY-325 26.00 PY-SB 23.39 PY-230 16.14 PY-127 8.47	Formula	PANTONE 547 C PY-230 56.90 PY-325 22.70 PY-TW 12.20 PY-SB 8.20	Formula	PANTONE 548 C PY-230 46.81 PY-TW 25.53 PY-325 21.28 PY-SB 6.38	Formula	PANTONE 549 C PY-TW 90.30 PY-230 6.70 PY-SB 2.90 PY-325 0.10	Formula
PANTONE 550 C PY-TW 96.00 PY-230 2.50 PY-SB 1.50	Formula	PANTONE 551 C PY-TW 98.03 PY-230 1.50 PY-SB 0.37 PY-127 0.10	Formula	PANTONE 5225 C PY-TW 97.10 PY-SB 0.90 PY-164 0.90 PY-066 0.80 PY-127 0.30	Formula	PANTONE 5235 C PY-TW 98.80 PY-SB 0.50 PY-164 0.40 PY-066 0.30	Formula
PANTONE 5245 C PY-TW 99.10 PY-164 0.30 PY-066 0.30 PY-SB 0.30	Formula	PANTONE 525 C PY-TW 36.38 PY-164 25.84 PY-127 23.86 PY-MX 9.94 PY-SB 3.98	Formula	PANTONE 526 C PY-165 27.00 PY-MX 23.60 PY-TW 23.00 PY-127 20.20 PY-064 6.20	Formula	PANTONE 527 C PY-165 28.28 PY-TW 28.28 PY-MX 23.15 PY-127 19.83 PY-230 0.46	Formula
PANTONE 528 C PY-TW 70.00 PY-MX 23.00 PY-127 5.40 PY-164 1.60	Formula	PANTONE 529 C PY-TW 59.30 PY-MX 37.40 PY-127 2.50 PY-066 0.50 PY-164 0.30	Formula	PANTONE 530 C PY-TW 70.60 PY-MX 26.90 PY-127 1.60 PY-066 0.60 PY-164 0.30	Formula	PANTONE 531 C PY-TW 98.20 PY-165 1.40 PY-127 0.30 PY-230 0.10	Formula

Polyplast PY

PANTONE 5255 C PY-127 39.71 PY-TW 30.69 PY-165 15.16 PY-SB 14.44	Formula	PANTONE 5265 C PY-TW 49.10 PY-127 39.50 PY-SB 7.90 PY-114 3.50	Formula	PANTONE 5275 C PY-TW 75.70 PY-127 17.20 PY-SB 5.50 PY-114 1.60	Formula	PANTONE 5285 C PY-TW 91.50 PY-127 5.30 PY-SB 2.60 PY-114 0.60	Formula
PANTONE 5295 C PY-TW 97.00 PY-127 1.60 PY-SB 1.20 PY-114 0.10 PY-230 0.10	Formula	PANTONE 5305 C PY-TW 98.10 PY-127 0.90 PY-SB 0.60 PY-114 0.30 PY-230 0.10	Formula	PANTONE 5315 C PY-TW 99.11 PY-SB 0.52 PY-127 0.27 PY-165 0.10	Formula	PANTONE 532 C PY-TW 50.38 PY-SB 25.17 PY-165 20.86 PY-230 3.59	Formula
PANTONE 533 C PY-TW 45.32 PY-165 29.56 PY-SB 9.85 PY-230 8.37 PY-064 6.90	Formula	PANTONE 534 C PY-TW 63.38 PY-127 14.09 PY-230 8.45 PY-SB 8.45 PY-165 5.63	Formula	PANTONE 535 C PY-TW 94.68 PY-165 2.80 PY-SB 1.40 PY-230 1.12	Formula	PANTONE 536 C PY-TW 83.29 PY-MX 13.88 PY-165 1.48 PY-SB 0.79 PY-230 0.56	Formula
PANTONE 514 C PY-TW 88.00 PY-165 11.30 PY-127 0.70	Formula	PANTONE 515 C PY-TW 92.00 PY-165 7.70 PY-127 0.30	Formula	PANTONE 516 C PY-TW 96.20 PY-165 3.80	Formula	PANTONE 517 C PY-TW 99.30 PY-164 0.60 PY-121 0.10	Formula

Polyplast PY

PANTONE 5115 C PY-165 58.80 PY-TW 17.60 PY-SB 14.20 PY-114 8.20 PY-127 1.20	Formula	PANTONE 5125 C PY-TW 42.98 PY-165 27.27 PY-MX 16.96 PY-SB 8.26 PY-164 4.53	Formula	PANTONE 5135 C PY-TW 81.90 PY-127 9.00 PY-066 7.10 PY-164 2.00	Formula	PANTONE 5145 C PY-TW 91.00 PY-127 4.40 PY-066 3.70 PY-164 0.90	Formula
PANTONE 5155 C PY-TW 97.00 PY-127 1.70 PY-066 1.30	Formula	PANTONE 5165 C PY-TW 98.60 PY-127 0.70 PY-066 0.60 PY-164 0.10	Formula	PANTONE 5175 C PY-TW 99.30 PY-066 0.30 PY-127 0.30 PY-164 0.10	Formula	PANTONE 518 C PY-TW 54.50 PY-164 18.20 PY-066 11.80 PY-SB 10.00 PY-127 5.50	Formula
PANTONE 519 C PY-TW 46.90 PY-164 33.00 PY-064 13.90 PY-325 5.20 PY-127 1.00	Formula	PANTONE 520 C PY-TW 58.40 PY-164 18.60 PY-127 17.90 PY-121 3.60 PY-SB 1.50	Formula	PANTONE 521 C PY-TW 94.80 PY-164 2.10 PY-127 2.10 PY-SB 1.00	Formula	PANTONE 522 C PY-TW 95.90 PY-127 2.80 PY-114 0.70 PY-066 0.60	Formula
PANTONE 523 C PY-TW 98.00 PY-127 1.40 PY-066 0.30 PY-114 0.30	Formula	PANTONE 524 C PY-TW 98.80 PY-127 0.80 PY-066 0.40	Formula	PANTONE 5185 C PY-164 34.30 PY-TW 24.50 PY-066 19.60 PY-SB 14.70 PY-127 6.90	Formula	PANTONE 5195 C PY-TW 42.80 PY-164 28.40 PY-066 13.20 PY-SB 8.90 PY-127 6.70	Formula

Polyplast PY

PANTONE 5205 C PY-TW 83.30 PY-164 6.60 PY-066 4.40 PY-SB 4.10 PY-127 1.60	Formula	PANTONE 5215 C PY-TW 94.10 PY-164 2.00 PY-SB 1.80 PY-066 1.70 PY-127 0.40	Formula	PANTONE 499 C PY-121 84.51 PY-SB 8.45 PY-TW 7.04	Formula	PANTONE 500 C PY-TW 91.20 PY-114 5.80 PY-164 2.00 PY-SB 1.00	Formula
PANTONE 501 C PY-TW 97.40 PY-114 1.80 PY-164 0.50 PY-SB 0.30	Formula	PANTONE 502 C PY-TW 98.20 PY-121 1.20 PY-165 0.60	Formula	PANTONE 503 C PY-TW 98.80 PY-121 0.90 PY-165 0.30	Formula	PANTONE 4975 C PY-114 38.50 PY-164 27.50 PY-SB 15.50 PY-066 13.20 PY-TW 5.30	Formula
PANTONE 4985 C PY-TW 46.90 PY-114 32.80 PY-165 15.60 PY-230 3.90 PY-SB 0.80	Formula	PANTONE 4995 C PY-TW 78.10 PY-114 10.50 PY-165 8.20 PY-SB 3.20	Formula	PANTONE 5005 C PY-TW 89.00 PY-114 5.20 PY-165 3.90 PY-SB 1.90	Formula	PANTONE 5015 C PY-TW 96.00 PY-114 1.90 PY-165 1.30 PY-SB 0.80	Formula
PANTONE 5025 C PY-TW 97.80 PY-114 1.00 PY-165 0.70 PY-SB 0.50	Formula	PANTONE 5035 C PY-TW 98.90 PY-114 0.70 PY-165 0.20 PY-SB 0.20	Formula	PANTONE 504 C PY-164 43.90 PY-066 36.50 PY-SB 10.80 PY-TW 8.80	Formula	PANTONE 505 C PY-165 66.70 PY-114 17.80 PY-SB 6.60 PY-TW 5.60 PY-127 3.30	Formula

Polyplast PY

PANTONE 506 C		Formula
PY-165	56.50	
PY-114	18.30	
PY-MX	14.90	
PY-TW	7.90	
PY-230	2.40	

PANTONE 507 C		Formula
PY-TW	85.10	
PY-165	11.20	
PY-114	3.00	
PY-SB	0.70	

PANTONE 508 C		Formula
PY-TW	93.20	
PY-165	5.00	
PY-114	1.50	
PY-SB	0.30	

PANTONE 509 C		Formula
PY-TW	96.40	
PY-165	2.40	
PY-114	1.00	
PY-SB	0.20	

PANTONE 510 C		Formula
PY-TW	97.40	
PY-165	1.60	
PY-114	0.90	
PY-SB	0.10	

PANTONE 511 C		Formula
PY-164	40.40	
PY-TW	34.90	
PY-127	12.80	
PY-066	9.30	
PY-SB	2.60	

PANTONE 512 C		Formula
PY-165	61.60	
PY-TW	30.80	
PY-127	4.10	
PY-SB	1.90	
PY-164	1.60	

PANTONE 513 C		Formula
PY-MX	62.73	
PY-165	30.84	
PY-127	5.23	
PY-SB	1.20	

PANTONE 477 C		Formula
PY-064	75.80	
PY-TW	8.90	
PY-164	7.90	
PY-SB	7.40	

PANTONE 478 C		Formula
PY-064	71.00	
PY-TW	8.90	
PY-164	7.70	
PY-MX	7.10	
PY-SB	5.30	

PANTONE 479 C		Formula
PY-TW	68.60	
PY-064	27.00	
PY-164	2.70	
PY-SB	1.70	

PANTONE 480 C		Formula
PY-TW	91.30	
PY-064	7.20	
PY-164	0.80	
PY-SB	0.70	

PANTONE 481 C		Formula
PY-TW	95.40	
PY-064	3.80	
PY-164	0.40	
PY-SB	0.40	

PANTONE 482 C		Formula
PY-TW	97.60	
PY-064	2.00	
PY-164	0.20	
PY-SB	0.20	

PANTONE 483 C		Formula
PY-MX	49.60	
PY-121	23.30	
PY-066	15.40	
PY-SB	7.70	
PY-TW	4.00	

PANTONE 484 C		Formula
PY-114	83.40	
PY-121	13.40	
PY-SB	3.20	

Polyplast PY

PANTONE 485 C PY-121 99.00 PY-164 1.00	Formula	PANTONE 486 C PY-TW 80.00 PY-064 16.70 PY-164 2.10 PY-121 0.70 PY-066 0.50	Formula	PANTONE 487 C PY-TW 89.50 PY-064 8.90 PY-164 1.10 PY-066 0.50	Formula	PANTONE 488 C PY-TW 94.30 PY-064 4.50 PY-164 0.80 PY-066 0.40	Formula
PANTONE 489 C PY-TW 98.20 PY-121 1.10 PY-066 0.70	Formula	PANTONE 490 C PY-114 50.80 PY-165 25.50 PY-TW 17.00 PY-230 4.20 PY-SB 2.50	Formula	PANTONE 491 C PY-164 51.90 PY-114 39.00 PY-SB 6.50 PY-TW 2.60	Formula	PANTONE 492 C PY-TW 28.60 PY-MX 26.80 PY-164 20.50 PY-066 19.60 PY-SB 4.50	Formula
PANTONE 493 C PY-TW 91.90 PY-114 4.80 PY-164 3.00 PY-SB 0.30	Formula	PANTONE 494 C PY-TW 97.50 PY-114 1.60 PY-164 0.90	Formula	PANTONE 495 C PY-TW 98.30 PY-164 1.10 PY-066 0.60	Formula	PANTONE 496 C PY-TW 98.90 PY-114 0.60 PY-164 0.40 PY-066 0.10	Formula
PANTONE 497 C PY-114 36.10 PY-066 24.80 PY-164 20.80 PY-SB 11.40 PY-TW 6.90	Formula	PANTONE 498 C PY-114 35.60 PY-066 26.10 PY-164 20.20 PY-TW 9.40 PY-SB 8.70	Formula	PANTONE 4625 C PY-064 42.80 PY-MX 36.20 PY-SB 15.50 PY-164 5.50	Formula	PANTONE 4635 C PY-MX 47.20 PY-066 19.40 PY-TW 19.00 PY-121 9.50 PY-SB 4.90	Formula

Polyplast PY

PANTONE 4645 C	Formula
PY-TW	48.50
PY-MX	38.00
PY-066	6.40
PY-121	4.50
PY-SB	2.60

PANTONE 4655 C	Formula
PY-TW	70.00
PY-MX	22.00
PY-066	3.40
PY-121	2.90
PY-SB	1.70

PANTONE 4665 C	Formula
PY-TW	95.30
PY-066	2.20
PY-121	1.80
PY-SB	0.70

PANTONE 4675 C	Formula
PY-TW	97.30
PY-066	1.30
PY-121	1.00
PY-SB	0.40

PANTONE 4685 C	Formula
PY-TW	98.40
PY-066	0.70
PY-121	0.70
PY-SB	0.20

PANTONE 469 C	Formula
PY-MX	43.00
PY-066	38.30
PY-121	7.10
PY-127	6.20
PY-SB	5.40

PANTONE 470 C	Formula
PY-066	48.60
PY-MX	31.50
PY-121	8.20
PY-127	7.00
PY-TW	4.70

PANTONE 471 C	Formula
PY-066	42.77
PY-MX	35.74
PY-121	9.91
PY-TW	7.72
PY-127	3.86

PANTONE 472 C	Formula
PY-TW	87.60
PY-066	8.20
PY-121	3.50
PY-127	0.70

PANTONE 473 C	Formula
PY-TW	96.10
PY-066	2.00
PY-121	1.50
PY-165	0.40

PANTONE 474 C	Formula
PY-TW	97.50
PY-066	1.30
PY-121	1.10
PY-165	0.10

PANTONE 475 C	Formula
PY-TW	98.00
PY-066	1.00
PY-121	0.90
PY-165	0.10

PANTONE 4695 C	Formula
PY-064	77.20
PY-164	12.30
PY-SB	10.50

PANTONE 4705 C	Formula
PY-064	57.90
PY-TW	28.20
PY-164	7.80
PY-SB	6.10

PANTONE 4715 C	Formula
PY-TW	55.20
PY-064	36.30
PY-164	4.80
PY-SB	3.70

PANTONE 4725 C	Formula
PY-TW	90.50
PY-066	5.00
PY-164	2.30
PY-SB	2.20

Polyplast PY

PANTONE 4735 C		Formula
PY-TW	95.90	
PY-066	1.90	
PY-SB	1.30	
PY-164	0.90	

PANTONE 4745 C		Formula
PY-TW	97.50	
PY-066	1.10	
PY-SB	0.80	
PY-164	0.60	

PANTONE 4755 C		Formula
PY-TW	98.60	
PY-066	0.60	
PY-SB	0.50	
PY-164	0.30	

PANTONE 476 C		Formula
PY-064	73.10	
PY-SB	10.40	
PY-TW	9.60	
PY-164	6.90	

PANTONE 454 C		Formula
PY-TW	97.90	
PY-064	1.50	
PY-SB	0.50	
PY-114	0.10	

PANTONE 4485 C		Formula
PY-064	47.90	
PY-066	36.70	
PY-SB	12.00	
PY-114	3.40	

PANTONE 4495 C		Formula
PY-064	75.60	
PY-TW	16.60	
PY-SB	5.70	
PY-114	2.10	

PANTONE 4505 C		Formula
PY-064	48.20	
PY-TW	46.20	
PY-SB	3.70	
PY-114	1.90	

PANTONE 4515 C		Formula
PY-TW	72.60	
PY-064	24.40	
PY-SB	1.90	
PY-114	1.10	

PANTONE 4525 C		Formula
PY-TW	88.00	
PY-064	10.20	
PY-SB	1.10	
PY-114	0.70	

PANTONE 4535 C		Formula
PY-TW	94.20	
PY-064	5.00	
PY-SB	0.50	
PY-114	0.30	

PANTONE 4545 C		Formula
PY-TW	96.50	
PY-064	3.00	
PY-SB	0.30	
PY-114	0.20	

PANTONE 455 C		Formula
PY-064	89.10	
PY-SB	9.60	
PY-114	1.30	

PANTONE 456 C		Formula
PY-064	88.20	
PY-TW	7.10	
PY-SB	3.50	
PY-114	1.20	

PANTONE 457 C		Formula
PY-064	88.00	
PY-TW	8.20	
PY-SB	2.40	
PY-114	1.40	

PANTONE 458 C		Formula
PY-TW	76.10	
PY-064	15.60	
PY-066	7.70	
PY-SB	0.60	

Polyplast PY

PANTONE 459 C	Formula
PY-TW 88.70	
PY-064 7.00	
PY-066 4.00	
PY-SB 0.30	

PANTONE 460 C	Formula
PY-TW 92.90	
PY-064 3.80	
PY-066 3.10	
PY-SB 0.20	

PANTONE 461 C	Formula
PY-TW 95.90	
PY-064 2.00	
PY-066 2.00	
PY-SB 0.10	

PANTONE 462 C	Formula
PY-064 74.90	
PY-SB 12.30	
PY-114 7.50	
PY-TW 5.30	

PANTONE 463 C	Formula
PY-064 76.90	
PY-SB 8.10	
PY-TW 7.70	
PY-114 7.30	

PANTONE 464 C	Formula
PY-064 79.80	
PY-114 9.30	
PY-SB 6.80	
PY-TW 4.10	

PANTONE 465 C	Formula
PY-TW 72.80	
PY-064 23.10	
PY-114 2.30	
PY-SB 1.80	

PANTONE 466 C	Formula
PY-TW 88.00	
PY-064 9.80	
PY-114 1.20	
PY-SB 1.00	

PANTONE 467 C	Formula
PY-TW 92.70	
PY-064 5.70	
PY-114 0.80	
PY-SB 0.80	

PANTONE 468 C	Formula
PY-TW 96.30	
PY-064 2.90	
PY-114 0.40	
PY-SB 0.40	

PANTONE Warm Gray 7 C	Formula
PY-TW 92.40	
PY-SB 4.00	
PY-066 2.20	
PY-121 1.40	

PANTONE Warm Gray 8 C	Formula
PY-TW 88.80	
PY-SB 5.60	
PY-066 3.40	
PY-121 2.20	

PANTONE Warm Gray 9 C	Formula
PY-TW 85.80	
PY-SB 6.40	
PY-066 4.90	
PY-121 2.90	

PANTONE Warm Gray 10 C	Formula
PY-TW 82.30	
PY-SB 7.80	
PY-066 6.20	
PY-121 3.70	

PANTONE Warm Gray 11 C	Formula
PY-TW 69.80	
PY-SB 12.50	
PY-066 11.20	
PY-121 6.50	

PANTONE Cool Gray 1 C	Formula
PY-TW 99.40	
PY-064 0.30	
PY-SB 0.30	

Polyplast PY

PANTONE Cool Gray 2 C PY-TW 98.80 PY-064 0.60 PY-SB 0.60	Formula	PANTONE Cool Gray 3 C PY-TW 97.70 PY-SB 1.20 PY-064 1.00 PY-165 0.10	Formula	PANTONE Cool Gray 4 C PY-TW 97.40 PY-SB 1.50 PY-064 1.00 PY-165 0.10	Formula	PANTONE Cool Gray 5 C PY-TW 96.70 PY-SB 2.10 PY-064 1.00 PY-165 0.20	Formula
PANTONE Cool Gray 6 C PY-TW 96.30 PY-SB 2.50 PY-064 1.00 PY-165 0.20	Formula	PANTONE Cool Gray 7 C PY-TW 95.40 PY-SB 3.30 PY-064 1.00 PY-165 0.30	Formula	PANTONE Cool Gray 8 C PY-TW 93.20 PY-SB 4.90 PY-064 1.50 PY-165 0.40	Formula	PANTONE Cool Gray 9 C PY-TW 90.60 PY-SB 6.50 PY-064 2.00 PY-165 0.70 PY-121 0.20	Formula
PANTONE Cool Gray 10 C PY-TW 85.90 PY-SB 9.40 PY-064 3.00 PY-121 1.70	Formula	PANTONE Cool Gray 11 C PY-TW 74.90 PY-SB 13.90 PY-064 8.30 PY-121 2.90	Formula	PANTONE 448 C PY-064 62.30 PY-114 17.30 PY-SB 8.50 PY-TW 6.50 PY-325 5.40	Formula	PANTONE 449 C PY-064 70.60 PY-114 19.20 PY-325 5.80 PY-SB 4.40	Formula
PANTONE 432 C PY-TW 69.80 PY-SB 23.30 PY-064 6.90	Formula	PANTONE 433 C PY-SB 54.55 PY-TW 36.36 PY-230 9.09	Formula	PANTONE 434 C PY-TW 98.60 PY-SB 0.40 PY-066 0.40 PY-165 0.40 PY-127 0.20	Formula	PANTONE 435 C PY-TW 97.70 PY-SB 0.70 PY-066 0.70 PY-165 0.60 PY-127 0.30	Formula

Polyplast PY

PANTONE 436 C PY-TW 95.90 PY-SB 1.50 PY-066 1.20 PY-165 1.00 PY-127 0.40	Formula	PANTONE 437 C PY-TW 85.40 PY-165 7.60 PY-SB 3.50 PY-066 3.00 PY-127 0.50	Formula	PANTONE 438 C PY-121 45.30 PY-TW 33.30 PY-SB 18.80 PY-066 2.60	Formula	PANTONE 439 C PY-121 39.50 PY-TW 29.10 PY-SB 23.90 PY-066 7.50	Formula
PANTONE 440 C PY-SB 27.30 PY-TW 27.30 PY-121 27.30 PY-066 18.10	Formula	PANTONE 441 C PY-TW 99.00 PY-SB 0.80 PY-066 0.10 PY-325 0.10	Formula	PANTONE 442 C PY-TW 98.20 PY-SB 1.40 PY-066 0.20 PY-325 0.20	Formula	PANTONE 443 C PY-TW 97.10 PY-SB 1.70 PY-121 0.60 PY-325 0.60	Formula
PANTONE 444 C PY-TW 95.30 PY-SB 2.60 PY-121 1.10 PY-325 1.00	Formula	PANTONE 445 C PY-TW 80.00 PY-SB 19.03 PY-325 0.97	Formula	PANTONE 446 C PY-TW 40.90 PY-121 30.70 PY-325 15.40 PY-SB 10.20 PY-066 2.80	Formula	PANTONE 447 C PY-TW 34.90 PY-121 34.90 PY-325 13.10 PY-SB 8.70 PY-066 8.40	Formula
PANTONE Warm Gray 1 C PY-TW 98.40 PY-064 1.00 PY-SB 0.40 PY-114 0.20	Formula	PANTONE Warm Gray 2 C PY-TW 97.00 PY-064 1.80 PY-SB 0.90 PY-114 0.30	Formula	PANTONE Warm Gray 3 C PY-TW 96.70 PY-064 1.80 PY-SB 1.10 PY-114 0.40	Formula	PANTONE Warm Gray 4 C PY-TW 95.70 PY-064 2.20 PY-SB 1.50 PY-114 0.60	Formula

Polyplast PY

PANTONE Warm Gray 5 C	Formula
PY-TW 93.80	
PY-SB 2.90	
PY-064 2.50	
PY-114 0.80	

PANTONE 409 C	Formula
PY-TW 88.70	
PY-064 4.80	
PY-SB 4.30	
PY-114 2.20	

PANTONE 410 C	Formula
PY-TW 77.30	
PY-064 11.40	
PY-SB 6.60	
PY-114 4.70	

PANTONE 411 C	Formula
PY-TW 73.20	
PY-064 13.30	
PY-SB 8.30	
PY-114 5.20	

PANTONE 412 C	Formula
PY-064 32.00	
PY-114 25.00	
PY-SB 22.00	
PY-TW 21.00	

PANTONE 413 C	Formula
PY-TW 97.30	
PY-064 1.50	
PY-SB 1.20	

PANTONE 414 C	Formula
PY-TW 94.70	
PY-064 3.00	
PY-SB 2.30	

PANTONE 415 C	Formula
PY-TW 91.90	
PY-064 4.90	
PY-SB 3.20	

PANTONE 416 C	Formula
PY-TW 85.90	
PY-064 7.00	
PY-SB 4.70	
PY-066 1.60	
PY-114 0.80	

PANTONE 417 C	Formula
PY-TW 75.00	
PY-064 11.00	
PY-SB 9.00	
PY-066 4.00	
PY-114 1.00	

PANTONE 418 C	Formula
PY-TW 72.10	
PY-064 13.40	
PY-SB 9.60	
PY-066 3.90	
PY-114 1.00	

PANTONE 419 C	Formula
PY-064 51.20	
PY-SB 23.30	
PY-114 11.50	
PY-TW 9.30	
PY-325 4.70	

PANTONE 420 C	Formula
PY-TW 98.60	
PY-SB 0.80	
PY-064 0.60	

PANTONE 421 C	Formula
PY-TW 98.00	
PY-SB 1.40	
PY-064 0.60	

PANTONE 422 C	Formula
PY-TW 96.40	
PY-SB 1.90	
PY-064 1.60	
PY-114 0.10	

PANTONE 423 C	Formula
PY-TW 93.90	
PY-SB 4.00	
PY-064 1.00	
PY-066 1.00	
PY-114 0.10	

Polyplast PY

PANTONE 424 C PY-TW 90.20 PY-SB 6.50 PY-066 1.90 PY-064 1.00 PY-114 0.40	Formula	PANTONE 425 C PY-TW 79.40 PY-SB 12.20 PY-066 5.10 PY-064 1.90 PY-114 1.40	Formula	PANTONE 426 C PY-SB 36.00 PY-064 36.00 PY-TW 15.00 PY-114 13.00	Formula	PANTONE 427 C PY-TW 99.40 PY-SB 0.40 PY-064 0.20	Formula
PANTONE 428 C PY-TW 98.70 PY-SB 1.00 PY-064 0.30	Formula	PANTONE 429 C PY-TW 97.10 PY-SB 2.00 PY-066 0.30 PY-114 0.30 PY-230 0.30	Formula	PANTONE 430 C PY-TW 95.10 PY-SB 3.40 PY-114 0.60 PY-066 0.50 PY-230 0.40	Formula	PANTONE 395 C PY-064 62.40 PY-TW 35.10 PY-066 2.30 PY-325 0.20	Formula
PANTONE 396 C PY-064 64.10 PY-TW 32.00 PY-066 3.50 PY-325 0.40	Formula	PANTONE 397 C PY-064 63.00 PY-066 36.00 PY-230 1.00	Formula	PANTONE 398 C PY-064 65.30 PY-066 32.10 PY-114 1.30 PY-230 1.30	Formula	PANTONE 399 C PY-064 62.80 PY-066 30.90 PY-114 4.10 PY-230 2.20	Formula
PANTONE 3935 C PY-TW 70.00 PY-064 28.00 PY-066 2.00	Formula	PANTONE 3945 C PY-064 71.00 PY-TW 28.00 PY-066 1.00	Formula	PANTONE 3955 C PY-064 98.80 PY-066 1.20	Formula	PANTONE 3965 C PY-064 95.60 PY-066 4.30 PY-230 0.10	Formula

Polyplast PY

PANTONE 3975 C PY-064 63.60 PY-066 33.30 PY-114 2.00 PY-230 1.10	Formula	PANTONE 3985 C PY-064 61.60 PY-066 32.30 PY-114 4.00 PY-230 2.10	Formula	PANTONE 3995 C PY-064 57.70 PY-066 28.90 PY-114 6.70 PY-SB 3.90 PY-230 2.80	Formula	PANTONE 400 C PY-TW 96.50 PY-064 2.00 PY-SB 1.10 PY-114 0.40	Formula
PANTONE 401 C PY-TW 94.80 PY-064 3.00 PY-SB 1.70 PY-114 0.50	Formula	PANTONE 402 C PY-TW 91.40 PY-064 4.40 PY-SB 2.90 PY-114 1.30	Formula	PANTONE 403 C PY-TW 85.70 PY-064 8.30 PY-SB 4.20 PY-114 1.80	Formula	PANTONE 404 C PY-TW 78.00 PY-064 12.80 PY-SB 6.40 PY-114 2.80	Formula
PANTONE 405 C PY-TW 65.20 PY-064 16.30 PY-SB 10.80 PY-114 4.40 PY-066 3.30	Formula	PANTONE Black C PY-064 35.00 PY-SB 27.00 PY-114 19.00 PY-TW 10.00 PY-066 9.00	Formula	PANTONE 406 C PY-TW 97.50 PY-SB 1.00 PY-064 1.00 PY-114 0.50	Formula	PANTONE 407 C PY-TW 94.70 PY-064 2.30 PY-SB 2.00 PY-114 1.00	Formula
PANTONE 408 C PY-TW 92.90 PY-064 2.90 PY-SB 2.90 PY-114 1.30	Formula	PANTONE 373 C PY-TW 83.10 PY-064 14.00 PY-066 2.50 PY-325 0.40	Formula	PANTONE 374 C PY-TW 78.00 PY-064 16.00 PY-066 5.10 PY-325 0.90	Formula	PANTONE 375 C PY-064 97.60 PY-325 2.40	Formula

Polyplast PY

PANTONE 376 C PY-064 96.00 PY-325 2.10 PY-066 1.10 PY-SB 0.80	Formula	PANTONE 377 C PY-064 93.10 PY-SB 2.40 PY-325 2.40 PY-066 2.10	Formula	PANTONE 378 C PY-064 88.60 PY-SB 7.10 PY-325 2.30 PY-066 2.00	Formula	PANTONE 379 C PY-TW 69.60 PY-064 28.20 PY-066 2.00 PY-325 0.20	Formula
PANTONE 380 C PY-TW 50.20 PY-064 46.50 PY-066 3.00 PY-325 0.30	Formula	PANTONE 381 C PY-064 50.90 PY-TW 43.90 PY-066 4.80 PY-325 0.40	Formula	PANTONE 382 C PY-064 60.00 PY-TW 33.70 PY-066 5.50 PY-325 0.80	Formula	PANTONE 383 C PY-066 46.80 PY-064 40.40 PY-TW 10.60 PY-325 1.60 PY-SB 0.60	Formula
PANTONE 384 C PY-066 46.30 PY-064 40.00 PY-TW 10.50 PY-325 1.60 PY-SB 1.60	Formula	PANTONE 385 C PY-066 81.20 PY-TW 10.20 PY-SB 5.10 PY-325 2.00 PY-114 1.50	Formula	PANTONE 386 C PY-TW 60.00 PY-064 40.00	Formula	PANTONE 387 C PY-064 50.00 PY-TW 49.90 PY-325 0.10	Formula
PANTONE 388 C PY-064 55.50 PY-TW 44.30 PY-325 0.20	Formula	PANTONE 389 C PY-064 97.30 PY-066 2.20 PY-325 0.50	Formula	PANTONE 390 C PY-064 93.00 PY-066 4.00 PY-114 1.50 PY-325 1.50	Formula	PANTONE 391 C PY-064 88.20 PY-066 5.90 PY-114 2.90 PY-325 2.00 PY-SB 1.00	Formula

Polyplast PY

PANTONE 392 C PY-064 86.50 PY-066 5.80 PY-SB 2.90 PY-114 2.90 PY-325 1.90	Formula	PANTONE 393 C PY-TW 82.80 PY-064 16.20 PY-066 1.00	Formula	PANTONE 394 C PY-TW 53.58 PY-064 45.41 PY-066 0.91 PY-325 0.10	Formula	PANTONE 351 C PY-TW 96.00 PY-064 2.00 PY-325 1.20 PY-066 0.80	Formula
PANTONE 352 C PY-TW 95.00 PY-064 2.00 PY-325 1.70 PY-066 1.30	Formula	PANTONE 353 C PY-TW 93.00 PY-325 2.60 PY-066 2.50 PY-064 1.90	Formula	PANTONE 354 C PY-064 74.30 PY-325 16.20 PY-TW 9.50	Formula	PANTONE 355 C PY-064 74.00 PY-325 16.00 PY-TW 9.00 PY-SB 1.00	Formula
PANTONE 356 C PY-064 70.90 PY-325 15.50 PY-TW 9.10 PY-SB 2.70 PY-066 1.80	Formula	PANTONE 357 C PY-066 39.50 PY-325 26.30 PY-TW 26.30 PY-SB 4.40 PY-121 3.50	Formula	PANTONE 358 C PY-TW 93.80 PY-066 4.90 PY-325 1.30	Formula	PANTONE 359 C PY-TW 93.60 PY-066 4.90 PY-325 1.50	Formula
PANTONE 360 C PY-064 54.10 PY-TW 43.20 PY-230 2.20 PY-066 0.50	Formula	PANTONE 361 C PY-064 64.50 PY-TW 28.60 PY-230 3.70 PY-066 3.20	Formula	PANTONE 362 C PY-064 61.80 PY-TW 31.00 PY-230 3.50 PY-066 3.00 PY-SB 0.70	Formula	PANTONE 363 C PY-064 63.30 PY-TW 28.00 PY-066 4.30 PY-230 3.60 PY-SB 0.80	Formula

Polyplast PY

PANTONE 364 C PY-064 63.00 PY-TW 25.00 PY-066 6.50 PY-230 3.00 PY-SB 2.50	Formula	PANTONE 365 C PY-TW 96.90 PY-066 2.60 PY-325 0.50	Formula	PANTONE 366 C PY-TW 94.50 PY-066 4.50 PY-325 1.00	Formula	PANTONE 367 C PY-TW 90.50 PY-066 8.10 PY-325 1.40	Formula
PANTONE 368 C PY-064 81.50 PY-066 13.00 PY-325 5.50	Formula	PANTONE 369 C PY-064 79.90 PY-066 13.70 PY-325 5.40 PY-SB 1.00	Formula	PANTONE 370 C PY-064 72.10 PY-066 17.30 PY-325 7.70 PY-SB 2.90	Formula	PANTONE 371 C PY-066 69.00 PY-064 21.70 PY-SB 5.30 PY-325 4.00	Formula
PANTONE 372 C PY-TW 88.20 PY-064 10.10 PY-066 1.40 PY-325 0.30	Formula	PANTONE 336 C PY-TW 44.60 PY-325 26.80 PY-064 22.30 PY-SB 6.30	Formula	PANTONE 337 C PY-TW 97.10 PY-064 1.30 PY-325 1.20 PY-SB 0.40	Formula	PANTONE 338 C PY-TW 94.90 PY-325 2.50 PY-064 2.00 PY-SB 0.60	Formula
PANTONE 339 C PY-TW 69.10 PY-325 17.20 PY-064 12.90 PY-SB 0.80	Formula	PANTONE 340 C PY-325 41.60 PY-TW 36.20 PY-064 21.70 PY-SB 0.50	Formula	PANTONE 341 C PY-325 40.80 PY-TW 30.70 PY-064 25.60 PY-SB 2.90	Formula	PANTONE 342 C PY-325 62.00 PY-TW 22.10 PY-066 11.50 PY-SB 4.40	Formula

Polyplast PY

PANTONE 343 C PY-325 52.60 PY-TW 18.80 PY-066 18.80 PY-SB 9.80	Formula	PANTONE 3375 C PY-TW 95.60 PY-064 2.70 PY-325 1.70	Formula	PANTONE 3385 C PY-TW 91.80 PY-064 4.30 PY-325 3.90	Formula	PANTONE 3395 C PY-TW 78.40 PY-064 10.80 PY-325 10.80	Formula
PANTONE 3405 C PY-TW 47.70 PY-064 20.50 PY-325 20.40 PY-MX 11.40	Formula	PANTONE 3415 C PY-325 47.20 PY-TW 29.30 PY-064 15.10 PY-066 7.50 PY-SB 0.90	Formula	PANTONE 3425 C PY-325 50.00 PY-TW 22.00 PY-066 13.00 PY-064 12.00 PY-SB 3.00	Formula	PANTONE 3435 C PY-325 43.90 PY-TW 19.30 PY-066 15.80 PY-064 12.30 PY-SB 8.70	Formula
PANTONE 344 C PY-TW 97.60 PY-066 1.30 PY-325 0.90 PY-SB 0.20	Formula	PANTONE 345 C PY-TW 96.30 PY-325 1.70 PY-066 1.70 PY-SB 0.30	Formula	PANTONE 346 C PY-TW 94.20 PY-325 3.00 PY-066 2.50 PY-SB 0.30	Formula	PANTONE 347 C PY-064 41.70 PY-325 32.40 PY-TW 24.10 PY-066 1.80	Formula
PANTONE 348 C PY-064 40.20 PY-325 31.20 PY-TW 23.20 PY-066 4.50 PY-SB 0.90	Formula	PANTONE 349 C PY-064 37.60 PY-325 28.20 PY-TW 18.80 PY-066 12.20 PY-SB 3.20	Formula	PANTONE 350 C PY-066 48.90 PY-325 30.90 PY-TW 10.60 PY-SB 9.60	Formula	PANTONE 3292 C PY-TW 41.67 PY-325 34.17 PY-064 11.16 PY-SB 7.17 PY-230 5.83	Formula

Polyplast PY

PANTONE 3302 C		Formula
PY-TW	28.86	
PY-325	28.86	
PY-064	24.24	
PY-SB	12.99	
PY-230	5.05	

PANTONE 3245 C		Formula
PY-TW	71.43	
PY-MX	26.36	
PY-325	1.70	
PY-064	0.34	
PY-230	0.17	

PANTONE 3255 C		Formula
PY-TW	70.00	
PY-MX	25.84	
PY-325	3.50	
PY-230	0.33	
PY-064	0.33	

PANTONE 3265 C		Formula
PY-TW	64.94	
PY-MX	25.16	
PY-325	8.60	
PY-230	0.98	
PY-064	0.32	

PANTONE 3275 C		Formula
PY-TW	55.78	
PY-325	21.15	
PY-MX	21.15	
PY-230	1.92	

PANTONE 3285 C		Formula
PY-TW	69.29	
PY-325	23.41	
PY-064	3.74	
PY-230	2.25	
PY-SB	1.31	

PANTONE 3295 C		Formula
PY-TW	62.92	
PY-325	26.36	
PY-064	6.12	
PY-230	2.38	
PY-SB	2.22	

PANTONE 3305 C		Formula
PY-TW	38.86	
PY-325	23.32	
PY-064	21.76	
PY-SB	11.74	
PY-MX	4.32	

PANTONE 3248 C		Formula
PY-TW	87.52	
PY-064	6.14	
PY-MX	3.73	
PY-230	2.42	
PY-SB	0.19	

PANTONE 3258 C		Formula
PY-TW	81.97	
PY-064	10.93	
PY-230	4.19	
PY-MX	2.73	
PY-SB	0.18	

PANTONE 3268 C		Formula
PY-TW	68.73	
PY-064	19.76	
PY-230	7.73	
PY-MX	3.61	
PY-SB	0.17	

PANTONE 3278 C		Formula
PY-TW	31.90	
PY-064	31.10	
PY-MX	23.92	
PY-230	12.92	
PY-SB	0.16	

PANTONE 3288 C		Formula
PY-064	32.98	
PY-TW	30.12	
PY-MX	22.60	
PY-230	13.10	
PY-SB	1.20	

PANTONE 3298 C		Formula
PY-064	35.69	
PY-TW	27.78	
PY-MX	20.83	
PY-230	12.23	
PY-SB	3.47	

PANTONE 3308 C		Formula
PY-064	50.48	
PY-TW	20.34	
PY-230	13.44	
PY-SB	11.90	
PY-MX	3.84	

PANTONE 331 C		Formula
PY-TW	98.30	
PY-064	1.00	
PY-325	0.60	
PY-SB	0.10	

Polyplast PY

PANTONE 332 C	Formula
PY-TW 97.20	
PY-325 1.60	
PY-064 1.10	
PY-SB 0.10	

PANTONE 333 C	Formula
PY-TW 95.10	
PY-325 3.50	
PY-064 1.40	

PANTONE Green C	Formula
PY-TW 54.60	
PY-325 27.30	
PY-064 9.10	
PY-MX 9.00	

PANTONE 334 C	Formula
PY-TW 56.30	
PY-325 32.00	
PY-064 11.00	
PY-SB 0.70	

PANTONE 335 C	Formula
PY-TW 54.50	
PY-325 30.20	
PY-064 12.70	
PY-SB 2.60	

PANTONE 3155 C	Formula
PY-TW 61.98	
PY-230 20.50	
PY-325 15.04	
PY-SB 2.48	

PANTONE 3165 C	Formula
PY-TW 40.80	
PY-230 26.56	
PY-325 18.03	
PY-MX 9.49	
PY-SB 5.12	

PANTONE 317 C	Formula
PY-TW 75.11	
PY-MX 24.23	
PY-325 0.42	
PY-230 0.24	

PANTONE 318 C	Formula
PY-TW 96.58	
PY-064 2.01	
PY-230 1.41	

PANTONE 319 C	Formula
PY-TW 94.67	
PY-230 2.37	
PY-064 1.97	
PY-325 0.99	

PANTONE 320 C	Formula
PY-TW 42.21	
PY-MX 36.72	
PY-325 10.70	
PY-230 10.37	

PANTONE 321 C	Formula
PY-TW 45.83	
PY-MX 18.34	
PY-325 17.83	
PY-230 17.50	
PY-SB 0.50	

PANTONE 322 C	Formula
PY-TW 43.72	
PY-325 20.03	
PY-MX 17.49	
PY-230 16.69	
PY-SB 2.07	

PANTONE 323 C	Formula
PY-TW 50.00	
PY-325 24.00	
PY-230 16.00	
PY-MX 5.00	
PY-SB 5.00	

PANTONE 324 C	Formula
PY-TW 74.45	
PY-MX 24.14	
PY-064 0.61	
PY-230 0.40	
PY-325 0.40	

PANTONE 325 C	Formula
PY-TW 76.05	
PY-MX 19.42	
PY-325 2.75	
PY-230 1.62	
PY-SB 0.16	

Polyplast PY

PANTONE 326 C	Formula
PY-TW	70.15
PY-MX	17.91
PY-325	8.36
PY-230	3.43
PY-SB	0.15

PANTONE 327 C	Formula
PY-TW	57.00
PY-325	30.00
PY-230	13.00

PANTONE 328 C	Formula
PY-TW	51.86
PY-325	30.33
PY-230	11.15
PY-MX	4.31
PY-SB	2.35

PANTONE 329 C	Formula
PY-TW	47.92
PY-325	34.36
PY-230	10.30
PY-MX	3.98
PY-SB	3.44

PANTONE 330 C	Formula
PY-TW	51.04
PY-325	32.33
PY-SB	10.40
PY-MX	3.77
PY-230	2.46

PANTONE 3242 C	Formula
PY-TW	86.92
PY-MX	10.93
PY-325	0.99
PY-230	0.66
PY-066	0.50

PANTONE 3252 C	Formula
PY-TW	84.46
PY-MX	10.98
PY-325	2.70
PY-230	1.35
PY-066	0.51

PANTONE 3262 C	Formula
PY-TW	88.08
PY-325	8.26
PY-230	2.38
PY-064	1.28

PANTONE 3272 C	Formula
PY-TW	47.07
PY-MX	34.20
PY-325	13.92
PY-230	4.81

PANTONE 3282 C	Formula
PY-TW	62.50
PY-325	26.12
PY-230	7.28
PY-064	2.98
PY-SB	1.12

PANTONE 3015 C	Formula
PY-TW	37.87
PY-230	31.88
PY-MX	27.30
PY-325	2.54
PY-SB	0.41

PANTONE 3025 C	Formula
PY-230	32.26
PY-MX	30.48
PY-TW	26.37
PY-325	7.02
PY-SB	3.87

PANTONE 3035 C	Formula
PY-TW	42.99
PY-230	25.23
PY-325	16.82
PY-SB	9.35
PY-127	5.61

PANTONE 304 C	Formula
PY-TW	98.56
PY-230	0.96
PY-325	0.48

PANTONE 305 C	Formula
PY-TW	96.19
PY-230	2.95
PY-064	0.76
PY-SB	0.10

PANTONE 306 C	Formula
PY-TW	93.26
PY-230	5.87
PY-325	0.87

Polyplast PY

PANTONE Process Blue C	Formula
PY-MX 70.16	
PY-TW 14.77	
PY-230 14.77	
PY-325 0.30	

PANTONE 307 C	Formula
PY-TW 50.09	
PY-230 33.99	
PY-MX 12.52	
PY-325 3.40	

PANTONE 308 C	Formula
PY-230 43.33	
PY-TW 32.93	
PY-MX 13.86	
PY-325 7.97	
PY-SB 1.91	

PANTONE 309 C	Formula
PY-230 46.83	
PY-TW 23.42	
PY-066 13.29	
PY-MX 10.76	
PY-SB 5.70	

PANTONE 310 C	Formula
PY-TW 83.00	
PY-MX 13.00	
PY-230 2.60	
PY-064 1.40	

PANTONE 311 C	Formula
PY-TW 81.69	
PY-MX 12.79	
PY-230 3.94	
PY-064 1.58	

PANTONE 312 C	Formula
PY-TW 58.32	
PY-MX 29.52	
PY-230 9.20	
PY-325 2.96	

PANTONE 313 C	Formula
PY-MX 46.16	
PY-TW 35.89	
PY-230 14.53	
PY-325 3.42	

PANTONE 314 C	Formula
PY-TW 47.55	
PY-230 29.14	
PY-MX 13.80	
PY-325 9.51	

PANTONE 315 C	Formula
PY-TW 43.30	
PY-230 28.91	
PY-325 12.57	
PY-MX 12.57	
PY-SB 2.65	

PANTONE 316 C	Formula
PY-TW 29.24	
PY-230 27.29	
PY-325 22.42	
PY-MX 14.62	
PY-SB 6.43	

PANTONE 3105 C	Formula
PY-TW 91.66	
PY-MX 5.87	
PY-230 1.29	
PY-064 1.06	
PY-SB 0.12	

PANTONE 3115 C	Formula
PY-TW 83.51	
PY-MX 10.71	
PY-230 3.43	
PY-064 2.14	
PY-325 0.21	

PANTONE 3125 C	Formula
PY-TW 84.81	
PY-MX 6.46	
PY-230 5.82	
PY-325 2.75	
PY-066 0.16	

PANTONE 3135 C	Formula
PY-TW 41.00	
PY-MX 41.00	
PY-230 12.00	
PY-325 6.00	

PANTONE 3145 C	Formula
PY-TW 66.84	
PY-230 20.68	
PY-325 11.76	
PY-SB 0.72	

Polyplast PY

PANTONE 293 C		Formula
PY-MX	71.10	
PY-230	17.80	
PY-127	11.10	

PANTONE 294 C		Formula
PY-230	69.82	
PY-TW	23.61	
PY-127	3.74	
PY-064	2.19	
PY-SB	0.64	

PANTONE 295 C		Formula
PY-230	68.20	
PY-TW	21.58	
PY-064	4.03	
PY-127	3.17	
PY-SB	3.02	

PANTONE 296 C		Formula
PY-230	33.30	
PY-TW	27.30	
PY-325	15.20	
PY-SB	14.10	
PY-127	10.10	

PANTONE 2905 C		Formula
PY-TW	97.26	
PY-230	1.76	
PY-165	0.88	
PY-SB	0.10	

PANTONE 2915 C		Formula
PY-TW	94.62	
PY-230	4.30	
PY-127	0.90	
PY-SB	0.18	

PANTONE 2925 C		Formula
PY-TW	83.40	
PY-230	14.37	
PY-127	2.23	

PANTONE 2935 C		Formula
PY-MX	71.46	
PY-230	20.94	
PY-127	6.85	
PY-SB	0.75	

PANTONE 2945 C		Formula
PY-230	62.95	
PY-TW	34.08	
PY-127	2.23	
PY-SB	0.74	

PANTONE 2955 C		Formula
PY-230	63.58	
PY-TW	26.43	
PY-SB	5.85	
PY-064	2.31	
PY-127	1.83	

PANTONE 2965 C		Formula
PY-230	33.70	
PY-TW	26.50	
PY-325	14.40	
PY-SB	12.90	
PY-127	12.50	

PANTONE 297 C		Formula
PY-TW	97.31	
PY-230	2.19	
PY-165	0.30	
PY-SB	0.20	

PANTONE 298 C		Formula
PY-TW	93.56	
PY-230	5.98	
PY-127	0.31	
PY-SB	0.15	

PANTONE 299 C		Formula
PY-TW	86.18	
PY-230	13.52	
PY-127	0.15	
PY-SB	0.15	

PANTONE 300 C		Formula
PY-230	40.48	
PY-MX	40.18	
PY-TW	18.11	
PY-127	1.23	

PANTONE 301 C		Formula
PY-230	65.85	
PY-TW	29.39	
PY-064	4.27	
PY-SB	0.49	

Polyplast PY

PANTONE 302 C PY-230 69.23 PY-TW 15.70 PY-064 12.75 PY-SB 1.90 PY-127 0.42	Formula	PANTONE 303 C PY-TW 39.10 PY-230 28.70 PY-325 14.80 PY-SB 10.40 PY-127 7.00	Formula	PANTONE 2975 C PY-TW 98.89 PY-230 1.01 PY-325 0.10	Formula	PANTONE 2985 C PY-TW 95.28 PY-230 4.32 PY-064 0.27 PY-SB 0.13	Formula
PANTONE 2995 C PY-TW 74.72 PY-MX 14.20 PY-230 10.83 PY-064 0.25	Formula	PANTONE 3005 C PY-TW 53.84 PY-230 23.08 PY-MX 23.08	Formula	PANTONE 2728 C PY-MX 39.20 PY-TW 23.01 PY-165 18.12 PY-230 16.20 PY-127 3.47	Formula	PANTONE 2738 C PY-MX 45.00 PY-127 32.00 PY-230 23.00	Formula
PANTONE 2748 C PY-230 50.47 PY-127 24.14 PY-MX 19.02 PY-TW 5.85 PY-SB 0.52	Formula	PANTONE 2758 C PY-230 57.33 PY-127 22.21 PY-MX 11.49 PY-TW 5.58 PY-SB 3.39	Formula	PANTONE 2768 C PY-TW 26.60 PY-230 23.40 PY-127 21.30 PY-164 15.90 PY-SB 12.80	Formula	PANTONE 277 C PY-TW 99.00 PY-230 0.70 PY-164 0.30	Formula
PANTONE 278 C PY-TW 97.48 PY-230 1.36 PY-127 1.16	Formula	PANTONE 279 C PY-TW 88.35 PY-230 7.30 PY-127 4.35	Formula	PANTONE Reflex Blue C PY-MX 37.85 PY-230 30.81 PY-TW 16.75 PY-127 14.59	Formula	PANTONE 280 C PY-230 74.95 PY-127 14.00 PY-TW 11.05	Formula

Polyplast PY

PANTONE 281 C PY-230 86.02 PY-127 10.24 PY-SB 3.74	Formula	PANTONE 282 C PY-230 35.30 PY-TW 29.40 PY-127 23.50 PY-SB 11.80	Formula	PANTONE 283 C PY-TW 97.31 PY-230 1.28 PY-165 1.27 PY-SB 0.14	Formula	PANTONE 284 C PY-TW 94.04 PY-230 3.94 PY-127 1.82 PY-SB 0.20	Formula
PANTONE 285 C PY-TW 53.03 PY-MX 23.64 PY-230 18.31 PY-127 5.02	Formula	PANTONE 286 C PY-MX 50.00 PY-230 38.46 PY-127 11.54	Formula	PANTONE 287 C PY-230 59.46 PY-MX 16.80 PY-TW 12.93 PY-127 10.65 PY-SB 0.16	Formula	PANTONE 288 C PY-230 74.57 PY-MX 12.09 PY-127 11.23 PY-SB 2.11	Formula
PANTONE 289 C PY-230 35.85 PY-TW 28.30 PY-127 18.87 PY-SB 11.32 PY-325 5.66	Formula	PANTONE 290 C PY-TW 75.18 PY-MX 23.81 PY-230 0.58 PY-165 0.29 PY-SB 0.14	Formula	PANTONE 291 C PY-TW 97.95 PY-230 1.32 PY-127 0.58 PY-SB 0.15	Formula	PANTONE 292 C PY-TW 95.23 PY-230 3.37 PY-127 1.26 PY-SB 0.14	Formula
PANTONE 2715 C PY-TW 90.69 PY-127 7.73 PY-230 0.95 PY-165 0.63	Formula	PANTONE 2725 C PY-TW 79.87 PY-127 18.37 PY-230 1.12 PY-165 0.64	Formula	PANTONE 2735 C PY-MX 54.87 PY-127 35.56 PY-230 5.21 PY-TW 4.36	Formula	PANTONE 2745 C PY-165 64.87 PY-TW 16.22 PY-230 9.91 PY-MX 9.00	Formula

Polyplast PY

PANTONE 2755 C PY-165 69.90 PY-TW 17.48 PY-230 10.68 PY-127 1.94	Formula	PANTONE 2765 C PY-127 39.68 PY-MX 36.51 PY-230 9.52 PY-SB 7.95 PY-164 6.34	Formula	PANTONE 2706 C PY-TW 99.00 PY-230 0.50 PY-164 0.50	Formula	PANTONE 2716 C PY-TW 94.45 PY-127 3.47 PY-230 1.21 PY-165 0.87	Formula
PANTONE 2726 C PY-TW 76.47 PY-127 18.63 PY-230 4.90	Formula	PANTONE 2736 C PY-MX 67.70 PY-127 20.20 PY-TW 7.10 PY-230 5.00	Formula	PANTONE 2746 C PY-TW 38.23 PY-127 37.51 PY-230 18.38 PY-MX 5.88	Formula	PANTONE 2756 C PY-127 42.20 PY-TW 41.28 PY-230 10.09 PY-MX 3.68 PY-SB 2.75	Formula
PANTONE 2766 C PY-TW 35.00 PY-127 20.00 PY-230 20.00 PY-164 15.00 PY-SB 10.00	Formula	PANTONE 2707 C PY-TW 97.50 PY-165 1.70 PY-230 0.80	Formula	PANTONE 2717 C PY-TW 96.52 PY-127 1.91 PY-230 1.57	Formula	PANTONE 2727 C PY-MX 50.72 PY-TW 35.09 PY-230 7.81 PY-127 6.38	Formula
PANTONE Blue 072 C PY-MX 46.10 PY-127 30.80 PY-230 23.10	Formula	PANTONE 2747 C PY-230 71.49 PY-127 23.56 PY-064 3.18 PY-SB 1.77	Formula	PANTONE 2757 C PY-230 59.95 PY-127 25.30 PY-064 7.67 PY-SB 5.28 PY-TW 1.80	Formula	PANTONE 2767 C PY-230 40.00 PY-127 40.00 PY-SB 20.00	Formula

Polyplast PY

PANTONE 2708 C PY-TW 98.30 PY-230 1.00 PY-164 0.70	Formula	PANTONE 2718 C PY-TW 81.81 PY-127 9.39 PY-230 8.02 PY-064 0.78	Formula	PANTONE 263 C PY-TW 99.12 PY-127 0.88	Formula	PANTONE 264 C PY-TW 97.40 PY-127 2.60	Formula
PANTONE 265 C PY-TW 56.50 PY-MX 30.30 PY-127 12.50 PY-165 0.70	Formula	PANTONE 266 C PY-MX 74.07 PY-127 24.69 PY-230 1.24	Formula	PANTONE 267 C PY-165 31.30 PY-MX 30.60 PY-TW 21.10 PY-127 14.40 PY-230 2.60	Formula	PANTONE 268 C PY-165 73.50 PY-TW 18.40 PY-230 6.40 PY-121 1.70	Formula
PANTONE 269 C PY-165 75.50 PY-230 10.00 PY-TW 8.50 PY-121 6.00	Formula	PANTONE 2635 C PY-TW 97.50 PY-127 2.50	Formula	PANTONE 2645 C PY-TW 48.70 PY-MX 47.80 PY-127 3.50	Formula	PANTONE 2655 C PY-MX 56.80 PY-TW 36.10 PY-127 7.10	Formula
PANTONE 2665 C PY-MX 55.30 PY-TW 31.70 PY-127 13.00	Formula	PANTONE Violet C PY-MX 67.57 PY-127 31.53 PY-230 0.90	Formula	PANTONE 2685 C PY-MX 52.50 PY-127 32.60 PY-TW 14.00 PY-165 0.90	Formula	PANTONE 2695 C PY-165 38.60 PY-127 34.21 PY-TW 21.05 PY-SB 6.14	Formula

Polyplast PY

PANTONE 270 C	Formula
PY-TW	96.77
PY-127	2.02
PY-230	0.61
PY-165	0.40
PY-066	0.20

PANTONE 271 C	Formula
PY-TW	93.96
PY-127	4.47
PY-230	0.90
PY-165	0.45
PY-066	0.22

PANTONE 272 C	Formula
PY-TW	87.87
PY-127	9.00
PY-165	1.46
PY-230	1.46
PY-066	0.21

PANTONE 273 C	Formula
PY-127	61.11
PY-TW	16.67
PY-230	16.67
PY-165	5.55

PANTONE 274 C	Formula
PY-127	58.37
PY-TW	30.16
PY-230	7.77
PY-165	1.95
PY-SB	1.75

PANTONE 275 C	Formula
PY-127	57.71
PY-TW	29.52
PY-230	8.58
PY-SB	2.29
PY-165	1.90

PANTONE 276 C	Formula
PY-165	56.86
PY-TW	20.59
PY-SB	9.80
PY-230	8.82
PY-127	3.93

PANTONE 2705 C	Formula
PY-TW	95.40
PY-127	3.40
PY-230	0.60
PY-165	0.60

PANTONE 262 C	Formula
PY-165	63.49
PY-TW	22.22
PY-SB	5.56
PY-127	4.76
PY-114	3.97

PANTONE 2562 C	Formula
PY-TW	97.06
PY-127	1.96
PY-164	0.98

PANTONE 2572 C	Formula
PY-TW	72.70
PY-MX	16.00
PY-165	8.60
PY-127	2.70

PANTONE 2582 C	Formula
PY-MX	53.40
PY-TW	27.80
PY-165	13.30
PY-127	5.50

PANTONE 2592 C	Formula
PY-MX	36.72
PY-TW	24.22
PY-165	24.22
PY-127	14.84

PANTONE 2602 C	Formula
PY-165	42.20
PY-MX	31.00
PY-TW	15.00
PY-127	11.80

PANTONE 2612 C	Formula
PY-165	82.00
PY-TW	14.80
PY-230	3.20

PANTONE 2622 C	Formula
PY-165	46.60
PY-TW	33.30
PY-121	15.80
PY-230	4.30

Polyplast PY

PANTONE 2563 C PY-TW 91.20 PY-165 6.40 PY-127 2.40	Formula	PANTONE 2573 C PY-TW 77.78 PY-165 17.78 PY-127 4.44	Formula	PANTONE 2583 C PY-TW 61.00 PY-165 31.00 PY-127 8.00	Formula	PANTONE 2593 C PY-MX 46.72 PY-165 26.84 PY-127 21.87 PY-TW 2.98 PY-SB 1.59	Formula
PANTONE 2603 C PY-165 55.04 PY-TW 15.60 PY-127 15.60 PY-MX 13.76	Formula	PANTONE 2613 C PY-165 48.40 PY-MX 23.20 PY-TW 15.70 PY-127 11.10 PY-SB 1.60	Formula	PANTONE 2623 C PY-165 56.82 PY-127 22.73 PY-MX 11.36 PY-SB 5.68 PY-TW 3.41	Formula	PANTONE 2567 C PY-TW 94.96 PY-127 4.05 PY-164 0.99	Formula
PANTONE 2577 C PY-TW 75.70 PY-MX 14.40 PY-127 6.90 PY-164 3.00	Formula	PANTONE 2587 C PY-MX 51.40 PY-TW 34.70 PY-127 10.40 PY-164 3.50	Formula	PANTONE 2597 C PY-MX 47.78 PY-127 29.34 PY-TW 15.93 PY-164 6.70 PY-230 0.25	Formula	PANTONE 2607 C PY-MX 57.40 PY-127 19.40 PY-TW 16.60 PY-164 6.60	Formula
PANTONE 2617 C PY-MX 47.50 PY-127 23.70 PY-TW 19.30 PY-164 9.50	Formula	PANTONE 2627 C PY-MX 50.40 PY-127 23.40 PY-TW 15.60 PY-164 10.60	Formula	PANTONE 2415 C PY-165 85.10 PY-MX 10.60 PY-127 3.20 PY-SB 1.10	Formula	PANTONE 2425 C PY-165 71.94 PY-TW 20.14 PY-127 5.04 PY-164 2.88	Formula

Polyplast PY

PANTONE 243 C	Formula
PY-TW	94.64
PY-165	5.25
PY-230	0.11

PANTONE 244 C	Formula
PY-TW	94.00
PY-165	6.00

PANTONE 245 C	Formula
PY-TW	84.00
PY-165	15.90
PY-230	0.10

PANTONE 246 C	Formula
PY-165	53.76
PY-TW	22.58
PY-MX	21.51
PY-127	2.15

PANTONE 247 C	Formula
PY-MX	48.03
PY-165	37.74
PY-TW	12.00
PY-127	2.23

PANTONE 248 C	Formula
PY-165	49.30
PY-MX	29.30
PY-TW	16.90
PY-127	4.50

PANTONE 249 C	Formula
PY-165	72.42
PY-TW	20.69
PY-127	4.14
PY-SB	2.75

PANTONE 250 C	Formula
PY-TW	99.10
PY-164	0.64
PY-127	0.26

PANTONE 251 C	Formula
PY-TW	92.59
PY-165	6.48
PY-127	0.93

PANTONE 252 C	Formula
PY-TW	51.08
PY-MX	31.43
PY-165	15.72
PY-127	1.77

PANTONE Purple C	Formula
PY-165	36.95
PY-TW	35.16
PY-MX	23.86
PY-127	4.03

PANTONE 253 C	Formula
PY-MX	42.70
PY-165	31.80
PY-TW	22.70
PY-127	2.80

PANTONE 254 C	Formula
PY-165	54.88
PY-TW	40.24
PY-127	4.88

PANTONE 255 C	Formula
PY-165	66.67
PY-TW	17.78
PY-127	11.11
PY-114	4.44

PANTONE 256 C	Formula
PY-TW	98.04
PY-165	1.09
PY-127	0.43
PY-114	0.22
PY-SB	0.22

PANTONE 257 C	Formula
PY-TW	96.40
PY-127	1.60
PY-165	1.10
PY-114	0.90

Polyplast PY

PANTONE 258 C PY-TW 58.41 PY-165 35.40 PY-127 5.31 PY-114 0.88	Formula	PANTONE 259 C PY-165 45.00 PY-TW 35.00 PY-127 15.00 PY-114 5.00	Formula	PANTONE 260 C PY-165 51.10 PY-TW 32.80 PY-127 10.90 PY-114 3.00 PY-SB 2.20	Formula	PANTONE 261 C PY-165 70.59 PY-TW 21.18 PY-SB 4.70 PY-127 3.53	Formula
PANTONE 227 C PY-165 98.36 PY-SB 1.64	Formula	PANTONE 228 C PY-165 95.79 PY-SB 3.83 PY-066 0.38	Formula	PANTONE 229 C PY-164 34.03 PY-MX 21.01 PY-TW 19.33 PY-165 17.23 PY-SB 8.40	Formula	PANTONE 230 C PY-MX 56.70 PY-TW 42.00 PY-164 1.00 PY-066 0.30	Formula
PANTONE 231 C PY-MX 52.80 PY-TW 35.60 PY-165 9.60 PY-164 2.00	Formula	PANTONE 232 C PY-MX 44.00 PY-TW 31.00 PY-165 25.00	Formula	PANTONE Rhodamine Red C PY-MX 47.60 PY-165 36.00 PY-TW 16.40	Formula	PANTONE 233 C PY-165 99.00 PY-127 1.00	Formula
PANTONE 234 C PY-165 88.40 PY-TW 9.50 PY-127 2.10	Formula	PANTONE 235 C PY-165 58.90 PY-TW 18.30 PY-164 16.60 PY-127 6.20	Formula	PANTONE 236 C PY-TW 97.00 PY-164 1.50 PY-165 1.50	Formula	PANTONE 237 C PY-TW 93.00 PY-165 4.00 PY-164 3.00	Formula

Polyplast PY

PANTONE 238 C PY-TW 76.60 PY-165 19.60 PY-164 3.80	Formula	PANTONE 239 C PY-MX 51.69 PY-165 40.75 PY-TW 6.96 PY-127 0.60	Formula	PANTONE 240 C PY-165 81.19 PY-TW 16.83 PY-127 1.98	Formula	PANTONE 241 C PY-165 79.37 PY-TW 17.46 PY-127 3.17	Formula
PANTONE 242 C PY-165 81.19 PY-TW 10.89 PY-SB 6.93 PY-127 0.99	Formula	PANTONE 2365 C PY-TW 97.00 PY-165 2.55 PY-121 0.45	Formula	PANTONE 2375 C PY-TW 78.62 PY-165 20.96 PY-127 0.42	Formula	PANTONE 2385 C PY-TW 43.10 PY-165 38.80 PY-MX 17.24 PY-127 0.86	Formula
PANTONE 2395 C PY-165 70.76 PY-MX 26.57 PY-127 1.43 PY-TW 1.24	Formula	PANTONE 2405 C PY-165 70.00 PY-MX 24.50 PY-TW 3.00 PY-127 1.50 PY-SB 1.00	Formula	PANTONE 206 C PY-MX 37.74 PY-165 37.74 PY-164 18.86 PY-121 5.66	Formula	PANTONE 207 C PY-MX 42.84 PY-165 42.84 PY-121 9.02 PY-TW 4.28 PY-SB 1.02	Formula
PANTONE 208 C PY-165 69.46 PY-TW 17.36 PY-121 10.41 PY-SB 2.77	Formula	PANTONE 209 C PY-165 66.68 PY-TW 16.66 PY-121 12.66 PY-SB 4.00	Formula	PANTONE 210 C PY-TW 62.70 PY-MX 31.36 PY-165 4.38 PY-121 1.56	Formula	PANTONE 211 C PY-MX 46.51 PY-TW 46.51 PY-165 4.65 PY-121 1.40 PY-164 0.93	Formula

Polyplast PY

PANTONE 212 C	Formula
PY-MX 62.50	
PY-TW 18.05	
PY-165 16.67	
PY-121 2.78	

PANTONE 213 C	Formula
PY-MX 46.74	
PY-165 37.38	
PY-TW 11.21	
PY-121 4.67	

PANTONE 214 C	Formula
PY-165 63.73	
PY-MX 19.61	
PY-TW 11.76	
PY-121 4.90	

PANTONE 215 C	Formula
PY-165 78.57	
PY-TW 10.00	
PY-121 10.00	
PY-SB 1.43	

PANTONE 216 C	Formula
PY-165 59.89	
PY-TW 18.18	
PY-121 18.18	
PY-SB 3.75	

PANTONE 217 C	Formula
PY-TW 98.90	
PY-164 1.00	
PY-066 0.10	

PANTONE 218 C	Formula
PY-TW 93.80	
PY-164 6.10	
PY-066 0.10	

PANTONE 219 C	Formula
PY-MX 33.50	
PY-165 33.40	
PY-TW 31.00	
PY-121 2.10	

PANTONE Rubine Red C	Formula
PY-MX 32.20	
PY-164 28.00	
PY-165 22.20	
PY-TW 17.60	

PANTONE 220 C	Formula
PY-165 80.16	
PY-164 10.62	
PY-TW 8.02	
PY-127 1.20	

PANTONE 221 C	Formula
PY-165 47.70	
PY-164 31.80	
PY-TW 17.20	
PY-127 3.30	

PANTONE 222 C	Formula
PY-MX 43.81	
PY-164 24.95	
PY-TW 13.62	
PY-SB 9.33	
PY-165 8.29	

PANTONE 223 C	Formula
PY-TW 93.17	
PY-165 5.69	
PY-164 1.04	
PY-066 0.10	

PANTONE 224 C	Formula
PY-TW 84.80	
PY-165 12.00	
PY-164 3.20	

PANTONE 225 C	Formula
PY-TW 65.55	
PY-165 26.67	
PY-164 7.78	

PANTONE 226 C	Formula
PY-165 61.66	
PY-MX 16.67	
PY-TW 16.67	
PY-164 5.00	

Polyplast PY

PANTONE 191 C PY-MX 51.18 PY-TW 29.92 PY-121 10.24 PY-164 8.66	Formula	PANTONE 192 C PY-MX 35.29 PY-121 27.06 PY-TW 23.53 PY-164 14.12	Formula	PANTONE 193 C PY-121 47.39 PY-TW 26.07 PY-164 26.07 PY-SB 0.47	Formula	PANTONE 194 C PY-121 44.31 PY-164 26.59 PY-TW 26.59 PY-SB 2.51	Formula
PANTONE 195 C PY-121 49.55 PY-TW 25.23 PY-164 18.01 PY-SB 7.21	Formula	PANTONE 1895 C PY-TW 77.33 PY-MX 20.95 PY-121 0.95 PY-164 0.77	Formula	PANTONE 1905 C PY-TW 78.42 PY-MX 17.13 PY-121 2.57 PY-164 1.88	Formula	PANTONE 1915 C PY-MX 51.28 PY-TW 34.19 PY-164 8.55 PY-121 5.98	Formula
PANTONE 1925 C PY-MX 39.82 PY-TW 26.55 PY-121 17.70 PY-164 15.93	Formula	PANTONE 1935 C PY-164 49.06 PY-121 28.30 PY-TW 22.64	Formula	PANTONE 1945 C PY-164 46.73 PY-121 28.04 PY-TW 24.30 PY-SB 0.93	Formula	PANTONE 1955 C PY-164 39.22 PY-121 29.41 PY-TW 29.41 PY-SB 1.96	Formula
PANTONE 196 C PY-TW 98.41 PY-121 1.09 PY-165 0.50	Formula	PANTONE 197 C PY-TW 87.36 PY-MX 5.52 PY-121 3.68 PY-165 3.44	Formula	PANTONE 198 C PY-TW 47.62 PY-MX 23.81 PY-121 15.87 PY-165 12.70	Formula	PANTONE 199 C PY-121 51.28 PY-TW 29.49 PY-164 19.23	Formula

Polyplast PY

PANTONE 200 C PY-121 54.42 PY-164 24.49 PY-TW 20.41 PY-SB 0.68	Formula	PANTONE 201 C PY-121 52.63 PY-TW 23.68 PY-164 21.93 PY-SB 1.76	Formula	PANTONE 202 C PY-121 56.34 PY-TW 21.13 PY-164 18.31 PY-SB 4.22	Formula	PANTONE 203 C PY-TW 95.70 PY-165 3.82 PY-114 0.48	Formula
PANTONE 204 C PY-TW 86.22 PY-165 11.20 PY-114 2.58	Formula	PANTONE 205 C PY-TW 62.50 PY-165 31.25 PY-114 6.25	Formula	PANTONE 1775 C PY-TW 71.70 PY-MX 18.80 PY-121 7.60 PY-164 1.90	Formula	PANTONE 1785 C PY-MX 72.20 PY-TW 15.40 PY-121 8.80 PY-164 3.60	Formula
PANTONE 1788 C PY-MX 54.60 PY-121 27.20 PY-TW 15.20 PY-164 3.00	Formula	PANTONE 1795 C PY-MX 51.80 PY-121 29.60 PY-165 11.10 PY-TW 7.40 PY-230 0.10	Formula	PANTONE 1805 C PY-121 57.60 PY-165 23.10 PY-TW 18.20 PY-SB 1.10	Formula	PANTONE 1815 C PY-121 62.30 PY-165 21.60 PY-TW 12.20 PY-SB 3.90	Formula
PANTONE 1767 C PY-TW 57.30 PY-MX 40.20 PY-121 2.10 PY-064 0.40	Formula	PANTONE 1777 C PY-MX 69.10 PY-TW 20.70 PY-121 7.10 PY-164 3.10	Formula	PANTONE 1787 C PY-MX 51.60 PY-TW 21.00 PY-121 18.00 PY-165 9.40	Formula	PANTONE Red 032 C PY-MX 54.00 PY-121 27.10 PY-TW 14.90 PY-165 4.00	Formula

Polyplast PY

PANTONE 1797 C PY-MX 51.40 PY-121 25.90 PY-TW 14.10 PY-165 8.00 PY-SB 0.60	Formula	PANTONE 1807 C PY-MX 49.50 PY-121 28.20 PY-165 12.70 PY-TW 7.00 PY-SB 2.60	Formula	PANTONE 1817 C PY-165 51.50 PY-066 27.00 PY-SB 14.10 PY-114 7.40	Formula	PANTONE 182 C PY-TW 96.69 PY-121 2.76 PY-164 0.55	Formula
PANTONE 183 C PY-TW 91.64 PY-121 6.43 PY-164 1.93	Formula	PANTONE 184 C PY-MX 46.91 PY-TW 39.51 PY-121 9.88 PY-164 3.70	Formula	PANTONE 185 C PY-121 51.80 PY-TW 21.50 PY-MX 15.20 PY-164 11.50	Formula	PANTONE 186 C PY-121 58.30 PY-164 24.80 PY-TW 16.90	Formula
PANTONE 187 C PY-121 56.50 PY-TW 22.00 PY-164 20.10 PY-SB 1.40	Formula	PANTONE 188 C PY-121 53.33 PY-TW 25.93 PY-164 16.42 PY-SB 4.32	Formula	PANTONE 189 C PY-TW 96.15 PY-121 2.40 PY-164 1.45	Formula	PANTONE 190 C PY-TW 44.00 PY-MX 40.00 PY-165 9.33 PY-121 6.67	Formula
PANTONE 168 C PY-114 56.30 PY-066 35.70 PY-SB 8.00	Formula	PANTONE 1625 C PY-TW 47.10 PY-MX 43.30 PY-121 5.00 PY-064 4.60	Formula	PANTONE 1635 C PY-TW 58.20 PY-MX 20.80 PY-064 10.30 PY-114 9.90 PY-121 0.80	Formula	PANTONE 1645 C PY-TW 64.80 PY-066 15.20 PY-114 10.90 PY-121 7.80 PY-164 1.30	Formula

Polyplast PY

PANTONE 1655 C PY-114 75.40 PY-066 22.20 PY-TW 2.40	Formula	PANTONE 1665 C PY-114 48.80 PY-066 38.70 PY-TW 12.10 PY-SB 0.40	Formula	PANTONE 1675 C PY-114 70.90 PY-066 25.80 PY-SB 3.30	Formula	PANTONE 1685 C PY-114 84.00 PY-066 10.60 PY-SB 5.40	Formula
PANTONE 169 C PY-TW 97.50 PY-121 1.08 PY-066 0.55 PY-164 0.55 PY-064 0.32	Formula	PANTONE 170 C PY-TW 48.96 PY-MX 41.67 PY-114 7.29 PY-121 2.08	Formula	PANTONE 171 C PY-MX 46.00 PY-TW 35.00 PY-114 17.00 PY-121 2.00	Formula	PANTONE 172 C PY-064 35.90 PY-114 28.20 PY-MX 23.70 PY-121 7.60 PY-TW 4.60	Formula
PANTONE 173 C PY-114 49.60 PY-066 24.80 PY-TW 16.20 PY-121 8.70 PY-SB 0.70	Formula	PANTONE 174 C PY-114 51.30 PY-121 25.60 PY-066 19.20 PY-SB 3.90	Formula	PANTONE 175 C PY-114 40.90 PY-165 25.60 PY-066 21.90 PY-SB 7.20 PY-121 4.40	Formula	PANTONE 176 C PY-TW 59.50 PY-MX 36.60 PY-121 1.40 PY-114 1.30 PY-165 1.20	Formula
PANTONE 177 C PY-MX 47.60 PY-TW 43.30 PY-114 5.20 PY-121 2.60 PY-164 1.30	Formula	PANTONE 178 C PY-MX 60.50 PY-TW 25.50 PY-114 10.20 PY-164 3.20 PY-064 0.60	Formula	PANTONE Warm Red C PY-MX 51.23 PY-121 23.99 PY-TW 13.65 PY-064 10.70 PY-164 0.43	Formula	PANTONE 179 C PY-MX 46.50 PY-121 30.90 PY-TW 17.80 PY-114 4.60 PY-SB 0.20	Formula

Polyplast PY

PANTONE 180 C PY-114 46.80 PY-TW 29.60 PY-165 22.70 PY-SB 0.90	Formula	PANTONE 181 C PY-165 48.50 PY-066 28.30 PY-TW 14.20 PY-121 4.80 PY-SB 4.20	Formula	PANTONE 1535 C PY-066 62.50 PY-114 33.30 PY-SB 4.20	Formula	PANTONE 1545 C PY-114 73.91 PY-SB 18.12 PY-066 7.97	Formula
PANTONE 155 C PY-TW 98.20 PY-066 1.30 PY-114 0.40 PY-SB 0.10	Formula	PANTONE 156 C PY-TW 87.40 PY-064 12.00 PY-164 0.60	Formula	PANTONE 157 C PY-TW 49.30 PY-064 48.10 PY-164 1.90 PY-066 0.70	Formula	PANTONE 158 C PY-066 82.00 PY-114 15.00 PY-TW 2.60 PY-SB 0.40	Formula
PANTONE 159 C PY-066 76.10 PY-114 19.00 PY-TW 3.80 PY-SB 1.10	Formula	PANTONE 160 C PY-066 92.70 PY-164 6.30 PY-230 1.00	Formula	PANTONE 161 C PY-066 70.60 PY-114 20.60 PY-SB 8.80	Formula	PANTONE 1555 C PY-TW 75.80 PY-MX 19.70 PY-066 2.30 PY-121 2.20	Formula
PANTONE 1565 C PY-TW 85.11 PY-064 10.64 PY-114 4.25	Formula	PANTONE 1575 C PY-064 50.40 PY-TW 37.80 PY-114 11.80	Formula	PANTONE 1585 C PY-064 70.10 PY-114 20.60 PY-TW 9.30	Formula	PANTONE 1595 C PY-066 71.00 PY-114 27.90 PY-SB 1.10	Formula

Polyplast PY

PANTONE 1605 C PY-064 75.70 PY-114 21.60 PY-SB 2.70	Formula	PANTONE 1615 C PY-066 55.30 PY-114 40.40 PY-SB 4.30	Formula	PANTONE 162 C PY-TW 52.50 PY-MX 44.40 PY-064 1.50 PY-114 1.20 PY-121 0.40	Formula	PANTONE 163 C PY-MX 50.90 PY-TW 38.10 PY-114 5.50 PY-064 5.10 PY-121 0.40	Formula
PANTONE 164 C PY-TW 37.70 PY-064 33.50 PY-MX 15.00 PY-114 12.60 PY-121 1.20	Formula	PANTONE 165 C PY-064 76.10 PY-114 21.70 PY-TW 2.20	Formula	PANTONE 166 C PY-066 58.50 PY-114 40.90 PY-SB 0.60	Formula	PANTONE 167 C PY-066 54.50 PY-114 34.60 PY-MX 9.10 PY-SB 1.80	Formula
PANTONE 1385 C PY-064 89.40 PY-114 9.50 PY-SB 1.10	Formula	PANTONE 1395 C PY-064 89.70 PY-114 7.70 PY-SB 2.60	Formula	PANTONE 1405 C PY-064 85.30 PY-114 7.90 PY-SB 6.80	Formula	PANTONE 141 C PY-TW 69.30 PY-064 28.60 PY-066 1.70 PY-164 0.40	Formula
PANTONE 142 C PY-064 50.30 PY-TW 45.00 PY-066 4.00 PY-164 0.70	Formula	PANTONE 143 C PY-064 59.72 PY-TW 36.70 PY-066 2.56 PY-164 1.02	Formula	PANTONE 144 C PY-066 87.09 PY-114 6.62 PY-064 5.96 PY-SB 0.33	Formula	PANTONE 145 C PY-066 89.00 PY-TW 7.80 PY-164 2.50 PY-230 0.70	Formula

Polyplast PY

PANTONE 146 C PY-066 86.50 PY-TW 8.00 PY-164 3.90 PY-230 1.60	Formula	PANTONE 147 C PY-066 72.10 PY-TW 12.30 PY-114 7.90 PY-SB 6.30 PY-325 1.40	Formula	PANTONE 148 C PY-TW 94.70 PY-066 2.90 PY-064 1.50 PY-114 0.90	Formula	PANTONE 149 C PY-TW 86.60 PY-064 10.50 PY-114 2.00 PY-066 0.90	Formula
PANTONE 150 C PY-064 48.40 PY-TW 47.00 PY-114 4.60	Formula	PANTONE 151 C PY-064 87.30 PY-114 12.70	Formula	PANTONE 152 C PY-064 85.50 PY-114 13.70 PY-SB 0.80	Formula	PANTONE 153 C PY-064 85.20 PY-114 13.00 PY-SB 1.80	Formula
PANTONE 154 C PY-064 85.10 PY-114 11.20 PY-SB 3.70	Formula	PANTONE 1485 C PY-TW 86.95 PY-066 8.70 PY-114 4.35	Formula	PANTONE 1495 C PY-TW 57.30 PY-066 38.40 PY-121 3.30 PY-164 1.00	Formula	PANTONE 1505 C PY-066 86.20 PY-114 13.80	Formula
PANTONE Orange 021 C PY-066 79.65 PY-114 17.70 PY-121 2.65	Formula	PANTONE 1525 C PY-066 66.50 PY-114 32.50 PY-SB 1.00	Formula	PANTONE 1235 C PY-066 98.00 PY-114 2.00	Formula	PANTONE 1245 C PY-064 90.50 PY-TW 4.70 PY-114 3.40 PY-SB 1.40	Formula

Polyplast PY

PANTONE 1255 C	Formula
PY-064 94.40	
PY-114 3.00	
PY-SB 2.60	

PANTONE 1265 C	Formula
PY-066 91.50	
PY-SB 5.00	
PY-114 3.50	

PANTONE 127 C	Formula
PY-TW 78.40	
PY-064 19.80	
PY-066 1.60	
PY-164 0.20	

PANTONE 128 C	Formula
PY-TW 66.00	
PY-064 30.60	
PY-066 3.10	
PY-164 0.30	

PANTONE 129 C	Formula
PY-064 59.60	
PY-TW 34.40	
PY-066 5.70	
PY-164 0.30	

PANTONE 130 C	Formula
PY-064 77.10	
PY-066 22.00	
PY-164 0.80	
PY-230 0.10	

PANTONE 131 C	Formula
PY-066 98.20	
PY-164 1.30	
PY-SB 0.30	
PY-230 0.20	

PANTONE 132 C	Formula
PY-066 96.90	
PY-164 1.70	
PY-230 1.40	

PANTONE 133 C	Formula
PY-066 86.20	
PY-114 6.90	
PY-SB 4.80	
PY-325 2.10	

PANTONE 134 C	Formula
PY-TW 89.60	
PY-064 5.20	
PY-066 4.50	
PY-114 0.70	

PANTONE 135 C	Formula
PY-TW 84.20	
PY-066 11.80	
PY-064 3.00	
PY-114 1.00	

PANTONE 136 C	Formula
PY-TW 75.90	
PY-066 22.50	
PY-114 1.60	

PANTONE 137 C	Formula
PY-066 89.00	
PY-TW 7.40	
PY-114 3.60	

PANTONE 138 C	Formula
PY-066 92.40	
PY-114 6.90	
PY-SB 0.70	

PANTONE 139 C	Formula
PY-066 87.80	
PY-114 5.20	
PY-064 4.80	
PY-SB 2.20	

PANTONE 140 C	Formula
PY-066 87.00	
PY-114 7.20	
PY-SB 5.80	

Polyplast PY

PANTONE 1345 C PY-TW 90.20 PY-064 7.60 PY-066 1.20 PY-114 1.00	Formula	PANTONE 1355 C PY-TW 85.10 PY-064 9.60 PY-066 3.20 PY-114 2.10	Formula	PANTONE 1365 C PY-TW 80.60 PY-064 13.70 PY-066 3.30 PY-114 2.40	Formula	PANTONE 1375 C PY-064 87.30 PY-TW 7.60 PY-114 5.10	Formula
PANTONE 108 C PY-064 68.10 PY-TW 22.90 PY-066 9.00	Formula	PANTONE 109 C PY-064 77.90 PY-066 22.10	Formula	PANTONE 110 C PY-066 82.30 PY-064 11.30 PY-TW 6.00 PY-230 0.40	Formula	PANTONE 111 C PY-066 93.20 PY-TW 5.10 PY-230 1.00 PY-164 0.70	Formula
PANTONE 112 C PY-066 94.80 PY-114 2.40 PY-325 1.50 PY-SB 1.30	Formula	PANTONE 113 C PY-TW 71.50 PY-064 21.40 PY-066 7.10	Formula	PANTONE 114 C PY-TW 66.00 PY-064 25.50 PY-066 8.50	Formula	PANTONE 115 C PY-TW 64.20 PY-064 26.80 PY-066 9.00	Formula
PANTONE 116 C PY-064 81.10 PY-066 13.50 PY-TW 4.70 PY-114 0.70	Formula	PANTONE 117 C PY-064 81.80 PY-066 13.60 PY-114 3.70 PY-325 0.90	Formula	PANTONE 118 C PY-064 80.20 PY-066 12.60 PY-114 5.60 PY-325 1.60	Formula	PANTONE 119 C PY-064 81.60 PY-114 7.40 PY-TW 7.40 PY-325 2.10 PY-SB 1.50	Formula

Polyplast PY

PANTONE 120 C PY-TW 86.80 PY-064 9.50 PY-066 3.30 PY-114 0.40	Formula	PANTONE 121 C PY-TW 83.00 PY-064 11.40 PY-066 5.20 PY-114 0.40	Formula	PANTONE 122 C PY-TW 71.20 PY-064 14.20 PY-066 14.20 PY-114 0.40	Formula	PANTONE 123 C PY-TW 41.40 PY-066 38.50 PY-064 19.30 PY-114 0.80	Formula
PANTONE 124 C PY-066 62.00 PY-064 35.40 PY-114 1.80 PY-SB 0.80	Formula	PANTONE 125 C PY-064 73.30 PY-066 22.60 PY-114 2.20 PY-SB 1.90	Formula	PANTONE 126 C PY-064 92.90 PY-SB 2.70 PY-066 2.20 PY-114 2.20	Formula	PANTONE 1205 C PY-TW 96.90 PY-064 1.70 PY-066 1.10 PY-114 0.30	Formula
PANTONE 1215 C PY-TW 92.70 PY-064 4.20 PY-066 2.80 PY-114 0.30	Formula	PANTONE 1225 C PY-TW 64.00 PY-064 20.00 PY-066 14.70 PY-114 1.30	Formula	PANTONE 1765 C PY-TW 77.50 PY-MX 15.60 PY-121 5.90 PY-164 1.00	Formula	PANTONE 101 C PY-TW 70.30 PY-064 28.10 PY-066 1.60	Formula
PANTONE 102 C PY-064 97.20 PY-066 2.80	Formula	PANTONE Yellow C PY-064 94.00 PY-066 6.00	Formula	PANTONE 103 C PY-064 88.00 PY-066 10.60 PY-SB 1.40	Formula	PANTONE 104 C PY-064 85.50 PY-066 6.90 PY-TW 5.10 PY-SB 2.50	Formula

Polyplast PY

PANTONE		Formula
105 C		
PY-064	73.10	
PY-066	25.30	
PY-SB	1.20	
PY-325	0.40	

PANTONE		Formula
106 C		
PY-TW	64.30	
PY-064	32.00	
PY-066	3.70	

PANTONE		Formula
107 C		
PY-064	60.60	
PY-TW	35.60	
PY-066	3.70	
PY-114	0.10	

PANTONE		Formula
Warm Gray 6 C		
PY-TW	94.40	
PY-SB	3.20	
PY-066	1.50	
PY-121	0.90	

PANTONE		Formula
450 C		
PY-064	86.10	
PY-164	7.60	
PY-230	4.20	
PY-MX	1.50	
PY-SB	0.60	

PANTONE		Formula
451 C		
PY-TW	79.30	
PY-064	17.00	
PY-SB	3.20	
PY-114	0.50	

PANTONE		Formula
452 C		
PY-TW	89.20	
PY-064	8.80	
PY-SB	1.70	
PY-114	0.30	

PANTONE		Formula
453 C		
PY-TW	95.40	
PY-064	3.50	
PY-SB	0.90	
PY-114	0.20	

PANTONE		Formula
431 C		
PY-TW	83.60	
PY-SB	12.30	
PY-066	2.30	
PY-064	1.80	