

LTO Ultrium 3 Data Cartridge

FUJIFILM's Linear Tape-Open (LTO) Ultrium 3 is the 3rd generation of tape technology based on FUJIFILM's proprietary ATOMM Technology. FUJIFILM's LTO Ultrium 3 tape format has been optimized for high-capacity and performance with outstanding reliability, in either stand-alone or automated environments. FUJIFILM draws on its long experience in precision manufacturing and has developed tapes with 800* GB capacity on a single cartridge, meeting the needs of the most demanding applications.

Keep your data FUJIFILM safe.




Your logo or graphic here (optional)



FUJIFILM solely uses and is the exclusive authorized manufacturer of Tri-Optic bar code labels

Call FUJIFILM toll-free or visit www.fujibarcodes.ca for more details.



FUJIFILM's Universal Cleaning Cartridge is designed for use with all Ultrium 1, 2, 3, and 4 tape drives

Product Specifications

Product Code	Standard: 126021 Labelled: 386739
Durability	Avg. 1,000,000+ head passes
Capacity	400/800* GB (Native/Compressed)
Transfer Rate	80/160* MB/sec (Native/Compressed)
Number of Tracks	704
Dimensions (mm)	21.5 x 105.4 x 102 (W x H x L)

*Assumes 2:1 data compression

© 2007 FUJIFILM Canada Inc., The FUJIFILM, NANOCUBIC, and ATOMM logos are trademarks of FUJIFILM Canada Inc. Linear Tape-Open, LTO, LTO logo, Ultrium and Ultrium logo are trademarks of Quantum, HP and IBM

