

型番	Product Name	HF25SA-1
焦点距離 [mm]	Focal length [mm] (design value)	25 (23.99)
絞り範囲 (F値)	Iris range (Fnumber)	F1.4-F22
画角 (H × V)	Angle of view	20.8° × 15.7° (2/3")
フォーカス範囲 (レンズメカ先端より) [mm]	Working distance (from front of lens barrel) [mm]	∞ - 100
操作方法:フォーカス	Operation of focus	Manual
操作方法:アイリス	Operation of iris	Manual
フィルタ径 [mm]	Filter thread [mm]	M49 × 0.75
マウント	Mount	C-mount
質量 (約) [g]	Weight (approx.) [g]	315
適合センサーサイズ (標準)	Sensor size (std.)	2/3" (3.45μm)
適合センサーサイズ (最大)	Sensor size (max.)	2/3" (3.45μm)
バックフォーカス (空気換算長) [mm]	Back focal length (in air) [mm]	22.32
フランジバック [mm]	Flange back [mm]	17.526
入射瞳位置 (マウント面から) [mm]	Entrance pupil position (from Mount) [mm]	-42.87
射出瞳位置 (結像面より) [mm]	Exit pupil position (from image plane) [mm]	-144.93
前側主点 (マウント面から) [mm]	Front principal point (from Mount) [mm]	-23.47
後側主点 (マウント面から) [mm]	Rear principal point (from Mount) [mm]	-6.47
主点間隔 [mm]	Distance between the principal points [mm]	17.00
TV歪み [%]	TV distortion [%]	-0.06
外形寸法 [mm]	Dimension [mm]	φ51 × 75.5
主光線入射角度 [°]	Chief Ray Angle [°]	2
周辺光量比 (F4.0・対角端) [%]	Relative illumination [%] (Aperture: F4.0, Image height : at diagonal)	100
周辺光量比 (開放・対角端) [%]	Relative illumination [%] (Aperture: at full open, Image height : at diagonal)	72
使用温度範囲	Operation Temperature Range	-10℃ ~ +50℃
保存温度範囲	Storage Temperature Range	-20℃ ~ +60℃

These specifications are subject to change without notice.

28-Feb-20