

FUJIFILM
Value from Innovation

LTO Ultrium 10

MAX KAPAZITÄT : 30TB (KOMPRIMIERT : 75TB)
MAX TRANSFER RATE : 400MB/SEC (1.000MB/SEC)



GROÙE KAPAZITÄT



SICHERHEIT



NIEDRIGE KOSTEN

MEDIA and DRIVE COMPATIBILITY

○:Read /Write △:Read Only ×: No Read/Write

Media \ Drive	LTO-10 Drive	LTO-9 Drive	LTO-8 Drive	LTO-7 Drive	LTO-6 Drive	LTO-5 Drive
LTO-10 Media	○	×	×	×	×	×
LTO-9 Media	×	○	×	×	×	×
LTO-8 Media	×	○	○	×	×	×
LTO-7 Media	×	×	○	○	×	×
LTO-6 Media	×	×	×	○	○	×
LTO-5 Media	×	×	×	△	○	○

MAIN SPECIFICATION of LTO CARTRIDGES

	LTO CL	LTO-5/5 WORM	LTO-6/6 WORM	LTO-7/7 WORM	LTO-8/8 WORM	LTO-9/9 WORM	LTO-10/10 WORM
Basic Specifications							
Native Capacity (Compressed)	—	1.5TB(3.0TB)	2.5TB(6.25TB)	6TB(15TB)	12TB(30TB)	18TB(45TB)	30TB(75TB)
Max. Transfer Rate*1 (Compressed)	—	140MB/sec. (Up to 280MB/sec.)	160MB/sec. (Up to 400MB/sec.)	300MB/sec. (Up to 750MB/sec.)	360MB/sec. (Up to 750MB/sec.)	400MB/sec. (Up to 1,000MB/sec.)	
Servo Band	—	Timing-based servo					
Cartridge Memory	32,786bits (4,096bytes); Internal EEPROM	65,280bits (8,160bytes); Internal EEPROM	130,816bits(16,352bytes); Internal EEPROM			261,888bits (32,736bytes); Internal EEPROM	
Physical Characteristics							
Tape Width	—	12.65mm					
Tape Thickness	8.9μm	6.4μm	6.1μm	5.6μm		5.2μm	
Tape Length	319m	846m		960m		1,035m	
Cartridge Dimensions	(L x W x H) 102 x 105.4 x 21.5 mm						
Recommended Operation Environment							
Temperature	10~45℃					15~25℃	
Humidity	10~80%RH					20~50%RH	
Max Wet Bulb Temperature	26℃					—	
Max Dew Point Temperature	—					22℃	
Recommended Storage Environment							
Temperature	16~35℃ (Short Term) / 16~25℃ (Long Term)					15~25℃	
Humidity	20~80%RH (Short Term) / 20~50%RH (Long Term)					20~50%RH	
Max Wet Bulb Temperature	26℃					—	
Max Dew Point Temperature	—					22℃	
Allowable Operation Environment							
Temperature	10~45℃					15~35℃	
Humidity	10~80%RH					20~80%RH	
Max Wet Bulb Temperature	26℃					—	
Max Dew Point Temperature	—					22℃	
Allowable Storage Environment							
Temperature	16~35℃ (Short Term) / 16~25℃ (Long Term)					15~35℃	
Humidity	20~80%RH (Short Term) / 20~50%RH (Long Term)					20~80%RH	
Max Wet Bulb Temperature	26℃					—	
Max Dew Point Temperature	—					22℃	

*1 The Cleaning Cartridge is universally usable for all LTO-5/ 6/ 7/ 8/ 9/ 10 drives. (Some exceptions may apply.)

*2 The Max. Transfer Rate varies depending on the type of drive.

LINEUP of LTO DATA CARTRIDGES

	LTO CL	LTO-5	LTO-6	LTO-7	LTO-8	LTO-9	LTO-10
MODEL NUMBER	LTO FB UL-1 CL UCC J	LTO FB UL-5 1.5T J	LTO FB UL-6 2.5T J	LTO FB UL-7 6.0T J	LTO FB UL-8 12.0T J	LTO FB UL-9 18.0T J	LTO FB UL-10 30.0T J
JAN CODE	4902520 241603	4547410 119169	4547410 237061	4547410 316971	4547410 364828	4547410 441239	4547410 556902

LINEUP of LTO WORM CARTRIDGES

	LTO CL	LTO-5 WORM	LTO-6 WORM	LTO-7 WORM	LTO-8 WORM	LTO-9 WORM	LTO-10 WORM
MODEL NUMBER	LTO FB UL-1 CL UCC J	LTO FB UL-5 WORM 1.5T J	LTO FB UL-6 WORM 2.5T J	LTO FB UL-7 WORM 6.0T J	LTO FB UL-8 WORM 12.0T J	LTO FB UL-9 WORM 18.0T J	LTO FB UL-10 WORM 30.0T J
JAN CODE	4902520 241603	4547410 119183	4547410 237078	4547410 316995	4547410 364835	4547410 441264	4547410 5556919

- Linear Tape-Open, LTO, LTO logo, Ultrium and Ultrium logo are registered trademarks of Hewlett Packard Enterprise, International Business Machines Corp. and Quantum Corporation in the US and other countries.
- Specifications are subjected to change without notice. This product catalogue is correct and accurate as of June 2025.

FUJIFILM

FUJIFILM Recording Media GmbH

Fujistraße 1
47533 Kleve
Germany

Offizielle Webseite
<http://www.fujifilm.com/de/de/business/data-management/datastorage>

Search keyword

FUJIFILM LTO



Kontakt

Philipp Stevens
Business Development Manager DACH
Data Storage Media
mobil: +49 160 99183452
email: Philipp.Stevens@fujifilm.com