

# UVIVID 650

## Fujifilm Formulation Guide

### Version 2.0 SMS Base Colors

# UVivid™ 650

UV Narrow Web Printing Inks

## Intense Matching System

### PANTONE® Shades Simulated From Seritone Base Colors

This booklet furnishes the necessary formulas to simulate all the colors in the PANTONE® Color Guide. The formulations used in this guide are hand matched and/or predictive simulations of the PANTONE®\* references using UVivid 650 Series UV Flexo colors. The printed formulas were achieved using a 355.34 pw monofilament polyester flat screen to duplicate a Gallus KS 325, 25% opening or a Stork RM 305 13% opening rotary screen. The ink was printed onto a Leneta Card Substrate. The printed formulas were viewed in Daylight (D65) light source.

The Intense Matching System (IMS) has been designed to enable screen printers to simulate almost any shade from ten IMS Base Colors plus Shading Black, Tinting White, and Mixing Clear.

Each IMS Base Color has been carefully selected for its cleanliness of tone, resistance to fading, and suitability for intermixing. In addition, each ink has been formulated to be free of lead and other heavy metals.

Although every care is taken in producing these formulations, variations in substrates and printing conditions may affect the color achieved. Fujifilm assumes no responsibility for actual color achieved versus the Pantone standard print. For this reason, all formulations must be proofed prior to a production run to ensure color accuracy.

All formulations are percentages by weight using the following UVivid 650 UV Flexo colors:

DESCRIPTION	
650-064 IMS Yellow GS	650-230 IMS Blue GS
650-066 IMS Yellow RS	650-233 IMS Blue RS
650-114 IMS Orange	650-325 IMS Green
650-121 IMS Red YS	650-SB Shading Black
650-127 IMS Violet	650-TW Tinting White
650-164 IMS Red BS	650-MX Mixing Clear
650-165 IMS Magenta	

Fujifilm's color mixing ink formulations for screen process printing produce only simulations of PANTONE Colors in this color reproduction method due to differences in ink film, opacity and pigment selection. The selection used in blending inks may cause metamerism. Pantone, Inc. assumes no responsibility for formula accuracy.

\*PANTONE® is the property of Pantone Inc.

# UVivid 650

PANTONE Yellow C <b>UV 650-MX</b> <b>70.00</b> <b>UV 650-064</b> <b>30.00</b>	Formula	PANTONE Yellow 012 C <b>UV 650-064</b> <b>100.00</b>	Formula	PANTONE Orange 021 C <b>UV 650-114</b> <b>64.81</b> <b>UV 650-MX</b> <b>35.19</b>	Formula	PANTONE Warm Red C <b>UV 650-MX</b> <b>70.80</b> <b>UV 650-114</b> <b>15.04</b> <b>UV 650-121</b> <b>14.16</b>	Formula
PANTONE Red 032 C <b>UV 650-MX</b> <b>71.72</b> <b>UV 650-121</b> <b>22.56</b> <b>UV 650-114</b> <b>5.72</b>	Formula	PANTONE Rubine Red C <b>UV 650-165</b> <b>73.22</b> <b>UV 650-MX</b> <b>20.92</b> <b>UV 650-114</b> <b>5.86</b>	Formula	PANTONE Rhodamine Red C <b>UV 650-MX</b> <b>63.64</b> <b>UV 650-165</b> <b>36.36</b>	Formula	PANTONE Purple C <b>UV 650-MX</b> <b>64.04</b> <b>UV 650-165</b> <b>24.63</b> <b>UV 650-TW</b> <b>8.21</b> <b>UV 650-127</b> <b>3.12</b>	Formula
PANTONE Violet C <b>UV 650-MX</b> <b>73.53</b> <b>UV 650-127</b> <b>24.51</b> <b>UV 650-230</b> <b>1.96</b>	Formula	PANTONE Blue 072 C <b>UV 650-MX</b> <b>48.27</b> <b>UV 650-233</b> <b>36.21</b> <b>UV 650-127</b> <b>15.52</b>	Formula	PANTONE Reflex Blue C <b>UV 650-230</b> <b>46.67</b> <b>UV 650-MX</b> <b>33.33</b> <b>UV 650-127</b> <b>20.00</b>	Formula	PANTONE Process Blue C <b>UV 650-MX</b> <b>66.19</b> <b>UV 650-230</b> <b>33.07</b> <b>UV 650-127</b> <b>0.74</b>	Formula
PANTONE Green C <b>UV 650-325</b> <b>55.66</b> <b>UV 650-MX</b> <b>42.45</b> <b>UV 650-TW</b> <b>1.89</b>	Formula	PANTONE Black C <b>UV 650-SB</b> <b>95.00</b> <b>UV 650-MX</b> <b>5.00</b>	Formula	PANTONE 100 C <b>UV 650-TW</b> <b>63.84</b> <b>UV 650-MX</b> <b>30.49</b> <b>UV 650-064</b> <b>5.67</b>	Formula	PANTONE 101 C <b>UV 650-TW</b> <b>60.09</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-064</b> <b>9.91</b>	Formula

# UVivid 650

PANTONE 102 C <b>UV 650-TW</b> 36.41 <b>UV 650-064</b> 33.59 <b>UV 650-MX</b> 30.00	Formula	PANTONE 103 C <b>UV 650-064</b> 63.83 <b>UV 650-TW</b> 31.85 <b>UV 650-SB</b> 4.32	Formula	PANTONE 104 C <b>UV 650-064</b> 41.95 <b>UV 650-MX</b> 28.50 <b>UV 650-TW</b> 22.77 <b>UV 650-SB</b> 6.78	Formula	PANTONE 105 C <b>UV 650-MX</b> 29.99 <b>UV 650-064</b> 27.89 <b>UV 650-TW</b> 27.17 <b>UV 650-SB</b> 14.95	Formula
PANTONE 106 C <b>UV 650-TW</b> 86.16 <b>UV 650-064</b> 13.84	Formula	PANTONE 107 C <b>UV 650-TW</b> 72.80 <b>UV 650-064</b> 27.20	Formula	PANTONE 108 C <b>UV 650-064</b> 52.27 <b>UV 650-TW</b> 47.73	Formula	PANTONE 109 C <b>UV 650-064</b> 64.29 <b>UV 650-066</b> 35.71	Formula
PANTONE 110 C <b>UV 650-066</b> 56.08 <b>UV 650-064</b> 25.53 <b>UV 650-TW</b> 15.62 <b>UV 650-SB</b> 2.77	Formula	PANTONE 111 C <b>UV 650-066</b> 39.24 <b>UV 650-064</b> 35.42 <b>UV 650-TW</b> 16.01 <b>UV 650-SB</b> 9.33	Formula	PANTONE 112 C <b>UV 650-064</b> 32.46 <b>UV 650-066</b> 30.72 <b>UV 650-TW</b> 24.86 <b>UV 650-SB</b> 11.96	Formula	PANTONE 113 C <b>UV 650-TW</b> 80.00 <b>UV 650-064</b> 12.86 <b>UV 650-066</b> 7.14	Formula
PANTONE 114 C <b>UV 650-TW</b> 73.28 <b>UV 650-064</b> 15.81 <b>UV 650-066</b> 10.91	Formula	PANTONE 115 C <b>UV 650-TW</b> 66.58 <b>UV 650-066</b> 15.20 <b>UV 650-064</b> 18.22	Formula	PANTONE 116 C <b>UV 650-066</b> 53.99 <b>UV 650-064</b> 24.92 <b>UV 650-TW</b> 21.09	Formula	PANTONE 117 C <b>UV 650-066</b> 74.81 <b>UV 650-TW</b> 10.71 <b>UV 650-064</b> 9.98 <b>UV 650-SB</b> 4.50	Formula

# UVivid 650

PANTONE 118 C <b>UV 650-066</b> <b>64.14</b> <b>UV 650-TW</b> <b>14.25</b> <b>UV 650-064</b> <b>14.06</b> <b>UV 650-SB</b> <b>7.55</b>	Formula	PANTONE 119 C <b>UV 650-066</b> <b>37.88</b> <b>UV 650-TW</b> <b>28.35</b> <b>UV 650-064</b> <b>19.32</b> <b>UV 650-SB</b> <b>14.45</b>	Formula	PANTONE 120 C <b>UV 650-TW</b> <b>79.50</b> <b>UV 650-066</b> <b>16.28</b> <b>UV 650-064</b> <b>4.22</b>	Formula	PANTONE 121 C <b>UV 650-TW</b> <b>73.94</b> <b>UV 650-066</b> <b>20.06</b> <b>UV 650-064</b> <b>6.00</b>	Formula
PANTONE 122 C <b>UV 650-TW</b> <b>62.23</b> <b>UV 650-066</b> <b>29.64</b> <b>UV 650-064</b> <b>8.13</b>	Formula	PANTONE 123 C <b>UV 650-066</b> <b>64.29</b> <b>UV 650-TW</b> <b>35.71</b>	Formula	PANTONE 124 C <b>UV 650-066</b> <b>83.18</b> <b>UV 650-TW</b> <b>15.11</b> <b>UV 650-SB</b> <b>1.71</b>	Formula	PANTONE 125 C <b>UV 650-066</b> <b>92.07</b> <b>UV 650-SB</b> <b>7.93</b>	Formula
PANTONE 126 C <b>UV 650-066</b> <b>81.80</b> <b>UV 650-SB</b> <b>10.74</b> <b>UV 650-064</b> <b>4.33</b> <b>UV 650-TW</b> <b>3.13</b>	Formula	PANTONE 1205 C <b>UV 650-TW</b> <b>95.83</b> <b>UV 650-064</b> <b>3.45</b> <b>UV 650-114</b> <b>0.72</b>	Formula	PANTONE 1215 C <b>UV 650-TW</b> <b>91.67</b> <b>UV 650-064</b> <b>7.05</b> <b>UV 650-114</b> <b>1.28</b>	Formula	PANTONE 1225 C <b>UV 650-066</b> <b>51.37</b> <b>UV 650-TW</b> <b>48.63</b>	Formula
PANTONE 1235 C <b>UV 650-066</b> <b>83.33</b> <b>UV 650-TW</b> <b>13.89</b> <b>UV 650-114</b> <b>2.78</b>	Formula	PANTONE 1245 C <b>UV 650-TW</b> <b>47.42</b> <b>UV 650-064</b> <b>41.16</b> <b>UV 650-114</b> <b>6.13</b> <b>UV 650-SB</b> <b>5.29</b>	Formula	PANTONE 1255 C <b>UV 650-TW</b> <b>47.48</b> <b>UV 650-064</b> <b>38.40</b> <b>UV 650-SB</b> <b>8.55</b> <b>UV 650-114</b> <b>5.57</b>	Formula	PANTONE 1265 C <b>UV 650-064</b> <b>39.01</b> <b>UV 650-TW</b> <b>37.04</b> <b>UV 650-SB</b> <b>16.78</b> <b>UV 650-114</b> <b>7.17</b>	Formula

# UVivid 650

PANTONE 127 C <b>UV 650-TW</b> <b>91.23</b> <b>UV 650-064</b> <b>8.22</b> <b>UV 650-165</b> <b>0.55</b>	Formula	PANTONE 128 C <b>UV 650-TW</b> <b>84.87</b> <b>UV 650-064</b> <b>14.28</b> <b>UV 650-165</b> <b>0.85</b>	Formula	PANTONE 129 C <b>UV 650-TW</b> <b>81.81</b> <b>UV 650-064</b> <b>17.11</b> <b>UV 650-165</b> <b>1.08</b>	Formula	PANTONE 130 C <b>UV 650-064</b> <b>87.77</b> <b>UV 650-165</b> <b>3.19</b> <b>UV 650-TW</b> <b>9.04</b>	Formula
PANTONE 131 C <b>UV 650-064</b> <b>60.20</b> <b>UV 650-TW</b> <b>32.25</b> <b>UV 650-165</b> <b>4.73</b> <b>UV 650-SB</b> <b>2.82</b>	Formula	PANTONE 132 C <b>UV 650-064</b> <b>58.39</b> <b>UV 650-TW</b> <b>28.03</b> <b>UV 650-SB</b> <b>8.74</b> <b>UV 650-165</b> <b>4.84</b>	Formula	PANTONE 133 C <b>UV 650-064</b> <b>46.60</b> <b>UV 650-TW</b> <b>25.46</b> <b>UV 650-SB</b> <b>22.87</b> <b>UV 650-165</b> <b>5.07</b>	Formula	PANTONE 134 C <b>UV 650-TW</b> <b>90.49</b> <b>UV 650-064</b> <b>7.64</b> <b>UV 650-114</b> <b>1.52</b> <b>UV 650-165</b> <b>0.35</b>	Formula
PANTONE 135 C <b>UV 650-TW</b> <b>82.60</b> <b>UV 650-064</b> <b>14.40</b> <b>UV 650-114</b> <b>2.60</b> <b>UV 650-165</b> <b>0.40</b>	Formula	PANTONE 136 C <b>UV 650-TW</b> <b>73.59</b> <b>UV 650-064</b> <b>21.91</b> <b>UV 650-114</b> <b>4.07</b> <b>UV 650-165</b> <b>0.43</b>	Formula	PANTONE 137 C <b>UV 650-064</b> <b>61.76</b> <b>UV 650-TW</b> <b>28.50</b> <b>UV 650-114</b> <b>9.50</b> <b>UV 650-165</b> <b>0.24</b>	Formula	PANTONE 138 C <b>UV 650-064</b> <b>53.24</b> <b>UV 650-TW</b> <b>26.78</b> <b>UV 650-114</b> <b>17.10</b> <b>UV 650-SB</b> <b>2.88</b>	Formula
PANTONE 139 C <b>UV 650-064</b> <b>52.88</b> <b>UV 650-TW</b> <b>24.52</b> <b>UV 650-114</b> <b>14.33</b> <b>UV 650-SB</b> <b>8.27</b>	Formula	PANTONE 140 C <b>UV 650-064</b> <b>37.90</b> <b>UV 650-TW</b> <b>29.82</b> <b>UV 650-SB</b> <b>21.01</b> <b>UV 650-114</b> <b>11.27</b>	Formula	PANTONE 1345 C <b>UV 650-TW</b> <b>93.61</b> <b>UV 650-064</b> <b>4.09</b> <b>UV 650-114</b> <b>1.93</b> <b>UV 650-165</b> <b>0.37</b>	Formula	PANTONE 1355 C <b>UV 650-TW</b> <b>89.72</b> <b>UV 650-064</b> <b>6.72</b> <b>UV 650-114</b> <b>3.13</b> <b>UV 650-165</b> <b>0.43</b>	Formula

# UVivid 650

PANTONE 1365 C <b>UV 650-TW</b> 79.44 <b>UV 650-064</b> 14.73 <b>UV 650-114</b> 5.31 <b>UV 650-165</b> 0.52	Formula	PANTONE 1375 C <b>UV 650-TW</b> 66.02 <b>UV 650-114</b> 11.00 <b>UV 650-064</b> 22.48 <b>UV 650-165</b> 0.50	Formula	PANTONE 1385 C <b>UV 650-064</b> 46.35 <b>UV 650-TW</b> 30.96 <b>UV 650-114</b> 18.84 <b>UV 650-SB</b> 3.85	Formula	PANTONE 1395 C <b>UV 650-064</b> 41.18 <b>UV 650-TW</b> 27.30 <b>UV 650-114</b> 18.71 <b>UV 650-SB</b> 12.81	Formula
PANTONE 1405 C <b>UV 650-064</b> 31.87 <b>UV 650-TW</b> 26.09 <b>UV 650-SB</b> 25.80 <b>UV 650-114</b> 16.24	Formula	PANTONE 141 C <b>UV 650-TW</b> 88.46 <b>UV 650-064</b> 9.80 <b>UV 650-165</b> 1.74	Formula	PANTONE 142 C <b>UV 650-TW</b> 79.56 <b>UV 650-064</b> 17.99 <b>UV 650-165</b> 2.45	Formula	PANTONE 143 C <b>UV 650-TW</b> 69.66 <b>UV 650-064</b> 27.09 <b>UV 650-165</b> 3.25	Formula
PANTONE 144 C <b>UV 650-064</b> 74.31 <b>UV 650-TW</b> 16.51 <b>UV 650-165</b> 9.18	Formula	PANTONE 145 C <b>UV 650-064</b> 55.81 <b>UV 650-TW</b> 33.61 <b>UV 650-165</b> 8.44 <b>UV 650-SB</b> 2.14	Formula	PANTONE 146 C <b>UV 650-064</b> 55.31 <b>UV 650-TW</b> 27.93 <b>UV 650-165</b> 8.94 <b>UV 650-SB</b> 7.82	Formula	PANTONE 147 C <b>UV 650-TW</b> 37.34 <b>UV 650-064</b> 35.65 <b>UV 650-SB</b> 20.73 <b>UV 650-165</b> 6.28	Formula
PANTONE 148 C <b>UV 650-TW</b> 95.14 <b>UV 650-114</b> 2.61 <b>UV 650-064</b> 2.25	Formula	PANTONE 149 C <b>UV 650-TW</b> 90.92 <b>UV 650-064</b> 4.82 <b>UV 650-114</b> 4.26	Formula	PANTONE 150 C <b>UV 650-TW</b> 79.39 <b>UV 650-064</b> 12.49 <b>UV 650-114</b> 8.12	Formula	PANTONE 151 C <b>UV 650-114</b> 36.32 <b>UV 650-064</b> 45.40 <b>UV 650-TW</b> 18.28	Formula

# UVivid 650

<b>PANTONE</b> <b>152 C</b> <b>UV 650-064</b> <b>43.34</b> <b>UV 650-TW</b> <b>29.86</b> <b>UV 650-114</b> <b>24.51</b> <b>UV 650-SB</b> <b>2.29</b>	Formula	<b>PANTONE</b> <b>153 C</b> <b>UV 650-064</b> <b>47.35</b> <b>UV 650-TW</b> <b>23.25</b> <b>UV 650-114</b> <b>22.65</b> <b>UV 650-SB</b> <b>6.75</b>	Formula	<b>PANTONE</b> <b>154 C</b> <b>UV 650-064</b> <b>42.02</b> <b>UV 650-114</b> <b>24.94</b> <b>UV 650-TW</b> <b>19.94</b> <b>UV 650-SB</b> <b>13.10</b>	Formula	<b>PANTONE</b> <b>1485 C</b> <b>UV 650-TW</b> <b>79.64</b> <b>UV 650-066</b> <b>12.19</b> <b>UV 650-114</b> <b>8.17</b>	Formula
<b>PANTONE</b> <b>1495 C</b> <b>UV 650-TW</b> <b>45.05</b> <b>UV 650-066</b> <b>41.21</b> <b>UV 650-114</b> <b>13.74</b>	Formula	<b>PANTONE</b> <b>1505 C</b> <b>UV 650-066</b> <b>74.82</b> <b>UV 650-114</b> <b>25.18</b>	Formula	<b>PANTONE</b> <b>1525 C</b> <b>UV 650-066</b> <b>40.91</b> <b>UV 650-114</b> <b>38.72</b> <b>UV 650-TW</b> <b>14.99</b> <b>UV 650-SB</b> <b>5.38</b>	Formula	<b>PANTONE</b> <b>1535 C</b> <b>UV 650-066</b> <b>53.64</b> <b>UV 650-114</b> <b>28.70</b> <b>UV 650-SB</b> <b>13.78</b> <b>UV 650-TW</b> <b>3.88</b>	Formula
<b>PANTONE</b> <b>1545 C</b> <b>UV 650-SB</b> <b>33.64</b> <b>UV 650-114</b> <b>23.19</b> <b>UV 650-TW</b> <b>22.37</b> <b>UV 650-064</b> <b>20.80</b>	Formula	<b>PANTONE</b> <b>155 C</b> <b>UV 650-TW</b> <b>96.10</b> <b>UV 650-064</b> <b>2.52</b> <b>UV 650-165</b> <b>1.38</b>	Formula	<b>PANTONE</b> <b>156 C</b> <b>UV 650-TW</b> <b>91.30</b> <b>UV 650-064</b> <b>5.94</b> <b>UV 650-165</b> <b>2.76</b>	Formula	<b>PANTONE</b> <b>157 C</b> <b>UV 650-TW</b> <b>74.79</b> <b>UV 650-064</b> <b>18.78</b> <b>UV 650-165</b> <b>6.43</b>	Formula
<b>PANTONE</b> <b>158 C</b> <b>UV 650-064</b> <b>48.78</b> <b>UV 650-TW</b> <b>39.02</b> <b>UV 650-165</b> <b>12.20</b>	Formula	<b>PANTONE</b> <b>159 C</b> <b>UV 650-064</b> <b>55.80</b> <b>UV 650-TW</b> <b>24.65</b> <b>UV 650-165</b> <b>17.27</b> <b>UV 650-SB</b> <b>2.28</b>	Formula	<b>PANTONE</b> <b>160 C</b> <b>UV 650-064</b> <b>54.67</b> <b>UV 650-165</b> <b>19.58</b> <b>UV 650-TW</b> <b>17.41</b> <b>UV 650-SB</b> <b>8.34</b>	Formula	<b>PANTONE</b> <b>161 C</b> <b>UV 650-064</b> <b>44.35</b> <b>UV 650-SB</b> <b>26.74</b> <b>UV 650-165</b> <b>16.45</b> <b>UV 650-TW</b> <b>12.46</b>	Formula



# UVivid 650

PANTONE 1555 C	Formula
UV 650-TW	94.70
UV 650-114	4.35
UV 650-064	0.57
UV 650-165	0.38

PANTONE 1565 C	Formula
UV 650-TW	87.74
UV 650-114	9.23
UV 650-064	2.54
UV 650-165	0.49

PANTONE 1575 C	Formula
UV 650-TW	66.24
UV 650-114	21.05
UV 650-064	12.20
UV 650-165	0.51

PANTONE 1585 C	Formula
UV 650-TW	43.75
UV 650-114	25.00
UV 650-064	25.00
UV 650-165	6.25

PANTONE 1595 C	Formula
UV 650-114	39.34
UV 650-TW	38.58
UV 650-064	19.03
UV 650-SB	3.05

PANTONE 1605 C	Formula
UV 650-114	39.52
UV 650-TW	28.48
UV 650-064	22.75
UV 650-SB	9.25

PANTONE 1615 C	Formula
UV 650-114	41.45
UV 650-TW	21.70
UV 650-064	20.93
UV 650-SB	15.92

PANTONE 162 C	Formula
UV 650-TW	95.08
UV 650-114	4.50
UV 650-165	0.42

PANTONE 163 C	Formula
UV 650-TW	84.56
UV 650-114	13.80
UV 650-064	1.06
UV 650-165	0.58

PANTONE 164 C	Formula
UV 650-TW	63.05
UV 650-114	27.78
UV 650-064	8.71
UV 650-165	0.46

PANTONE 165 C	Formula
UV 650-TW	42.86
UV 650-114	28.57
UV 650-064	23.81
UV 650-165	4.76

PANTONE 166 C	Formula
UV 650-114	51.01
UV 650-TW	29.09
UV 650-064	17.76
UV 650-SB	2.14

PANTONE 167 C	Formula
UV 650-114	46.04
UV 650-064	25.59
UV 650-TW	22.29
UV 650-SB	6.08

PANTONE 168 C	Formula
UV 650-114	39.40
UV 650-SB	24.66
UV 650-064	22.15
UV 650-TW	13.79

PANTONE 1625 C	Formula
UV 650-TW	89.95
UV 650-114	8.03
UV 650-165	2.02

PANTONE 1635 C	Formula
UV 650-TW	80.93
UV 650-114	17.30
UV 650-165	1.77

# UVivid 650

PANTONE 1645 C <b>UV 650-TW</b> <b>54.59</b> <b>UV 650-114</b> <b>44.92</b> <b>UV 650-165</b> <b>0.49</b>	Formula	PANTONE 1655 C <b>UV 650-TW</b> <b>31.25</b> <b>UV 650-114</b> <b>41.25</b> <b>UV 650-064</b> <b>18.75</b> <b>UV 650-165</b> <b>8.75</b>	Formula	PANTONE 1665 C <b>UV 650-114</b> <b>68.50</b> <b>UV 650-TW</b> <b>21.71</b> <b>UV 650-064</b> <b>7.42</b> <b>UV 650-SB</b> <b>2.37</b>	Formula	PANTONE 1675 C <b>UV 650-114</b> <b>54.84</b> <b>UV 650-TW</b> <b>27.37</b> <b>UV 650-SB</b> <b>9.67</b> <b>UV 650-064</b> <b>8.12</b>	Formula
PANTONE 1685 C <b>UV 650-114</b> <b>48.87</b> <b>UV 650-TW</b> <b>23.54</b> <b>UV 650-SB</b> <b>17.38</b> <b>UV 650-064</b> <b>10.21</b>	Formula	PANTONE 169 C <b>UV 650-TW</b> <b>94.14</b> <b>UV 650-114</b> <b>3.23</b> <b>UV 650-165</b> <b>2.63</b>	Formula	PANTONE 170 C <b>UV 650-TW</b> <b>80.72</b> <b>UV 650-114</b> <b>14.37</b> <b>UV 650-165</b> <b>4.91</b>	Formula	PANTONE 171 C <b>UV 650-114</b> <b>48.13</b> <b>UV 650-TW</b> <b>47.90</b> <b>UV 650-165</b> <b>3.97</b>	Formula
PANTONE 172 C <b>UV 650-TW</b> <b>30.93</b> <b>UV 650-114</b> <b>43.30</b> <b>UV 650-064</b> <b>13.40</b> <b>UV 650-165</b> <b>12.37</b>	Formula	PANTONE 173 C <b>UV 650-114</b> <b>62.06</b> <b>UV 650-TW</b> <b>32.63</b> <b>UV 650-SB</b> <b>3.37</b> <b>UV 650-165</b> <b>1.94</b>	Formula	PANTONE 174 C <b>UV 650-114</b> <b>70.73</b> <b>UV 650-TW</b> <b>15.48</b> <b>UV 650-SB</b> <b>12.92</b> <b>UV 650-064</b> <b>0.87</b>	Formula	PANTONE 175 C <b>UV 650-114</b> <b>46.61</b> <b>UV 650-SB</b> <b>26.37</b> <b>UV 650-TW</b> <b>24.09</b> <b>UV 650-064</b> <b>2.93</b>	Formula
PANTONE 176 C <b>UV 650-TW</b> <b>96.18</b> <b>UV 650-121</b> <b>3.82</b>	Formula	PANTONE 177 C <b>UV 650-TW</b> <b>87.60</b> <b>UV 650-121</b> <b>11.24</b> <b>UV 650-114</b> <b>1.16</b>	Formula	PANTONE 178 C <b>UV 650-TW</b> <b>46.50</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-121</b> <b>23.50</b>	Formula	PANTONE 179 C <b>UV 650-TW</b> <b>48.29</b> <b>UV 650-114</b> <b>41.77</b> <b>UV 650-121</b> <b>8.73</b> <b>UV 650-SB</b> <b>1.21</b>	Formula

# UVivid 650

PANTONE 180 C <b>UV 650-TW</b> <b>45.45</b> <b>UV 650-114</b> <b>39.87</b> <b>UV 650-121</b> <b>10.32</b> <b>UV 650-SB</b> <b>4.36</b>	Formula	PANTONE 181 C <b>UV 650-114</b> <b>47.20</b> <b>UV 650-TW</b> <b>26.11</b> <b>UV 650-SB</b> <b>17.66</b> <b>UV 650-121</b> <b>9.03</b>	Formula	PANTONE 1765 C <b>UV 650-TW</b> <b>94.87</b> <b>UV 650-121</b> <b>5.13</b>	Formula	PANTONE 1775 C <b>UV 650-TW</b> <b>92.35</b> <b>UV 650-121</b> <b>7.65</b>	Formula
PANTONE 1785 C <b>UV 650-TW</b> <b>47.19</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-121</b> <b>22.81</b>	Formula	PANTONE 1788 C <b>UV 650-TW</b> <b>36.34</b> <b>UV 650-121</b> <b>36.02</b> <b>UV 650-114</b> <b>9.12</b> <b>UV 650-MX</b> <b>18.52</b>	Formula	PANTONE 1795 C <b>UV 650-114</b> <b>41.21</b> <b>UV 650-TW</b> <b>37.35</b> <b>UV 650-121</b> <b>19.85</b> <b>UV 650-SB</b> <b>1.59</b>	Formula	PANTONE 1805 C <b>UV 650-TW</b> <b>39.29</b> <b>UV 650-114</b> <b>35.98</b> <b>UV 650-121</b> <b>19.21</b> <b>UV 650-SB</b> <b>5.52</b>	Formula
PANTONE 1815 C <b>UV 650-114</b> <b>35.94</b> <b>UV 650-MX</b> <b>30.01</b> <b>UV 650-TW</b> <b>18.04</b> <b>UV 650-121</b> <b>9.42</b> <b>UV 650-SB</b> <b>6.59</b>	Formula	PANTONE 1767 C <b>UV 650-TW</b> <b>96.22</b> <b>UV 650-121</b> <b>3.78</b>	Formula	PANTONE 1777 C <b>UV 650-TW</b> <b>83.78</b> <b>UV 650-121</b> <b>16.22</b>	Formula	PANTONE 1787 C <b>UV 650-TW</b> <b>45.20</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-121</b> <b>24.80</b>	Formula
PANTONE 1797 C <b>UV 650-121</b> <b>52.04</b> <b>UV 650-TW</b> <b>46.49</b> <b>UV 650-SB</b> <b>1.47</b>	Formula	PANTONE 1807 C <b>UV 650-121</b> <b>51.39</b> <b>UV 650-TW</b> <b>41.32</b> <b>UV 650-SB</b> <b>7.29</b>	Formula	PANTONE 1817 C <b>UV 650-SB</b> <b>28.47</b> <b>UV 650-121</b> <b>27.16</b> <b>UV 650-TW</b> <b>25.28</b> <b>UV 650-114</b> <b>19.09</b>	Formula	PANTONE 182 C <b>UV 650-TW</b> <b>96.38</b> <b>UV 650-165</b> <b>2.99</b> <b>UV 650-121</b> <b>0.63</b>	Formula

# UVivid 650

<b>PANTONE</b> <b>183 C</b> <b>UV 650-TW</b> <b>62.59</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>4.66</b> <b>UV 650-121</b> <b>2.75</b>	Formula	<b>PANTONE</b> <b>184 C</b> <b>UV 650-TW</b> <b>49.59</b> <b>UV 650-MX</b> <b>29.99</b> <b>UV 650-121</b> <b>12.31</b> <b>UV 650-165</b> <b>8.11</b>	Formula	<b>PANTONE</b> <b>185 C</b> <b>UV 650-121</b> <b>58.33</b> <b>UV 650-TW</b> <b>41.67</b>	Formula	<b>PANTONE</b> <b>186 C</b> <b>UV 650-121</b> <b>55.15</b> <b>UV 650-TW</b> <b>43.45</b> <b>UV 650-SB</b> <b>1.40</b>	Formula
<b>PANTONE</b> <b>187 C</b> <b>UV 650-121</b> <b>44.31</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-TW</b> <b>20.23</b> <b>UV 650-SB</b> <b>5.46</b>	Formula	<b>PANTONE</b> <b>188 C</b> <b>UV 650-121</b> <b>50.04</b> <b>UV 650-TW</b> <b>32.22</b> <b>UV 650-SB</b> <b>17.74</b>	Formula	<b>PANTONE</b> <b>189 C</b> <b>UV 650-TW</b> <b>92.99</b> <b>UV 650-165</b> <b>4.46</b> <b>UV 650-164</b> <b>2.55</b>	Formula	<b>PANTONE</b> <b>190 C</b> <b>UV 650-TW</b> <b>57.48</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>6.28</b> <b>UV 650-164</b> <b>6.24</b>	Formula
<b>PANTONE</b> <b>191 C</b> <b>UV 650-TW</b> <b>49.70</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-164</b> <b>20.30</b>	Formula	<b>PANTONE</b> <b>192 C</b> <b>UV 650-MX</b> <b>48.38</b> <b>UV 650-164</b> <b>32.04</b> <b>UV 650-TW</b> <b>19.58</b>	Formula	<b>PANTONE</b> <b>193 C</b> <b>UV 650-164</b> <b>54.16</b> <b>UV 650-TW</b> <b>44.45</b> <b>UV 650-SB</b> <b>1.39</b>	Formula	<b>PANTONE</b> <b>194 C</b> <b>UV 650-164</b> <b>50.93</b> <b>UV 650-TW</b> <b>42.11</b> <b>UV 650-SB</b> <b>6.96</b>	Formula
<b>PANTONE</b> <b>195 C</b> <b>UV 650-165</b> <b>31.10</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-TW</b> <b>21.55</b> <b>UV 650-SB</b> <b>17.35</b>	Formula	<b>PANTONE</b> <b>1895 C</b> <b>UV 650-TW</b> <b>95.81</b> <b>UV 650-165</b> <b>3.78</b> <b>UV 650-164</b> <b>0.41</b>	Formula	<b>PANTONE</b> <b>1905 C</b> <b>UV 650-TW</b> <b>62.84</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>5.17</b> <b>UV 650-164</b> <b>1.99</b>	Formula	<b>PANTONE</b> <b>1915 C</b> <b>UV 650-TW</b> <b>46.36</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>14.06</b> <b>UV 650-164</b> <b>9.58</b>	Formula

# UVivid 650

PANTONE 1925 C <b>UV 650-TW</b> 17.87 <b>UV 650-164</b> 30.52 <b>UV 650-165</b> 6.42 <b>UV 650-MX</b> 45.19	Formula	PANTONE 1935 C <b>UV 650-TW</b> 50.92 <b>UV 650-164</b> 49.08	Formula	PANTONE 1945 C <b>UV 650-164</b> 41.08 <b>UV 650-MX</b> 30.00 <b>UV 650-TW</b> 24.17 <b>UV 650-SB</b> 4.75	Formula	PANTONE 1955 C <b>UV 650-164</b> 41.50 <b>UV 650-MX</b> 29.99 <b>UV 650-TW</b> 18.73 <b>UV 650-SB</b> 9.78	Formula
PANTONE 196 C <b>UV 650-TW</b> 97.36 <b>UV 650-165</b> 1.80 <b>UV 650-SB</b> 0.43 <b>UV 650-164</b> 0.41	Formula	PANTONE 197 C <b>UV 650-TW</b> 93.80 <b>UV 650-164</b> 5.55 <b>UV 650-SB</b> 0.65	Formula	PANTONE 198 C <b>UV 650-TW</b> 69.00 <b>UV 650-164</b> 31.00	Formula	PANTONE 199 C <b>UV 650-164</b> 66.67 <b>UV 650-TW</b> 33.33	Formula
PANTONE 200 C <b>UV 650-164</b> 47.85 <b>UV 650-MX</b> 28.13 <b>UV 650-TW</b> 21.95 <b>UV 650-SB</b> 2.07	Formula	PANTONE 201 C <b>UV 650-164</b> 55.05 <b>UV 650-TW</b> 30.03 <b>UV 650-MX</b> 8.91 <b>UV 650-SB</b> 6.01	Formula	PANTONE 202 C <b>UV 650-164</b> 57.65 <b>UV 650-TW</b> 31.44 <b>UV 650-SB</b> 10.91	Formula	PANTONE 203 C <b>UV 650-TW</b> 95.43 <b>UV 650-165</b> 4.57	Formula
PANTONE 204 C <b>UV 650-TW</b> 86.51 <b>UV 650-165</b> 10.28 <b>UV 650-164</b> 3.21	Formula	PANTONE 205 C <b>UV 650-TW</b> 41.14 <b>UV 650-MX</b> 30.00 <b>UV 650-165</b> 20.42 <b>UV 650-164</b> 8.44	Formula	PANTONE 206 C <b>UV 650-TW</b> 23.08 <b>UV 650-165</b> 41.50 <b>UV 650-164</b> 35.42	Formula	PANTONE 207 C <b>UV 650-164</b> 32.80 <b>UV 650-MX</b> 30.01 <b>UV 650-165</b> 19.94 <b>UV 650-TW</b> 13.71 <b>UV 650-SB</b> 3.54	Formula

# UVivid 650

<b>PANTONE</b> <b>208 C</b> <b>UV 650-164</b> <b>31.95</b> <b>UV 650-MX</b> <b>29.99</b> <b>UV 650-TW</b> <b>15.47</b> <b>UV 650-165</b> <b>12.19</b> <b>UV 650-SB</b> <b>10.4</b>	Formula	<b>PANTONE</b> <b>209 C</b> <b>UV 650-164</b> <b>36.18</b> <b>UV 650-MX</b> <b>30.01</b> <b>UV 650-SB</b> <b>17.79</b> <b>UV 650-TW</b> <b>16.02</b>	Formula	<b>PANTONE</b> <b>210 C</b> <b>UV 650-TW</b> <b>62.46</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>7.54</b>	Formula	<b>PANTONE</b> <b>211 C</b> <b>UV 650-TW</b> <b>55.38</b> <b>UV 650-MX</b> <b>30.01</b> <b>UV 650-165</b> <b>13.78</b> <b>UV 650-164</b> <b>0.83</b>	Formula
<b>PANTONE</b> <b>212 C</b> <b>UV 650-TW</b> <b>42.91</b> <b>UV 650-MX</b> <b>29.99</b> <b>UV 650-165</b> <b>25.10</b> <b>UV 650-164</b> <b>2.00</b>	Formula	<b>PANTONE</b> <b>213 C</b> <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-165</b> <b>25.00</b> <b>UV 650-164</b> <b>15.00</b>	Formula	<b>PANTONE</b> <b>214 C</b> <b>UV 650-165</b> <b>60.61</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-164</b> <b>9.39</b>	Formula	<b>PANTONE</b> <b>215 C</b> <b>UV 650-165</b> <b>35.02</b> <b>UV 650-MX</b> <b>29.99</b> <b>UV 650-TW</b> <b>20.48</b> <b>UV 650-164</b> <b>11.30</b> <b>UV 650-SB</b> <b>3.21</b>	Formula
<b>PANTONE</b> <b>216 C</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>21.22</b> <b>UV 650-TW</b> <b>18.42</b> <b>UV 650-164</b> <b>17.50</b> <b>UV 650-SB</b> <b>12.86</b>	Formula	<b>PANTONE</b> <b>217 C</b> <b>UV 650-TW</b> <b>95.90</b> <b>UV 650-165</b> <b>4.10</b>	Formula	<b>PANTONE</b> <b>218 C</b> <b>UV 650-TW</b> <b>53.90</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>16.10</b>	Formula	<b>PANTONE</b> <b>219 C</b> <b>UV 650-165</b> <b>41.86</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-TW</b> <b>28.14</b>	Formula
<b>PANTONE</b> <b>220 C</b> <b>UV 650-165</b> <b>65.45</b> <b>UV 650-MX</b> <b>25.09</b> <b>UV 650-114</b> <b>6.29</b> <b>UV 650-SB</b> <b>3.17</b>	Formula	<b>PANTONE</b> <b>221 C</b> <b>UV 650-165</b> <b>67.41</b> <b>UV 650-MX</b> <b>19.20</b> <b>UV 650-114</b> <b>6.91</b> <b>UV 650-SB</b> <b>6.48</b>	Formula	<b>PANTONE</b> <b>222 C</b> <b>UV 650-165</b> <b>46.14</b> <b>UV 650-MX</b> <b>27.27</b> <b>UV 650-SB</b> <b>19.19</b> <b>UV 650-114</b> <b>7.40</b>	Formula	<b>PANTONE</b> <b>223 C</b> <b>UV 650-TW</b> <b>60.53</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>9.47</b>	Formula

# UVivid 650

PANTONE 224 C	Formula
<b>UV 650-TW</b>	<b>51.96</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-165</b>	<b>18.04</b>

PANTONE 225 C	Formula
<b>UV 650-165</b>	<b>37.82</b>
<b>UV 650-TW</b>	<b>32.18</b>
<b>UV 650-MX</b>	<b>30.00</b>

PANTONE 226 C	Formula
<b>UV 650-165</b>	<b>59.49</b>
<b>UV 650-164</b>	<b>7.68</b>
<b>UV 650-MX</b>	<b>32.83</b>

PANTONE 227 C	Formula
<b>UV 650-165</b>	<b>62.48</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-164</b>	<b>4.89</b>
<b>UV 650-SB</b>	<b>2.63</b>

PANTONE 228 C	Formula
<b>UV 650-165</b>	<b>52.99</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-SB</b>	<b>10.20</b>
<b>UV 650-164</b>	<b>6.81</b>

PANTONE 229 C	Formula
<b>UV 650-165</b>	<b>33.47</b>
<b>UV 650-MX</b>	<b>30.01</b>
<b>UV 650-SB</b>	<b>23.94</b>
<b>UV 650-164</b>	<b>12.58</b>

PANTONE 230 C	Formula
<b>UV 650-TW</b>	<b>63.05</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-165</b>	<b>6.95</b>

PANTONE 231 C	Formula
<b>UV 650-TW</b>	<b>52.37</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-165</b>	<b>17.63</b>

PANTONE 232 C	Formula
<b>UV 650-TW</b>	<b>39.45</b>
<b>UV 650-165</b>	<b>30.55</b>
<b>UV 650-MX</b>	<b>30.00</b>

PANTONE 233 C	Formula
<b>UV 650-165</b>	<b>70.00</b>
<b>UV 650-MX</b>	<b>30.00</b>

PANTONE 234 C	Formula
<b>UV 650-165</b>	<b>65.64</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-SB</b>	<b>4.36</b>

PANTONE 235 C	Formula
<b>UV 650-165</b>	<b>66.82</b>
<b>UV 650-MX</b>	<b>22.36</b>
<b>UV 650-SB</b>	<b>10.82</b>

PANTONE 236 C	Formula
<b>UV 650-TW</b>	<b>91.75</b>
<b>UV 650-165</b>	<b>8.00</b>
<b>UV 650-127</b>	<b>0.25</b>

PANTONE 237 C	Formula
<b>UV 650-TW</b>	<b>56.33</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-165</b>	<b>13.04</b>
<b>UV 650-127</b>	<b>0.63</b>

PANTONE 238 C	Formula
<b>UV 650-TW</b>	<b>45.81</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-165</b>	<b>23.65</b>
<b>UV 650-127</b>	<b>0.54</b>

PANTONE 239 C	Formula
<b>UV 650-165</b>	<b>36.36</b>
<b>UV 650-127</b>	<b>0.58</b>
<b>UV 650-MX</b>	<b>63.06</b>

# UVivid 650

PANTONE 240 C <b>UV 650-165</b> <b>36.93</b> <b>UV 650-TW</b> <b>31.52</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>1.55</b>	Formula	PANTONE 241 C <b>UV 650-165</b> <b>45.03</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-TW</b> <b>22.12</b> <b>UV 650-127</b> <b>2.85</b>	Formula	PANTONE 242 C <b>UV 650-165</b> <b>53.56</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-SB</b> <b>16.44</b>	Formula	PANTONE 2365 C <b>UV 650-TW</b> <b>95.90</b> <b>UV 650-165</b> <b>3.64</b> <b>UV 650-127</b> <b>0.46</b>	Formula
PANTONE 2375 C <b>UV 650-TW</b> <b>52.25</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>16.64</b> <b>UV 650-127</b> <b>1.11</b>	Formula	PANTONE 2385 C <b>UV 650-TW</b> <b>38.09</b> <b>UV 650-165</b> <b>30.67</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>1.24</b>	Formula	PANTONE 2395 C <b>UV 650-165</b> <b>54.65</b> <b>UV 650-127</b> <b>1.62</b> <b>UV 650-MX</b> <b>43.73</b>	Formula	PANTONE 2405 C <b>UV 650-165</b> <b>65.62</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>4.38</b>	Formula
PANTONE 2415 C <b>UV 650-165</b> <b>64.09</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>5.91</b>	Formula	PANTONE 2425 C <b>UV 650-165</b> <b>60.40</b> <b>UV 650-MX</b> <b>26.50</b> <b>UV 650-SB</b> <b>9.27</b> <b>UV 650-127</b> <b>3.83</b>	Formula	PANTONE 243 C <b>UV 650-TW</b> <b>95.77</b> <b>UV 650-165</b> <b>3.48</b> <b>UV 650-127</b> <b>0.75</b>	Formula	PANTONE 244 C <b>UV 650-TW</b> <b>91.12</b> <b>UV 650-165</b> <b>7.83</b> <b>UV 650-127</b> <b>1.05</b>	Formula
PANTONE 245 C <b>UV 650-TW</b> <b>56.03</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>12.34</b> <b>UV 650-127</b> <b>1.63</b>	Formula	PANTONE 246 C <b>UV 650-165</b> <b>36.33</b> <b>UV 650-127</b> <b>1.69</b> <b>UV 650-MX</b> <b>61.98</b>	Formula	PANTONE 247 C <b>UV 650-165</b> <b>35.34</b> <b>UV 650-TW</b> <b>31.90</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>2.76</b>	Formula	PANTONE 248 C <b>UV 650-165</b> <b>63.68</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>6.32</b>	Formula



# UVivid 650

PANTONE 249 C <b>UV 650-165</b> <b>54.33</b> <b>UV 650-TW</b> <b>34.45</b> <b>UV 650-SB</b> <b>7.30</b> <b>UV 650-127</b> <b>3.92</b>	Formula	PANTONE 250 C <b>UV 650-TW</b> <b>96.11</b> <b>UV 650-165</b> <b>3.03</b> <b>UV 650-127</b> <b>0.86</b>	Formula	PANTONE 251 C <b>UV 650-TW</b> <b>62.32</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>6.12</b> <b>UV 650-127</b> <b>1.56</b>	Formula	PANTONE 252 C <b>UV 650-TW</b> <b>50.77</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>16.07</b> <b>UV 650-127</b> <b>3.16</b>	Formula
PANTONE 253 C <b>UV 650-TW</b> <b>36.33</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>29.21</b> <b>UV 650-127</b> <b>4.46</b>	Formula	PANTONE 254 C <b>UV 650-165</b> <b>61.18</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>8.82</b>	Formula	PANTONE 255 C <b>UV 650-165</b> <b>46.70</b> <b>UV 650-TW</b> <b>25.30</b> <b>UV 650-MX</b> <b>14.94</b> <b>UV 650-127</b> <b>7.15</b> <b>UV 650-SB</b> <b>5.91</b>	Formula	PANTONE 256 C <b>UV 650-TW</b> <b>98.22</b> <b>UV 650-127</b> <b>1.78</b>	Formula
PANTONE 257 C <b>UV 650-TW</b> <b>66.27</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-127</b> <b>2.38</b> <b>UV 650-165</b> <b>1.35</b>	Formula	PANTONE 258 C <b>UV 650-TW</b> <b>36.98</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>29.90</b> <b>UV 650-230</b> <b>3.12</b>	Formula	PANTONE 259 C <b>UV 650-TW</b> <b>25.28</b> <b>UV 650-165</b> <b>63.85</b> <b>UV 650-230</b> <b>3.79</b> <b>UV 650-SB</b> <b>0.76</b> <b>UV 650-MX</b> <b>6.32</b>	Formula	PANTONE 260 C <b>UV 650-165</b> <b>52.35</b> <b>UV 650-MX</b> <b>29.99</b> <b>UV 650-SB</b> <b>8.34</b> <b>UV 650-TW</b> <b>5.50</b> <b>UV 650-230</b> <b>3.82</b>	Formula
PANTONE 261 C <b>UV 650-165</b> <b>46.41</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-SB</b> <b>14.99</b> <b>UV 650-TW</b> <b>5.92</b> <b>UV 650-230</b> <b>2.68</b>	Formula	PANTONE 262 C <b>UV 650-165</b> <b>40.03</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-SB</b> <b>23.92</b> <b>UV 650-TW</b> <b>4.51</b> <b>UV 650-230</b> <b>1.54</b>	Formula	PANTONE 2562 C <b>UV 650-TW</b> <b>94.60</b> <b>UV 650-165</b> <b>2.99</b> <b>UV 650-127</b> <b>2.41</b>	Formula	PANTONE 2572 C <b>UV 650-TW</b> <b>61.04</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>5.40</b> <b>UV 650-127</b> <b>3.56</b>	Formula

# UVivid 650

PANTONE 2582 C <b>UV 650-TW</b> <b>50.33</b> <b>UV 650-MX</b> <b>30.00</b> <b>UV 650-165</b> <b>10.22</b> <b>UV 650-127</b> <b>9.45</b>	Formula	PANTONE 2592 C <b>UV 650-TW</b> <b>19.93</b> <b>UV 650-165</b> <b>19.85</b> <b>UV 650-127</b> <b>7.28</b> <b>UV 650-MX</b> <b>52.94</b>	Formula	PANTONE 2602 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-165</b> <b>25.39</b> <b>UV 650-127</b> <b>14.61</b>	Formula	PANTONE 2612 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-165</b> <b>25.11</b> <b>UV 650-127</b> <b>11.29</b> <b>UV 650-SB</b> <b>3.60</b>	Formula
PANTONE 2622 C <b>UV 650-165</b> <b>39.26</b> <b>UV 650-TW</b> <b>32.23</b> <b>UV 650-SB</b> <b>11.33</b> <b>UV 650-MX</b> <b>9.26</b> <b>UV 650-127</b> <b>7.92</b>	Formula	PANTONE 2563 C <b>UV 650-TW</b> <b>95.48</b> <b>UV 650-127</b> <b>2.87</b> <b>UV 650-165</b> <b>1.65</b>	Formula	PANTONE 2573 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-TW</b> <b>33.92</b> <b>UV 650-127</b> <b>3.74</b> <b>UV 650-165</b> <b>2.34</b>	Formula	PANTONE 2583 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-TW</b> <b>27.19</b> <b>UV 650-127</b> <b>6.73</b> <b>UV 650-165</b> <b>6.08</b>	Formula
PANTONE 2593 C <b>UV 650-TW</b> <b>36.76</b> <b>UV 650-165</b> <b>22.06</b> <b>UV 650-127</b> <b>8.83</b> <b>UV 650-MX</b> <b>32.35</b>	Formula	PANTONE 2603 C <b>UV 650-MX</b> <b>54.39</b> <b>UV 650-165</b> <b>25.59</b> <b>UV 650-127</b> <b>10.38</b> <b>UV 650-TW</b> <b>8.97</b> <b>UV 650-230</b> <b>0.67</b>	Formula	PANTONE 2613 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-165</b> <b>23.58</b> <b>UV 650-127</b> <b>11.50</b> <b>UV 650-SB</b> <b>4.92</b>	Formula	PANTONE 2623 C <b>UV 650-MX</b> <b>51.13</b> <b>UV 650-165</b> <b>27.02</b> <b>UV 650-SB</b> <b>11.36</b> <b>UV 650-127</b> <b>10.49</b>	Formula
PANTONE 2567 C <b>UV 650-TW</b> <b>67.26</b> <b>UV 650-MX</b> <b>29.99</b> <b>UV 650-127</b> <b>2.53</b> <b>UV 650-230</b> <b>0.22</b>	Formula	PANTONE 2577 C <b>UV 650-MX</b> <b>58.13</b> <b>UV 650-TW</b> <b>37.78</b> <b>UV 650-127</b> <b>3.80</b> <b>UV 650-230</b> <b>0.29</b>	Formula	PANTONE 2587 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-165</b> <b>30.12</b> <b>UV 650-127</b> <b>5.24</b> <b>UV 650-230</b> <b>4.64</b>	Formula	PANTONE 2597 C <b>UV 650-TW</b> <b>16.51</b> <b>UV 650-127</b> <b>22.02</b> <b>UV 650-165</b> <b>15.60</b> <b>UV 650-MX</b> <b>45.87</b>	Formula

# UVivid 650

PANTONE 2607 C <b>UV 650-MX</b> <b>50.71</b> <b>UV 650-127</b> <b>24.17</b> <b>UV 650-165</b> <b>23.47</b> <b>UV 650-SB</b> <b>1.65</b>	Formula	PANTONE 2617 C <b>UV 650-MX</b> <b>53.65</b> <b>UV 650-165</b> <b>20.87</b> <b>UV 650-127</b> <b>20.45</b> <b>UV 650-SB</b> <b>5.03</b>	Formula	PANTONE 2627 C <b>UV 650-MX</b> <b>35.95</b> <b>UV 650-165</b> <b>31.28</b> <b>UV 650-127</b> <b>19.59</b> <b>UV 650-SB</b> <b>13.18</b>	Formula	PANTONE 263 C <b>UV 650-TW</b> <b>98.00</b> <b>UV 650-127</b> <b>1.60</b> <b>UV 650-165</b> <b>0.40</b>	Formula
PANTONE 264 C <b>UV 650-TW</b> <b>96.27</b> <b>UV 650-127</b> <b>3.00</b> <b>UV 650-165</b> <b>0.73</b>	Formula	PANTONE 265 C <b>UV 650-MX</b> <b>59.42</b> <b>UV 650-TW</b> <b>29.55</b> <b>UV 650-127</b> <b>8.02</b> <b>UV 650-165</b> <b>3.01</b>	Formula	PANTONE 266 C <b>UV 650-TW</b> <b>52.83</b> <b>UV 650-127</b> <b>16.98</b> <b>UV 650-MX</b> <b>30.19</b>	Formula	PANTONE 267 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-127</b> <b>24.35</b> <b>UV 650-TW</b> <b>15.65</b>	Formula
PANTONE 268 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-127</b> <b>23.31</b> <b>UV 650-TW</b> <b>12.48</b> <b>UV 650-SB</b> <b>4.21</b>	Formula	PANTONE 269 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-127</b> <b>16.05</b> <b>UV 650-SB</b> <b>14.64</b> <b>UV 650-165</b> <b>9.31</b>	Formula	PANTONE 2635 C <b>UV 650-TW</b> <b>96.90</b> <b>UV 650-127</b> <b>2.73</b> <b>UV 650-230</b> <b>0.37</b>	Formula	PANTONE 2645 C <b>UV 650-TW</b> <b>51.72</b> <b>UV 650-MX</b> <b>45.01</b> <b>UV 650-127</b> <b>2.85</b> <b>UV 650-230</b> <b>0.42</b>	Formula
PANTONE 2655 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-TW</b> <b>32.18</b> <b>UV 650-127</b> <b>7.08</b> <b>UV 650-230</b> <b>0.74</b>	Formula	PANTONE 2665 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-TW</b> <b>26.65</b> <b>UV 650-127</b> <b>12.83</b> <b>UV 650-230</b> <b>0.52</b>	Formula	PANTONE 2685 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-127</b> <b>40.00</b>	Formula	PANTONE 2695 C <b>UV 650-MX</b> <b>48.41</b> <b>UV 650-SB</b> <b>26.83</b> <b>UV 650-127</b> <b>24.76</b>	Formula

# UVivid 650

PANTONE 270 C <b>UV 650-TW</b> <b>93.98</b> <b>UV 650-165</b> <b>4.08</b> <b>UV 650-127</b> <b>1.94</b>	Formula	PANTONE 271 C <b>UV 650-TW</b> <b>46.61</b> <b>UV 650-MX</b> <b>45.94</b> <b>UV 650-165</b> <b>4.87</b> <b>UV 650-233</b> <b>2.58</b>	Formula	PANTONE 272 C <b>UV 650-MX</b> <b>60.01</b> <b>UV 650-TW</b> <b>22.89</b> <b>UV 650-165</b> <b>11.42</b> <b>UV 650-233</b> <b>5.68</b>	Formula	PANTONE 273 C <b>UV 650-165</b> <b>71.26</b> <b>UV 650-233</b> <b>28.74</b>	Formula
PANTONE 274 C <b>UV 650-165</b> <b>76.37</b> <b>UV 650-233</b> <b>16.19</b> <b>UV 650-SB</b> <b>7.44</b>	Formula	PANTONE 275 C <b>UV 650-165</b> <b>71.05</b> <b>UV 650-SB</b> <b>15.60</b> <b>UV 650-233</b> <b>13.35</b>	Formula	PANTONE 276 C <b>UV 650-165</b> <b>54.32</b> <b>UV 650-SB</b> <b>38.71</b> <b>UV 650-233</b> <b>6.97</b>	Formula	PANTONE 2705 C <b>UV 650-TW</b> <b>94.78</b> <b>UV 650-127</b> <b>3.64</b> <b>UV 650-233</b> <b>1.58</b>	Formula
PANTONE 2715 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-TW</b> <b>34.46</b> <b>UV 650-127</b> <b>3.06</b> <b>UV 650-233</b> <b>2.48</b>	Formula	PANTONE 2725 C <b>UV 650-MX</b> <b>60.00</b> <b>UV 650-TW</b> <b>25.60</b> <b>UV 650-127</b> <b>10.08</b> <b>UV 650-233</b> <b>4.32</b>	Formula	PANTONE 2735 C <b>UV 650-127</b> <b>44.62</b> <b>UV 650-233</b> <b>34.33</b> <b>UV 650-MX</b> <b>21.05</b>	Formula	PANTONE 2745 C <b>UV 650-127</b> <b>50.39</b> <b>UV 650-MX</b> <b>42.52</b> <b>UV 650-233</b> <b>7.09</b>	Formula
PANTONE 2755 C <b>UV 650-127</b> <b>46.31</b> <b>UV 650-MX</b> <b>42.26</b> <b>UV 650-SB</b> <b>7.96</b> <b>UV 650-233</b> <b>3.47</b>	Formula	PANTONE 2765 C <b>UV 650-127</b> <b>41.35</b> <b>UV 650-MX</b> <b>30.77</b> <b>UV 650-SB</b> <b>27.88</b>	Formula	PANTONE 2706 C <b>UV 650-TW</b> <b>98.28</b> <b>UV 650-127</b> <b>0.98</b> <b>UV 650-233</b> <b>0.74</b>	Formula	PANTONE 2716 C <b>UV 650-TW</b> <b>94.93</b> <b>UV 650-127</b> <b>2.88</b> <b>UV 650-233</b> <b>2.19</b>	Formula

# UVivid 650

PANTONE 2726 C UV 650-MX      60.00 UV 650-TW      22.11 UV 650-127      10.04 UV 650-233      7.85	Formula	PANTONE 2736 C UV 650-MX      55.00 UV 650-233      20.00 UV 650-127      15.00 UV 650-165      10.00	Formula	PANTONE 2746 C UV 650-MX      60.00 UV 650-127      25.59 UV 650-233      14.41	Formula	PANTONE 2756 C UV 650-165      60.76 UV 650-233      27.89 UV 650-TW      6.89 UV 650-MX      4.46	Formula
PANTONE 2766 C UV 650-165      59.71 UV 650-233      22.44 UV 650-SB      17.85	Formula	PANTONE 2707 C UV 650-TW      98.21 UV 650-233      1.04 UV 650-127      0.75	Formula	PANTONE 2717 C UV 650-TW      96.63 UV 650-233      2.11 UV 650-127      1.26	Formula	PANTONE 2727 C UV 650-MX      60.00 UV 650-TW      31.77 UV 650-233      6.43 UV 650-127      1.80	Formula
PANTONE 2747 C UV 650-233      35.93 UV 650-127      33.49 UV 650-MX      28.17 UV 650-SB      2.41	Formula	PANTONE 2757 C UV 650-127      53.13 UV 650-233      30.04 UV 650-SB      8.69 UV 650-MX      8.14	Formula	PANTONE 2767 C UV 650-127      37.47 UV 650-SB      35.02 UV 650-MX      27.51	Formula	PANTONE 2708 C UV 650-TW      97.61 UV 650-233      1.38 UV 650-127      1.01	Formula
PANTONE 2718 C UV 650-MX      60.00 UV 650-TW      33.11 UV 650-233      4.14 UV 650-127      2.75	Formula	PANTONE 2728 C UV 650-MX      60.00 UV 650-233      15.66 UV 650-TW      13.30 UV 650-127      11.04	Formula	PANTONE 2738 C UV 650-233      52.94 UV 650-127      23.53 UV 650-MX      23.53	Formula	PANTONE 2748 C UV 650-MX      48.57 UV 650-127      33.37 UV 650-233      13.06 UV 650-SB      5.00	Formula

# UVivid 650

PANTONE 2758 C <b>UV 650-MX</b> 47.76 <b>UV 650-127</b> 29.50 <b>UV 650-SB</b> 12.09 <b>UV 650-233</b> 10.65	Formula	PANTONE 2768 C <b>UV 650-MX</b> 60.00 <b>UV 650-127</b> 30.33 <b>UV 650-TW</b> 9.67	Formula	PANTONE 277 C <b>UV 650-TW</b> 97.03 <b>UV 650-230</b> 1.83 <b>UV 650-127</b> 1.14	Formula	PANTONE 278 C <b>UV 650-TW</b> 95.08 <b>UV 650-230</b> 3.24 <b>UV 650-127</b> 1.68	Formula
PANTONE 279 C <b>UV 650-TW</b> 48.40 <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 8.27 <b>UV 650-127</b> 3.33	Formula	PANTONE 280 C <b>UV 650-MX</b> 40.00 <b>UV 650-127</b> 30.55 <b>UV 650-230</b> 23.60 <b>UV 650-SB</b> 5.85	Formula	PANTONE 281 C <b>UV 650-MX</b> 40.00 <b>UV 650-127</b> 27.08 <b>UV 650-230</b> 21.03 <b>UV 650-SB</b> 11.89	Formula	PANTONE 282 C <b>UV 650-230</b> 30.00 <b>UV 650-SB</b> 27.15 <b>UV 650-127</b> 22.84 <b>UV 650-MX</b> 20.01	Formula
PANTONE 283 C <b>UV 650-TW</b> 95.88 <b>UV 650-230</b> 3.13 <b>UV 650-127</b> 0.99	Formula	PANTONE 284 C <b>UV 650-TW</b> 92.36 <b>UV 650-233</b> 6.13 <b>UV 650-127</b> 1.51	Formula	PANTONE 285 C <b>UV 650-MX</b> 40.00 <b>UV 650-TW</b> 39.19 <b>UV 650-233</b> 17.19 <b>UV 650-127</b> 3.62	Formula	PANTONE 286 C <b>UV 650-233</b> 55.56 <b>UV 650-127</b> 11.11 <b>UV 650-MX</b> 33.33	Formula
PANTONE 287 C <b>UV 650-233</b> 42.91 <b>UV 650-MX</b> 39.99 <b>UV 650-127</b> 15.90 <b>UV 650-SB</b> 1.20	Formula	PANTONE 288 C <b>UV 650-MX</b> 39.99 <b>UV 650-233</b> 37.88 <b>UV 650-127</b> 16.01 <b>UV 650-SB</b> 6.12	Formula	PANTONE 289 C <b>UV 650-SB</b> 31.89 <b>UV 650-MX</b> 28.31 <b>UV 650-127</b> 26.33 <b>UV 650-233</b> 13.47	Formula	PANTONE 290 C <b>UV 650-TW</b> 98.24 <b>UV 650-230</b> 1.20 <b>UV 650-127</b> 0.56	Formula

# UVivid 650

PANTONE 291 C <b>UV 650-TW</b> <b>96.76</b> <b>UV 650-230</b> <b>2.29</b> <b>UV 650-127</b> <b>0.95</b>	Formula	PANTONE 292 C <b>UV 650-TW</b> <b>92.75</b> <b>UV 650-233</b> <b>6.16</b> <b>UV 650-127</b> <b>1.09</b>	Formula	PANTONE 293 C <b>UV 650-233</b> <b>86.36</b> <b>UV 650-TW</b> <b>13.64</b>	Formula	PANTONE 294 C <b>UV 650-233</b> <b>46.33</b> <b>UV 650-MX</b> <b>34.01</b> <b>UV 650-127</b> <b>10.75</b> <b>UV 650-SB</b> <b>8.91</b>	Formula
PANTONE 295 C <b>UV 650-233</b> <b>38.90</b> <b>UV 650-MX</b> <b>30.48</b> <b>UV 650-SB</b> <b>19.31</b> <b>UV 650-127</b> <b>11.31</b>	Formula	PANTONE 296 C <b>UV 650-SB</b> <b>55.72</b> <b>UV 650-127</b> <b>29.82</b> <b>UV 650-233</b> <b>8.24</b> <b>UV 650-MX</b> <b>6.22</b>	Formula	PANTONE 2905 C <b>UV 650-TW</b> <b>96.37</b> <b>UV 650-233</b> <b>3.63</b>	Formula	PANTONE 2915 C <b>UV 650-TW</b> <b>92.50</b> <b>UV 650-233</b> <b>7.50</b>	Formula
PANTONE 2925 C <b>UV 650-TW</b> <b>82.57</b> <b>UV 650-233</b> <b>17.43</b>	Formula	PANTONE 2935 C <b>UV 650-233</b> <b>50.00</b> <b>UV 650-TW</b> <b>50.00</b>	Formula	PANTONE 2945 C <b>UV 650-233</b> <b>72.45</b> <b>UV 650-MX</b> <b>15.25</b> <b>UV 650-TW</b> <b>12.30</b>	Formula	PANTONE 2955 C <b>UV 650-233</b> <b>85.47</b> <b>UV 650-SB</b> <b>13.31</b> <b>UV 650-TW</b> <b>1.22</b>	Formula
PANTONE 2965 C <b>UV 650-233</b> <b>63.09</b> <b>UV 650-SB</b> <b>36.91</b>	Formula	PANTONE 297 C <b>UV 650-TW</b> <b>95.31</b> <b>UV 650-233</b> <b>4.69</b>	Formula	PANTONE 298 C <b>UV 650-TW</b> <b>91.77</b> <b>UV 650-233</b> <b>8.23</b>	Formula	PANTONE 299 C <b>UV 650-TW</b> <b>54.07</b> <b>UV 650-MX</b> <b>33.80</b> <b>UV 650-233</b> <b>12.13</b>	Formula

# UVivid 650

PANTONE 300 C <b>UV 650-233</b> <b>35.48</b> <b>UV 650-TW</b> <b>32.26</b> <b>UV 650-MX</b> <b>32.26</b>	Formula	PANTONE 301 C <b>UV 650-233</b> <b>54.17</b> <b>UV 650-MX</b> <b>39.99</b> <b>UV 650-SB</b> <b>4.35</b> <b>UV 650-127</b> <b>1.49</b>	Formula	PANTONE 302 C <b>UV 650-233</b> <b>39.07</b> <b>UV 650-MX</b> <b>38.48</b> <b>UV 650-SB</b> <b>19.94</b> <b>UV 650-127</b> <b>2.51</b>	Formula	PANTONE 303 C <b>UV 650-SB</b> <b>39.60</b> <b>UV 650-233</b> <b>36.36</b> <b>UV 650-MX</b> <b>19.89</b> <b>UV 650-127</b> <b>4.15</b>	Formula
PANTONE 2975 C <b>UV 650-TW</b> <b>97.20</b> <b>UV 650-230</b> <b>2.80</b>	Formula	PANTONE 2985 C <b>UV 650-TW</b> <b>92.72</b> <b>UV 650-230</b> <b>7.28</b>	Formula	PANTONE 2995 C <b>UV 650-TW</b> <b>82.16</b> <b>UV 650-230</b> <b>17.84</b>	Formula	PANTONE 3005 C <b>UV 650-MX</b> <b>65.83</b> <b>UV 650-230</b> <b>32.63</b> <b>UV 650-127</b> <b>1.54</b>	Formula
PANTONE 3015 C <b>UV 650-230</b> <b>59.55</b> <b>UV 650-MX</b> <b>22.78</b> <b>UV 650-TW</b> <b>17.67</b>	Formula	PANTONE 3025 C <b>UV 650-230</b> <b>56.64</b> <b>UV 650-MX</b> <b>16.62</b> <b>UV 650-TW</b> <b>15.24</b> <b>UV 650-SB</b> <b>11.50</b>	Formula	PANTONE 3035 C <b>UV 650-230</b> <b>48.90</b> <b>UV 650-SB</b> <b>26.00</b> <b>UV 650-MX</b> <b>17.70</b> <b>UV 650-TW</b> <b>7.40</b>	Formula	PANTONE 304 C <b>UV 650-TW</b> <b>97.36</b> <b>UV 650-230</b> <b>2.64</b>	Formula
PANTONE 305 C <b>UV 650-TW</b> <b>94.31</b> <b>UV 650-230</b> <b>5.69</b>	Formula	PANTONE 306 C <b>UV 650-TW</b> <b>50.18</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-230</b> <b>9.82</b>	Formula	PANTONE 307 C <b>UV 650-230</b> <b>41.47</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-TW</b> <b>18.13</b> <b>UV 650-SB</b> <b>0.40</b>	Formula	PANTONE 308 C <b>UV 650-230</b> <b>49.12</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-SB</b> <b>10.88</b>	Formula



# UVivid 650

PANTONE 309 C <b>UV 650-SB</b> 35.10 <b>UV 650-230</b> 34.77 <b>UV 650-MX</b> 29.30 <b>UV 650-127</b> 0.83	Formula	PANTONE 310 C <b>UV 650-TW</b> 95.34 <b>UV 650-230</b> 4.66	Formula	PANTONE 311 C <b>UV 650-TW</b> 53.75 <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 6.25	Formula	PANTONE 312 C <b>UV 650-TW</b> 44.71 <b>UV 650-MX</b> 39.99 <b>UV 650-230</b> 12.98 <b>UV 650-325</b> 2.32	Formula
PANTONE 313 C <b>UV 650-TW</b> 51.29 <b>UV 650-MX</b> 25.64 <b>UV 650-230</b> 15.38 <b>UV 650-325</b> 7.69	Formula	PANTONE 314 C <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 30.91 <b>UV 650-TW</b> 21.46 <b>UV 650-325</b> 7.63	Formula	PANTONE 315 C <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 35.41 <b>UV 650-TW</b> 9.51 <b>UV 650-325</b> 8.99 <b>UV 650-SB</b> 6.09	Formula	PANTONE 316 C <b>UV 650-MX</b> 40.00 <b>UV 650-SB</b> 29.89 <b>UV 650-230</b> 26.34 <b>UV 650-325</b> 3.77	Formula
PANTONE 3105 C <b>UV 650-TW</b> 56.33 <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 3.67	Formula	PANTONE 3115 C <b>UV 650-TW</b> 52.14 <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 6.19 <b>UV 650-325</b> 1.67	Formula	PANTONE 3125 C <b>UV 650-TW</b> 44.35 <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 11.28 <b>UV 650-325</b> 4.37	Formula	PANTONE 3135 C <b>UV 650-230</b> 20.50 <b>UV 650-325</b> 11.50 <b>UV 650-TW</b> 8.00 <b>UV 650-MX</b> 60.00	Formula
PANTONE 3145 C <b>UV 650-MX</b> 40.00 <b>UV 650-230</b> 30.08 <b>UV 650-TW</b> 14.86 <b>UV 650-325</b> 13.26 <b>UV 650-SB</b> 1.8	Formula	PANTONE 3155 C <b>UV 650-MX</b> 40.01 <b>UV 650-230</b> 32.61 <b>UV 650-325</b> 14.51 <b>UV 650-SB</b> 8.43 <b>UV 650-TW</b> 4.44	Formula	PANTONE 3165 C <b>UV 650-MX</b> 35.71 <b>UV 650-230</b> 30.30 <b>UV 650-SB</b> 21.35 <b>UV 650-325</b> 12.64	Formula	PANTONE 317 C <b>UV 650-TW</b> 98.43 <b>UV 650-230</b> 1.57	Formula

# UVivid 650

<b>PANTONE</b> <b>318 C</b> <b>UV 650-TW</b> <b>97.36</b> <b>UV 650-230</b> <b>2.64</b>	Formula	<b>PANTONE</b> <b>319 C</b> <b>UV 650-TW</b> <b>53.93</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-230</b> <b>4.09</b> <b>UV 650-325</b> <b>1.98</b>	Formula	<b>PANTONE</b> <b>320 C</b> <b>UV 650-TW</b> <b>45.46</b> <b>UV 650-MX</b> <b>20.66</b> <b>UV 650-325</b> <b>20.66</b> <b>UV 650-230</b> <b>13.22</b>	Formula	<b>PANTONE</b> <b>321 C</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-TW</b> <b>22.04</b> <b>UV 650-230</b> <b>20.36</b> <b>UV 650-325</b> <b>17.60</b>	Formula
<b>PANTONE</b> <b>322 C</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-230</b> <b>20.73</b> <b>UV 650-325</b> <b>17.58</b> <b>UV 650-TW</b> <b>16.21</b> <b>UV 650-SB</b> <b>5.48</b>	Formula	<b>PANTONE</b> <b>323 C</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-230</b> <b>20.19</b> <b>UV 650-325</b> <b>16.90</b> <b>UV 650-SB</b> <b>15.88</b> <b>UV 650-TW</b> <b>7.03</b>	Formula	<b>PANTONE</b> <b>324 C</b> <b>UV 650-TW</b> <b>97.71</b> <b>UV 650-230</b> <b>1.86</b> <b>UV 650-325</b> <b>0.43</b>	Formula	<b>PANTONE</b> <b>325 C</b> <b>UV 650-TW</b> <b>94.43</b> <b>UV 650-230</b> <b>3.01</b> <b>UV 650-325</b> <b>2.43</b> <b>UV 650-SB</b> <b>0.13</b>	Formula
<b>PANTONE</b> <b>326 C</b> <b>UV 650-TW</b> <b>79.44</b> <b>UV 650-325</b> <b>13.43</b> <b>UV 650-230</b> <b>6.75</b> <b>UV 650-SB</b> <b>0.38</b>	Formula	<b>PANTONE</b> <b>327 C</b> <b>UV 650-325</b> <b>76.93</b> <b>UV 650-230</b> <b>15.38</b> <b>UV 650-TW</b> <b>7.69</b>	Formula	<b>PANTONE</b> <b>328 C</b> <b>UV 650-325</b> <b>50.83</b> <b>UV 650-TW</b> <b>22.92</b> <b>UV 650-230</b> <b>22.32</b> <b>UV 650-SB</b> <b>3.93</b>	Formula	<b>PANTONE</b> <b>329 C</b> <b>UV 650-325</b> <b>45.64</b> <b>UV 650-TW</b> <b>26.34</b> <b>UV 650-230</b> <b>20.69</b> <b>UV 650-SB</b> <b>7.33</b>	Formula
<b>PANTONE</b> <b>330 C</b> <b>UV 650-SB</b> <b>25.26</b> <b>UV 650-325</b> <b>22.29</b> <b>UV 650-TW</b> <b>21.98</b> <b>UV 650-MX</b> <b>18.44</b> <b>UV 650-230</b> <b>12.03</b>	Formula	<b>PANTONE</b> <b>3242 C</b> <b>UV 650-TW</b> <b>61.24</b> <b>UV 650-MX</b> <b>34.61</b> <b>UV 650-325</b> <b>2.47</b> <b>UV 650-230</b> <b>1.68</b>	Formula	<b>PANTONE</b> <b>3252 C</b> <b>UV 650-TW</b> <b>53.91</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-325</b> <b>3.78</b> <b>UV 650-230</b> <b>2.31</b>	Formula	<b>PANTONE</b> <b>3262 C</b> <b>UV 650-TW</b> <b>44.08</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-325</b> <b>11.02</b> <b>UV 650-230</b> <b>4.90</b>	Formula

# UVivid 650

PANTONE 3272 C	Formula
UV 650-TW	44.64
UV 650-325	31.25
UV 650-MX	17.86
UV 650-230	6.25

PANTONE 3282 C	Formula
UV 650-MX	40.00
UV 650-325	29.16
UV 650-TW	14.63
UV 650-230	13.14
UV 650-SB	3.07

PANTONE 3292 C	Formula
UV 650-MX	40.00
UV 650-325	26.01
UV 650-SB	19.04
UV 650-230	12.27
UV 650-TW	2.68

PANTONE 3302 C	Formula
UV 650-MX	40.00
UV 650-SB	34.01
UV 650-325	16.51
UV 650-230	9.48

PANTONE 3245 C	Formula
UV 650-TW	95.18
UV 650-325	3.22
UV 650-230	1.60

PANTONE 3255 C	Formula
UV 650-TW	52.34
UV 650-MX	39.99
UV 650-325	5.59
UV 650-230	2.08

PANTONE 3265 C	Formula
UV 650-TW	43.47
UV 650-MX	40.00
UV 650-325	13.25
UV 650-230	3.28

PANTONE 3275 C	Formula
UV 650-325	24.27
UV 650-MX	48.55
UV 650-TW	24.27
UV 650-230	2.91

PANTONE 3285 C	Formula
UV 650-MX	39.99
UV 650-TW	25.36
UV 650-325	25.37
UV 650-230	6.61
UV 650-SB	2.67

PANTONE 3295 C	Formula
UV 650-MX	40.00
UV 650-325	35.96
UV 650-SB	9.45
UV 650-230	8.64
UV 650-TW	5.95

PANTONE 3305 C	Formula
UV 650-MX	40.00
UV 650-SB	33.67
UV 650-325	20.58
UV 650-230	5.75

PANTONE 3248 C	Formula
UV 650-TW	95.62
UV 650-325	2.60
UV 650-233	1.57
UV 650-064	0.21

PANTONE 3258 C	Formula
UV 650-TW	53.14
UV 650-MX	40.01
UV 650-325	3.82
UV 650-233	2.39
UV 650-064	0.64

PANTONE 3268 C	Formula
UV 650-MX	40.00
UV 650-TW	39.88
UV 650-325	13.60
UV 650-233	5.03
UV 650-064	1.49

PANTONE 3278 C	Formula
UV 650-325	34.32
UV 650-233	11.35
UV 650-064	6.42
UV 650-MX	47.91

PANTONE 3288 C	Formula
UV 650-MX	39.99
UV 650-TW	25.07
UV 650-233	15.30
UV 650-325	12.77
UV 650-064	6.87

# UVivid 650

PANTONE 3298 C	Formula
UV 650-MX	40.00
UV 650-233	22.82
UV 650-TW	22.64
UV 650-064	11.46
UV 650-SB	3.08

PANTONE 3308 C	Formula
UV 650-MX	40.00
UV 650-SB	30.26
UV 650-233	17.53
UV 650-064	8.55
UV 650-TW	3.66

PANTONE 331 C	Formula
UV 650-TW	97.93
UV 650-325	1.35
UV 650-230	0.72

PANTONE 332 C	Formula
UV 650-TW	97.07
UV 650-325	2.20
UV 650-230	0.73

PANTONE 333 C	Formula
UV 650-TW	90.82
UV 650-325	8.17
UV 650-230	1.01

PANTONE 334 C	Formula
UV 650-325	42.03
UV 650-MX	30.01
UV 650-TW	22.86
UV 650-230	3.52
UV 650-SB	1.58

PANTONE 335 C	Formula
UV 650-325	40.20
UV 650-MX	30.01
UV 650-TW	17.72
UV 650-SB	8.83
UV 650-230	3.24

PANTONE 336 C	Formula
UV 650-325	39.14
UV 650-MX	30.00
UV 650-SB	21.04
UV 650-TW	6.51
UV 650-230	3.31

PANTONE 337 C	Formula
UV 650-TW	96.47
UV 650-325	1.85
UV 650-233	1.20
UV 650-064	0.48

PANTONE 338 C	Formula
UV 650-TW	93.57
UV 650-325	3.34
UV 650-233	1.89
UV 650-064	1.20

PANTONE 339 C	Formula
UV 650-TW	52.00
UV 650-MX	30.01
UV 650-325	11.49
UV 650-233	3.86
UV 650-064	2.64

PANTONE 340 C	Formula
UV 650-325	37.98
UV 650-TW	8.77
UV 650-064	8.31
UV 650-233	8.21
UV 650-MX	36.73

PANTONE 341 C	Formula
UV 650-TW	48.42
UV 650-233	18.93
UV 650-325	17.98
UV 650-064	14.67

PANTONE 342 C	Formula
UV 650-MX	30.00
UV 650-TW	27.47
UV 650-233	21.47
UV 650-064	15.82
UV 650-SB	5.24

PANTONE 343 C	Formula
UV 650-MX	30.01
UV 650-TW	20.36
UV 650-233	18.08
UV 650-SB	17.72
UV 650-064	13.83

PANTONE 3375 C	Formula
UV 650-TW	93.80
UV 650-325	6.20

# UVivid 650

PANTONE 3385 C	Formula
<b>UV 650-TW</b>	<b>88.54</b>
<b>UV 650-325</b>	<b>11.04</b>
<b>UV 650-064</b>	<b>0.42</b>

PANTONE 3395 C	Formula
<b>UV 650-TW</b>	<b>43.68</b>
<b>UV 650-MX</b>	<b>30.00</b>
<b>UV 650-325</b>	<b>24.79</b>
<b>UV 650-064</b>	<b>1.53</b>

PANTONE 3405 C	Formula
<b>UV 650-325</b>	<b>62.25</b>
<b>UV 650-MX</b>	<b>33.11</b>
<b>UV 650-064</b>	<b>4.64</b>

PANTONE 3415 C	Formula
<b>UV 650-325</b>	<b>53.06</b>
<b>UV 650-MX</b>	<b>23.01</b>
<b>UV 650-SB</b>	<b>13.44</b>
<b>UV 650-TW</b>	<b>7.43</b>
<b>UV 650-064</b>	<b>3.06</b>

PANTONE 3425 C	Formula
<b>UV 650-325</b>	<b>42.93</b>
<b>UV 650-MX</b>	<b>29.99</b>
<b>UV 650-SB</b>	<b>24.84</b>
<b>UV 650-064</b>	<b>2.24</b>

PANTONE 3435 C	Formula
<b>UV 650-325</b>	<b>48.83</b>
<b>UV 650-SB</b>	<b>41.50</b>
<b>UV 650-TW</b>	<b>7.21</b>
<b>UV 650-064</b>	<b>2.46</b>

PANTONE 344 C	Formula
<b>UV 650-TW</b>	<b>95.50</b>
<b>UV 650-325</b>	<b>3.52</b>
<b>UV 650-066</b>	<b>0.98</b>

PANTONE 345 C	Formula
<b>UV 650-TW</b>	<b>93.51</b>
<b>UV 650-325</b>	<b>4.72</b>
<b>UV 650-066</b>	<b>1.77</b>

PANTONE 346 C	Formula
<b>UV 650-TW</b>	<b>88.29</b>
<b>UV 650-325</b>	<b>7.75</b>
<b>UV 650-066</b>	<b>3.96</b>

PANTONE 347 C	Formula
<b>UV 650-325</b>	<b>57.45</b>
<b>UV 650-066</b>	<b>33.07</b>
<b>UV 650-MX</b>	<b>9.48</b>

PANTONE 348 C	Formula
<b>UV 650-325</b>	<b>51.25</b>
<b>UV 650-066</b>	<b>27.01</b>
<b>UV 650-TW</b>	<b>17.72</b>
<b>UV 650-SB</b>	<b>4.02</b>

PANTONE 349 C	Formula
<b>UV 650-325</b>	<b>42.04</b>
<b>UV 650-066</b>	<b>26.85</b>
<b>UV 650-TW</b>	<b>16.65</b>
<b>UV 650-SB</b>	<b>14.46</b>

PANTONE 350 C	Formula
<b>UV 650-SB</b>	<b>31.13</b>
<b>UV 650-066</b>	<b>25.72</b>
<b>UV 650-325</b>	<b>23.04</b>
<b>UV 650-TW</b>	<b>20.11</b>

PANTONE 351 C	Formula
<b>UV 650-TW</b>	<b>95.76</b>
<b>UV 650-325</b>	<b>3.51</b>
<b>UV 650-064</b>	<b>0.73</b>

PANTONE 352 C	Formula
<b>UV 650-TW</b>	<b>94.19</b>
<b>UV 650-325</b>	<b>4.72</b>
<b>UV 650-064</b>	<b>1.09</b>

PANTONE 353 C	Formula
<b>UV 650-TW</b>	<b>81.07</b>
<b>UV 650-MX</b>	<b>11.87</b>
<b>UV 650-325</b>	<b>5.74</b>
<b>UV 650-064</b>	<b>1.32</b>

# UVivid 650

PANTONE 354 C	Formula
UV 650-325	47.92
UV 650-064	11.66
UV 650-MX	40.42

PANTONE 355 C	Formula
UV 650-325	41.55
UV 650-MX	34.07
UV 650-064	12.46
UV 650-TW	9.19
UV 650-SB	2.73

PANTONE 356 C	Formula
UV 650-325	38.47
UV 650-MX	31.07
UV 650-064	12.17
UV 650-SB	9.92
UV 650-TW	8.37

PANTONE 357 C	Formula
UV 650-325	27.35
UV 650-SB	27.15
UV 650-MX	17.83
UV 650-TW	16.16
UV 650-064	11.51

PANTONE 358 C	Formula
UV 650-TW	87.19
UV 650-066	8.69
UV 650-325	3.58
UV 650-064	0.54

PANTONE 359 C	Formula
UV 650-TW	84.80
UV 650-066	10.11
UV 650-325	4.30
UV 650-064	0.79

PANTONE 360 C	Formula
UV 650-066	44.22
UV 650-MX	40.00
UV 650-325	15.78

PANTONE 361 C	Formula
UV 650-TW	26.67
UV 650-325	22.86
UV 650-MX	22.86
UV 650-064	15.24
UV 650-066	12.37

PANTONE 362 C	Formula
UV 650-TW	51.19
UV 650-064	27.21
UV 650-325	17.31
UV 650-SB	4.29

PANTONE 363 C	Formula
UV 650-TW	47.54
UV 650-064	28.10
UV 650-325	17.12
UV 650-SB	7.24

PANTONE 364 C	Formula
UV 650-TW	38.38
UV 650-064	30.65
UV 650-325	17.53
UV 650-SB	13.44

PANTONE 365 C	Formula
UV 650-TW	94.50
UV 650-064	3.47
UV 650-325	1.73
UV 650-SB	0.30

PANTONE 366 C	Formula
UV 650-TW	54.66
UV 650-MX	40.00
UV 650-064	3.34
UV 650-325	2.00

PANTONE 367 C	Formula
UV 650-TW	86.56
UV 650-064	9.54
UV 650-325	3.90

PANTONE 368 C	Formula
UV 650-TW	37.27
UV 650-064	24.84
UV 650-230	3.11
UV 650-MX	34.78

PANTONE 369 C	Formula
UV 650-MX	40.01
UV 650-064	25.01
UV 650-TW	19.99
UV 650-325	11.55
UV 650-SB	3.44

# UVivid 650

<b>PANTONE</b> <b>370 C</b> <b>UV 650-066</b> <b>67.14</b> <b>UV 650-325</b> <b>15.07</b> <b>UV 650-MX</b> <b>12.70</b> <b>UV 650-SB</b> <b>5.09</b>	Formula	<b>PANTONE</b> <b>371 C</b> <b>UV 650-066</b> <b>62.55</b> <b>UV 650-SB</b> <b>18.29</b> <b>UV 650-325</b> <b>10.57</b> <b>UV 650-TW</b> <b>8.59</b>	Formula	<b>PANTONE</b> <b>372 C</b> <b>UV 650-TW</b> <b>95.68</b> <b>UV 650-064</b> <b>3.34</b> <b>UV 650-325</b> <b>0.98</b>	Formula	<b>PANTONE</b> <b>373 C</b> <b>UV 650-TW</b> <b>94.01</b> <b>UV 650-064</b> <b>4.75</b> <b>UV 650-325</b> <b>1.24</b>	Formula
<b>PANTONE</b> <b>374 C</b> <b>UV 650-TW</b> <b>52.57</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-064</b> <b>5.83</b> <b>UV 650-325</b> <b>1.60</b>	Formula	<b>PANTONE</b> <b>375 C</b> <b>UV 650-TW</b> <b>27.78</b> <b>UV 650-064</b> <b>22.22</b> <b>UV 650-325</b> <b>5.56</b> <b>UV 650-MX</b> <b>44.44</b>	Formula	<b>PANTONE</b> <b>376 C</b> <b>UV 650-TW</b> <b>52.57</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-064</b> <b>5.83</b> <b>UV 650-325</b> <b>1.60</b>	Formula	<b>PANTONE</b> <b>377 C</b> <b>UV 650-066</b> <b>62.93</b> <b>UV 650-SB</b> <b>18.32</b> <b>UV 650-MX</b> <b>10.67</b> <b>UV 650-325</b> <b>8.08</b>	Formula
<b>PANTONE</b> <b>378 C</b> <b>UV 650-MX</b> <b>32.27</b> <b>UV 650-066</b> <b>26.56</b> <b>UV 650-SB</b> <b>20.87</b> <b>UV 650-TW</b> <b>15.28</b> <b>UV 650-325</b> <b>5.02</b>	Formula	<b>PANTONE</b> <b>379 C</b> <b>UV 650-TW</b> <b>53.30</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-064</b> <b>5.99</b> <b>UV 650-325</b> <b>0.71</b>	Formula	<b>PANTONE</b> <b>380 C</b> <b>UV 650-TW</b> <b>48.04</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-064</b> <b>10.90</b> <b>UV 650-325</b> <b>1.06</b>	Formula	<b>PANTONE</b> <b>381 C</b> <b>UV 650-TW</b> <b>44.59</b> <b>UV 650-MX</b> <b>33.23</b> <b>UV 650-064</b> <b>20.44</b> <b>UV 650-325</b> <b>1.74</b>	Formula
<b>PANTONE</b> <b>382 C</b> <b>UV 650-064</b> <b>18.88</b> <b>UV 650-325</b> <b>1.14</b> <b>UV 650-230</b> <b>0.50</b> <b>UV 650-MX</b> <b>79.48</b>	Formula	<b>PANTONE</b> <b>383 C</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-064</b> <b>31.96</b> <b>UV 650-TW</b> <b>24.00</b> <b>UV 650-SB</b> <b>2.74</b> <b>UV 650-230</b> <b>1.3</b>	Formula	<b>PANTONE</b> <b>384 C</b> <b>UV 650-MX</b> <b>39.99</b> <b>UV 650-064</b> <b>33.18</b> <b>UV 650-TW</b> <b>16.52</b> <b>UV 650-SB</b> <b>7.85</b> <b>UV 650-325</b> <b>2.46</b>	Formula	<b>PANTONE</b> <b>385 C</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-064</b> <b>23.41</b> <b>UV 650-TW</b> <b>18.28</b> <b>UV 650-SB</b> <b>16.96</b> <b>UV 650-325</b> <b>1.35</b>	Formula

# UVivid 650

PANTONE 386 C	Formula
UV 650-TW	53.08
UV 650-MX	40.00
UV 650-064	6.45
UV 650-325	0.47

PANTONE 387 C	Formula
UV 650-TW	44.45
UV 650-MX	40.00
UV 650-064	14.71
UV 650-325	0.84

PANTONE 388 C	Formula
UV 650-MX	40.00
UV 650-TW	39.78
UV 650-064	19.12
UV 650-325	1.10

PANTONE 389 C	Formula
UV 650-MX	42.43
UV 650-064	30.30
UV 650-TW	25.25
UV 650-325	2.02

PANTONE 390 C	Formula
UV 650-MX	40.01
UV 650-064	38.79
UV 650-TW	17.16
UV 650-325	2.03
UV 650-SB	2.01

PANTONE 391 C	Formula
UV 650-MX	38.97
UV 650-064	35.19
UV 650-TW	16.91
UV 650-SB	7.42
UV 650-325	1.51

PANTONE 392 C	Formula
UV 650-064	35.87
UV 650-MX	32.12
UV 650-TW	17.13
UV 650-SB	13.46
UV 650-325	1.42

PANTONE 393 C	Formula
UV 650-TW	93.51
UV 650-064	6.18
UV 650-325	0.31

PANTONE 394 C	Formula
UV 650-TW	46.26
UV 650-MX	40.00
UV 650-064	13.27
UV 650-325	0.47

PANTONE 395 C	Formula
UV 650-MX	39.99
UV 650-TW	39.30
UV 650-064	19.96
UV 650-325	0.75

PANTONE 396 C	Formula
UV 650-MX	42.11
UV 650-064	31.58
UV 650-TW	25.26
UV 650-325	1.05

PANTONE 397 C	Formula
UV 650-064	43.07
UV 650-MX	40.00
UV 650-TW	13.21
UV 650-SB	2.59
UV 650-325	1.13

PANTONE 398 C	Formula
UV 650-064	50.19
UV 650-MX	28.33
UV 650-TW	15.21
UV 650-SB	5.26
UV 650-325	1.01

PANTONE 399 C	Formula
UV 650-064	42.10
UV 650-MX	40.00
UV 650-TW	8.64
UV 650-SB	8.47
UV 650-325	0.79

PANTONE 3935 C	Formula
UV 650-TW	53.51
UV 650-MX	40.01
UV 650-064	6.35
UV 650-325	0.13

PANTONE 3945 C	Formula
UV 650-MX	40.01
UV 650-TW	34.79
UV 650-064	24.77
UV 650-325	0.43



# UVivid 650

PANTONE 3955 C	Formula
UV 650-064	44.89
UV 650-MX	40.00
UV 650-TW	14.34
UV 650-325	0.77

PANTONE 3965 C	Formula
UV 650-MX	60.24
UV 650-064	30.12
UV 650-066	9.04
UV 650-325	0.60

PANTONE 3975 C	Formula
UV 650-064	40.13
UV 650-MX	40.01
UV 650-TW	14.74
UV 650-SB	4.84
UV 650-325	0.28

PANTONE 3985 C	Formula
UV 650-MX	40.00
UV 650-064	35.14
UV 650-TW	13.84
UV 650-SB	11.02

PANTONE 3995 C	Formula
UV 650-MX	40.00
UV 650-064	26.14
UV 650-SB	26.07
UV 650-TW	7.79

PANTONE 400 C	Formula
UV 650-TW	95.98
UV 650-SB	4.02

PANTONE 401 C	Formula
UV 650-TW	93.08
UV 650-SB	6.47
UV 650-114	0.45

PANTONE 402 C	Formula
UV 650-TW	90.11
UV 650-SB	9.06
UV 650-114	0.83

PANTONE 403 C	Formula
UV 650-TW	80.93
UV 650-SB	15.64
UV 650-114	2.48
UV 650-064	0.95

PANTONE 404 C	Formula
UV 650-TW	43.33
UV 650-MX	29.04
UV 650-SB	24.13
UV 650-114	3.50

PANTONE 405 C	Formula
UV 650-MX	34.15
UV 650-TW	31.30
UV 650-SB	30.44
UV 650-114	4.11

PANTONE 406 C	Formula
UV 650-TW	96.66
UV 650-SB	3.21
UV 650-121	0.13

PANTONE 407 C	Formula
UV 650-TW	92.92
UV 650-SB	6.32
UV 650-121	0.76

PANTONE 408 C	Formula
UV 650-TW	65.94
UV 650-MX	22.46
UV 650-SB	10.29
UV 650-121	1.31

PANTONE 409 C	Formula
UV 650-TW	78.67
UV 650-SB	16.22
UV 650-114	2.66
UV 650-121	1.32
UV 650-064	1.13

PANTONE 410 C	Formula
UV 650-MX	40.00
UV 650-TW	35.69
UV 650-SB	21.26
UV 650-121	2.60
UV 650-114	0.45

# UVivid 650

PANTONE 411 C <b>UV 650-MX</b> <b>40.01</b> <b>UV 650-SB</b> <b>32.08</b> <b>UV 650-TW</b> <b>23.19</b> <b>UV 650-121</b> <b>3.88</b> <b>UV 650-114</b> <b>0.84</b>	Formula	PANTONE 412 C <b>UV 650-SB</b> <b>57.50</b> <b>UV 650-MX</b> <b>35.66</b> <b>UV 650-121</b> <b>4.00</b> <b>UV 650-114</b> <b>2.84</b>	Formula	PANTONE 413 C <b>UV 650-TW</b> <b>95.79</b> <b>UV 650-SB</b> <b>4.01</b> <b>UV 650-325</b> <b>0.20</b>	Formula	PANTONE 414 C <b>UV 650-TW</b> <b>92.51</b> <b>UV 650-SB</b> <b>7.09</b> <b>UV 650-066</b> <b>0.20</b> <b>UV 650-325</b> <b>0.20</b>	Formula
PANTONE 415 C <b>UV 650-TW</b> <b>86.77</b> <b>UV 650-SB</b> <b>11.75</b> <b>UV 650-066</b> <b>1.34</b> <b>UV 650-325</b> <b>0.14</b>	Formula	PANTONE 416 C <b>UV 650-TW</b> <b>43.30</b> <b>UV 650-MX</b> <b>34.09</b> <b>UV 650-SB</b> <b>16.16</b> <b>UV 650-066</b> <b>5.68</b> <b>UV 650-325</b> <b>0.77</b>	Formula	PANTONE 417 C <b>UV 650-TW</b> <b>57.35</b> <b>UV 650-SB</b> <b>28.45</b> <b>UV 650-066</b> <b>9.20</b> <b>UV 650-MX</b> <b>5.00</b>	Formula	PANTONE 418 C <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-SB</b> <b>36.21</b> <b>UV 650-TW</b> <b>21.86</b> <b>UV 650-325</b> <b>1.93</b>	Formula
PANTONE 419 C <b>UV 650-SB</b> <b>99.00</b> <b>UV 650-325</b> <b>1.00</b>	Formula	PANTONE 420 C <b>UV 650-TW</b> <b>96.61</b> <b>UV 650-165</b> <b>1.53</b> <b>UV 650-325</b> <b>1.26</b> <b>UV 650-SB</b> <b>0.60</b>	Formula	PANTONE 421 C <b>UV 650-TW</b> <b>93.20</b> <b>UV 650-SB</b> <b>3.48</b> <b>UV 650-165</b> <b>1.81</b> <b>UV 650-325</b> <b>1.51</b>	Formula	PANTONE 422 C <b>UV 650-TW</b> <b>89.47</b> <b>UV 650-SB</b> <b>5.70</b> <b>UV 650-165</b> <b>2.71</b> <b>UV 650-325</b> <b>2.12</b>	Formula
PANTONE 423 C <b>UV 650-TW</b> <b>58.52</b> <b>UV 650-SB</b> <b>13.31</b> <b>UV 650-325</b> <b>0.32</b> <b>UV 650-MX</b> <b>27.85</b>	Formula	PANTONE 424 C <b>UV 650-TW</b> <b>71.56</b> <b>UV 650-SB</b> <b>21.26</b> <b>UV 650-165</b> <b>4.21</b> <b>UV 650-325</b> <b>2.97</b>	Formula	PANTONE 425 C <b>UV 650-TW</b> <b>53.81</b> <b>UV 650-SB</b> <b>33.84</b> <b>UV 650-165</b> <b>7.41</b> <b>UV 650-325</b> <b>4.94</b>	Formula	PANTONE 426 C <b>UV 650-SB</b> <b>74.90</b> <b>UV 650-165</b> <b>12.31</b> <b>UV 650-MX</b> <b>11.10</b> <b>UV 650-325</b> <b>1.69</b>	Formula

# UVivid 650

PANTONE 427 C <b>UV 650-TW</b> <b>98.00</b> <b>UV 650-SB</b> <b>2.00</b>	Formula	PANTONE 428 C <b>UV 650-TW</b> <b>97.50</b> <b>UV 650-SB</b> <b>1.50</b> <b>UV 650-230</b> <b>1.00</b>	Formula	PANTONE 429 C <b>UV 650-TW</b> <b>94.50</b> <b>UV 650-SB</b> <b>3.50</b> <b>UV 650-230</b> <b>2.00</b>	Formula	PANTONE 430 C <b>UV 650-TW</b> <b>83.57</b> <b>UV 650-SB</b> <b>15.24</b> <b>UV 650-114</b> <b>0.64</b> <b>UV 650-230</b> <b>0.55</b>	Formula
PANTONE 431 C <b>UV 650-TW</b> <b>85.21</b> <b>UV 650-SB</b> <b>12.48</b> <b>UV 650-230</b> <b>2.31</b>	Formula	PANTONE 432 C <b>UV 650-SB</b> <b>52.88</b> <b>UV 650-TW</b> <b>33.94</b> <b>UV 650-230</b> <b>13.18</b>	Formula	PANTONE 433 C <b>UV 650-SB</b> <b>100.00</b>	Formula	PANTONE 434 C <b>UV 650-TW</b> <b>96.59</b> <b>UV 650-165</b> <b>2.08</b> <b>UV 650-325</b> <b>1.06</b> <b>UV 650-114</b> <b>0.27</b>	Formula
PANTONE 435 C <b>UV 650-TW</b> <b>93.72</b> <b>UV 650-165</b> <b>3.38</b> <b>UV 650-325</b> <b>1.90</b> <b>UV 650-114</b> <b>1.00</b>	Formula	PANTONE 436 C <b>UV 650-TW</b> <b>88.54</b> <b>UV 650-165</b> <b>5.70</b> <b>UV 650-325</b> <b>3.36</b> <b>UV 650-114</b> <b>2.40</b>	Formula	PANTONE 437 C <b>UV 650-TW</b> <b>60.38</b> <b>UV 650-165</b> <b>14.79</b> <b>UV 650-114</b> <b>13.89</b> <b>UV 650-325</b> <b>10.94</b>	Formula	PANTONE 438 C <b>UV 650-TW</b> <b>30.54</b> <b>UV 650-165</b> <b>25.52</b> <b>UV 650-114</b> <b>22.59</b> <b>UV 650-325</b> <b>21.35</b>	Formula
PANTONE 439 C <b>UV 650-325</b> <b>30.23</b> <b>UV 650-165</b> <b>29.38</b> <b>UV 650-114</b> <b>26.11</b> <b>UV 650-TW</b> <b>14.28</b>	Formula	PANTONE 440 C <b>UV 650-SB</b> <b>65.29</b> <b>UV 650-114</b> <b>17.91</b> <b>UV 650-TW</b> <b>15.22</b> <b>UV 650-325</b> <b>1.58</b>	Formula	PANTONE 441 C <b>UV 650-TW</b> <b>95.49</b> <b>UV 650-325</b> <b>1.63</b> <b>UV 650-165</b> <b>1.55</b> <b>UV 650-SB</b> <b>1.33</b>	Formula	PANTONE 442 C <b>UV 650-TW</b> <b>90.89</b> <b>UV 650-325</b> <b>4.23</b> <b>UV 650-165</b> <b>3.59</b> <b>UV 650-114</b> <b>1.29</b>	Formula

# UVivid 650

PANTONE 443 C <b>UV 650-TW</b> <b>85.36</b> <b>UV 650-325</b> <b>6.71</b> <b>UV 650-165</b> <b>5.61</b> <b>UV 650-114</b> <b>2.32</b>	Formula	PANTONE 444 C <b>UV 650-TW</b> <b>75.96</b> <b>UV 650-325</b> <b>11.09</b> <b>UV 650-165</b> <b>6.71</b> <b>UV 650-114</b> <b>6.24</b>	Formula	PANTONE 445 C <b>UV 650-TW</b> <b>50.10</b> <b>UV 650-SB</b> <b>49.90</b>	Formula	PANTONE 446 C <b>UV 650-325</b> <b>35.77</b> <b>UV 650-165</b> <b>25.40</b> <b>UV 650-TW</b> <b>20.79</b> <b>UV 650-114</b> <b>18.04</b>	Formula
PANTONE 447 C <b>UV 650-SB</b> <b>57.25</b> <b>UV 650-TW</b> <b>23.71</b> <b>UV 650-114</b> <b>9.76</b> <b>UV 650-325</b> <b>9.28</b>	Formula	PANTONE WARM GRAY 1 C <b>UV 650-TW</b> <b>98.40</b> <b>UV 650-SB</b> <b>1.60</b>	Formula	PANTONE WARM GRAY 2 C <b>UV 650-TW</b> <b>97.20</b> <b>UV 650-SB</b> <b>2.80</b>	Formula	PANTONE WARM GRAY 3 C <b>UV 650-TW</b> <b>95.65</b> <b>UV 650-SB</b> <b>3.68</b> <b>UV 650-114</b> <b>0.67</b>	Formula
PANTONE WARM GRAY 4 C <b>UV 650-TW</b> <b>93.58</b> <b>UV 650-SB</b> <b>5.88</b> <b>UV 650-114</b> <b>0.54</b>	Formula	PANTONE WARM GRAY 5 C <b>UV 650-TW</b> <b>91.03</b> <b>UV 650-SB</b> <b>7.96</b> <b>UV 650-114</b> <b>1.01</b>	Formula	PANTONE WARM GRAY 6 C <b>UV 650-TW</b> <b>89.65</b> <b>UV 650-SB</b> <b>8.96</b> <b>UV 650-114</b> <b>1.39</b>	Formula	PANTONE WARM GRAY 7 C <b>UV 650-TW</b> <b>88.75</b> <b>UV 650-SB</b> <b>9.25</b> <b>UV 650-114</b> <b>2.00</b>	Formula
PANTONE WARM GRAY 8 C <b>UV 650-TW</b> <b>81.61</b> <b>UV 650-SB</b> <b>15.43</b> <b>UV 650-114</b> <b>2.96</b>	Formula	PANTONE WARM GRAY 9 C <b>UV 650-TW</b> <b>75.99</b> <b>UV 650-SB</b> <b>19.89</b> <b>UV 650-114</b> <b>4.12</b>	Formula	PANTONE WARM GRAY 10 C <b>UV 650-TW</b> <b>68.40</b> <b>UV 650-SB</b> <b>25.73</b> <b>UV 650-114</b> <b>5.87</b>	Formula	PANTONE WARM GRAY 11 C <b>UV 650-TW</b> <b>62.81</b> <b>UV 650-SB</b> <b>28.10</b> <b>UV 650-114</b> <b>8.26</b> <b>UV 650-064</b> <b>0.83</b>	Formula

# UVivid 650

PANTONE COOL GRAY 1 C <b>UV 650-TW 53.20</b> <b>UV 650-MX 45.93</b> <b>UV 650-SB 0.77</b> <b>UV 650-325 0.10</b>	Formula	PANTONE COOL GRAY 2 C <b>UV 650-TW 99.19</b> <b>UV 650-127 0.39</b> <b>UV 650-233 0.26</b> <b>UV 650-SB 0.16</b>	Formula	PANTONE COOL GRAY 3 C <b>UV 650-TW 58.44</b> <b>UV 650-MX 40.00</b> <b>UV 650-SB 0.88</b> <b>UV 650-127 0.39</b> <b>UV 650-233 0.29</b>	Formula	PANTONE COOL GRAY 4 C <b>UV 650-TW 96.63</b> <b>UV 650-SB 2.45</b> <b>UV 650-127 0.57</b> <b>UV 650-230 0.35</b>	Formula
PANTONE COOL GRAY 5 C <b>UV 650-TW 94.87</b> <b>UV 650-SB 4.06</b> <b>UV 650-127 0.66</b> <b>UV 650-230 0.41</b>	Formula	PANTONE COOL GRAY 6 C <b>UV 650-TW 93.92</b> <b>UV 650-SB 5.62</b> <b>UV 650-233 0.24</b> <b>UV 650-127 0.22</b>	Formula	PANTONE COOL GRAY 7 C <b>UV 650-TW 52.49</b> <b>UV 650-MX 39.99</b> <b>UV 650-SB 6.22</b> <b>UV 650-127 0.71</b> <b>UV 650-233 0.59</b>	Formula	PANTONE COOL GRAY 8 C <b>UV 650-TW 86.76</b> <b>UV 650-SB 11.51</b> <b>UV 650-127 1.08</b> <b>UV 650-230 0.65</b>	Formula
PANTONE COOL GRAY 9 C <b>UV 650-TW 77.60</b> <b>UV 650-SB 20.38</b> <b>UV 650-127 1.28</b> <b>UV 650-233 0.74</b>	Formula	PANTONE COOL GRAY 10 C <b>UV 650-MX 40.00</b> <b>UV 650-TW 35.17</b> <b>UV 650-SB 21.49</b> <b>UV 650-233 1.69</b> <b>UV 650-127 1.65</b>	Formula	PANTONE COOL GRAY 11 C <b>UV 650-SB 36.81</b> <b>UV 650-MX 30.68</b> <b>UV 650-TW 30.68</b> <b>UV 650-233 1.22</b> <b>UV 650-127 0.61</b>	Formula	PANTONE BLACK 2 C <b>UV 650-SB 81.48</b> <b>UV 650-064 18.52</b>	Formula
PANTONE BLACK 3 C <b>UV 650-SB 90.00</b> <b>UV 650-325 10.00</b>	Formula	PANTONE BLACK 4 C <b>UV 650-SB 83.33</b> <b>UV 650-114 16.67</b>	Formula	PANTONE BLACK 5 C <b>UV 650-SB 66.67</b> <b>UV 650-TW 13.33</b> <b>UV 650-165 13.33</b> <b>UV 650-114 6.67</b>	Formula	PANTONE BLACK 6 C <b>UV 650-SB 85.72</b> <b>UV 650-233 9.52</b> <b>UV 650-127 4.76</b>	Formula

# UVivid 650

PANTONE BLACK 7 C	Formula
<b>UV 650-SB</b>	<b>74.08</b>
<b>UV 650-TW</b>	<b>22.22</b>
<b>UV 650-114</b>	<b>3.70</b>

PANTONE 448 C	Formula
<b>UV 650-SB</b>	<b>43.97</b>
<b>UV 650-066</b>	<b>31.59</b>
<b>UV 650-MX</b>	<b>24.44</b>

PANTONE 449 C	Formula
<b>UV 650-066</b>	<b>46.22</b>
<b>UV 650-SB</b>	<b>41.73</b>
<b>UV 650-MX</b>	<b>12.05</b>

PANTONE 450 C	Formula
<b>UV 650-066</b>	<b>54.07</b>
<b>UV 650-SB</b>	<b>37.53</b>
<b>UV 650-MX</b>	<b>8.40</b>

PANTONE 451 C	Formula
<b>UV 650-TW</b>	<b>65.11</b>
<b>UV 650-066</b>	<b>24.69</b>
<b>UV 650-SB</b>	<b>9.50</b>
<b>UV 650-325</b>	<b>0.70</b>

PANTONE 452 C	Formula
<b>UV 650-TW</b>	<b>46.39</b>
<b>UV 650-MX</b>	<b>40.00</b>
<b>UV 650-066</b>	<b>8.25</b>
<b>UV 650-SB</b>	<b>5.36</b>

PANTONE 453 C	Formula
<b>UV 650-TW</b>	<b>89.66</b>
<b>UV 650-SB</b>	<b>3.65</b>
<b>UV 650-066</b>	<b>6.15</b>
<b>UV 650-325</b>	<b>0.54</b>

PANTONE 454 C	Formula
<b>UV 650-TW</b>	<b>93.81</b>
<b>UV 650-066</b>	<b>3.55</b>
<b>UV 650-SB</b>	<b>2.24</b>
<b>UV 650-325</b>	<b>0.40</b>

PANTONE 4485 C	Formula
<b>UV 650-064</b>	<b>33.77</b>
<b>UV 650-114</b>	<b>31.93</b>
<b>UV 650-TW</b>	<b>23.08</b>
<b>UV 650-233</b>	<b>11.22</b>

PANTONE 4495 C	Formula
<b>UV 650-MX</b>	<b>40.00</b>
<b>UV 650-SB</b>	<b>30.89</b>
<b>UV 650-064</b>	<b>18.53</b>
<b>UV 650-TW</b>	<b>6.95</b>
<b>UV 650-165</b>	<b>3.63</b>

PANTONE 4505 C	Formula
<b>UV 650-TW</b>	<b>53.45</b>
<b>UV 650-064</b>	<b>24.04</b>
<b>UV 650-SB</b>	<b>11.00</b>
<b>UV 650-MX</b>	<b>8.93</b>
<b>UV 650-165</b>	<b>2.58</b>

PANTONE 4515 C	Formula
<b>UV 650-TW</b>	<b>63.62</b>
<b>UV 650-MX</b>	<b>21.03</b>
<b>UV 650-064</b>	<b>7.52</b>
<b>UV 650-SB</b>	<b>6.60</b>
<b>UV 650-165</b>	<b>1.23</b>

PANTONE 4525 C	Formula
<b>UV 650-TW</b>	<b>91.55</b>
<b>UV 650-064</b>	<b>4.06</b>
<b>UV 650-SB</b>	<b>3.72</b>
<b>UV 650-165</b>	<b>0.67</b>

PANTONE 4535 C	Formula
<b>UV 650-TW</b>	<b>55.39</b>
<b>UV 650-MX</b>	<b>40.01</b>
<b>UV 650-SB</b>	<b>2.42</b>
<b>UV 650-064</b>	<b>1.85</b>
<b>UV 650-165</b>	<b>0.33</b>

PANTONE 4545 C	Formula
<b>UV 650-TW</b>	<b>96.41</b>
<b>UV 650-SB</b>	<b>1.82</b>
<b>UV 650-064</b>	<b>1.53</b>
<b>UV 650-165</b>	<b>0.24</b>

PANTONE 455 C	Formula
<b>UV 650-MX</b>	<b>39.99</b>
<b>UV 650-SB</b>	<b>26.27</b>
<b>UV 650-064</b>	<b>23.00</b>
<b>UV 650-TW</b>	<b>9.22</b>
<b>UV 650-165</b>	<b>1.52</b>

# UVivid 650

PANTONE 456 C	Formula
<b>UV 650-MX</b>	<b>40.00</b>
<b>UV 650-064</b>	<b>27.64</b>
<b>UV 650-TW</b>	<b>21.46</b>
<b>UV 650-SB</b>	<b>9.49</b>
<b>UV 650-165</b>	<b>1.41</b>

PANTONE 457 C	Formula
<b>UV 650-064</b>	<b>30.22</b>
<b>UV 650-SB</b>	<b>6.05</b>
<b>UV 650-165</b>	<b>2.75</b>
<b>UV 650-233</b>	<b>0.38</b>
<b>UV 650-MX</b>	<b>60.6</b>

PANTONE 458 C	Formula
<b>UV 650-TW</b>	<b>48.99</b>
<b>UV 650-MX</b>	<b>40.01</b>
<b>UV 650-064</b>	<b>9.22</b>
<b>UV 650-SB</b>	<b>1.39</b>
<b>UV 650-165</b>	<b>0.39</b>

PANTONE 459 C	Formula
<b>UV 650-TW</b>	<b>89.47</b>
<b>UV 650-064</b>	<b>9.39</b>
<b>UV 650-165</b>	<b>0.82</b>
<b>UV 650-233</b>	<b>0.32</b>

PANTONE 460 C	Formula
<b>UV 650-TW</b>	<b>94.36</b>
<b>UV 650-064</b>	<b>4.88</b>
<b>UV 650-165</b>	<b>0.55</b>
<b>UV 650-233</b>	<b>0.21</b>

PANTONE 461 C	Formula
<b>UV 650-TW</b>	<b>97.19</b>
<b>UV 650-064</b>	<b>2.39</b>
<b>UV 650-165</b>	<b>0.29</b>
<b>UV 650-233</b>	<b>0.13</b>

PANTONE 462 C	Formula
<b>UV 650-064</b>	<b>34.44</b>
<b>UV 650-SB</b>	<b>30.21</b>
<b>UV 650-TW</b>	<b>27.44</b>
<b>UV 650-121</b>	<b>7.91</b>

PANTONE 463 C	Formula
<b>UV 650-064</b>	<b>42.99</b>
<b>UV 650-TW</b>	<b>25.45</b>
<b>UV 650-SB</b>	<b>22.09</b>
<b>UV 650-121</b>	<b>9.47</b>

PANTONE 464 C	Formula
<b>UV 650-066</b>	<b>50.23</b>
<b>UV 650-SB</b>	<b>23.26</b>
<b>UV 650-121</b>	<b>8.70</b>
<b>UV 650-064</b>	<b>17.81</b>

PANTONE 465 C	Formula
<b>UV 650-TW</b>	<b>58.43</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-064</b>	<b>12.74</b>
<b>UV 650-SB</b>	<b>6.61</b>
<b>UV 650-121</b>	<b>2.22</b>

PANTONE 466 C	Formula
<b>UV 650-TW</b>	<b>70.04</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-064</b>	<b>5.04</b>
<b>UV 650-SB</b>	<b>3.87</b>
<b>UV 650-121</b>	<b>1.05</b>

PANTONE 467 C	Formula
<b>UV 650-TW</b>	<b>85.90</b>
<b>UV 650-066</b>	<b>10.92</b>
<b>UV 650-SB</b>	<b>3.18</b>

PANTONE 468 C	Formula
<b>UV 650-TW</b>	<b>91.90</b>
<b>UV 650-066</b>	<b>6.02</b>
<b>UV 650-SB</b>	<b>2.08</b>

PANTONE 4625 C	Formula
<b>UV 650-SB</b>	<b>41.99</b>
<b>UV 650-114</b>	<b>27.40</b>
<b>UV 650-064</b>	<b>22.20</b>
<b>UV 650-TW</b>	<b>8.41</b>

PANTONE 4635 C	Formula
<b>UV 650-TW</b>	<b>49.48</b>
<b>UV 650-114</b>	<b>25.02</b>
<b>UV 650-SB</b>	<b>13.68</b>
<b>UV 650-064</b>	<b>8.38</b>
<b>UV 650-MX</b>	<b>3.44</b>

PANTONE 4645 C	Formula
<b>UV 650-TW</b>	<b>73.40</b>
<b>UV 650-114</b>	<b>14.06</b>
<b>UV 650-SB</b>	<b>9.27</b>
<b>UV 650-064</b>	<b>3.27</b>

# UVivid 650

PANTONE 4655 C	Formula
<b>UV 650-TW</b>	<b>85.75</b>
<b>UV 650-114</b>	<b>7.59</b>
<b>UV 650-SB</b>	<b>5.72</b>
<b>UV 650-064</b>	<b>0.94</b>

PANTONE 4665 C	Formula
<b>UV 650-TW</b>	<b>91.73</b>
<b>UV 650-114</b>	<b>4.28</b>
<b>UV 650-SB</b>	<b>3.70</b>
<b>UV 650-064</b>	<b>0.29</b>

PANTONE 4675 C	Formula
<b>UV 650-TW</b>	<b>95.90</b>
<b>UV 650-SB</b>	<b>2.13</b>
<b>UV 650-114</b>	<b>1.97</b>

PANTONE 4685 C	Formula
<b>UV 650-TW</b>	<b>97.19</b>
<b>UV 650-SB</b>	<b>1.59</b>
<b>UV 650-114</b>	<b>1.22</b>

PANTONE 469 C	Formula
<b>UV 650-114</b>	<b>54.14</b>
<b>UV 650-064</b>	<b>21.33</b>
<b>UV 650-TW</b>	<b>14.79</b>
<b>UV 650-233</b>	<b>9.74</b>

PANTONE 470 C	Formula
<b>UV 650-TW</b>	<b>34.25</b>
<b>UV 650-114</b>	<b>31.67</b>
<b>UV 650-064</b>	<b>23.11</b>
<b>UV 650-SB</b>	<b>10.97</b>

PANTONE 471 C	Formula
<b>UV 650-114</b>	<b>32.63</b>
<b>UV 650-064</b>	<b>19.17</b>
<b>UV 650-121</b>	<b>3.92</b>
<b>UV 650-233</b>	<b>2.45</b>
<b>UV 650-MX</b>	<b>41.83</b>

PANTONE 472 C	Formula
<b>UV 650-TW</b>	<b>85.15</b>
<b>UV 650-114</b>	<b>11.80</b>
<b>UV 650-064</b>	<b>2.37</b>
<b>UV 650-233</b>	<b>0.68</b>

PANTONE 473 C	Formula
<b>UV 650-TW</b>	<b>94.83</b>
<b>UV 650-114</b>	<b>4.84</b>
<b>UV 650-233</b>	<b>0.33</b>

PANTONE 474 C	Formula
<b>UV 650-TW</b>	<b>96.12</b>
<b>UV 650-114</b>	<b>3.62</b>
<b>UV 650-233</b>	<b>0.26</b>

PANTONE 475 C	Formula
<b>UV 650-TW</b>	<b>97.38</b>
<b>UV 650-114</b>	<b>2.41</b>
<b>UV 650-233</b>	<b>0.21</b>

PANTONE 4695 C	Formula
<b>UV 650-MX</b>	<b>40.01</b>
<b>UV 650-SB</b>	<b>27.30</b>
<b>UV 650-164</b>	<b>12.55</b>
<b>UV 650-064</b>	<b>12.07</b>
<b>UV 650-TW</b>	<b>8.07</b>

PANTONE 4705 C	Formula
<b>UV 650-TW</b>	<b>45.71</b>
<b>UV 650-064</b>	<b>19.10</b>
<b>UV 650-164</b>	<b>17.74</b>
<b>UV 650-SB</b>	<b>17.45</b>

PANTONE 4715 C	Formula
<b>UV 650-TW</b>	<b>13.47</b>
<b>UV 650-SB</b>	<b>12.36</b>
<b>UV 650-164</b>	<b>5.87</b>
<b>UV 650-064</b>	<b>4.36</b>
<b>UV 650-MX</b>	<b>63.94</b>

PANTONE 4725 C	Formula
<b>UV 650-TW</b>	<b>85.12</b>
<b>UV 650-SB</b>	<b>6.87</b>
<b>UV 650-164</b>	<b>4.34</b>
<b>UV 650-064</b>	<b>3.67</b>

PANTONE 4735 C	Formula
<b>UV 650-TW</b>	<b>53.69</b>
<b>UV 650-MX</b>	<b>40.00</b>
<b>UV 650-SB</b>	<b>3.82</b>
<b>UV 650-164</b>	<b>1.69</b>
<b>UV 650-064</b>	<b>0.8</b>



# UVivid 650

<b>PANTONE</b> 4745 C <b>UV 650-TW</b> <b>94.95</b> <b>UV 650-SB</b> <b>2.93</b> <b>UV 650-164</b> <b>1.41</b> <b>UV 650-064</b> <b>0.71</b>	Formula	<b>PANTONE</b> 4755 C <b>UV 650-TW</b> <b>97.01</b> <b>UV 650-SB</b> <b>1.93</b> <b>UV 650-164</b> <b>0.78</b> <b>UV 650-064</b> <b>0.28</b>	Formula	<b>PANTONE</b> 476 C <b>UV 650-SB</b> <b>37.22</b> <b>UV 650-MX</b> <b>34.42</b> <b>UV 650-165</b> <b>14.52</b> <b>UV 650-064</b> <b>13.84</b>	Formula	<b>PANTONE</b> 477 C <b>UV 650-064</b> <b>40.75</b> <b>UV 650-165</b> <b>39.39</b> <b>UV 650-TW</b> <b>13.15</b> <b>UV 650-230</b> <b>6.71</b>	Formula
<b>PANTONE</b> 478 C <b>UV 650-165</b> <b>41.76</b> <b>UV 650-064</b> <b>36.02</b> <b>UV 650-TW</b> <b>18.00</b> <b>UV 650-230</b> <b>4.22</b>	Formula	<b>PANTONE</b> 479 C <b>UV 650-TW</b> <b>74.43</b> <b>UV 650-165</b> <b>12.39</b> <b>UV 650-064</b> <b>11.31</b> <b>UV 650-230</b> <b>1.87</b>	Formula	<b>PANTONE</b> 480 C <b>UV 650-TW</b> <b>91.05</b> <b>UV 650-165</b> <b>4.75</b> <b>UV 650-064</b> <b>3.34</b> <b>UV 650-230</b> <b>0.86</b>	Formula	<b>PANTONE</b> 481 C <b>UV 650-TW</b> <b>89.67</b> <b>UV 650-MX</b> <b>5.01</b> <b>UV 650-165</b> <b>2.92</b> <b>UV 650-064</b> <b>1.83</b> <b>UV 650-230</b> <b>0.57</b>	Formula
<b>PANTONE</b> 482 C <b>UV 650-TW</b> <b>96.31</b> <b>UV 650-SB</b> <b>1.73</b> <b>UV 650-165</b> <b>1.17</b> <b>UV 650-064</b> <b>0.79</b>	Formula	<b>PANTONE</b> 483 C <b>UV 650-114</b> <b>54.78</b> <b>UV 650-SB</b> <b>30.88</b> <b>UV 650-TW</b> <b>14.34</b>	Formula	<b>PANTONE</b> 484 C <b>UV 650-114</b> <b>54.33</b> <b>UV 650-TW</b> <b>23.17</b> <b>UV 650-121</b> <b>12.24</b> <b>UV 650-SB</b> <b>10.26</b>	Formula	<b>PANTONE</b> 485 C <b>UV 650-114</b> <b>54.91</b> <b>UV 650-121</b> <b>27.46</b> <b>UV 650-TW</b> <b>16.47</b> <b>UV 650-SB</b> <b>1.16</b>	Formula
<b>PANTONE</b> 486 C <b>UV 650-TW</b> <b>50.47</b> <b>UV 650-MX</b> <b>40.01</b> <b>UV 650-114</b> <b>5.43</b> <b>UV 650-121</b> <b>2.66</b> <b>UV 650-SB</b> <b>1.43</b>	Formula	<b>PANTONE</b> 487 C <b>UV 650-TW</b> <b>54.41</b> <b>UV 650-MX</b> <b>40.01</b> <b>UV 650-114</b> <b>2.96</b> <b>UV 650-121</b> <b>1.45</b> <b>UV 650-SB</b> <b>1.17</b>	Formula	<b>PANTONE</b> 488 C <b>UV 650-TW</b> <b>96.14</b> <b>UV 650-114</b> <b>1.97</b> <b>UV 650-SB</b> <b>1.02</b> <b>UV 650-121</b> <b>0.87</b>	Formula	<b>PANTONE</b> 489 C <b>UV 650-TW</b> <b>97.39</b> <b>UV 650-114</b> <b>1.23</b> <b>UV 650-SB</b> <b>0.83</b> <b>UV 650-121</b> <b>0.55</b>	Formula

# UVivid 650

PANTONE 490 C <b>UV 650-066</b> <b>28.10</b> <b>UV 650-SB</b> <b>27.60</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-121</b> <b>14.07</b> <b>UV 650-TW</b> <b>10.23</b>	Formula	PANTONE 491 C <b>UV 650-066</b> <b>25.76</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-121</b> <b>18.42</b> <b>UV 650-TW</b> <b>20.48</b> <b>UV 650-SB</b> <b>15.34</b>	Formula	PANTONE 492 C <b>UV 650-TW</b> <b>43.29</b> <b>UV 650-121</b> <b>43.29</b> <b>UV 650-SB</b> <b>11.26</b> <b>UV 650-066</b> <b>2.16</b>	Formula	PANTONE 493 C <b>UV 650-TW</b> <b>90.90</b> <b>UV 650-164</b> <b>7.79</b> <b>UV 650-SB</b> <b>1.31</b>	Formula
PANTONE 494 C <b>UV 650-TW</b> <b>95.17</b> <b>UV 650-164</b> <b>4.37</b> <b>UV 650-SB</b> <b>0.46</b>	Formula	PANTONE 495 C <b>UV 650-TW</b> <b>97.41</b> <b>UV 650-164</b> <b>2.59</b>	Formula	PANTONE 496 C <b>UV 650-TW</b> <b>98.26</b> <b>UV 650-164</b> <b>1.74</b>	Formula	PANTONE 497 C <b>UV 650-SB</b> <b>34.12</b> <b>UV 650-066</b> <b>26.38</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-121</b> <b>10.01</b> <b>UV 650-TW</b> <b>9.49</b>	Formula
PANTONE 498 C <b>UV 650-066</b> <b>41.53</b> <b>UV 650-SB</b> <b>25.00</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-164</b> <b>13.47</b>	Formula	PANTONE 499 C <b>UV 650-121</b> <b>30.38</b> <b>UV 650-066</b> <b>30.09</b> <b>UV 650-TW</b> <b>28.89</b> <b>UV 650-325</b> <b>10.64</b>	Formula	PANTONE 500 C <b>UV 650-TW</b> <b>71.14</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-164</b> <b>6.36</b> <b>UV 650-SB</b> <b>2.50</b>	Formula	PANTONE 501 C <b>UV 650-TW</b> <b>95.34</b> <b>UV 650-164</b> <b>3.42</b> <b>UV 650-SB</b> <b>1.24</b>	Formula
PANTONE 502 C <b>UV 650-TW</b> <b>97.49</b> <b>UV 650-164</b> <b>2.05</b> <b>UV 650-SB</b> <b>0.46</b>	Formula	PANTONE 503 C <b>UV 650-TW</b> <b>98.54</b> <b>UV 650-164</b> <b>1.46</b>	Formula	PANTONE 4975 C <b>UV 650-SB</b> <b>48.07</b> <b>UV 650-114</b> <b>33.58</b> <b>UV 650-MX</b> <b>9.22</b> <b>UV 650-TW</b> <b>9.13</b>	Formula	PANTONE 4985 C <b>UV 650-TW</b> <b>53.88</b> <b>UV 650-165</b> <b>18.40</b> <b>UV 650-SB</b> <b>13.97</b> <b>UV 650-114</b> <b>13.75</b>	Formula

# UVivid 650

PANTONE 4995 C	Formula
UV 650-MX	60.36
UV 650-TW	15.90
UV 650-114	10.94
UV 650-165	10.46
UV 650-230	2.34

PANTONE 5005 C	Formula
UV 650-TW	82.88
UV 650-165	7.40
UV 650-SB	5.93
UV 650-114	3.79

PANTONE 5015 C	Formula
UV 650-TW	92.39
UV 650-165	3.55
UV 650-SB	2.91
UV 650-114	1.15

PANTONE 5025 C	Formula
UV 650-TW	95.90
UV 650-165	2.44
UV 650-114	1.17
UV 650-230	0.49

PANTONE 5035 C	Formula
UV 650-TW	97.58
UV 650-165	1.51
UV 650-SB	0.91

PANTONE 504 C	Formula
UV 650-SB	34.50
UV 650-164	29.64
UV 650-MX	20.00
UV 650-TW	15.86

PANTONE 505 C	Formula
UV 650-164	33.64
UV 650-TW	26.20
UV 650-SB	20.16
UV 650-MX	20.00

PANTONE 506 C	Formula
UV 650-164	45.37
UV 650-TW	40.83
UV 650-SB	12.70
UV 650-230	1.10

PANTONE 507 C	Formula
UV 650-TW	92.26
UV 650-165	5.46
UV 650-164	1.25
UV 650-SB	1.03

PANTONE 508 C	Formula
UV 650-TW	75.84
UV 650-MX	20.00
UV 650-165	3.76
UV 650-164	0.40

PANTONE 509 C	Formula
UV 650-TW	96.10
UV 650-165	3.23
UV 650-164	0.67

PANTONE 510 C	Formula
UV 650-TW	77.43
UV 650-MX	20.00
UV 650-165	2.57

PANTONE 511 C	Formula
UV 650-165	52.81
UV 650-TW	24.77
UV 650-SB	22.42

PANTONE 512 C	Formula
UV 650-165	65.44
UV 650-TW	31.17
UV 650-230	3.39

PANTONE 513 C	Formula
UV 650-TW	16.89
UV 650-165	37.57
UV 650-325	3.38
UV 650-127	1.85
UV 650-MX	40.31

PANTONE 514 C	Formula
UV 650-TW	67.58
UV 650-MX	20.00
UV 650-165	11.80
UV 650-230	0.62

# UVivid 650

PANTONE 515 C <b>UV 650-TW</b> <b>94.10</b> <b>UV 650-165</b> <b>4.97</b> <b>UV 650-127</b> <b>0.93</b>	Formula	PANTONE 516 C <b>UV 650-TW</b> <b>96.43</b> <b>UV 650-165</b> <b>2.81</b> <b>UV 650-127</b> <b>0.76</b>	Formula	PANTONE 517 C <b>UV 650-TW</b> <b>97.53</b> <b>UV 650-165</b> <b>1.91</b> <b>UV 650-127</b> <b>0.56</b>	Formula	PANTONE 5115 C <b>UV 650-165</b> <b>30.25</b> <b>UV 650-SB</b> <b>29.39</b> <b>UV 650-TW</b> <b>20.35</b> <b>UV 650-MX</b> <b>20.01</b>	Formula
PANTONE 5125 C <b>UV 650-TW</b> <b>49.67</b> <b>UV 650-165</b> <b>32.46</b> <b>UV 650-SB</b> <b>17.87</b>	Formula	PANTONE 5135 C <b>UV 650-TW</b> <b>67.84</b> <b>UV 650-SB</b> <b>14.47</b> <b>UV 650-165</b> <b>16.79</b> <b>UV 650-127</b> <b>0.90</b>	Formula	PANTONE 5145 C <b>UV 650-TW</b> <b>85.08</b> <b>UV 650-165</b> <b>6.75</b> <b>UV 650-SB</b> <b>6.59</b> <b>UV 650-127</b> <b>1.58</b>	Formula	PANTONE 5155 C <b>UV 650-TW</b> <b>95.93</b> <b>UV 650-SB</b> <b>1.68</b> <b>UV 650-127</b> <b>1.30</b> <b>UV 650-165</b> <b>1.09</b>	Formula
PANTONE 5165 C <b>UV 650-TW</b> <b>98.81</b> <b>UV 650-127</b> <b>1.04</b> <b>UV 650-SB</b> <b>0.15</b>	Formula	PANTONE 5175 C <b>UV 650-TW</b> <b>98.79</b> <b>UV 650-127</b> <b>0.87</b> <b>UV 650-SB</b> <b>0.34</b>	Formula	PANTONE 518 C <b>UV 650-SB</b> <b>31.30</b> <b>UV 650-165</b> <b>30.35</b> <b>UV 650-TW</b> <b>27.98</b> <b>UV 650-MX</b> <b>10.37</b>	Formula	PANTONE 519 C <b>UV 650-165</b> <b>44.31</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-TW</b> <b>17.91</b> <b>UV 650-325</b> <b>9.32</b> <b>UV 650-SB</b> <b>8.46</b>	Formula
PANTONE 520 C <b>UV 650-165</b> <b>48.54</b> <b>UV 650-MX</b> <b>19.42</b> <b>UV 650-TW</b> <b>19.42</b> <b>UV 650-325</b> <b>12.62</b>	Formula	PANTONE 521 C <b>UV 650-TW</b> <b>69.47</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-165</b> <b>6.64</b> <b>UV 650-127</b> <b>2.10</b> <b>UV 650-325</b> <b>1.79</b>	Formula	PANTONE 522 C <b>UV 650-TW</b> <b>96.12</b> <b>UV 650-127</b> <b>2.48</b> <b>UV 650-165</b> <b>0.96</b> <b>UV 650-SB</b> <b>0.44</b>	Formula	PANTONE 523 C <b>UV 650-TW</b> <b>78.15</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-127</b> <b>1.85</b>	Formula

# UVivid 650

PANTONE 524 C	Formula
<b>UV 650-TW</b>	<b>98.66</b>
<b>UV 650-127</b>	<b>1.34</b>

PANTONE 5185 C	Formula
<b>UV 650-TW</b>	<b>23.78</b>
<b>UV 650-114</b>	<b>20.75</b>
<b>UV 650-SB</b>	<b>20.07</b>
<b>UV 650-MX</b>	<b>20.01</b>
<b>UV 650-127</b>	<b>15.39</b>

PANTONE 5195 C	Formula
<b>UV 650-TW</b>	<b>45.43</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-127</b>	<b>15.43</b>
<b>UV 650-114</b>	<b>14.37</b>
<b>UV 650-SB</b>	<b>4.77</b>

PANTONE 5205 C	Formula
<b>UV 650-MX</b>	<b>49.62</b>
<b>UV 650-TW</b>	<b>34.74</b>
<b>UV 650-SB</b>	<b>6.95</b>
<b>UV 650-114</b>	<b>4.47</b>
<b>UV 650-127</b>	<b>4.22</b>

PANTONE 5215 C	Formula
<b>UV 650-TW</b>	<b>93.44</b>
<b>UV 650-127</b>	<b>2.79</b>
<b>UV 650-SB</b>	<b>2.03</b>
<b>UV 650-114</b>	<b>1.74</b>

PANTONE 5225 C	Formula
<b>UV 650-TW</b>	<b>97.04</b>
<b>UV 650-127</b>	<b>1.51</b>
<b>UV 650-SB</b>	<b>0.88</b>
<b>UV 650-114</b>	<b>0.57</b>

PANTONE 5235 C	Formula
<b>UV 650-TW</b>	<b>98.53</b>
<b>UV 650-127</b>	<b>1.13</b>
<b>UV 650-114</b>	<b>0.34</b>

PANTONE 5245 C	Formula
<b>UV 650-TW</b>	<b>99.27</b>
<b>UV 650-127</b>	<b>0.73</b>

PANTONE 525 C	Formula
<b>UV 650-165</b>	<b>32.51</b>
<b>UV 650-TW</b>	<b>20.71</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-SB</b>	<b>15.81</b>
<b>UV 650-127</b>	<b>10.97</b>

PANTONE 526 C	Formula
<b>UV 650-TW</b>	<b>41.15</b>
<b>UV 650-127</b>	<b>25.52</b>
<b>UV 650-165</b>	<b>16.67</b>
<b>UV 650-MX</b>	<b>16.66</b>

PANTONE 527 C	Formula
<b>UV 650-MX</b>	<b>67.42</b>
<b>UV 650-127</b>	<b>16.85</b>
<b>UV 650-165</b>	<b>15.73</b>

PANTONE 528 C	Formula
<b>UV 650-TW</b>	<b>71.25</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-127</b>	<b>6.18</b>
<b>UV 650-165</b>	<b>2.57</b>

PANTONE 529 C	Formula
<b>UV 650-TW</b>	<b>94.66</b>
<b>UV 650-127</b>	<b>3.31</b>
<b>UV 650-165</b>	<b>2.03</b>

PANTONE 530 C	Formula
<b>UV 650-TW</b>	<b>96.86</b>
<b>UV 650-127</b>	<b>2.02</b>
<b>UV 650-165</b>	<b>1.12</b>

PANTONE 531 C	Formula
<b>UV 650-TW</b>	<b>97.89</b>
<b>UV 650-127</b>	<b>1.27</b>
<b>UV 650-165</b>	<b>0.84</b>

PANTONE 5255 C	Formula
<b>UV 650-SB</b>	<b>36.44</b>
<b>UV 650-127</b>	<b>32.30</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-TW</b>	<b>11.26</b>

# UVivid 650

<b>PANTONE</b> <b>5265 C</b> <b>UV 650-TW</b> <b>38.24</b> <b>UV 650-127</b> <b>20.35</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-SB</b> <b>18.03</b> <b>UV 650-233</b> <b>3.37</b>	Formula	<b>PANTONE</b> <b>5275 C</b> <b>UV 650-TW</b> <b>61.96</b> <b>UV 650-066</b> <b>18.58</b> <b>UV 650-127</b> <b>15.04</b> <b>UV 650-233</b> <b>4.42</b>	Formula	<b>PANTONE</b> <b>5285 C</b> <b>UV 650-TW</b> <b>86.57</b> <b>UV 650-066</b> <b>6.66</b> <b>UV 650-127</b> <b>4.83</b> <b>UV 650-233</b> <b>1.94</b>	Formula	<b>PANTONE</b> <b>5295 C</b> <b>UV 650-TW</b> <b>95.33</b> <b>UV 650-127</b> <b>1.91</b> <b>UV 650-066</b> <b>1.91</b> <b>UV 650-233</b> <b>0.85</b>	Formula
<b>PANTONE</b> <b>5305 C</b> <b>UV 650-TW</b> <b>98.13</b> <b>UV 650-127</b> <b>1.08</b> <b>UV 650-233</b> <b>0.49</b> <b>UV 650-066</b> <b>0.30</b>	Formula	<b>PANTONE</b> <b>5315 C</b> <b>UV 650-TW</b> <b>99.00</b> <b>UV 650-127</b> <b>0.68</b> <b>UV 650-233</b> <b>0.32</b>	Formula	<b>PANTONE</b> <b>532 C</b> <b>UV 650-SB</b> <b>40.94</b> <b>UV 650-165</b> <b>23.69</b> <b>UV 650-MX</b> <b>19.78</b> <b>UV 650-325</b> <b>15.59</b>	Formula	<b>PANTONE</b> <b>533 C</b> <b>UV 650-165</b> <b>41.38</b> <b>UV 650-325</b> <b>31.27</b> <b>UV 650-SB</b> <b>18.83</b> <b>UV 650-MX</b> <b>8.52</b>	Formula
<b>PANTONE</b> <b>534 C</b> <b>UV 650-TW</b> <b>18.68</b> <b>UV 650-325</b> <b>44.58</b> <b>UV 650-165</b> <b>26.75</b> <b>UV 650-127</b> <b>9.99</b>	Formula	<b>PANTONE</b> <b>535 C</b> <b>UV 650-TW</b> <b>93.81</b> <b>UV 650-325</b> <b>3.35</b> <b>UV 650-127</b> <b>2.84</b>	Formula	<b>PANTONE</b> <b>536 C</b> <b>UV 650-TW</b> <b>95.54</b> <b>UV 650-325</b> <b>2.40</b> <b>UV 650-127</b> <b>2.06</b>	Formula	<b>PANTONE</b> <b>537 C</b> <b>UV 650-TW</b> <b>97.37</b> <b>UV 650-325</b> <b>1.35</b> <b>UV 650-127</b> <b>1.28</b>	Formula
<b>PANTONE</b> <b>538 C</b> <b>UV 650-TW</b> <b>98.25</b> <b>UV 650-127</b> <b>0.88</b> <b>UV 650-325</b> <b>0.87</b>	Formula	<b>PANTONE</b> <b>539 C</b> <b>UV 650-233</b> <b>45.35</b> <b>UV 650-164</b> <b>31.43</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-064</b> <b>3.22</b>	Formula	<b>PANTONE</b> <b>540 C</b> <b>UV 650-233</b> <b>57.53</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-164</b> <b>16.26</b> <b>UV 650-TW</b> <b>5.65</b> <b>UV 650-064</b> <b>0.56</b>	Formula	<b>PANTONE</b> <b>541 C</b> <b>UV 650-233</b> <b>71.77</b> <b>UV 650-TW</b> <b>17.92</b> <b>UV 650-SB</b> <b>7.07</b> <b>UV 650-164</b> <b>2.09</b> <b>UV 650-064</b> <b>1.15</b>	Formula

# UVivid 650

PANTONE 542 C <b>UV 650-TW</b> <b>91.97</b> <b>UV 650-233</b> <b>6.44</b> <b>UV 650-164</b> <b>1.59</b>	Formula	PANTONE 543 C <b>UV 650-TW</b> <b>96.36</b> <b>UV 650-233</b> <b>2.81</b> <b>UV 650-164</b> <b>0.83</b>	Formula	PANTONE 544 C <b>UV 650-TW</b> <b>97.68</b> <b>UV 650-233</b> <b>1.73</b> <b>UV 650-164</b> <b>0.59</b>	Formula	PANTONE 545 C <b>UV 650-TW</b> <b>98.63</b> <b>UV 650-233</b> <b>0.92</b> <b>UV 650-127</b> <b>0.45</b>	Formula
PANTONE 5395 C <b>UV 650-230</b> <b>59.21</b> <b>UV 650-SB</b> <b>22.19</b> <b>UV 650-114</b> <b>18.60</b>	Formula	PANTONE 5405 C <b>UV 650-TW</b> <b>60.68</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-230</b> <b>9.73</b> <b>UV 650-114</b> <b>5.98</b> <b>UV 650-127</b> <b>3.61</b>	Formula	PANTONE 5415 C <b>UV 650-TW</b> <b>86.41</b> <b>UV 650-114</b> <b>5.40</b> <b>UV 650-230</b> <b>4.56</b> <b>UV 650-127</b> <b>2.23</b> <b>UV 650-SB</b> <b>1.4</b>	Formula	PANTONE 5425 C <b>UV 650-TW</b> <b>90.40</b> <b>UV 650-SB</b> <b>5.05</b> <b>UV 650-230</b> <b>3.05</b> <b>UV 650-127</b> <b>1.50</b>	Formula
PANTONE 5435 C <b>UV 650-TW</b> <b>96.38</b> <b>UV 650-SB</b> <b>1.40</b> <b>UV 650-230</b> <b>1.32</b> <b>UV 650-127</b> <b>0.90</b>	Formula	PANTONE 5445 C <b>UV 650-TW</b> <b>78.05</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-230</b> <b>0.89</b> <b>UV 650-127</b> <b>0.69</b> <b>UV 650-SB</b> <b>0.37</b>	Formula	PANTONE 5455 C <b>UV 650-TW</b> <b>98.59</b> <b>UV 650-230</b> <b>0.67</b> <b>UV 650-127</b> <b>0.55</b> <b>UV 650-SB</b> <b>0.19</b>	Formula	PANTONE 546 C <b>UV 650-233</b> <b>37.95</b> <b>UV 650-164</b> <b>24.46</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-064</b> <b>10.85</b> <b>UV 650-TW</b> <b>6.73</b>	Formula
PANTONE 547 C <b>UV 650-233</b> <b>47.28</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-164</b> <b>15.17</b> <b>UV 650-064</b> <b>9.25</b> <b>UV 650-TW</b> <b>8.3</b>	Formula	PANTONE 548 C <b>UV 650-230</b> <b>78.12</b> <b>UV 650-064</b> <b>12.50</b> <b>UV 650-127</b> <b>9.38</b>	Formula	PANTONE 549 C <b>UV 650-TW</b> <b>90.67</b> <b>UV 650-233</b> <b>5.30</b> <b>UV 650-SB</b> <b>4.03</b>	Formula	PANTONE 550 C <b>UV 650-TW</b> <b>96.25</b> <b>UV 650-233</b> <b>2.72</b> <b>UV 650-164</b> <b>0.88</b> <b>UV 650-064</b> <b>0.15</b>	Formula

# UVivid 650

PANTONE 551 C <b>UV 650-TW</b> <b>97.57</b> <b>UV 650-233</b> <b>1.84</b> <b>UV 650-164</b> <b>0.59</b>	Formula	PANTONE 552 C <b>UV 650-TW</b> <b>98.74</b> <b>UV 650-233</b> <b>0.97</b> <b>UV 650-127</b> <b>0.29</b>	Formula	PANTONE 5463 C <b>UV 650-SB</b> <b>51.60</b> <b>UV 650-230</b> <b>48.40</b>	Formula	PANTONE 5473 C <b>UV 650-TW</b> <b>59.27</b> <b>UV 650-230</b> <b>20.18</b> <b>UV 650-SB</b> <b>19.06</b> <b>UV 650-064</b> <b>1.49</b>	Formula
PANTONE 5483 C <b>UV 650-TW</b> <b>83.04</b> <b>UV 650-SB</b> <b>11.86</b> <b>UV 650-230</b> <b>4.74</b> <b>UV 650-064</b> <b>0.36</b>	Formula	PANTONE 5493 C <b>UV 650-TW</b> <b>92.91</b> <b>UV 650-SB</b> <b>4.23</b> <b>UV 650-230</b> <b>2.86</b>	Formula	PANTONE 5503 C <b>UV 650-TW</b> <b>95.03</b> <b>UV 650-SB</b> <b>2.93</b> <b>UV 650-230</b> <b>2.04</b>	Formula	PANTONE 5513 C <b>UV 650-TW</b> <b>97.07</b> <b>UV 650-SB</b> <b>1.58</b> <b>UV 650-230</b> <b>1.35</b>	Formula
PANTONE 5523 C <b>UV 650-TW</b> <b>97.61</b> <b>UV 650-SB</b> <b>1.38</b> <b>UV 650-230</b> <b>1.01</b>	Formula	PANTONE 5467 C <b>UV 650-SB</b> <b>55.00</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-066</b> <b>18.91</b> <b>UV 650-233</b> <b>6.10</b>	Formula	PANTONE 5477 C <b>UV 650-066</b> <b>44.83</b> <b>UV 650-TW</b> <b>29.02</b> <b>UV 650-233</b> <b>13.19</b> <b>UV 650-165</b> <b>12.96</b>	Formula	PANTONE 5487 C <b>UV 650-TW</b> <b>73.67</b> <b>UV 650-SB</b> <b>10.87</b> <b>UV 650-114</b> <b>5.52</b> <b>UV 650-066</b> <b>5.34</b> <b>UV 650-230</b> <b>4.6</b>	Formula
PANTONE 5497 C <b>UV 650-TW</b> <b>69.25</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>7.03</b> <b>UV 650-066</b> <b>1.94</b> <b>UV 650-233</b> <b>1.78</b>	Formula	PANTONE 5507 C <b>UV 650-TW</b> <b>94.53</b> <b>UV 650-SB</b> <b>4.20</b> <b>UV 650-233</b> <b>0.97</b> <b>UV 650-066</b> <b>0.30</b>	Formula	PANTONE 5517 C <b>UV 650-TW</b> <b>96.87</b> <b>UV 650-SB</b> <b>2.39</b> <b>UV 650-233</b> <b>0.74</b>	Formula	PANTONE 5527 C <b>UV 650-TW</b> <b>97.89</b> <b>UV 650-SB</b> <b>1.51</b> <b>UV 650-233</b> <b>0.60</b>	Formula



# UVivid 650

PANTONE 553 C	Formula
UV 650-066	40.37
UV 650-SB	30.50
UV 650-MX	20.00
UV 650-233	9.13

PANTONE 554 C	Formula
UV 650-066	48.97
UV 650-MX	20.00
UV 650-230	15.52
UV 650-TW	8.44
UV 650-121	7.07

PANTONE 555 C	Formula
UV 650-066	52.66
UV 650-TW	30.69
UV 650-230	10.84
UV 650-SB	3.27
UV 650-121	2.54

PANTONE 556 C	Formula
UV 650-TW	59.94
UV 650-MX	20.00
UV 650-066	13.78
UV 650-230	4.78
UV 650-121	1.5

PANTONE 557 C	Formula
UV 650-TW	68.36
UV 650-MX	20.00
UV 650-066	7.70
UV 650-230	2.92
UV 650-121	1.02

PANTONE 558 C	Formula
UV 650-TW	72.86
UV 650-MX	20.01
UV 650-066	4.56
UV 650-230	1.91
UV 650-121	0.66

PANTONE 559 C	Formula
UV 650-TW	95.28
UV 650-066	2.93
UV 650-230	1.32
UV 650-121	0.47

PANTONE 5535 C	Formula
UV 650-SB	66.09
UV 650-066	21.28
UV 650-230	12.63

PANTONE 5545 C	Formula
UV 650-TW	55.21
UV 650-066	22.37
UV 650-SB	21.07
UV 650-230	1.35

PANTONE 5555 C	Formula
UV 650-TW	69.90
UV 650-066	12.87
UV 650-SB	6.29
UV 650-114	5.88
UV 650-230	5.06

PANTONE 5565 C	Formula
UV 650-TW	86.57
UV 650-114	5.81
UV 650-230	5.04
UV 650-066	2.58

PANTONE 5575 C	Formula
UV 650-TW	73.91
UV 650-MX	20.00
UV 650-114	3.29
UV 650-230	2.80

PANTONE 5585 C	Formula
UV 650-TW	96.39
UV 650-114	1.85
UV 650-230	1.76

PANTONE 5595 C	Formula
UV 650-TW	97.97
UV 650-SB	1.13
UV 650-230	0.64
UV 650-114	0.26

PANTONE 560 C	Formula
UV 650-SB	47.84
UV 650-325	20.67
UV 650-MX	17.89
UV 650-TW	13.60

PANTONE 561 C	Formula
UV 650-TW	41.37
UV 650-325	33.37
UV 650-SB	25.26

# UVivid 650

PANTONE 562 C	Formula
UV 650-TW	42.30
UV 650-325	42.12
UV 650-SB	8.42
UV 650-114	4.21
UV 650-230	2.95

PANTONE 563 C	Formula
UV 650-TW	72.40
UV 650-MX	20.00
UV 650-325	2.92
UV 650-230	2.72
UV 650-114	1.96

PANTONE 564 C	Formula
UV 650-TW	95.13
UV 650-325	2.19
UV 650-SB	1.72
UV 650-230	0.96

PANTONE 565 C	Formula
UV 650-TW	97.52
UV 650-325	0.93
UV 650-230	0.81
UV 650-SB	0.74

PANTONE 566 C	Formula
UV 650-TW	98.95
UV 650-230	0.72
UV 650-SB	0.18
UV 650-325	0.15

PANTONE 5605 C	Formula
UV 650-SB	61.89
UV 650-MX	20.00
UV 650-064	11.15
UV 650-233	4.19
UV 650-TW	2.77

PANTONE 5615 C	Formula
UV 650-TW	67.10
UV 650-064	18.42
UV 650-127	7.34
UV 650-233	7.14

PANTONE 5625 C	Formula
UV 650-TW	81.49
UV 650-064	10.00
UV 650-127	4.37
UV 650-233	4.14

PANTONE 5635 C	Formula
UV 650-TW	92.16
UV 650-064	3.87
UV 650-127	2.01
UV 650-233	1.96

PANTONE 5645 C	Formula
UV 650-TW	95.50
UV 650-064	2.09
UV 650-127	1.21
UV 650-233	1.20

PANTONE 5655 C	Formula
UV 650-TW	96.88
UV 650-064	1.43
UV 650-233	0.86
UV 650-127	0.83

PANTONE 5665 C	Formula
UV 650-TW	97.92
UV 650-064	0.86
UV 650-233	0.63
UV 650-127	0.59

PANTONE 567 C	Formula
UV 650-SB	49.20
UV 650-325	33.63
UV 650-TW	17.17

PANTONE 568 C	Formula
UV 650-325	57.81
UV 650-TW	28.63
UV 650-114	7.77
UV 650-127	5.79

PANTONE 569 C	Formula
UV 650-TW	48.73
UV 650-325	46.56
UV 650-114	3.25
UV 650-127	1.46

PANTONE 570 C	Formula
UV 650-TW	91.81
UV 650-325	7.47
UV 650-127	0.72

# UVivid 650

PANTONE 571 C <b>UV 650-TW</b> <b>96.03</b> <b>UV 650-325</b> <b>3.43</b> <b>UV 650-127</b> <b>0.54</b>	Formula	PANTONE 572 C <b>UV 650-TW</b> <b>97.07</b> <b>UV 650-325</b> <b>2.50</b> <b>UV 650-127</b> <b>0.43</b>	Formula	PANTONE 573 C <b>UV 650-TW</b> <b>97.67</b> <b>UV 650-325</b> <b>1.97</b> <b>UV 650-127</b> <b>0.36</b>	Formula	PANTONE 574 C <b>UV 650-064</b> <b>35.75</b> <b>UV 650-SB</b> <b>31.05</b> <b>UV 650-TW</b> <b>29.45</b> <b>UV 650-230</b> <b>3.75</b>	Formula
PANTONE 575 C <b>UV 650-TW</b> <b>47.04</b> <b>UV 650-064</b> <b>35.29</b> <b>UV 650-SB</b> <b>12.62</b> <b>UV 650-230</b> <b>5.05</b>	Formula	PANTONE 576 C <b>UV 650-TW</b> <b>65.04</b> <b>UV 650-064</b> <b>22.76</b> <b>UV 650-114</b> <b>7.05</b> <b>UV 650-230</b> <b>5.15</b>	Formula	PANTONE 577 C <b>UV 650-TW</b> <b>92.19</b> <b>UV 650-064</b> <b>4.69</b> <b>UV 650-230</b> <b>1.83</b> <b>UV 650-114</b> <b>1.29</b>	Formula	PANTONE 578 C <b>UV 650-TW</b> <b>75.99</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-064</b> <b>2.23</b> <b>UV 650-SB</b> <b>1.09</b> <b>UV 650-230</b> <b>0.7</b>	Formula
PANTONE 579 C <b>UV 650-TW</b> <b>96.29</b> <b>UV 650-064</b> <b>2.17</b> <b>UV 650-SB</b> <b>0.94</b> <b>UV 650-230</b> <b>0.60</b>	Formula	PANTONE 580 C <b>UV 650-TW</b> <b>96.84</b> <b>UV 650-064</b> <b>1.77</b> <b>UV 650-230</b> <b>0.78</b> <b>UV 650-114</b> <b>0.61</b>	Formula	PANTONE 5743 C <b>UV 650-SB</b> <b>42.84</b> <b>UV 650-064</b> <b>33.44</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-230</b> <b>3.73</b>	Formula	PANTONE 5753 C <b>UV 650-066</b> <b>50.70</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>16.89</b> <b>UV 650-TW</b> <b>8.82</b> <b>UV 650-233</b> <b>3.59</b>	Formula
PANTONE 5763 C <b>UV 650-066</b> <b>48.38</b> <b>UV 650-TW</b> <b>36.22</b> <b>UV 650-SB</b> <b>12.94</b> <b>UV 650-233</b> <b>2.46</b>	Formula	PANTONE 5773 C <b>UV 650-TW</b> <b>49.59</b> <b>UV 650-066</b> <b>22.19</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>6.84</b> <b>UV 650-233</b> <b>1.38</b>	Formula	PANTONE 5783 C <b>UV 650-TW</b> <b>82.05</b> <b>UV 650-066</b> <b>12.44</b> <b>UV 650-SB</b> <b>4.66</b> <b>UV 650-233</b> <b>0.85</b>	Formula	PANTONE 5793 C <b>UV 650-TW</b> <b>91.22</b> <b>UV 650-066</b> <b>5.57</b> <b>UV 650-SB</b> <b>2.70</b> <b>UV 650-233</b> <b>0.51</b>	Formula

# UVivid 650

PANTONE 5803 C	Formula
UV 650-TW	74.24
UV 650-MX	20.00
UV 650-066	3.71
UV 650-SB	1.68
UV 650-233	0.37

PANTONE 5747 C	Formula
UV 650-066	66.96
UV 650-SB	27.86
UV 650-233	5.18

PANTONE 5757 C	Formula
UV 650-066	73.39
UV 650-TW	13.06
UV 650-SB	10.05
UV 650-233	3.50

PANTONE 5767 C	Formula
UV 650-066	50.68
UV 650-TW	40.54
UV 650-SB	6.75
UV 650-233	2.03

PANTONE 5777 C	Formula
UV 650-TW	64.27
UV 650-066	32.68
UV 650-230	1.79
UV 650-127	1.26

PANTONE 5787 C	Formula
UV 650-TW	86.72
UV 650-066	9.50
UV 650-325	2.43
UV 650-121	1.35

PANTONE 5797 C	Formula
UV 650-TW	95.35
UV 650-064	2.08
UV 650-114	1.57
UV 650-233	1.00

PANTONE 5807 C	Formula
UV 650-TW	97.68
UV 650-064	1.54
UV 650-127	0.46
UV 650-230	0.32

PANTONE 581 C	Formula
UV 650-066	70.08
UV 650-SB	19.47
UV 650-MX	7.79
UV 650-230	2.66

PANTONE 582 C	Formula
UV 650-064	41.25
UV 650-TW	29.38
UV 650-MX	20.00
UV 650-SB	8.27
UV 650-230	1.1

PANTONE 583 C	Formula
UV 650-066	53.03
UV 650-TW	29.36
UV 650-064	16.14
UV 650-230	1.47

PANTONE 584 C	Formula
UV 650-TW	85.93
UV 650-064	13.45
UV 650-230	0.62

PANTONE 585 C	Formula
UV 650-TW	93.08
UV 650-064	6.58
UV 650-230	0.34

PANTONE 586 C	Formula
UV 650-TW	75.68
UV 650-MX	20.00
UV 650-064	4.04
UV 650-230	0.28

PANTONE 587 C	Formula
UV 650-TW	94.64
UV 650-064	3.10
UV 650-066	2.00
UV 650-230	0.26

PANTONE 5815 C	Formula
UV 650-066	58.58
UV 650-SB	25.99
UV 650-MX	13.14
UV 650-230	2.29

# UVivid 650

PANTONE 5825 C <b>UV 650-066</b> <b>53.04</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-TW</b> <b>15.27</b> <b>UV 650-SB</b> <b>10.25</b> <b>UV 650-230</b> <b>1.44</b>	Formula	PANTONE 5835 C <b>UV 650-TW</b> <b>51.99</b> <b>UV 650-066</b> <b>42.70</b> <b>UV 650-SB</b> <b>3.91</b> <b>UV 650-230</b> <b>0.91</b> <b>UV 650-121</b> <b>0.49</b>	Formula	PANTONE 5845 C <b>UV 650-TW</b> <b>66.08</b> <b>UV 650-066</b> <b>30.13</b> <b>UV 650-230</b> <b>1.97</b> <b>UV 650-121</b> <b>1.82</b>	Formula	PANTONE 5855 C <b>UV 650-TW</b> <b>82.84</b> <b>UV 650-066</b> <b>14.90</b> <b>UV 650-230</b> <b>1.16</b> <b>UV 650-121</b> <b>1.10</b>	Formula
PANTONE 5865 C <b>UV 650-TW</b> <b>90.06</b> <b>UV 650-066</b> <b>8.48</b> <b>UV 650-230</b> <b>0.75</b> <b>UV 650-121</b> <b>0.71</b>	Formula	PANTONE 5875 C <b>UV 650-TW</b> <b>90.20</b> <b>UV 650-066</b> <b>5.53</b> <b>UV 650-MX</b> <b>3.16</b> <b>UV 650-230</b> <b>0.57</b> <b>UV 650-121</b> <b>0.54</b>	Formula	PANTONE 600 C <b>UV 650-TW</b> <b>78.14</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-064</b> <b>1.86</b>	Formula	PANTONE 601 C <b>UV 650-TW</b> <b>77.29</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-064</b> <b>2.71</b>	Formula
PANTONE 602 C <b>UV 650-TW</b> <b>95.30</b> <b>UV 650-064</b> <b>4.70</b>	Formula	PANTONE 603 C <b>UV 650-TW</b> <b>89.55</b> <b>UV 650-064</b> <b>9.95</b> <b>UV 650-SB</b> <b>0.50</b>	Formula	PANTONE 604 C <b>UV 650-TW</b> <b>61.84</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-064</b> <b>17.72</b> <b>UV 650-SB</b> <b>0.44</b>	Formula	PANTONE 605 C <b>UV 650-064</b> <b>45.43</b> <b>UV 650-TW</b> <b>33.56</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>1.01</b>	Formula
PANTONE 606 C <b>UV 650-064</b> <b>65.07</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-TW</b> <b>12.37</b> <b>UV 650-SB</b> <b>2.56</b>	Formula	PANTONE 607 C <b>UV 650-TW</b> <b>97.52</b> <b>UV 650-064</b> <b>2.01</b> <b>UV 650-SB</b> <b>0.47</b>	Formula	PANTONE 608 C <b>UV 650-TW</b> <b>76.58</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-064</b> <b>2.83</b> <b>UV 650-SB</b> <b>0.60</b>	Formula	PANTONE 609 C <b>UV 650-TW</b> <b>75.17</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-064</b> <b>4.06</b> <b>UV 650-SB</b> <b>0.77</b>	Formula

# UVivid 650

PANTONE 610 C <b>UV 650-TW</b> <b>89.87</b> <b>UV 650-064</b> <b>8.63</b> <b>UV 650-SB</b> <b>1.50</b>	Formula	PANTONE 611 C <b>UV 650-TW</b> <b>61.05</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-064</b> <b>16.93</b> <b>UV 650-SB</b> <b>2.03</b>	Formula	PANTONE 612 C <b>UV 650-064</b> <b>42.19</b> <b>UV 650-TW</b> <b>33.93</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-SB</b> <b>3.87</b>	Formula	PANTONE 613 C <b>UV 650-064</b> <b>52.69</b> <b>UV 650-TW</b> <b>21.51</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-SB</b> <b>5.79</b>	Formula
PANTONE 614 C <b>UV 650-TW</b> <b>97.31</b> <b>UV 650-064</b> <b>1.43</b> <b>UV 650-SB</b> <b>1.26</b>	Formula	PANTONE 615 C <b>UV 650-TW</b> <b>95.43</b> <b>UV 650-064</b> <b>2.62</b> <b>UV 650-SB</b> <b>1.95</b>	Formula	PANTONE 616 C <b>UV 650-TW</b> <b>93.84</b> <b>UV 650-064</b> <b>3.73</b> <b>UV 650-SB</b> <b>2.43</b>	Formula	PANTONE 617 C <b>UV 650-TW</b> <b>86.59</b> <b>UV 650-064</b> <b>5.59</b> <b>UV 650-SB</b> <b>4.19</b> <b>UV 650-066</b> <b>3.63</b>	Formula
PANTONE 618 C <b>UV 650-TW</b> <b>55.39</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-064</b> <b>17.57</b> <b>UV 650-SB</b> <b>7.04</b>	Formula	PANTONE 619 C <b>UV 650-TW</b> <b>42.66</b> <b>UV 650-064</b> <b>27.86</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>9.48</b>	Formula	PANTONE 620 C <b>UV 650-064</b> <b>37.53</b> <b>UV 650-TW</b> <b>28.90</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>13.57</b>	Formula	PANTONE 621 C <b>UV 650-TW</b> <b>97.90</b> <b>UV 650-325</b> <b>1.20</b> <b>UV 650-SB</b> <b>0.90</b>	Formula
PANTONE 622 C <b>UV 650-TW</b> <b>96.40</b> <b>UV 650-325</b> <b>2.47</b> <b>UV 650-164</b> <b>1.13</b>	Formula	PANTONE 623 C <b>UV 650-TW</b> <b>93.26</b> <b>UV 650-325</b> <b>3.70</b> <b>UV 650-SB</b> <b>1.75</b> <b>UV 650-164</b> <b>1.29</b>	Formula	PANTONE 624 C <b>UV 650-TW</b> <b>86.39</b> <b>UV 650-325</b> <b>8.68</b> <b>UV 650-164</b> <b>2.71</b> <b>UV 650-114</b> <b>1.82</b> <b>UV 650-064</b> <b>0.4</b>	Formula	PANTONE 625 C <b>UV 650-TW</b> <b>54.70</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-SB</b> <b>14.83</b> <b>UV 650-325</b> <b>9.84</b> <b>UV 650-064</b> <b>0.62</b>	Formula

# UVivid 650

PANTONE 626 C <b>UV 650-TW</b> 36.79 <b>UV 650-325</b> 33.86 <b>UV 650-SB</b> 24.68 <b>UV 650-114</b> 4.67	Formula	PANTONE 627 C <b>UV 650-325</b> 43.15 <b>UV 650-SB</b> 37.01 <b>UV 650-164</b> 10.65 <b>UV 650-MX</b> 9.19	Formula	PANTONE 628 C <b>UV 650-TW</b> 98.84 <b>UV 650-233</b> 1.16	Formula	PANTONE 629 C <b>UV 650-TW</b> 98.00 <b>UV 650-233</b> 2.00	Formula
PANTONE 630 C <b>UV 650-TW</b> 77.28 <b>UV 650-MX</b> 20.00 <b>UV 650-233</b> 2.72	Formula	PANTONE 631 C <b>UV 650-TW</b> 49.88 <b>UV 650-MX</b> 42.88 <b>UV 650-233</b> 4.99 <b>UV 650-325</b> 1.75 <b>UV 650-SB</b> 0.5	Formula	PANTONE 632 C <b>UV 650-TW</b> 60.73 <b>UV 650-MX</b> 20.00 <b>UV 650-230</b> 15.89 <b>UV 650-325</b> 1.71 <b>UV 650-SB</b> 1.67	Formula	PANTONE 633 C <b>UV 650-TW</b> 48.35 <b>UV 650-233</b> 34.23 <b>UV 650-325</b> 14.18 <b>UV 650-MX</b> 3.24	Formula
PANTONE 634 C <b>UV 650-233</b> 42.81 <b>UV 650-TW</b> 21.31 <b>UV 650-MX</b> 19.99 <b>UV 650-325</b> 13.58 <b>UV 650-SB</b> 2.31	Formula	PANTONE 635 C <b>UV 650-TW</b> 97.93 <b>UV 650-230</b> 2.07	Formula	PANTONE 636 C <b>UV 650-TW</b> 96.50 <b>UV 650-230</b> 3.50	Formula	PANTONE 637 C <b>UV 650-TW</b> 93.00 <b>UV 650-230</b> 7.00	Formula
PANTONE 638 C <b>UV 650-TW</b> 91.31 <b>UV 650-230</b> 8.22 <b>UV 650-066</b> 0.47	Formula	PANTONE 639 C <b>UV 650-TW</b> 58.73 <b>UV 650-230</b> 21.27 <b>UV 650-MX</b> 20.00	Formula	PANTONE 640 C <b>UV 650-TW</b> 48.78 <b>UV 650-230</b> 31.22 <b>UV 650-MX</b> 20.00	Formula	PANTONE 641 C <b>UV 650-230</b> 48.84 <b>UV 650-TW</b> 30.01 <b>UV 650-MX</b> 20.00 <b>UV 650-066</b> 1.15	Formula

# UVivid 650

PANTONE 642 C <b>UV 650-TW</b> <b>98.94</b> <b>UV 650-233</b> <b>0.58</b> <b>UV 650-127</b> <b>0.48</b>	Formula	PANTONE 643 C <b>UV 650-TW</b> <b>98.50</b> <b>UV 650-233</b> <b>0.87</b> <b>UV 650-127</b> <b>0.63</b>	Formula	PANTONE 644 C <b>UV 650-TW</b> <b>96.84</b> <b>UV 650-233</b> <b>1.86</b> <b>UV 650-127</b> <b>1.09</b> <b>UV 650-SB</b> <b>0.21</b>	Formula	PANTONE 645 C <b>UV 650-TW</b> <b>92.90</b> <b>UV 650-325</b> <b>2.30</b> <b>UV 650-127</b> <b>2.19</b> <b>UV 650-233</b> <b>1.75</b> <b>UV 650-SB</b> <b>0.86</b>	Formula
PANTONE 646 C <b>UV 650-TW</b> <b>69.41</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-233</b> <b>5.52</b> <b>UV 650-SB</b> <b>2.68</b> <b>UV 650-127</b> <b>2.38</b>	Formula	PANTONE 647 C <b>UV 650-TW</b> <b>48.93</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-233</b> <b>18.60</b> <b>UV 650-SB</b> <b>6.73</b> <b>UV 650-127</b> <b>5.75</b>	Formula	PANTONE 648 C <b>UV 650-233</b> <b>38.65</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-127</b> <b>17.09</b> <b>UV 650-SB</b> <b>13.07</b> <b>UV 650-TW</b> <b>11.2</b>	Formula	PANTONE 649 C <b>UV 650-TW</b> <b>98.40</b> <b>UV 650-165</b> <b>0.87</b> <b>UV 650-233</b> <b>0.73</b>	Formula
PANTONE 650 C <b>UV 650-TW</b> <b>97.74</b> <b>UV 650-165</b> <b>1.19</b> <b>UV 650-233</b> <b>1.07</b>	Formula	PANTONE 651 C <b>UV 650-TW</b> <b>95.75</b> <b>UV 650-165</b> <b>2.15</b> <b>UV 650-233</b> <b>2.10</b>	Formula	PANTONE 652 C <b>UV 650-TW</b> <b>90.74</b> <b>UV 650-233</b> <b>3.66</b> <b>UV 650-165</b> <b>2.89</b> <b>UV 650-SB</b> <b>2.71</b>	Formula	PANTONE 653 C <b>UV 650-TW</b> <b>49.63</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-233</b> <b>16.05</b> <b>UV 650-165</b> <b>9.59</b> <b>UV 650-SB</b> <b>4.74</b>	Formula
PANTONE 654 C <b>UV 650-233</b> <b>37.10</b> <b>UV 650-165</b> <b>22.94</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-TW</b> <b>10.98</b> <b>UV 650-SB</b> <b>8.97</b>	Formula	PANTONE 655 C <b>UV 650-165</b> <b>46.49</b> <b>UV 650-233</b> <b>37.09</b> <b>UV 650-SB</b> <b>16.42</b>	Formula	PANTONE 656 C <b>UV 650-TW</b> <b>98.96</b> <b>UV 650-127</b> <b>0.57</b> <b>UV 650-230</b> <b>0.47</b>	Formula	PANTONE 657 C <b>UV 650-TW</b> <b>98.42</b> <b>UV 650-233</b> <b>0.90</b> <b>UV 650-127</b> <b>0.68</b>	Formula



# UVivid 650

PANTONE 658 C <b>UV 650-TW</b> <b>97.18</b> <b>UV 650-233</b> <b>1.73</b> <b>UV 650-127</b> <b>1.09</b>	Formula	PANTONE 659 C <b>UV 650-TW</b> <b>95.29</b> <b>UV 650-233</b> <b>2.97</b> <b>UV 650-127</b> <b>1.23</b> <b>UV 650-SB</b> <b>0.51</b>	Formula	PANTONE 660 C <b>UV 650-TW</b> <b>63.53</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-233</b> <b>12.39</b> <b>UV 650-127</b> <b>4.08</b>	Formula	PANTONE 661 C <b>UV 650-233</b> <b>70.18</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-127</b> <b>9.82</b>	Formula
PANTONE 662 C <b>UV 650-233</b> <b>65.46</b> <b>UV 650-127</b> <b>25.28</b> <b>UV 650-MX</b> <b>9.26</b>	Formula	PANTONE 663 C <b>UV 650-TW</b> <b>99.20</b> <b>UV 650-127</b> <b>0.60</b> <b>UV 650-233</b> <b>0.20</b>	Formula	PANTONE 664 C <b>UV 650-TW</b> <b>99.00</b> <b>UV 650-127</b> <b>0.75</b> <b>UV 650-233</b> <b>0.25</b>	Formula	PANTONE 665 C <b>UV 650-TW</b> <b>98.31</b> <b>UV 650-127</b> <b>1.40</b> <b>UV 650-233</b> <b>0.29</b>	Formula
PANTONE 666 C <b>UV 650-TW</b> <b>93.38</b> <b>UV 650-127</b> <b>3.44</b> <b>UV 650-SB</b> <b>2.89</b> <b>UV 650-233</b> <b>0.29</b>	Formula	PANTONE 667 C <b>UV 650-TW</b> <b>81.55</b> <b>UV 650-SB</b> <b>9.44</b> <b>UV 650-127</b> <b>6.01</b> <b>UV 650-165</b> <b>3.00</b>	Formula	PANTONE 668 C <b>UV 650-TW</b> <b>67.96</b> <b>UV 650-127</b> <b>14.95</b> <b>UV 650-SB</b> <b>11.27</b> <b>UV 650-165</b> <b>5.82</b>	Formula	PANTONE 669 C <b>UV 650-127</b> <b>25.09</b> <b>UV 650-TW</b> <b>23.95</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>16.85</b> <b>UV 650-165</b> <b>14.11</b>	Formula
PANTONE 670 C <b>UV 650-TW</b> <b>98.69</b> <b>UV 650-127</b> <b>0.76</b> <b>UV 650-165</b> <b>0.55</b>	Formula	PANTONE 671 C <b>UV 650-TW</b> <b>96.77</b> <b>UV 650-165</b> <b>2.51</b> <b>UV 650-127</b> <b>0.72</b>	Formula	PANTONE 672 C <b>UV 650-TW</b> <b>92.65</b> <b>UV 650-165</b> <b>7.04</b> <b>UV 650-233</b> <b>0.31</b>	Formula	PANTONE 673 C <b>UV 650-TW</b> <b>88.74</b> <b>UV 650-165</b> <b>10.07</b> <b>UV 650-SB</b> <b>1.19</b>	Formula

# UVivid 650

<b>PANTONE</b> <b>674 C</b> <b>UV 650-TW</b> <b>69.22</b> <b>UV 650-165</b> <b>30.28</b> <b>UV 650-230</b> <b>0.50</b>	Formula	<b>PANTONE</b> <b>675 C</b> <b>UV 650-165</b> <b>51.84</b> <b>UV 650-TW</b> <b>25.31</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>2.85</b>	Formula	<b>PANTONE</b> <b>676 C</b> <b>UV 650-165</b> <b>86.16</b> <b>UV 650-TW</b> <b>9.04</b> <b>UV 650-SB</b> <b>4.80</b>	Formula	<b>PANTONE</b> <b>677 C</b> <b>UV 650-TW</b> <b>97.74</b> <b>UV 650-165</b> <b>1.92</b> <b>UV 650-230</b> <b>0.34</b>	Formula
<b>PANTONE</b> <b>678 C</b> <b>UV 650-TW</b> <b>97.04</b> <b>UV 650-165</b> <b>2.58</b> <b>UV 650-230</b> <b>0.38</b>	Formula	<b>PANTONE</b> <b>679 C</b> <b>UV 650-TW</b> <b>96.26</b> <b>UV 650-165</b> <b>3.32</b> <b>UV 650-230</b> <b>0.42</b>	Formula	<b>PANTONE</b> <b>680 C</b> <b>UV 650-TW</b> <b>89.89</b> <b>UV 650-165</b> <b>6.32</b> <b>UV 650-SB</b> <b>3.16</b> <b>UV 650-066</b> <b>0.63</b>	Formula	<b>PANTONE</b> <b>681 C</b> <b>UV 650-TW</b> <b>76.60</b> <b>UV 650-165</b> <b>17.78</b> <b>UV 650-SB</b> <b>5.62</b>	Formula
<b>PANTONE</b> <b>682 C</b> <b>UV 650-TW</b> <b>35.80</b> <b>UV 650-165</b> <b>31.64</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-066</b> <b>10.41</b> <b>UV 650-230</b> <b>2.14</b>	Formula	<b>PANTONE</b> <b>683 C</b> <b>UV 650-165</b> <b>44.33</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-SB</b> <b>13.07</b> <b>UV 650-066</b> <b>11.58</b> <b>UV 650-TW</b> <b>11.03</b>	Formula	<b>PANTONE</b> <b>684 C</b> <b>UV 650-TW</b> <b>97.80</b> <b>UV 650-165</b> <b>2.20</b>	Formula	<b>PANTONE</b> <b>685 C</b> <b>UV 650-TW</b> <b>95.94</b> <b>UV 650-165</b> <b>3.39</b> <b>UV 650-SB</b> <b>0.67</b>	Formula
<b>PANTONE</b> <b>686 C</b> <b>UV 650-TW</b> <b>93.41</b> <b>UV 650-165</b> <b>5.08</b> <b>UV 650-SB</b> <b>1.51</b>	Formula	<b>PANTONE</b> <b>687 C</b> <b>UV 650-TW</b> <b>86.13</b> <b>UV 650-165</b> <b>8.61</b> <b>UV 650-SB</b> <b>3.45</b> <b>UV 650-066</b> <b>1.81</b>	Formula	<b>PANTONE</b> <b>688 C</b> <b>UV 650-TW</b> <b>57.48</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-165</b> <b>17.04</b> <b>UV 650-SB</b> <b>5.47</b>	Formula	<b>PANTONE</b> <b>689 C</b> <b>UV 650-165</b> <b>35.49</b> <b>UV 650-TW</b> <b>34.38</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>10.13</b>	Formula

# UVivid 650

PANTONE 690 C <b>UV 650-165</b> <b>39.64</b> <b>UV 650-SB</b> <b>23.08</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-066</b> <b>17.28</b>	Formula	PANTONE 691 C <b>UV 650-TW</b> <b>98.82</b> <b>UV 650-165</b> <b>0.81</b> <b>UV 650-127</b> <b>0.37</b>	Formula	PANTONE 692 C <b>UV 650-TW</b> <b>97.00</b> <b>UV 650-165</b> <b>2.14</b> <b>UV 650-SB</b> <b>0.86</b>	Formula	PANTONE 693 C <b>UV 650-TW</b> <b>93.43</b> <b>UV 650-165</b> <b>3.87</b> <b>UV 650-SB</b> <b>1.85</b> <b>UV 650-114</b> <b>0.85</b>	Formula
PANTONE 694 C <b>UV 650-TW</b> <b>89.42</b> <b>UV 650-164</b> <b>5.52</b> <b>UV 650-SB</b> <b>4.14</b> <b>UV 650-114</b> <b>0.92</b>	Formula	PANTONE 695 C <b>UV 650-TW</b> <b>55.68</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-165</b> <b>15.44</b> <b>UV 650-114</b> <b>5.95</b> <b>UV 650-325</b> <b>2.92</b>	Formula	PANTONE 696 C <b>UV 650-TW</b> <b>46.97</b> <b>UV 650-165</b> <b>31.54</b> <b>UV 650-114</b> <b>12.10</b> <b>UV 650-SB</b> <b>9.39</b>	Formula	PANTONE 697 C <b>UV 650-TW</b> <b>43.63</b> <b>UV 650-164</b> <b>43.12</b> <b>UV 650-SB</b> <b>13.25</b>	Formula
PANTONE 698 C <b>UV 650-TW</b> <b>98.68</b> <b>UV 650-165</b> <b>1.10</b> <b>UV 650-127</b> <b>0.22</b>	Formula	PANTONE 699 C <b>UV 650-TW</b> <b>97.57</b> <b>UV 650-165</b> <b>2.43</b>	Formula	PANTONE 700 C <b>UV 650-TW</b> <b>92.77</b> <b>UV 650-165</b> <b>4.98</b> <b>UV 650-066</b> <b>2.25</b>	Formula	PANTONE 701 C <b>UV 650-TW</b> <b>91.96</b> <b>UV 650-164</b> <b>6.90</b> <b>UV 650-SB</b> <b>0.57</b> <b>UV 650-165</b> <b>0.57</b>	Formula
PANTONE 702 C <b>UV 650-TW</b> <b>53.51</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-165</b> <b>18.89</b> <b>UV 650-114</b> <b>6.27</b> <b>UV 650-SB</b> <b>1.33</b>	Formula	PANTONE 703 C <b>UV 650-TW</b> <b>57.71</b> <b>UV 650-121</b> <b>25.95</b> <b>UV 650-165</b> <b>15.40</b> <b>UV 650-230</b> <b>0.94</b>	Formula	PANTONE 704 C <b>UV 650-164</b> <b>51.21</b> <b>UV 650-TW</b> <b>23.11</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-SB</b> <b>5.68</b>	Formula	PANTONE 705 C <b>UV 650-TW</b> <b>98.46</b> <b>UV 650-165</b> <b>1.54</b>	Formula

# UVivid 650

PANTONE 706 C <b>UV 650-TW</b> <b>97.79</b> <b>UV 650-165</b> <b>2.21</b>	Formula	PANTONE 707 C <b>UV 650-TW</b> <b>95.43</b> <b>UV 650-165</b> <b>3.88</b> <b>UV 650-114</b> <b>0.69</b>	Formula	PANTONE 708 C <b>UV 650-TW</b> <b>94.41</b> <b>UV 650-164</b> <b>4.59</b> <b>UV 650-121</b> <b>1.00</b>	Formula	PANTONE 709 C <b>UV 650-TW</b> <b>63.38</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-121</b> <b>9.55</b> <b>UV 650-165</b> <b>7.07</b>	Formula
PANTONE 710 C <b>UV 650-TW</b> <b>51.69</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-121</b> <b>18.08</b> <b>UV 650-165</b> <b>10.22</b>	Formula	PANTONE 711 C <b>UV 650-TW</b> <b>40.83</b> <b>UV 650-121</b> <b>33.13</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-164</b> <b>5.74</b> <b>UV 650-230</b> <b>0.3</b>	Formula	PANTONE 712 C <b>UV 650-TW</b> <b>95.53</b> <b>UV 650-114</b> <b>3.11</b> <b>UV 650-066</b> <b>1.36</b>	Formula	PANTONE 713 C <b>UV 650-TW</b> <b>91.84</b> <b>UV 650-114</b> <b>4.54</b> <b>UV 650-066</b> <b>3.62</b>	Formula
PANTONE 714 C <b>UV 650-TW</b> <b>63.25</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-066</b> <b>9.20</b> <b>UV 650-114</b> <b>7.55</b>	Formula	PANTONE 715 C <b>UV 650-TW</b> <b>30.46</b> <b>UV 650-MX</b> <b>30.46</b> <b>UV 650-066</b> <b>25.38</b> <b>UV 650-114</b> <b>13.20</b> <b>UV 650-SB</b> <b>0.5</b>	Formula	PANTONE 716 C <b>UV 650-066</b> <b>45.83</b> <b>UV 650-114</b> <b>22.56</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-TW</b> <b>11.09</b> <b>UV 650-230</b> <b>0.52</b>	Formula	PANTONE 717 C <b>UV 650-064</b> <b>41.02</b> <b>UV 650-114</b> <b>37.97</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-233</b> <b>1.01</b>	Formula
PANTONE 718 C <b>UV 650-114</b> <b>55.30</b> <b>UV 650-064</b> <b>42.91</b> <b>UV 650-230</b> <b>1.79</b>	Formula	PANTONE 719 C <b>UV 650-TW</b> <b>76.82</b> <b>UV 650-MX</b> <b>20.00</b> <b>UV 650-114</b> <b>2.86</b> <b>UV 650-230</b> <b>0.32</b>	Formula	PANTONE 720 C <b>UV 650-TW</b> <b>89.63</b> <b>UV 650-114</b> <b>5.13</b> <b>UV 650-066</b> <b>4.71</b> <b>UV 650-233</b> <b>0.53</b>	Formula	PANTONE 721 C <b>UV 650-TW</b> <b>82.85</b> <b>UV 650-066</b> <b>8.39</b> <b>UV 650-114</b> <b>7.99</b> <b>UV 650-233</b> <b>0.77</b>	Formula

# UVivid 650

PANTONE 722 C <b>UV 650-TW</b> 41.29 <b>UV 650-066</b> 22.21 <b>UV 650-MX</b> 20.00 <b>UV 650-114</b> 15.03 <b>UV 650-233</b> 1.47	Formula	PANTONE 723 C <b>UV 650-066</b> 38.32 <b>UV 650-MX</b> 20.01 <b>UV 650-114</b> 18.27 <b>UV 650-TW</b> 16.06 <b>UV 650-SB</b> 7.34	Formula	PANTONE 724 C <b>UV 650-066</b> 56.70 <b>UV 650-114</b> 29.70 <b>UV 650-SB</b> 13.60	Formula	PANTONE 725 C <b>UV 650-064</b> 43.77 <b>UV 650-114</b> 36.14 <b>UV 650-SB</b> 20.09	Formula
PANTONE 726 C <b>UV 650-TW</b> 95.47 <b>UV 650-114</b> 3.17 <b>UV 650-066</b> 0.86 <b>UV 650-233</b> 0.50	Formula	PANTONE 727 C <b>UV 650-TW</b> 92.71 <b>UV 650-114</b> 5.01 <b>UV 650-066</b> 1.53 <b>UV 650-233</b> 0.75	Formula	PANTONE 728 C <b>UV 650-TW</b> 69.22 <b>UV 650-MX</b> 20.01 <b>UV 650-114</b> 7.31 <b>UV 650-066</b> 2.38 <b>UV 650-233</b> 1.08	Formula	PANTONE 729 C <b>UV 650-TW</b> 49.08 <b>UV 650-MX</b> 20.00 <b>UV 650-066</b> 13.82 <b>UV 650-114</b> 10.51 <b>UV 650-SB</b> 6.59	Formula
PANTONE 730 C <b>UV 650-066</b> 27.07 <b>UV 650-TW</b> 26.75 <b>UV 650-MX</b> 20.01 <b>UV 650-114</b> 16.22 <b>UV 650-SB</b> 9.95	Formula	PANTONE 731 C <b>UV 650-066</b> 50.58 <b>UV 650-114</b> 27.77 <b>UV 650-SB</b> 21.65	Formula	PANTONE 732 C <b>UV 650-066</b> 50.20 <b>UV 650-SB</b> 28.61 <b>UV 650-114</b> 21.19	Formula	PANTONE 7401 C <b>UV 650-TW</b> 98.34 <b>UV 650-064</b> 1.29 <b>UV 650-121</b> 0.37	Formula
PANTONE 7402 C <b>UV 650-TW</b> 96.76 <b>UV 650-064</b> 2.57 <b>UV 650-165</b> 0.67	Formula	PANTONE 7403 C <b>UV 650-TW</b> 92.52 <b>UV 650-064</b> 6.23 <b>UV 650-165</b> 1.25	Formula	PANTONE 7404 C <b>UV 650-TW</b> 78.25 <b>UV 650-064</b> 21.53 <b>UV 650-127</b> 0.22	Formula	PANTONE 7405 C <b>UV 650-TW</b> 30.55 <b>UV 650-064</b> 29.97 <b>UV 650-MX</b> 20.01 <b>UV 650-066</b> 18.59 <b>UV 650-SB</b> 0.88	Formula

# UVivid 650

PANTONE 7406 C	Formula
UV 650-066	74.62
UV 650-MX	20.00
UV 650-064	4.47
UV 650-325	0.91

PANTONE 7407 C	Formula
UV 650-TW	50.56
UV 650-066	44.46
UV 650-SB	3.25
UV 650-165	1.73

PANTONE 7408 C	Formula
UV 650-066	79.51
UV 650-MX	20.00
UV 650-233	0.49

PANTONE 7409 C	Formula
UV 650-TW	47.18
UV 650-064	30.93
UV 650-MX	20.03
UV 650-164	1.86

PANTONE 7410 C	Formula
UV 650-TW	68.26
UV 650-MX	20.00
UV 650-114	8.74
UV 650-066	3.00

PANTONE 7411 C	Formula
UV 650-TW	75.29
UV 650-064	18.77
UV 650-165	5.62
UV 650-230	0.32

PANTONE 7412 C	Formula
UV 650-066	33.71
UV 650-TW	26.57
UV 650-MX	20.01
UV 650-114	15.76
UV 650-SB	3.95

PANTONE 7413 C	Formula
UV 650-066	72.17
UV 650-MX	20.01
UV 650-165	7.15
UV 650-233	0.67

PANTONE 7414 C	Formula
UV 650-066	61.06
UV 650-114	21.13
UV 650-TW	11.33
UV 650-SB	6.48

PANTONE 7415 C	Formula
UV 650-TW	96.30
UV 650-121	2.15
UV 650-064	1.31
UV 650-233	0.24

PANTONE 7416 C	Formula
UV 650-TW	64.97
UV 650-064	17.36
UV 650-165	16.56
UV 650-164	1.11

PANTONE 7417 C	Formula
UV 650-TW	47.73
UV 650-064	26.37
UV 650-165	18.71
UV 650-121	7.19

PANTONE 7418 C	Formula
UV 650-TW	53.88
UV 650-121	24.79
UV 650-MX	19.99
UV 650-325	1.34

PANTONE 7419 C	Formula
UV 650-TW	51.20
UV 650-165	28.44
UV 650-114	18.81
UV 650-233	1.55

PANTONE 7420 C	Formula
UV 650-TW	33.40
UV 650-165	30.96
UV 650-121	28.42
UV 650-SB	7.22

PANTONE 7421 C	Formula
UV 650-165	32.73
UV 650-114	23.96
UV 650-SB	23.31
UV 650-MX	20.00

# UVivid 650

PANTONE 7422 C	Formula
<b>UV 650-TW</b>	<b>98.33</b>
<b>UV 650-165</b>	<b>1.67</b>

PANTONE 7423 C	Formula
<b>UV 650-TW</b>	<b>80.19</b>
<b>UV 650-164</b>	<b>9.94</b>
<b>UV 650-165</b>	<b>9.87</b>

PANTONE 7424 C	Formula
<b>UV 650-MX</b>	<b>40.00</b>
<b>UV 650-165</b>	<b>27.35</b>
<b>UV 650-TW</b>	<b>27.11</b>
<b>UV 650-121</b>	<b>5.54</b>

PANTONE 7425 C	Formula
<b>UV 650-MX</b>	<b>40.00</b>
<b>UV 650-165</b>	<b>26.55</b>
<b>UV 650-TW</b>	<b>16.95</b>
<b>UV 650-121</b>	<b>14.91</b>
<b>UV 650-325</b>	<b>1.59</b>

PANTONE 7426 C	Formula
<b>UV 650-TW</b>	<b>34.85</b>
<b>UV 650-121</b>	<b>32.26</b>
<b>UV 650-165</b>	<b>27.91</b>
<b>UV 650-SB</b>	<b>4.98</b>

PANTONE 7427 C	Formula
<b>UV 650-121</b>	<b>65.14</b>
<b>UV 650-TW</b>	<b>25.54</b>
<b>UV 650-SB</b>	<b>9.32</b>

PANTONE 7428 C	Formula
<b>UV 650-SB</b>	<b>40.13</b>
<b>UV 650-121</b>	<b>30.58</b>
<b>UV 650-165</b>	<b>21.68</b>
<b>UV 650-TW</b>	<b>7.61</b>

PANTONE 7429 C	Formula
<b>UV 650-TW</b>	<b>97.89</b>
<b>UV 650-164</b>	<b>1.24</b>
<b>UV 650-127</b>	<b>0.87</b>

PANTONE 7430 C	Formula
<b>UV 650-TW</b>	<b>95.22</b>
<b>UV 650-165</b>	<b>2.30</b>
<b>UV 650-164</b>	<b>1.99</b>
<b>UV 650-233</b>	<b>0.49</b>

PANTONE 7431 C	Formula
<b>UV 650-TW</b>	<b>85.56</b>
<b>UV 650-165</b>	<b>9.08</b>
<b>UV 650-SB</b>	<b>3.26</b>
<b>UV 650-121</b>	<b>2.10</b>

PANTONE 7432 C	Formula
<b>UV 650-TW</b>	<b>74.61</b>
<b>UV 650-165</b>	<b>14.87</b>
<b>UV 650-121</b>	<b>9.05</b>
<b>UV 650-230</b>	<b>1.47</b>

PANTONE 7433 C	Formula
<b>UV 650-TW</b>	<b>33.09</b>
<b>UV 650-MX</b>	<b>25.00</b>
<b>UV 650-164</b>	<b>20.19</b>
<b>UV 650-165</b>	<b>19.62</b>
<b>UV 650-230</b>	<b>2.1</b>

PANTONE 7434 C	Formula
<b>UV 650-TW</b>	<b>25.51</b>
<b>UV 650-165</b>	<b>25.39</b>
<b>UV 650-MX</b>	<b>25.00</b>
<b>UV 650-121</b>	<b>21.18</b>
<b>UV 650-230</b>	<b>2.92</b>

PANTONE 7435 C	Formula
<b>UV 650-165</b>	<b>34.31</b>
<b>UV 650-MX</b>	<b>23.83</b>
<b>UV 650-TW</b>	<b>14.87</b>
<b>UV 650-SB</b>	<b>13.50</b>
<b>UV 650-121</b>	<b>13.49</b>

PANTONE 7436 C	Formula
<b>UV 650-TW</b>	<b>98.97</b>
<b>UV 650-127</b>	<b>0.79</b>
<b>UV 650-165</b>	<b>0.24</b>

PANTONE 7437 C	Formula
<b>UV 650-TW</b>	<b>97.36</b>
<b>UV 650-127</b>	<b>1.69</b>
<b>UV 650-165</b>	<b>0.95</b>

# UVivid 650

PANTONE 7438 C <b>UV 650-TW</b> <b>54.35</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-165</b> <b>3.70</b> <b>UV 650-127</b> <b>1.95</b>	Formula	PANTONE 7439 C <b>UV 650-TW</b> <b>89.59</b> <b>UV 650-165</b> <b>8.13</b> <b>UV 650-233</b> <b>1.60</b> <b>UV 650-164</b> <b>0.68</b>	Formula	PANTONE 7440 C <b>UV 650-TW</b> <b>82.58</b> <b>UV 650-165</b> <b>13.26</b> <b>UV 650-SB</b> <b>2.75</b> <b>UV 650-233</b> <b>1.41</b>	Formula	PANTONE 7441 C <b>UV 650-TW</b> <b>47.39</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-127</b> <b>7.90</b> <b>UV 650-165</b> <b>4.71</b>	Formula
PANTONE 7442 C <b>UV 650-TW</b> <b>44.51</b> <b>UV 650-MX</b> <b>40.00</b> <b>UV 650-127</b> <b>15.49</b>	Formula	PANTONE 7443 C <b>UV 650-TW</b> <b>98.88</b> <b>UV 650-127</b> <b>0.78</b> <b>UV 650-233</b> <b>0.34</b>	Formula	PANTONE 7444 C <b>UV 650-TW</b> <b>97.40</b> <b>UV 650-127</b> <b>1.72</b> <b>UV 650-233</b> <b>0.88</b>	Formula	PANTONE 7445 C <b>UV 650-TW</b> <b>95.73</b> <b>UV 650-127</b> <b>1.74</b> <b>UV 650-233</b> <b>1.39</b> <b>UV 650-164</b> <b>1.14</b>	Formula
PANTONE 7446 C <b>UV 650-TW</b> <b>73.76</b> <b>UV 650-MX</b> <b>19.99</b> <b>UV 650-127</b> <b>4.50</b> <b>UV 650-233</b> <b>1.75</b>	Formula	PANTONE 7447 C <b>UV 650-TW</b> <b>63.84</b> <b>UV 650-127</b> <b>20.32</b> <b>UV 650-SB</b> <b>11.38</b> <b>UV 650-165</b> <b>4.46</b>	Formula	PANTONE 7448 C <b>UV 650-TW</b> <b>34.89</b> <b>UV 650-SB</b> <b>33.98</b> <b>UV 650-165</b> <b>22.15</b> <b>UV 650-127</b> <b>8.98</b>	Formula	PANTONE 7449 C <b>UV 650-SB</b> <b>44.80</b> <b>UV 650-TW</b> <b>20.03</b> <b>UV 650-165</b> <b>19.00</b> <b>UV 650-121</b> <b>16.17</b>	Formula
PANTONE 7450 C <b>UV 650-TW</b> <b>98.21</b> <b>UV 650-127</b> <b>1.00</b> <b>UV 650-233</b> <b>0.79</b>	Formula	PANTONE 7451 C <b>UV 650-TW</b> <b>94.77</b> <b>UV 650-233</b> <b>3.16</b> <b>UV 650-127</b> <b>2.07</b>	Formula	PANTONE 7452 C <b>UV 650-TW</b> <b>72.66</b> <b>UV 650-MX</b> <b>20.01</b> <b>UV 650-127</b> <b>3.79</b> <b>UV 650-233</b> <b>3.54</b>	Formula	PANTONE 7453 C <b>UV 650-TW</b> <b>93.86</b> <b>UV 650-233</b> <b>4.05</b> <b>UV 650-127</b> <b>2.09</b>	Formula



# UVivid 650

PANTONE 7454 C <b>UV 650-TW</b> 86.44 <b>UV 650-233</b> 6.96 <b>UV 650-165</b> 4.01 <b>UV 650-SB</b> 2.59	Formula	PANTONE 7455 C <b>UV 650-TW</b> 58.80 <b>UV 650-MX</b> 20.00 <b>UV 650-233</b> 13.08 <b>UV 650-127</b> 8.12	Formula	PANTONE 7456 C <b>UV 650-TW</b> 82.49 <b>UV 650-233</b> 7.52 <b>UV 650-165</b> 5.64 <b>UV 650-127</b> 4.35	Formula	PANTONE 7457 C <b>UV 650-TW</b> 98.76 <b>UV 650-230</b> 0.88 <b>UV 650-127</b> 0.36	Formula
PANTONE 7458 C <b>UV 650-TW</b> 93.38 <b>UV 650-230</b> 4.45 <b>UV 650-165</b> 1.47 <b>UV 650-SB</b> 0.70	Formula	PANTONE 7459 C <b>UV 650-TW</b> 79.63 <b>UV 650-233</b> 8.74 <b>UV 650-MX</b> 8.44 <b>UV 650-SB</b> 3.19	Formula	PANTONE 7460 C <b>UV 650-TW</b> 51.76 <b>UV 650-230</b> 26.92 <b>UV 650-MX</b> 20.00 <b>UV 650-325</b> 1.32	Formula	PANTONE 7461 C <b>UV 650-TW</b> 74.87 <b>UV 650-233</b> 23.85 <b>UV 650-SB</b> 1.28	Formula
PANTONE 7462 C <b>UV 650-TW</b> 50.84 <b>UV 650-233</b> 34.24 <b>UV 650-165</b> 8.29 <b>UV 650-SB</b> 6.63	Formula	PANTONE 7463 C <b>UV 650-233</b> 36.99 <b>UV 650-SB</b> 31.79 <b>UV 650-127</b> 15.72 <b>UV 650-TW</b> 15.50	Formula	PANTONE 7464 C <b>UV 650-TW</b> 97.62 <b>UV 650-233</b> 1.97 <b>UV 650-064</b> 0.41	Formula	PANTONE 7465 C <b>UV 650-TW</b> 70.98 <b>UV 650-MX</b> 19.99 <b>UV 650-230</b> 4.50 <b>UV 650-325</b> 3.25 <b>UV 650-064</b> 1.28	Formula
PANTONE 7466 C <b>UV 650-TW</b> 69.65 <b>UV 650-325</b> 28.84 <b>UV 650-127</b> 1.51	Formula	PANTONE 7467 C <b>UV 650-TW</b> 51.55 <b>UV 650-MX</b> 20.00 <b>UV 650-325</b> 15.31 <b>UV 650-230</b> 13.14	Formula	PANTONE 7468 C <b>UV 650-TW</b> 64.91 <b>UV 650-230</b> 28.43 <b>UV 650-SB</b> 5.75 <b>UV 650-165</b> 0.91	Formula	PANTONE 7469 C <b>UV 650-230</b> 55.22 <b>UV 650-TW</b> 40.85 <b>UV 650-114</b> 3.93	Formula

# UVivid 650

PANTONE 7470 C	Formula
UV 650-233	44.75
UV 650-TW	31.06
UV 650-066	24.19

PANTONE 7471 C	Formula
UV 650-TW	95.64
UV 650-325	2.78
UV 650-230	1.58

PANTONE 7472 C	Formula
UV 650-TW	88.44
UV 650-230	5.88
UV 650-066	5.45
UV 650-121	0.23

PANTONE 7473 C	Formula
UV 650-TW	73.01
UV 650-325	22.07
UV 650-121	3.13
UV 650-233	1.79

PANTONE 7474 C	Formula
UV 650-TW	42.29
UV 650-MX	19.99
UV 650-230	18.55
UV 650-325	12.03
UV 650-SB	7.14

PANTONE 7475 C	Formula
UV 650-TW	53.24
UV 650-MX	19.99
UV 650-SB	12.67
UV 650-230	8.41
UV 650-066	5.69

PANTONE 7476 C	Formula
UV 650-230	35.66
UV 650-TW	22.94
UV 650-MX	19.99
UV 650-114	16.33
UV 650-325	5.08

PANTONE 7477 C	Formula
UV 650-TW	45.02
UV 650-233	35.19
UV 650-114	19.15
UV 650-164	0.64

PANTONE 7478 C	Formula
UV 650-TW	95.69
UV 650-325	3.81
UV 650-064	0.50

PANTONE 7479 C	Formula
UV 650-TW	61.35
UV 650-MX	20.01
UV 650-325	13.56
UV 650-064	5.08

PANTONE 7480 C	Formula
UV 650-TW	47.31
UV 650-325	26.29
UV 650-MX	19.99
UV 650-064	6.41

PANTONE 7481 C	Formula
UV 650-TW	36.44
UV 650-325	29.71
UV 650-MX	20.00
UV 650-064	13.85

PANTONE 7482 C	Formula
UV 650-TW	37.29
UV 650-325	25.32
UV 650-MX	19.99
UV 650-064	12.45
UV 650-230	4.95

PANTONE 7483 C	Formula
UV 650-066	36.18
UV 650-325	27.35
UV 650-SB	22.43
UV 650-TW	14.04

PANTONE 7484 C	Formula
UV 650-325	58.01
UV 650-TW	18.96
UV 650-SB	15.63
UV 650-114	7.40

PANTONE 7485 C	Formula
UV 650-TW	99.05
UV 650-064	0.53
UV 650-233	0.42

# UVivid 650

PANTONE 7486 C	Formula
UV 650-TW	76.30
UV 650-MX	20.00
UV 650-064	2.49
UV 650-325	0.62
UV 650-230	0.59

PANTONE 7487 C	Formula
UV 650-TW	66.99
UV 650-MX	20.00
UV 650-064	7.99
UV 650-325	5.02

PANTONE 7488 C	Formula
UV 650-TW	53.75
UV 650-MX	20.00
UV 650-064	17.67
UV 650-325	8.58

PANTONE 7489 C	Formula
UV 650-TW	66.18
UV 650-064	19.23
UV 650-066	9.65
UV 650-233	4.94

PANTONE 7490 C	Formula
UV 650-TW	45.75
UV 650-064	25.59
UV 650-MX	20.00
UV 650-233	4.74
UV 650-SB	3.92

PANTONE 7491 C	Formula
UV 650-066	70.85
UV 650-TW	21.28
UV 650-230	5.61
UV 650-164	2.26

PANTONE 7492 C	Formula
UV 650-TW	93.55
UV 650-064	5.14
UV 650-233	0.87
UV 650-121	0.44

PANTONE 7493 C	Formula
UV 650-TW	74.00
UV 650-MX	20.00
UV 650-064	2.90
UV 650-SB	2.47
UV 650-233	0.63

PANTONE 7494 C	Formula
UV 650-TW	71.95
UV 650-MX	18.79
UV 650-SB	5.21
UV 650-064	3.01
UV 650-230	1.04

PANTONE 7495 C	Formula
UV 650-066	60.40
UV 650-MX	20.00
UV 650-TW	14.54
UV 650-230	3.82
UV 650-121	1.24

PANTONE 7496 C	Formula
UV 650-066	91.26
UV 650-230	6.49
UV 650-165	2.25

PANTONE 7497 C	Formula
UV 650-TW	49.10
UV 650-SB	21.71
UV 650-MX	20.00
UV 650-064	6.80
UV 650-114	2.39

PANTONE 7498 C	Formula
UV 650-064	36.63
UV 650-TW	31.20
UV 650-SB	29.94
UV 650-233	2.23

PANTONE 7499 C	Formula
UV 650-TW	98.84
UV 650-064	0.97
UV 650-127	0.19

PANTONE 7500 C	Formula
UV 650-TW	97.39
UV 650-064	1.63
UV 650-SB	0.59
UV 650-127	0.39

PANTONE 7501 C	Formula
UV 650-TW	90.98
UV 650-066	7.40
UV 650-SB	1.19
UV 650-127	0.43

# UVivid 650

PANTONE 7502 C	Formula
UV 650-TW	84.50
UV 650-066	11.97
UV 650-SB	2.95
UV 650-164	0.58

PANTONE 7503 C	Formula
UV 650-TW	45.37
UV 650-066	31.14
UV 650-MX	20.00
UV 650-127	2.20
UV 650-230	1.29

PANTONE 7504 C	Formula
UV 650-TW	69.57
UV 650-SB	13.54
UV 650-064	11.50
UV 650-164	5.39

PANTONE 7505 C	Formula
UV 650-TW	25.60
UV 650-066	23.07
UV 650-MX	20.01
UV 650-SB	19.45
UV 650-114	11.87

PANTONE 7506 C	Formula
UV 650-TW	97.85
UV 650-064	1.14
UV 650-165	0.76
UV 650-SB	0.25

PANTONE 7507 C	Formula
UV 650-TW	93.73
UV 650-066	4.76
UV 650-114	1.30
UV 650-121	0.21

PANTONE 7508 C	Formula
UV 650-TW	80.97
UV 650-066	16.54
UV 650-164	1.00
UV 650-SB	1.49

PANTONE 7509 C	Formula
UV 650-TW	64.83
UV 650-066	30.84
UV 650-165	2.20
UV 650-SB	2.13

PANTONE 7510 C	Formula
UV 650-TW	63.28
UV 650-064	20.85
UV 650-114	10.53
UV 650-SB	5.34

PANTONE 7511 C	Formula
UV 650-064	41.42
UV 650-TW	35.63
UV 650-114	15.38
UV 650-SB	7.57

PANTONE 7512 C	Formula
UV 650-064	47.65
UV 650-TW	22.59
UV 650-114	19.79
UV 650-SB	9.97

PANTONE 7513 C	Formula
UV 650-TW	96.11
UV 650-114	2.75
UV 650-127	0.63
UV 650-SB	0.51

PANTONE 7514 C	Formula
UV 650-TW	84.88
UV 650-066	10.18
UV 650-121	2.70
UV 650-SB	2.24

PANTONE 7515 C	Formula
UV 650-TW	79.57
UV 650-114	12.35
UV 650-SB	5.64
UV 650-066	2.44

PANTONE 7516 C	Formula
UV 650-114	35.09
UV 650-066	28.57
UV 650-TW	22.69
UV 650-SB	13.65

PANTONE 7517 C	Formula
UV 650-114	45.18
UV 650-064	20.67
UV 650-SB	19.62
UV 650-TW	14.53

# UVivid 650

PANTONE 7518 C	Formula
<b>UV 650-TW</b>	<b>36.13</b>
<b>UV 650-SB</b>	<b>28.06</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-114</b>	<b>9.60</b>
<b>UV 650-121</b>	<b>6.21</b>

PANTONE 7519 C	Formula
<b>UV 650-SB</b>	<b>33.34</b>
<b>UV 650-066</b>	<b>32.83</b>
<b>UV 650-TW</b>	<b>26.97</b>
<b>UV 650-164</b>	<b>6.86</b>

PANTONE 7520 C	Formula
<b>UV 650-TW</b>	<b>96.82</b>
<b>UV 650-114</b>	<b>2.47</b>
<b>UV 650-127</b>	<b>0.71</b>

PANTONE 7521 C	Formula
<b>UV 650-TW</b>	<b>91.20</b>
<b>UV 650-121</b>	<b>4.37</b>
<b>UV 650-064</b>	<b>3.28</b>
<b>UV 650-233</b>	<b>1.15</b>

PANTONE 7522 C	Formula
<b>UV 650-TW</b>	<b>56.06</b>
<b>UV 650-066</b>	<b>30.76</b>
<b>UV 650-121</b>	<b>11.35</b>
<b>UV 650-230</b>	<b>1.83</b>

PANTONE 7523 C	Formula
<b>UV 650-TW</b>	<b>63.41</b>
<b>UV 650-114</b>	<b>17.15</b>
<b>UV 650-165</b>	<b>11.60</b>
<b>UV 650-SB</b>	<b>7.84</b>

PANTONE 7524 C	Formula
<b>UV 650-TW</b>	<b>59.72</b>
<b>UV 650-114</b>	<b>19.77</b>
<b>UV 650-121</b>	<b>11.12</b>
<b>UV 650-SB</b>	<b>9.39</b>

PANTONE 7525 C	Formula
<b>UV 650-TW</b>	<b>63.53</b>
<b>UV 650-121</b>	<b>15.30</b>
<b>UV 650-064</b>	<b>14.96</b>
<b>UV 650-325</b>	<b>6.21</b>

PANTONE 7526 C	Formula
<b>UV 650-114</b>	<b>64.73</b>
<b>UV 650-SB</b>	<b>16.67</b>
<b>UV 650-TW</b>	<b>12.98</b>
<b>UV 650-064</b>	<b>5.62</b>

PANTONE 7527 C	Formula
<b>UV 650-TW</b>	<b>97.73</b>
<b>UV 650-325</b>	<b>1.18</b>
<b>UV 650-121</b>	<b>1.09</b>

PANTONE 7528 C	Formula
<b>UV 650-TW</b>	<b>95.34</b>
<b>UV 650-SB</b>	<b>3.76</b>
<b>UV 650-165</b>	<b>0.49</b>
<b>UV 650-114</b>	<b>0.41</b>

PANTONE 7529 C	Formula
<b>UV 650-TW</b>	<b>89.05</b>
<b>UV 650-066</b>	<b>5.98</b>
<b>UV 650-SB</b>	<b>3.68</b>
<b>UV 650-127</b>	<b>1.29</b>

PANTONE 7530 C	Formula
<b>UV 650-TW</b>	<b>63.96</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-SB</b>	<b>8.13</b>
<b>UV 650-066</b>	<b>5.73</b>
<b>UV 650-165</b>	<b>2.18</b>

PANTONE 7531 C	Formula
<b>UV 650-TW</b>	<b>54.55</b>
<b>UV 650-SB</b>	<b>20.21</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-114</b>	<b>1.43</b>
<b>UV 650-066</b>	<b>3.81</b>

PANTONE 7532 C	Formula
<b>UV 650-TW</b>	<b>30.37</b>
<b>UV 650-SB</b>	<b>29.82</b>
<b>UV 650-MX</b>	<b>20.00</b>
<b>UV 650-114</b>	<b>10.65</b>
<b>UV 650-066</b>	<b>9.16</b>

PANTONE 7533 C	Formula
<b>UV 650-SB</b>	<b>48.78</b>
<b>UV 650-MX</b>	<b>16.17</b>
<b>UV 650-066</b>	<b>15.49</b>
<b>UV 650-114</b>	<b>11.47</b>
<b>UV 650-TW</b>	<b>8.09</b>

# UVivid 650

PANTONE 7534 C	Formula
<b>UV 650-TW</b>	<b>96.20</b>
<b>UV 650-066</b>	<b>2.84</b>
<b>UV 650-127</b>	<b>0.63</b>
<b>UV 650-233</b>	<b>0.33</b>

PANTONE 7535 C	Formula
<b>UV 650-TW</b>	<b>87.97</b>
<b>UV 650-066</b>	<b>9.78</b>
<b>UV 650-127</b>	<b>1.49</b>
<b>UV 650-233</b>	<b>0.76</b>

PANTONE 7536 C	Formula
<b>UV 650-TW</b>	<b>79.49</b>
<b>UV 650-066</b>	<b>15.73</b>
<b>UV 650-127</b>	<b>2.79</b>
<b>UV 650-325</b>	<b>1.99</b>

PANTONE 7537 C	Formula
<b>UV 650-TW</b>	<b>88.04</b>
<b>UV 650-066</b>	<b>7.51</b>
<b>UV 650-325</b>	<b>2.26</b>
<b>UV 650-127</b>	<b>2.19</b>

PANTONE 7538 C	Formula
<b>UV 650-TW</b>	<b>83.11</b>
<b>UV 650-066</b>	<b>10.62</b>
<b>UV 650-325</b>	<b>3.15</b>
<b>UV 650-127</b>	<b>3.12</b>

PANTONE 7539 C	Formula
<b>UV 650-TW</b>	<b>78.18</b>
<b>UV 650-066</b>	<b>14.02</b>
<b>UV 650-127</b>	<b>4.22</b>
<b>UV 650-325</b>	<b>3.58</b>

PANTONE 7540 C	Formula
<b>UV 650-066</b>	<b>43.69</b>
<b>UV 650-TW</b>	<b>35.60</b>
<b>UV 650-127</b>	<b>13.44</b>
<b>UV 650-230</b>	<b>7.27</b>

PANTONE 7541 C	Formula
<b>UV 650-TW</b>	<b>99.15</b>
<b>UV 650-233</b>	<b>0.47</b>
<b>UV 650-127</b>	<b>0.38</b>

PANTONE 7542 C	Formula
<b>UV 650-TW</b>	<b>96.48</b>
<b>UV 650-233</b>	<b>1.95</b>
<b>UV 650-114</b>	<b>0.98</b>
<b>UV 650-164</b>	<b>0.59</b>

PANTONE 7543 C	Formula
<b>UV 650-TW</b>	<b>93.97</b>
<b>UV 650-233</b>	<b>2.71</b>
<b>UV 650-114</b>	<b>1.66</b>
<b>UV 650-164</b>	<b>1.66</b>

PANTONE 7544 C	Formula
<b>UV 650-TW</b>	<b>86.95</b>
<b>UV 650-SB</b>	<b>6.58</b>
<b>UV 650-233</b>	<b>3.59</b>
<b>UV 650-121</b>	<b>2.88</b>

PANTONE 7545 C	Formula
<b>UV 650-TW</b>	<b>60.69</b>
<b>UV 650-SB</b>	<b>18.59</b>
<b>UV 650-233</b>	<b>12.91</b>
<b>UV 650-121</b>	<b>7.81</b>

PANTONE 7546 C	Formula
<b>UV 650-TW</b>	<b>23.89</b>
<b>UV 650-233</b>	<b>22.43</b>
<b>UV 650-MX</b>	<b>19.99</b>
<b>UV 650-SB</b>	<b>17.80</b>
<b>UV 650-121</b>	<b>15.89</b>

PANTONE 7547 C	Formula
<b>UV 650-SB</b>	<b>58.96</b>
<b>UV 650-127</b>	<b>35.27</b>
<b>UV 650-164</b>	<b>5.77</b>