

Chemicals for Konica NPS 4,5&6-series film processors
using CNK-4-40 process

The following products are recommended for use with Konica NPS 4, 5, & 6-series film processors using the Konica CNK-4-40 process.

Product	To make	Cat No
EnviroNeg Developer Replenisher Kit AC ⁽¹⁾	2 x 10L	954 693
EnviroNeg Developer Replenisher 60 AC	2 x 5L	998 518
EnviroNeg RA Bleach Replenisher 10 AC	2 x 5L	998 534
Negacolor RA Fixer & Replenisher	4 x 5L	992 016
	4 x 10L	992 024
EnviroNeg FF Superflo Stabilizer MB AC	2x (10 x 10L)	991 596

Starters	Conc	Cat No
EnviroNeg Universal Developer Starter AC	6 x 1L	972 497

⁽¹⁾ For low volume C41 processors you should consider the use of EnviroNeg Developer 60 AC (60 ml/135-24 film), giving the best possible negative quality.

Please see the Product Information Sheet for full details.

A Product Information Sheet (PIS) giving additional details, mixing instructions and technical information about Konica CNK-4-40 equivalent film chemistry can be found on our [Esclusivo](#) web site (for authorised users only).