

C-TOUCH MK2: Overview

All-in-one flexo water-wash processor

The C-TOUCH MK2 is an ideal system for small and medium-size companies to bring plate making in-house. An easy access all-in-one clamshell design provides efficient plate handling and in combination with Flenex FW plates, the C-TOUCH MK2 offers the industry's fastest plate-making times.

Key features

- ▶ All-in-one clamshell design
- ▶ Robust and reliable operation
- ▶ Best-in-class waste-water capabilities
- ▶ Remote diagnostics service
- ▶ Colour display and touch screen
- ▶ Integrated air gun and spray-nozzle
- ▶ Transport rollers for easy installation
- ▶ 3 versions available based on maximum plate size:
 - C-TOUCH MK2 2530:
63 x 76 cm
 - C-TOUCH MK2 3040:
76 x 102 cm
 - C-TOUCH MK2 3648:
92 x 122 cm

Produce plates as you need them

Combining the C-TOUCH MK2 with Flenex FW plates minimises platemaking processing times to under 40 minutes (depending on plate type). This is 3 times faster than leading solvent systems and 1.5 times faster than current thermal and water technologies.

Compact all-in-one design for efficient production

The clamshell design provides easy access for mounting and washing plates. It also includes pullout drawers for making exposure steps, light finishing and drying with temperature control. An air-gun and spray-nozzle are built-in for efficient cleaning and pre-drying.

Consistent, high quality plate output

High quality equipment design and build for consistent, reliable operation, every day. Back and forth orbital rotation achieves excellent relief washout that results in clean dot reproduction even for HD flexo.

Environmentally friendly system

With best in class waste water capabilities, the C-TOUCH MK2 is part of Fujifilm's on-going development program to deliver products with the lowest environmental impact.

Easy to use with comprehensive support

The user interface is accessible in different languages (selectable on the display), with English, German, Spanish, French and Italian available. In addition, Fujifilm's unique remote diagnostic services provide peace of mind, with fast and efficient support.




Specifications

C-TOUCH MK2	2530	3040	3648
Processor type	Clamshell	Clamshell	Clamshell
Maximum plate size	63 x 76 cm	76 x 102 cm	92 x 122 cm
Plates per hour*	5 – 6	5 – 6	4 – 5
Wash time*	10 minutes	10 minutes	12 minutes
External dimensions (W x L x H)	135 x 162 x 120 cm (190 when open)	130 x 198 x 120 cm (190 when open)	145 x 220 x 120 cm (210 when open)
Weight	642 kg	730 kg	990 kg
Filter dimensions	70 x 45 x 100 cm	70 x 45 x 135 cm	70 x 45 x 135 cm
Filtration weight	45 kg	48 kg	48 kg
Power requirements	400 VAC / 25 A 3 phase	400 VAC / 40 A 3 phase	400 VAC / 50 A 3 phase
Drip tray	180 x 172 x 5 cm	175 x 208 x 5 cm	190 x 230 x 5 cm

*Average productivity – depends on plate type. Times vary according to plate parameters.

All-in-one easy to use unit

- 1 Accessible exposure section
- 2 Accessible washout section
- 3 Colour display and touch screen
- 4 Integrated tools for comfortable working conditions: air gun for fast drying and water spray for easy cleaning
- 5 Easy access drying drawers
- 6 Double air cylinder for even closing of the lid on both sides
- 7 Transport rollers for easy installation



For further information:

Please contact your local Fujifilm partner.

web www.fujifilm.eu/flex **YouTube** Fujifilm Print **Twitter** @FujifilmPrint

Specifications are subject to change without notice. The name FUJIFILM and the FUJIFILM logo are trademarks of FUJIFILM Corporation. All other trademarks shown are trademarks of their respective owners. All rights reserved. E&OE.

FUJIFILM