

Chemicals for Agfa AP71 Film Processors

The following products are recommended for use with all Agfa AP71 process film processors, such as the following:

Agfa Minilab series FP1-71, FP2-71, FP3-71

Product	To make	Cat No
EnviroNeg Developer Replenisher LR Kit AC ⁽¹⁾	2 x 5L	990 101
	2 x 10L	954 743
EnviroNeg Developer Replenisher Kit AC	2 x 10L	954 693
EnviroNeg Developer Replenisher 60 AC	2 x 5L	998 518
EnviroNeg RA Bleach Replenisher 10 AC	2 x 5L	998 534
Negacolor RA Fixer & Replenisher	4 x 5L	992 016
	4 x 10L	992 024
EnviroNeg FF Superflo Stabilizer MB AC	2x (10 x 10L)	991 596

⁽¹⁾ For low volume C41 processors you should consider the use of EnviroNeg Developer AC (41ml/135-24 film) or even EnviroNeg Developer 60 AC (60 ml/135-24 film), giving greatly improved process quality and ease of use by avoiding the need to retank your developer regularly as film volumes decrease.

Starters	Conc	Cat No
EnviroNeg Universal Developer Starter AC	6 x 1L	972 497

A Product Information Sheet (PIS) for Agfa AP71 (C41B) film chemistry is available through [Esclusivo](#), giving mixing instructions and full technical details (for authorised users only).