

“Prescale” Pressure Measurement Film

Easily Visualize Surface Pressure Data





Pressure Measurement Film: “Prescale” Help you solve your challenges

● How to Use / Benefits of Use


1. Cut



2. Insert and Press





3. Check




- Deployed by over **10,000 customers** across more than **20 industries** in worldwide
- **Achieves high precision** using our microcapsule coating technology
- Available in 9 variants, covering a wide pressure range from **0.006 to 300 MPa**
- **Anyone can easily cut it to any size for use**
- When used in conjunction with our analysis app, **quantitative data can also be obtained**

● Customer Applications

Semiconductor : Checking the bonding pressure in the wafer bonding process



Others




Nip pressure



Tightening pressure



Contact pressure




Compression pressure




Squeegee pressure

Substrate : Checking the Laminate pressure



Automobile : Checking the body press pressure



<Sample request>

PRESCALE



<Contact>

FUJIFILM ASIA PASIFIC PTE.LTD

Advanced functional Materials Division

E-mail : yoshihiro.kumahara@fujifilm.com