

Chemicals for Agfa AP72 Film Processors

The following products are recommended for use with all Agfa AP72 process film processors, such as the following:

Agfa Minilab series FP100, FP200, FP1-72, FP2-72, FP3-72

Product	To make	Cat No
EnviroNeg Developer Replenisher LR Kit AC ⁽¹⁾	2 x 5L	990 101
	2 x 10L	954 743
EnviroNeg Developer Replenisher Kit AC	2 x 10L	954 693
EnviroNeg Developer Replenisher 60 AC ⁽²⁾	2 x 5L	998 518
EnviroNeg RA Bleach Replenisher AC	2 x 5L	971 135
EnviroNeg RA Bleach Replenisher 10 AC ⁽²⁾	2 x 5L	998 534
Negacolor RA Fixer & Replenisher	4 x 5L	992 016
	4 x 10L	992 024
EnviroNeg FF Superflo Stabilizer MB AC	2x (10 x 10L)	991 596

- ⁽¹⁾ For low volume C41 processors you should consider the use of EnviroNeg Developer AC (41ml/135-24 film) or even EnviroNeg Developer 60 AC (60 ml/135-24 film), giving greatly improved process quality and ease of use by avoiding the need to retank your developer regularly as film volumes decrease.
- ⁽²⁾ EnviroNeg Developer Replenisher 60 AC should be used in combination with EnviroNeg RA Bleach 10 AC.

Starters	Conc	Cat No
EnviroNeg Universal Developer Starter AC	6 x 1L	972 497

A Product Information Sheet (PIS) for Agfa AP72 film chemistry is available through [Esclusivo](#), giving mixing instructions and full technical details (for authorised users only).