

### Chemicals for KODAK RP30 and SRP30 Laser Printers

FUJIFILM has ADM Paper Cartridges to replace the original KODAK Ektacolor Processing Cartridge 75 used for the KODAK RP30 and SRP30 Laser Printers. There is also an ADM Paper Tank Kit available for all retanks.



Replenishment Rates must be adjusted (11% lower) on the minilab to suit FUJIFILM's recommendations.

You can use the following products in your KODAK RP30 and SRP30 Laser Printer:

Product	To make	Cat No
EnviroPrint ADM Paper Cartridge Developer	2 x 110 m <sup>2</sup>	997 569
EnviroPrint ADM Paper tank kit colour Developer	1 x 9.5L	993 808
EnviroPrint ADM Paper tank kit Bleach-Fix	1 x 9.5L	993 816
EnviroPrint FP Super Stabilizer	2 x (25 x 5L)	994 426

More information such as mixing instructions, replenishment rates and full technical details can be found in our Product Information Sheet (PIS), who is available on our Esclusivo web site (for authorised users only).