

Chemicals for E6 film processing

FUJIFILM offers two processes for developing E6 films. Fuji Hunt Pro6 chemicals are designed for pro labs and finishers. Photographers and small pro labs wishing to process in-house can use the 7-bath Chrome 6X chemistry which is available in a convenient 5L kit.

The Pro 6 range of chemicals has been designed for processing all brands of film compatible with the E6 process. Pro 6 chemicals are all-liquid and can be used in various types of automatic processing machines.

Pro 6 First Developer Replenisher and **Pro 6 Colour Developer Replenisher** are recognised as the highest quality products available for E6 processing, with superb colour and contrast rendition and unsurpassed process stability. They are of course totally compatible with all E6 films found in the market place.

Pro6 Reversal 2 has been introduced to give an improved process with the latest generations of film emulsions from all manufacturers.

Pro 6 Pre-Bleach 2 and **Pro 6 Final Rinse** have completed our product offering and have been very successfully introduced and accepted in the market. Using Pro 6 Pre-Bleach 2 and Pro 6 Final Rinse creates a safer and more user friendly working environment for the operators and your customers.

It is important to realize that all latest Colour Reversal films are being designed for processing using Pro6 Reversal 2, Pro 6 Pre-Bleach 2 and Pro 6 Final Rinse chemistry.

Fuji Hunt Pro 6 is rapidly becoming the industry standard for E6 processing. The chemical range gives exceptional process stability. Colour balance is optimally balanced to give excellent results not just with Fujifilm but with all major brands of film. What most impresses photographers is the clean whites, neutral grey tones and excellent D-Max. The extended contrast range also ensures superb shadow detail.

The following E6 chemicals are available:

Product	To make	Cat No
Chrome 6X Kit ⁽¹⁾	5L	979 641
Pro6 First Developer Replenisher	20L	994 645
	100L	944 652
	300L	944 660
Pro6 Colour Developer Replenisher Kit	20L	944 694
Pro6 Colour Developer Replenisher Part A	100L	944 702
	300L	944 710
Pro6 Colour Developer Replenisher Part B	100L	944 736
	300L	944 744
Pro6 Reversal 2 Bath & Replenisher	20L	991 323
	400L	991 331
	1200L	991 349
Pro6 Pre-Bleach 2 & Replenisher	2 x 20L	979 070
	200L	976 662
	600L	976 761
Pro6 Bleach Replenisher	20L	818 377
	60L	912 733
Super Unilec Fixer	40L	919 407
	200L (Cube)	918 060
	200L	916 445
	600L	954 123
Pro6 Final Rinse & Replenisher	6 x 20L	979 088
	2000L	976 670

⁽¹⁾ To be used by Photographers and small pro labs.

Starter	Conc	Cat No
Pro6 First Developer Starter	6 x 1L	944 637
Pro6 Universal Colour Developer Starter	6 x 1L	976 977
Pro6 Bleach Starter	6 x 1L	818 369

More information about this E6 chemistry, such as mixing instructions and full technical details are available on our [Esclusivo](#) web site (for authorised users only).