





















# Heatset

## PRODUCT TABLE

Water-based Coatings				Visual effect*	Suitable for Paper/Board	Properties
<b>UNIVERSAL COATINGS INLINE COATING UNIT</b>						
Single sided						
CoatMax S 40.70 HG	HG	P	For application with Jetweb coater			
CoatMax S 50.45 SM	S	P	For application with Jetweb coater			
* HG = High Gloss   S = Silk						
Washes				Flashpoint (C°)	Non VOC	Properties
<b>SUITED FOR NBR</b>						
Not water miscible						
WashMax 60.40 NM	62		Manual and automatic ink roller cleaning systems			
Water miscible						
WashMax 60.10 MI	64		Manual and automatic cleaning			
WashMax 100.20 BIO	105	x	Non VOC, automatic blanket washing systems			
WashMax 100.40 BIO	104	x	Maximum dryer security, improved cleaning properties			
Glues				Visc. (mPas)	Main glue systems	Properties
<b>CROSSWEB GLUEING</b>						
GlueMax D 90.16 HS	3,400		<b>Planatol</b> Crossweb			
<b>FOLD GLUEING</b>						
GlueMax D 90.14 HS	50		<b>Baldwin</b> Microset			
GlueMax D 90.11 HS	60		<b>Baldwin</b> Microset			
GlueMax D 90.15 HS	200		<b>Planatol</b> Combijet; <b>HHS</b> Vario glue			
GlueMax D 90.13 HS	240		<b>Planatol</b> Combijet; <b>HHS</b> Vario glue			
GlueMax D 90.50 HS	280		<b>Planatol</b> Combijet; <b>HHS</b> Vario glue			
GlueMax D 90.12 HS	2,000		<b>Planatol</b> Opimatic, <b>Baldwin</b> Webtack, <b>Valco</b> RoBond			
GlueMax D 90.17 HS	2,000		<b>Planatol</b> Opimatic, <b>Baldwin</b> Webtack, <b>Valco</b> RoBond			
<b>REMOISTABLE GLUEING</b>						
GlueMax D 90.20 HS	900		Jetweb Coater			
GlueMax D 90.41 HS	400		Jetweb Coater			
Founts				Dosage (%)	Properties	Properties
<b>IPA-FREE</b>						
FountMax Red 20.10 AF	3-4		For all dampening systems			
FountMax Red 20.21 AF	3-4		Reduced piling, extended washing intervals			
FountMax Red 20.90 AF	3-4		For use with FUJIFILM PRO-V and unbaked plates			
FountMax Red 22.21 AF	3-4		Strong buffer capacity, suited for hard water			

## Silicones

	Dosage (%)	Active content (%)	Properties	
<b>WITHOUT WAX</b>				
SilMax G60 CT	6-9	20	Optimum wetting	  
SilMax G70 CT	4-7	40	Optimum wetting	  
SilMax G80 CT	2-5	60	Optimum wetting	  
<b>WITH WAX</b>				
SilMax G60 CXT	6-9	20	Premium rub resistance	  
SilMax G70 CXT	4-7	40	Premium rub resistance	  
SilMax G80 CXT	2-5	60	Premium rub resistance	  

## Auxiliaries

<b>FOUNT AUXILIARIES</b>				
ANTI FOAM	Anti foam for the ready mixed fountain solution			 
XtraMax System Cleaner F15	Cleaning concentrate for the dampening water circuit			  
FOUNTCONTROL	Monitoring kit for the fountain concentration			 
IPAFIX	Economical substitute for isopropylalcohol, VOC reduction			   
XtraMax Water Mineral F12	Rehardener for RO water			  
XtraMax Damp Wash F10	Degreasing cleaner for the dampening rollers			  
WATER MINERAL S1	Rehardener for optimum water conditions, safety label free			   
<b>COATING AUXILIARIES</b>				
VARNISH REMOVER	Mild effective cleaner for water based coatings			  
ANILOX CLEANING GEL	Anilox cleaner for removing dried water based coating residues			  
<b>CLEANING AUXILIARIES</b>				
XtraMax Cylinder Wash C21	Protective cleaner for impression cylinders and other metal parts			  
REVIVAL GEL	Glaze remover for rollers and blankets			  
XtraMax Revival Wash R70	Rubber rejuvenator for roller and blankets - fast evaporation			  
XtraMax Rejuvenator Wash R73	Rubber rejuvenator for roller and blankets - medium evaporation			  
XtraMax Revival Wash R72	Rubber rejuvenator for roller and blankets - slow evaporation			  
XtraMax Hand Cleaner C31	Skin-friendly hand cleaner			
XtraMax Ink Cleaner I45	Powerful cleaner for dried ink residues			  
MULTICLEAN 2010	Multipurpose and powerful cleaner			   
<b>SPECIALITY CHEMICALS</b>				
XtraMax Anti-Static S90	Antistatic additive for the ready to use silicone emulsion			  
ANTISTAT LIQUID	Antistatic liquid for machine parts			  
XtraMax Cylinder Oil S92	Protection oil for rollers running idle			  
ROLLER PASTE	Protection paste for rollers when running idle			  
XtraMax Water Flow S85	Protective additive for water used in automatic cleaning devices			  
FORMASIL SPRAY	Universal silicone spray			 
XtraMax Cylinder Oil C15	Corrosion protective oil for all press parts			  
XtraMax Easy Fold S95	Folding concentrate			  

Specifications are subject to change without notice. The FUJIFILM name and logo, the PRESSMAX name and logo, the FountMax and CoatMax names are trademarks of FUJIFILM Corporation. All other trademarks shown are trademarks of their respective owners. All rights reserved.



Please contact your local Fujifilm partner for further information

**FUJIFILM Belgium NV**  
marketing\_ffbe@fujifilm.eu  
www.fujifilm.eu/pressmax

**FUJIFILM Italia S.p.A.**  
graphic.arts@fujifilm.it  
www.fujifilm.it

**FUJIFILM Deutschland  
Niederlassung der FUJIFILM Europe GmbH**  
grafische\_systeme@fujifilm.de  
www.fujifilm.de

**FUJIFILM UK Ltd**  
marketing\_fgs@fuji.co.uk  
www.fujifilm.co.uk/gs

**FUJIFILM Danmark A/S**  
fujifilm@fujifilm.dk  
www.fujifilm.dk

**FUJIFILM Graphic Systems France SAS**  
commercial@fujigraphic.fr  
www.fujifilmgraphic.fr

POWER TO SUCCEED

