



PRODUCT LIST

2020-2021

RA4 Process
MINILAB

September 2020
Version E01 / 09-20

I. FUJI HUNT RA4 PROCESSING

Catn°	Product Name	Conc	Size to make
ADM CARTRIDGE			
997569	EnviroPrint ADM Paper Cartridge *		2 x 110 m ²
DEVELOPER			
971657	<i>EnviroPrint General Developer Starter AC</i>	6x1L conc	
998104	EnviroPrint 47 Developer Replenisher AC		4x10L sz
994345	EnviroPrint Developer Replenisher MP60 AC		6x10L sz
994368	EnviroPrint Developer Replenisher MP60 AC	10L conc	50L sz
992911	EnviroPrint Developer Replenisher MP73 AC		6x10L sz
992917	EnviroPrint Developer Replenisher MP73 AC	10L conc	50L sz
990912	EnviroPrint Developer Replenisher MP108		6x10L sz
990994	EnviroPrint Developer Replenisher MP108	10L conc	50L sz
991702	EnviroPrint Developer Replenisher MP160		6x10L sz
991281	EnviroPrint Developer Replenisher MP160	10L conc	50L sz
BLEACH-FIX			
992420	<i>EnviroPrint Bleach-Fix MP Starter AC</i>	6x500mL conc	
998112	EnviroPrint 47 Bleach-Fix Replenisher AC		2x10L sz
995654	EnviroPrint Bleach-Fix Replenisher 55 AC		2x10L sz
995670	EnviroPrint Bleach-Fix Replenisher 70 AC		2x10L sz
995688	EnviroPrint Bleach-Fix Replenisher 70 AC Part A		50L sz
995696	EnviroPrint Bleach-Fix Replenisher 70AC Part B		50L sz
995712	EnviroPrint Bleach-Fix Replenisher 108 AC		2x10L sz
995720	EnviroPrint Bleach-Fix Replenisher 108 AC Part A		50L sz
995738	EnviroPrint Bleach-Fix Replenisher 108 AC Part B		50L sz
995746	EnviroPrint Bleach-Fix Replenisher 215 AC		2x10L sz
995753	EnviroPrint Bleach-Fix Replenisher 215 AC		50L sz
999622	EnviroPrint Bleach-Fix Replenisher MP215 AC		4x10L sz
STABILIZER			
990630	EnviroPrint Super Stabilizer AC		2x(10x10L) sz
976035	EnviroPrint Super Stabilizer AC		6x50L sz

* Check PIS682 for replacement for EnviroPrint ADM Paper Tank Kit Colour Developer & Bleach-Fix

* Check PIS 721 for replacement RA4 starters & TIS049 Starter substitution table for RA4 Developers

II. FUJI HUNT FAST PROCESSING

Catn°	Product Name	Conc	Size to make
DEVELOPER			
971657	EnviroPrint General Developer Starter AC	6x1L conc	
994186	EnviroPrint FP Developer Replenisher MR		6x5L sz
995472	EnviroPrint K15 Developer Replenisher MP90		4x12,5L sz
BLEACH-FIX			
992420	EnviroPrint Bleach-Fix MP Starter AC	6x500mL conc	
994178	EnviroPrint FP Bleach-Fix Replenisher MR		4x5L sz
STABILIZER			
994228	EnviroPrint FP Super Stabilizer AC	6x1L conc	

Check PIS 721 for replacement RA4 starters & TIS049 Starter substitution table for RA4 Developers