

型番	Product Name	FE185C086HA-1
焦点距離 [mm]	Focal length [mm] (design value)	2.7 (2.68)
絞り範囲 (F値)	Iris range (Fnumber)	F1.8 - F16
画角 (H × V)	Angle of view	185.0° × 185.0° (1" (φ8.6))
		185.0° × 140.6° (2/3")
		136.3° × 102.3° (1/2")
フォーカス範囲 (レンズ先端より) [mm]	Working distance (from front of lens) [mm]	∞ - 200
操作方法:フォーカス	Operation of focus	fixed
操作方法:アイリス	Operation of iris	Manual
フィルタ径 [mm]	Filter thread [mm]	-
マウント	Mount	C-mount
質量 (約) [g]	Weight (approx.) [g]	160
適合センサーサイズ (標準)	Sensor size (std.)	-
適合センサーサイズ (最大)	Sensor size (max.)	1" (5μm)
バックフォーカス (空気換算長) [mm]	Back focal length (in air) [mm]	9.75
フランジバック [mm]	Flange back [mm]	17.526
入射瞳位置 (マウント面から) [mm]	Entrance pupil position (from Mount) [mm]	-40.08
射出瞳位置 (結像面より) [mm]	Exit pupil position (from image plane) [mm]	-43.43
前側主点 (マウント面から) [mm]	Front principal point (from Mount) [mm]	-35.00
後側主点 (マウント面から) [mm]	Rear principal point (from Mount) [mm]	14.85
主点間隔 [mm]	Distance between the principal points [mm]	49.85
光学歪み [%]	Optical distortion [%]	-0.53 (y=f*θ)
外形寸法 [mm]	Dimension [mm]	φ56.5×52.2
主光線入射角度 [°]	Chief Ray Angle [°]	5.06
周辺光量比 (F4.0・φ8.6) [%]	Relative illumination [%] (Aperture: F4.0, Image height : at φ8.6)	94
	Relative illumination [%] (Aperture: at full open, Image height : at φ8.6)	82
使用温度範囲	Operation Temperature Range	-10℃~50℃
保存温度範囲	Storage Temperature Range	-20℃~60℃

These specifications are subject to change without notice.

05-Mar-20