

SB-938 FLW: Overview

All-in-one flexo water-wash processor

The SB-938 FLW is an ideal system for medium-size businesses looking to bring plate making in house. Its easy-access all-in-one autofeed design provides efficient plate handling. And in combination with Flenex FW plates, the SB-938 FLW offers the industry's fastest plate-making times.

Key features

- ▶ All-in-one autofeed design
- ▶ Robust and reliable operation
- ▶ Stable, chain-driven transport table to ensure optimum and even washing conditions.
- ▶ Automatic brush adjustment to ensure optimum brush pressure depending on plate thickness
- ▶ Brush frame and main tank can be moved for good cleaning access
- ▶ Best-in-class waste water capabilities
- ▶ Remote diagnostics service
- ▶ Colour touch screen operator interface with multiple language options
- ▶ Integrated air knife and spray bar
- ▶ Transport rollers for easy installation
- ▶ Maximum plate size:

SB-938 FLW:
92 x 122 cm

Produce plates as you need them

Combining the SB-938 FLW with Flenex FW plates can keep your plate processing times under 40 minutes (depending on plate type). This is 3 times faster than leading solvent systems and 1.5 times faster than current thermal and water technologies.

Compact all-in-one design for efficient production

The liftable sticky plate and autofeed design provides easy access for mounting and washing plates. The unit also includes pullout drawers for making exposure steps, light finishing and drying with temperature control. Air knife and spray bar are built-in for efficient cleaning and pre-drying.

Consistent, high-quality plate output

The SB-938 FLW features high-quality equipment design and a robust build that delivers consistent, reliable operation, day after day. Back-and-forth orbital rotation achieves excellent relief washout that results in clean dot reproduction – even for high definition flexo printing.

Environmentally friendly system

With best-in-class waste water capabilities, the SB-938 FLW is part of Fujifilm's on-going programme to deliver products with the lowest environmental impact.

Filtration system

In combination with the Aquarius water filtration system, the bath life of the SB-938 FLW can be considerably extended, helping to protect the environment by saving water. The Aquarius system also helps to save time and cost as it results in a cleaner processor, and extends the time between cleaning cycles.

Support when you need it

Fujifilm's unique remote diagnostic services provide peace of mind with fast and efficient support.



Specifications

SB-938 FLW	
Processor type	autofeed
Maximum plate size	92 x 122 cm
Plates per hour*	4
Water capacity	250 litres
Wash time*	15 mins
Air	6 bar/ 80 CFM
External dimensions (W x L x H)	192 x 335 x 120 cm (210 cm when open)
Weight	1450 kg
Filter dimensions	integrated
Power requirements	400 VAC / 50 A 3 phase
Drip tray	202 x 345 x 5 cm

*Average productivity. Times vary according to plate parameters.

All-in-one easy to use unit

- 1 Accessible exposure section
- 2 Accessible washout section
- 3 Colour display and touch screen
- 4 Integrated tools for comfortable working conditions: air gun for fast drying and water spray for easy cleaning
- 5 Easy access drying drawers
- 6 Double air cylinder for even closing of the lid on both sides
- 7 Transport rollers for easy installation



For further information:

Please contact your local Fujifilm partner.

web www.fujifilm.eu/flexen **YouTube** Fujifilm Print **Twitter** @FujifilmPrint

Specifications are subject to change without notice. The name FUJIFILM and the FUJIFILM logo are trademarks of FUJIFILM Corporation. All other trademarks shown are trademarks of their respective owners. All rights reserved. E&OE.

FUJIFILM