

Meet Demand with the

FUJIFILM

CX 3240 Creative Duplex Printer

Small Footprint, Big-Time Production

The CX 3240 Takes your On-Site Creative Products to the Next Level

- Greeting Cards & Invitations
- Photobooks & Calendars
- Counter Cards & more

Smart & Versatile

- Up to a 4 tray configuration allows for extreme versatility in size and substrate preference
- Auto duplex flat and folded card printing
- Borderless* printing with rounded corners or scalloped edge finishes
- Handles paper of greater weight & thickness up to 120 lb cover (324 gsm)
- Cards as small as 3.5" x 5" to images as large as 8.5" x 14"

Small Footprint

- Small footprint considering all of its capabilities

Easy & Efficient

- No post cutting required



*All print sizes except 8.5" x 11" and larger are borderless.

Printer includes 1 tray, but additional trays (up to 4 total) may be purchased separately. Printer as shown includes 3 trays.



Photo Cards



Calendars**



Photobooks**

**May require some additional finishing.

Total Photo Card Sales/Year

(Units in millions)

658
2017

661
2018

663
2019

Keypoint Intelligence

9 of 10 U.S. households purchase about 30 cards per year

Greeting Card Association

This includes 658M annual unit sales with revenues of \$522M

Keypoint Intelligence

CX 3240 Creative Duplex Printer Specifications

Print Technology	LED Printhead
Print Resolution	1200 x 2400 dpi
Print Speed	Simplex: 24 ppm (Letter); 23 ppm (A4) Duplex: 23.6 ppm (Letter); 22.6 ppm (A4)
Paper Sizes (Custom)	Minimum: 3.5 x 5 in; Maximum: 8.5 x 14 in (88.9 x 127 mm; 215.9 x 355.6 mm)
Paper Weight	140 to 324 gsm (for Approved Paper) Bypass Tray: 140 to 220 gsm
Dimensions (W x D x H & Weight)*	18.5 x 21.1 x 17.5 in; (470 x 536 x 444 mm) Approximately 86 lb/39 kg (with Toner Cartridges)
Power Requirements	AC100-127V ±10%; 12 A; 50/60Hz ±3%
Environment (When Printing)	Temperature: 41°F-90°F (5°C-32°C); Humidity: 15%-85%
Connectivity	Device Port x1 (USB 3.0)/Host Port x2 (USB 2.0), Ethernet 10/100/1000 Base-T
Consumables**	FUJIFILM Toner Cartridges: Cyan, Magenta, Yellow, Black FUJIFILM Drum Cartridges: Cyan, Magenta, Yellow, Black FUJIFILM Waste Toner Cartridge
Routine Maintenance Items**	Fusing Unit, Transfer Roller, Maintenance Kit, Paper Roller Kit

*Dimensions are for printer with 1 tray. Up to 3 additional trays may be purchased separately.

**Use of non FUJIFILM approved consumables and routine maintenance items may affect performance, warranty, and service contract availability. Descriptions and/or printer specifications in this material are subject to change.

Ask your Fujifilm Representative for a Demonstration of the CX 3240 Creative Duplex Printer.

For More Information: **877.845.1608**

FUJIFILM and Value from Innovation are a trademarks of Fujifilm Corporation and its affiliates.
©2019 FUJIFILM North America Corporation. All rights reserved.

FUJIFILM