

For the processing of color paper compatible with RA-4 Process in minilabs and Pro labs with minimum processing 150m<sup>2</sup>/week.


## PROCESS PARAMETERS

Tank	Product Name	Cat. No.	To Make	Per Bottle	Timing	Temp. (° C)	Repl. Rate	m/m
P1	UNIPACK 90 P1R	722222	2x10L	1L Single Part	45"	38.0 ± 0.3	90ml/m <sup>2</sup>	11.43
P2	UNIPACK 90 P2R	722223	2x10L	2.5L Single Part	45"	35.0 ± 3.0	90ml/m <sup>2</sup>	11.43
P3	CP-3R	822524	4x100L	1L Single Part	90"	35.0 ± 3.0	250ml/m <sup>2</sup>	31.75


Developer Starter: Use Cat. No. 830070 Universal Starter 6 x 1L

### REPLENISHER


**P1R**



**P2R**




**P3R**




### WORKING TANK

**P1**



**P2**



**P3**

