

For the Processing of Color Paper compatible with Roller Transport (RT) Process

PROCESS PARAMETERS


Process	Product Name	Cat. No.	To Make	Parts	Timing	Temp. (° C)	Repl. Rate	m/m
CD P1	CP RA Pro D/R	822545	2x40L	A=2L B=2L C=2L	45"	35.0 ± 0.3	215ml/m ²	27.31
BF P2	CP RA B/F/R	830083	2x25L	A=3.6L B=5L	45"	35.0 ± 3.0	215ml/m ²	27.31
W P3	WASH WATER	NA	NA	NA	90"	35.0 ± 3.0	2-11L/m ²	NA

P1S Developer Starter = CP RA Pro P1S (6 x 1L Conc.) - 822520
 P1R CP RA Pro D/R = Also available in 4 x 10L - 822540
 P2R CP RA B/F/R = Also available in 2 x 10L - 830045


REPLENISHER

WORKING TANK


P1R




P1




P2R



P2



P3R



P3

