

For the Processing of Color Paper compatible with RA-4 Process

PROCESS PARAMETERS


Process	Product Name	Cat. No.	To Make	Parts	Timing	Temp. (°C)	Repl. Rate	ml/m
CD P1	CD 161 P1R	822565	4x10L	A=500ml B=250ml C=500ml	45"	35.0 ± 0.3	161ml/m ²	20.45
BF P2	BF VR P2R	822536	2x20L	A = 2.5L B = 2.5L	45"	35.0 ± 3.0	215ml/m ²	27.31
STB P3	CP 3R	822524	4x100L	1L Single	90"	35.0 ± 3.0	250ml/m ²	31.75

P1S Developer Starter = Universal Print Starter 6 x 1L 830070
 CD 161 P1R is also available in 1 x 100L - 822575 (A:5L , B:2.5L , C:5L)


REPLENISHER

WORKING TANK


P1R




P1




P2R



P2



P3R



P3

