

For the processing of color paper compatible with RA-4 Process in minilabs with minimum processing 200m²/week.


PROCESS PARAMETERS

Tank	Product Name	Cat. No.	To Make	Per Bottle	Timing	Temp. (°C)	Repl. Rate	m/m
P1	UNIPACK 60 P1R	722333	2x10L	1.32L Single Part	45"	38.0 ± 0.3	60ml/m ²	7.62
P2	UNIPACK 60 P2R	722334	2x10L	2.85L Single Part	45"	35.0 ± 3.0	60ml/m ²	7.62
P3	CP-3R	822524	4x100L	1L Single Part	90"	35.0 ± 3.0	250ml/m ²	31.75


Developer Starter: Use Cat. No. 830070 Universal Starter 6 x 1L

REPLENISHER


P1R



P2R




P3R




WORKING TANK

P1



P2



P3

