

型番	Product Name	HF16SA-1
焦点距離 [mm]	Focal length [mm] (design value)	16 (16.33)
絞り範囲 (F値)	Iris range (Fnumber)	F1.4-F22
画角 (H × V)	Angle of view	30.2° × 22.9° (2/3")
フォーカス範囲 (レンズメカ先端より) [mm]	Working distance (from front of lens barrel) [mm]	∞ - 100
操作方法:フォーカス	Operation of focus	Manual
操作方法:アイリス	Operation of iris	Manual
フィルタ径 [mm]	Filter thread [mm]	M49 × 0.75
マウント	Mount	C-mount
質量 (約) [g]	Weight (approx.) [g]	285
適合センサーサイズ (標準)	Sensor size (std.)	2/3" (3.45μm)
適合センサーサイズ (最大)	Sensor size (max.)	2/3" (3.45μm)
バックフォーカス (空気換算長) [mm]	Back focal length (in air) [mm]	17.99
フランジバック [mm]	Flange back [mm]	17.53
入射瞳位置 (マウント面から) [mm]	Entrance pupil position (from Mount) [mm]	-38.25
射出瞳位置 (結像面より) [mm]	Exit pupil position (from image plane) [mm]	-191.63
前側主点 (マウント面から) [mm]	Front principal point (from Mount) [mm]	-24.15
後側主点 (マウント面から) [mm]	Rear principal point (from Mount) [mm]	1.20
主点間隔 [mm]	Distance between the principal points [mm]	25.35
TVディストーション [%]	TV distortion [%]	0.11
外形寸法 [mm]	Dimension [mm]	φ51 × 70.5
主光線入射角度 [°]	Chief Ray Angle [°]	1.29
周辺光量比 (F4.0・対角端) [%]	Relative illumination [%] (Aperture: F4.0, Image height : at diagonal)	100
周辺光量比 (開放・対角端) [%]	Relative illumination [%] (Aperture: at full open, Image height : at diagonal)	77
使用温度範囲	Operation Temperature Range	-10°C ~ +50°C
保存温度範囲	Storage Temperature Range	-20°C ~ +60°C

These specifications are subject to change without notice.

Entrance pupil position and Exit pupil position are calculated by "chief ray of 60% image height".