

型番	Product Name	TF4XA-1
焦点距離 [mm]	Focal length [mm] (design value)	4 (4.12)
絞り範囲 (F値)	Iris range (Fnumber)	F2.2-F16・Close
画角 (H×V)	Angle of view	64.5°×49.1° (1/3")
フォーカス範囲 (レンズメカ先端より) [mm]	Working distance (from front of lens barrel) [mm]	∞ - 100
操作方法:フォーカス	Operation of focus	Manual
操作方法:アイリス	Operation of iris	Manual
フィルタ径 [mm]	Filter thread [mm]	M27×0.5 (INSIDE) M30.5×0.5 (OUTSIDE)
マウント	Mount	C-mount
質量 (約) [g]	Weight (approx.) [g]	100
適合センサーサイズ (標準)	Sensor size (std.)	1/3" (6.7μm)
適合センサーサイズ (最大)	Sensor size (max.)	1/3" (6.7μm)
バックフォーカス (空気換算長) [mm]	Back focal length (in air) [mm]	14.01
フランジバック [mm]	Flange back [mm]	17.53
入射瞳位置 (マウント面から) [mm]	Entrance pupil position (from Mount) [mm]	-30.61
射出瞳位置 (結像面より) [mm]	Exit pupil position (from image plane) [mm]	-116.95
前側主点 (マウント面から) [mm]	Front principal point (from Mount) [mm]	-26.71
後側主点 (マウント面から) [mm]	Rear principal point (from Mount) [mm]	13.41
主点間隔 [mm]	Distance between the principal points [mm]	40.12
TVディストーション [%]	TV distortion [%]	-3.59
外形寸法 [mm]	Dimension [mm]	φ30.5×44.0
主光線入射角度 [°]	Chief Ray Angle [°]	1.26
周辺光量比 (F4.0・対角端) [%]	Relative illumination [%] (Aperture: F4.0, Image height : at diagonal)	95
周辺光量比 (開放・対角端) [%]	Relative illumination [%] (Aperture: at full open, Image height : at diagonal)	55
使用温度範囲	Operation Temperature Range	-10°C ~ +50°C
保存温度範囲	Storage Temperature Range	-20°C ~ +60°C

These specifications are subject to change without notice.

Entrance pupil position and Exit pupil position are calculated by "chief ray of 60% image height".

17-Oct-22