


### Features:

- 15 picoliter nominal drop size
- 512 individual addressable nozzles
- Incorporates VersaDrop<sup>TM</sup> binary jetting capability
- Excellent channel-to-channel uniformity
- High frequency continuous operation
- Designed for long service life
- Supports UV-curable, solvent, and aqueous-based inks
- Configurable for single- and two-color operation
- Integral mounting bezel with precision features
- Optimized for high viscosity jetting fluids
- Built-in heaters and temperature sensors
- Operation up to 60°C [140°F]
- Simplified field repair with no special tools required



Building upon the legendary reliability and performance of the Spectra Nova and Galaxy printheads, the Polaris PQ-512 AAA family of printheads uses field proven materials and a repairable design to deliver a long service life and consistent output. And by leveraging the inherent flexibility of the Q-Class platform, the Polaris PQ-512 AAA offers even greater jetting performance, nozzle packing density, and configuration flexibility.

The Polaris PQ-512/15 AAA Printhead has 512 independent channels arranged in multiple rows at 200 dots-per-inch spacing for single color operation, or 100 dots-per-inch spacing for two color operation. The printhead is designed for binary jetting using a 15-picoliter native drop size with 8-meters per second nominal drop velocity for jetting fluids in the 8 to 20 centipoise range. Using VersaDrop jetting technology, the printhead is capable of adjustable binary operation at drop sizes up to 30 picoliters.

The PQ-512/15 AAA Printhead is compatible with a broad range of inks, including UV-curable, aggressive organic solvent and aqueous inks and associated maintenance fluids.

The unique design of Polaris PQ-512/15 AAA Printhead allows each 256-channel module to be replaced and accurately registered in the field with no special tools or recalibration. An integral mounting bezel with precision registration points enables drop-in alignment with other carriage features.

Two electrical connectors contain eight serial data lines that supports fire frequencies in excess of 50 kHz.

The flexible fluid interface allows single and two-color operation. Each 256-channel module is dual ported to facilitate easy priming, flushing and ink recirculation. Heaters and temperature sensors allow precise control of ink viscosity at jetting temperatures up to 60°C.




www.dimatix.com




Parameter	Polaris PQ-512/15 AAA
Number of addressable jets	512
Print width	64.897 mm (2.555 inches)
NOZZLE SPACING:	
Single color (4 rows of jets)	127 microns [0.005 in.] (200 dpi)
Two color (2 rows of jets/per color)	254 microns [0.010 in.] (100 dpi)
Jet straightness, 1 sigma*	2.0 mrad [0.11°]
Nominal drop velocity	8 m/s
Calibrated drop mass	15ng
Compatible jetting fluids	UV-curable, organic solvents, aqueous
BINARY OPERATION:	
Adjustment for drop size	15 - 30 picoliters
Productivity	Drop Size Maximum Frequency
	15 pl 40 kHz
	30 pl 25 kHz
Operating temperature range	up to 60° C
Fluid viscosity at jetting	8 to 20 centipoise
Dry weight	160 grams


\*typical


# **Physical Characteristics**





# **Jetting Characteristics**





Product data presented above are for guideline purposes only. For design and engineering work using this product, please contact Dimatix Technical Support for the appropriate Product Manual containing full Product Specifications.



(2) 20-Pin Connectors

## Corporate Office:

FUJIFILM Dimatix, Inc. 2230 Martin Avenue Santa Clara, CA 95050

Tel: (408) 565-9150 Fax: (408) 565-9151 Email: info@dimatix.com

## New Hampshire Facility:

FUJIFILM Dimatix, Inc. 109 Etna Road Lebanon, NH 03766

Tel: (603) 443-5300 Fax: (603) 448-9870 Email: info@dimatix.com

#### Japan Office:

Advanced Marking Business Division FUJIFILM Corporation Midtown West, 7-3, Akasaka 9-Chome Minato-ku, Tokyo 107-0002

Japan

Tel: +81 3 6271 1091 Fax: +81 3 6271 1165 E-mail: front.ambd@fujifilm.co.jp

#### European Office:

Tel: +44 7739 863 505 Fax: +44 870 167 4328 Email: euro@dimatix.com

## Korean Office:

Tel: +82 2 6242 6012 Fax: +82 2 6247 6012 Email: korea@dimatix.com China Office: Email: china@dimatix.com

www.dimatix.com