

| 型番 | Product Name | CF8ZA-1S |
|--------------------------|--|----------------------|
| 焦点距離 [mm] | Focal length [mm] (design value) | 8 (8.31) |
| 絞り範囲 (F値) | Iris range (Fnumber) | F1.8-F16 |
| 画角 (H × V) | Angle of view | 85.7° × 67.5° (1.1") |
| フォーカス範囲 (レンズメカ先端より) [mm] | Working distance (from front of lens barrel) [mm] | ∞ - 100 |
| 操作方法:フォーカス | Operation of focus | Manual |
| 操作方法:アイリス | Operation of iris | Manual |
| フィルタ径 [mm] | Filter thread [mm] | M52 × 0.75 |
| マウント | Mount | C-mount |
| 質量 (約) [g] | Weight (approx.) [g] | 180 |
| 適合センサーサイズ (標準) | Sensor size (std.) | 1.1" (2.5μm) |
| 適合センサーサイズ (最大) | Sensor size (max.) | 1.2" (2.74μm) |
| バックフォーカス (空気換算長) [mm] | Back focal length (in air) [mm] | 19.39 |
| フランジバック [mm] | Flange back [mm] | 17.53 |
| 入射瞳位置 (マウント面から) [mm] | Entrance pupil position (from Mount) [mm] | -52.17 |
| 射出瞳位置 (結像面より) [mm] | Exit pupil position (from image plane) [mm] | -93.99 |
| 前側主点 (マウント面から) [mm] | Front principal point (from Mount) [mm] | -44.95 |
| 後側主点 (マウント面から) [mm] | Rear principal point (from Mount) [mm] | 9.22 |
| 主点間隔 [mm] | Distance between the principal points [mm] | 54.17 |
| TVディストーション [%] | TV distortion [%] | -4.81 |
| 外形寸法 [mm] | Dimension [mm] | φ54 × 67.0 |
| 主光線入射角度 [°] | Chief Ray Angle [°] | 4.49 |
| 周辺光量比 (F4.0・対角端) [%] | Relative illumination [%] (Aperture: F4.0, Image height : at diagonal) | 97 |
| 周辺光量比 (開放・対角端) [%] | Relative illumination [%] (Aperture: at full open, Image height : at diagonal) | 38 |
| 使用温度範囲 | Operation Temperature Range | -10°C ~ +50°C |
| 保存温度範囲 | Storage Temperature Range | -30°C ~ +60°C |

These specifications are subject to change without notice.

20-Aug-20