

For the Processing of Color Film compatible with C-41RA Process


PROCESS PARAMETERS

Process	Product Name	Cat. No.	To Make	Parts	Timing	Temp. (°C)	R/R 24 exp./36 exp.
CD N1	Nega LR D/R	873205	4 x 10L	A=800ml B=195ml C=250ml	3'15"	37.8 ± 0.3	19.8 29
BL N2	Nega RA N2R	873801	2 x 5L	Single (RTU)	45"	37.8 ± 3.0	5 7.5
FIX N3	Nega RA N3R	873831	4 x 10L	2.5L Single	1'30"	37.8 ± 3.0	33 50
STB N4	CN4R	815317	4 x 100L	1L Single	1'05"	37.8 ± 3.0	40 59


N1 Developer Starter = Nega LR N1S 873213
 N1R Nega LR D/R = Also available in 2x50L 873208 (A:4L, B:975ml, C:1L)
 N2 Bleach Starter = CN2RS 815305

REPLENISHER


N1R




N2R



N3R




N4R




WORKING TANK


N1



N2



N3



N4

