
FUJ!FILM



Jet Press 750S

PRODUCT BROCHURE

Powerful third generation B2 sheet-fed digital inkjet press






The market is changing

The world of commercial print is changing fast. Long run jobs are becoming more and more unprofitable as overcapacity in the market drives down prices and run lengths continue to reduce. Print buyers, on the other hand, need shorter and shorter print runs and ultra-fast turnarounds, but with no compromise in quality. It is medium run jobs that are feeling the squeeze. We are going through a transition to a situation where high quality, valuedriven, short run jobs will be the norm, where turnaround times will be hours not days, and where long run jobs will be the exception not the rule.

Your business needs to adapt to this change through the adoption of new technologies tailored to this new world of print. This is where forward-thinking printers can prepare for the future and position their businesses at the forefront of these developments. B2 inkjet is the perfect technology to address these changing market conditions, and the Jet Press 750S is without doubt the front runner.




The nature of print is changing, with the classic long run vs short run print model set to be turned on its head.



We're very conscious that the market is changing and that shorter and shorter runs are becoming the norm."

ROY KILLEN Managing partner, Push Print




Jet Press 750S: Transforming short-run print

Digital printing has come a long way in the last twenty years, with toner-based technologies having had the most success in delivering on demand print. Despite this success, however, the majority of commercial print is still produced using traditional offset presses. This is because toner-based technologies do not deliver the quality and productivity required to drive many more print jobs to digital.



Ultimately, we are convinced that inkjet technology is the future for high quality, short run print."

SANDRA HAKET
Co-owner, Impressed Druk en Print




The potential of the Jet Press 750S to transform short-run printing is huge.


Fujifilm Inkjet Technology

Over the last ten years, however, Fujifilm's inkjet deposition technologies have evolved to such an extent that our single pass Samba printheads are able to deposit ink at the speeds and quality levels required by the discerning consumers of commercial print. It is these printheads, combined with sophisticated control systems, ink and paper handling technologies, that are now set to ignite a revolution in the way that commercial print is produced, as they address the rapid changes that are taking place in the market.


The evolution of the Jet Press

The Jet Press 720S was the first B2 inkjet press to gain a foothold in this market, and was ahead of the game in terms of productivity and quality. And with around 150 Jet Press installations worldwide, more and more print buyers are now recognising what you can achieve with the inkjet technologies built into this groundbreaking press. But with the steady increase in the number of short run jobs, and the introduction of the Jet Press 750S, capable of printing 3600 sheets per hour, more and more jobs are going to fit the sweet spot of this industry-leading press.






Jet Press 750S: The perfect blend of old and new



The Jet Press 750S is the perfect blend of the old and new. The other

Combining the best in offset paper handling with the best digital inkjet technologies not only makes perfect sense, it represents the third generation of this ground-breaking press. Built on an offset chassis, it features superb sheet-to-sheet registration, and combined with the industry's leading Samba inkjet deposition system, it is unique in delivering print quality that out-performs offset.

The other key advantage of an offset paper handling system is that the Jet Press 750S is ultra-reliable, with up-time figures comparable to a traditional offset press. Combine that with the latest inkjet printhead and ink technologies, software improvements, a more efficient maintenance regime and a completely new drying system, you get the fastest 4 colour, B2 sheet-fed digital press.








Productivity


Print buyers these days require ultra-fast turnaround times with no compromise to quality, and this is where the Jet Press 750S excels. With a productivity of 3600 sheets per hour, the Jet Press 750S is quite simply the fastest 4 colour, B2 sheet-fed digital press available.

This means the Jet Press 750S allows you to take on more work and get more sheets on the floor than with multiple toner digital presses. So if you produce a lot of short run print, the Jet Press 750S will revolutionise your business, improve the service you offer your customers and enhance your competitive edge.



THE FASTEST B2 SHEET-FED, FULL COLOUR DIGITAL PRESS AVAILABLE

Overall productivity is governed by more than just the top-line press speed. Job productivity can be defined as the combined effect of the following:




Pre-press preparation

The Jet Press 750S eliminates all the preparation and set-up time of an offset press. There are no plates to produce, no platesetters or processors to maintain, no make readies, no run up to colour, no waste sheets and virtually no pressroom consumables. It operates in the most efficient way possible – just send the PDF to the press and print.

In addition, the Jet Press 750S takes advantage of software improvements to ensure productivity is maximised. Job management is so efficient, that jobs can be prepared by XMF while the press is printing, ensuring continuous operation and no down-time. This even applies to data-hungry collated or personalised variable data jobs.

The Jet Press is so easy and quick to run that we can produce a day's worth of proofing in a few minutes, with the same quality and on the same paper stock as the final job. It's the fastest proofer we've ever had and it speeds up the approval process downstream too."

> JOHN EMMERSON sales director, Emmerson Press



With the Jet Press 750S, the production time for short run jobs is much lower.

Straight-forward operator use

The Jet Press 750S is also incredibly easy to use. This is partly down to the simplicity of the operator interface, but also down to the consistency of results, with minimal operator set-up and intervention required to achieve remarkably consistent, high quality print. With the Jet Press 750S, it is also possible to carry out the job management, including allocating new jobs, and certain press functions remotely via an iPad (optional extra).



Press up-time




The second element critical in determining overall press productivity is the up-time or time the press is available to print. The up-time of the Jet Press 750S is unprecedented for a digital press, with reliability figures comparable to an offset press, as it is built on an offset chassis with ultra-reliable paper handling technologies, combined with next generation Samba printheads. Up-time figures above 90% are typically quoted by current Jet

Press customers, with the Jet Press 750S set to improve on this even further. This is because the Jet Press 750S features a new printhead self-cleaning process. This includes a process called "Overflow Cleaning" which reduces the head cleaning frequency by carrying out the cleaning at times when the press is between jobs or the printhead assembly is moving back to the maintenance position.



1. Dried ink, dust or other contaminants on the print head nozzle plate can build up to cause mis-directed droplets or eventually block nozzles completely.



2. To remove these at an early stage a small amount of ink is secreted from the nozzle to "pick up" the contaminants.



3. The process is then reversed and ink is drawn back into the head.



4. Contamination is removed by the ink filtration system

Stable paper feeding

The printhead assembly in the Jet Press 750S also features a new Active Head Retraction (AHR) system to reduce the impact of any paper deformations on press operation. This system lifts the printbars from the drum when a paper deformation is detected (where the deformation is <3mm). This new system minimises the impact of paper deformation, and limits the number of times paper jams occur, maximising press up-time and productivity.



The up-time, at around 90%, is exceptional and has allowed us to significantly reduce our delivery times, something many of our customers have noticed and commented on."

> MARIO PERL - Vice president of production & supply chain management, posterXXL

The print bars are lifted away from the impression cylinder when a paper deformation is detected



The deformed paper passes through before the system automatically resumes printing


Press print speeds



The third key element in determining press productivity is the raw press speed. The Jet Press 750S has a productivity of 3600 sheets per hour, 33% faster than the Jet Press 720S, making it the fastest 4 colour, B2 sheet-fed digital press available. There are a number of technologies introduced in the Jet Press 750S that make this increase in press speeds possible:

i) New Samba printheads deliver higher frequency jetting

Printing on paper moving at the higher speed of 3600 sheets per hour in a single pass requires a similar speed upgrade to the number of droplets of ink deposited per second. The jetting frequency of the new generation Samba printheads has been increased from 25 kHz to 33 kHz to speed up dot placement, ensure superb accuracy, and counteract the increased effects of possible turbulence.




ii) New drying system

A completely new drying system has been introduced in the Jet Press 750S to increase the efficiency of the drying process and facilitate higher press speeds. In the new system, the printed sheet emerges from the imaging section of the press onto a transport belt heated via rollers, with a vacuum applied as the sheet passes through the drying section.


Drying is carried out via a combination of the heated belt and hot air applied from above. The vacuum applied to the transport belt ensures the sheet is dimensionally stable as the heat is applied, optimising the drying process. This new system can operate at higher speeds, and allows greater control and fine-tuning of temperatures, extending the range of substrates that can be printed.

This new drying system has the additional benefit of requiring 23% less power, resulting in significant environmental benefits.



iii) Larger sheet size

The Jet Press 750S also features a slightly larger sheet size, maximising the available print area and optimising productivity.



Productivity on the press floor




The final element that determines productivity is the time required to take the printed sheets and finish them. The Jet Press 750S has a number of features that help optimise this process.

High productivity book printing

Whether it's just a few books printed cut and stack, as shown below, or a longer run in folded sections, the Jet Press 750S can print all sheets in collated order, removing the need to handle stacks of different sections. That makes folding easier to manage and eliminates the gathering stage completely. Another bonus is that books can be bound as soon as the first sheets are printed when the Jet Press 750S is operating in collated print mode. As a result, the press and the binder can both be running the same job at the same time, a real advantage for fast turnaround work.

Optimised sheet dryness

Due to the new drying mechanism, more print jobs emerge from the press dry. With the wide variety of paper types and thicknesses that can be the printed using the Jet Press 750S, the new drying system means more types of paper and more print jobs are dry when they emerge from the press, meaning that either the back side can be printed sooner, or the job can be finished more quickly.







And, because we often print collated, the finishing time of many of the jobs we print on the press can be reduced by several hours."

HENNING ROSE CEO, Wegner GmbH



Be more productive with the Jet Press 750S

Printers investing in the Jet Press 750S can be more productive. They can take on more work and get more sheets on the floor than with multiple digital presses. They also have no pre-press plates or chemistry and no make readies, with the first printed sheet saleable. So if you produce a lot of short run print, the Jet Press 750S will revolutionise your business, improve the service you offer your customers and enhance your competitive edge.



With 30% of our run lengths now less than 700, 40% between 700 and 1500, and 30% over 1500, it was clear we could improve the efficiency and profitability of our shorter run work by investing in Fujifilm's Jet Press."

> BAS GRAVESTEIJN director, Impressed Druk en Print

THE FASTEST B2 SHEET-FED, FULL COLOUR DIGITAL PRESS AVAILABLE

Pre-press preparation,

Zero make readies

Press up-time

Typically >90%

Press print speed

3600 sheets per hour

On the floor productivity


Dryer sheets, quicker finishing

Ultra-high quality

The Jet Press 750S takes the print quality produced by a digital printing system to new heights thanks to a combination of fundamental Fujifilm technologies. The end result is stunning, vibrant colours, superb skin tones, extraordinary fine text and line detail, and incredible flat tints, all produced on standard coated or uncoated offset paper.

However, the perception of print quality is not only limited to the technical specifications. There is a tactile, emotional and physical element to a piece of high quality print that sets it apart. The Jet Press 750S is the only digital press that delivers on both the technical and the intangible qualities that buyers of offset print are so used to, setting it apart from any other press.

In many cases, Jet Press owners end up printing more on the press as their customers love the quality so much, they specify their work to be printed only on the Jet Press.









It starts in the workflow

Quality starts in the workflow with print jobs automatically flowing through XMF's print production process. Print jobs are pre-flighted, colour managed, imposed and ripped for output automatically. If manual intervention is required, however, to make last minute changes to production such as late file revisions or imposing for different finishing equipment, all the tools to manage this are built right into XMF.

The Jet Press 750S also takes advantage of unique Fujifilm FM screening algorithms that eliminate moiré and produce ultrasmooth tints.

COLOUR MANAGEMENT, WORKLOW AND SCREENING

For colour management, XMF ColorPath provides all the tools required to create and manage colour profiles that will allow the Jet Press 750S to match any chosen colour standards as defined by FOGRA, G7 or other organisations. Colour consistency from sheet-to-sheet and job-to-job is second to none with the Jet Press 750S, thanks to the consistency of the VIVIDIA ink formulations and manufacturing process. As such, most of the time there will be no need to adjust colour settings, but XMF ColorPath can be used to verify colour conformance to a given standard at any time. Want to start printing work on a new media type? Creating new profiles for new media takes no time at all whether the new media is coated or uncoated stock.

Comparison of screening technologies at 2x magnification



Print with standard AM screening



Jet Press 750S print with FM screening



REGISTRATION ACCURACY BETTER THAN OFFSET



Registration, registration

Quality is nothing without consistency. Because the Jet Press 750S makes use of an offset paper feed mechanism, which adjusts automatically when the paper size is selected, registration accuracy is superb. This removes one of the limitations of current digital printing systems, where the tolerance from sheet-to-sheet limits the jobs that can be run. With the Jet Press 750S, the registration and repeatability from sheet-to-sheet are second to none.

Industry-leading Samba printheads

There is no doubt that Samba printheads lead the industry in terms of performance. Fabricated using precision MEMS¹ technology, they can achieve 1200 x 1200 dpi native resolutions. However, they also take advantage of Fujifilm's unique VersaDrop technology, allowing the size and shape of each ink drop to be precisely controlled and placed on the paper. Thanks to VersaDrop technology, the ink droplets can be reproduced in four levels of greyscale, with the effective resolution therefore much higher.

The Jet Press 750S features a new generation Samba printhead technology that achieves even greater accuracy and higher quality, thanks to higher



frequency jetting and better stability. In addition, the new Samba printheads feature higher reliability and robustness for better long term performance.


¹ Micro Electro Mechanical System




LATEST GENERATION SAMBA 1200 X 1200 DPI PRINTHEADS

Automatic Nozzle Control

Quality is further enhanced through the use of a CCD sensor that makes any necessary alterations to the way the ink is discharged from the printhead in real time. The proprietary In-Line Sensor (ILS) system detects any nozzle and ink deposition inconsistencies, modifying the printhead nozzle map and ink deposition parameters in real time to correct deviations from the norm.



REAL-TIME CLOSED-LOOP QUALITY CONTROL



Reading Accuracy at Higher Press Speeds

In the Jet Press 750S, this system has now been moved to enable it to read the data directly without the need of a mirror, reducing the periodic maintenance required to clean the mirror. The resolution has also been doubled to enhance the reading accuracy at the higher press speed.



Ultra-consistent, high performance ink

The performance of the ink through the printhead onto the printed sheet is critical to delivering benchmark quality. So Fujifilm scientists made use of the company's advanced chemical technologies to develop a new water-based ink.

The result is VIVIDIA - a new range of high performance CMYK ink colours that have each been painstakingly developed to match the Samba printheads and achieve the best consistent performance on the widest range of standard offset papers. Ink grains as small as 0.5 trillionths of a litre, invisible to the naked eye, are discharged at high speed to deliver breathtaking print quality. In the Jet Press 750S, these inks have been refined even further, optimising the combined performance criteria of quality, drying and ink rub-off from sheet to sheet.



A wide colour gamut

One of the key advantages of the Jet Press 750S is its enhanced colour gamut – we call it 'MaxGamut' – that allows you to reproduce more spot colours and produce more vibrant print with just four CMYK inks, without having to add or swap special inks or toners to boost the colour.


Jet Press owners have told us that when their customers start to experience MaxGamut print, they start specifying the Jet Press to print their work. They have a unique advantage in the marketplace, as the quality surpasses other digital technologies and even what offset litho presses can achieve. This is a key differentiator that helps you stand out in a crowded and highly competitive market.

A wide colour gamut enables vibrant images to be reproduced and allows colour matching to the ISO 12647-2 standard, critical for mixed offset and digital production environments.



Rapid Coagulation Primer (RCP)

To counter the natural tendency of an ink droplet to spread when it hits the paper and ensure uniform ink formation whatever the paper type, the Jet Press 750S applies a Rapid Coagulation Primer (RCP) prior to ink deposition via an anilox roller. The RCP features a unique 'rapid coagulation ink' technology which prevents dot gain, and is a critical component in the formation of a high quality image.



Halftone dot comparison (magenta 20%)

BLEED-FREE INK COAGULATION TECHNOLOGY



Predict spot colour matching prior to printing

One advantage of MaxGamut is its ability to accurately reproduce a high percentage of Pantone colours. Via a simple calibration process within Fujifilm's XMF ColorPath Brand Colour Optimiser module, it is possible to profile the entire Pantone library for any chosen media type. This will ensure that each and every Pantone colour will be printed as accurately as physically possible.

What is unique to Brand Color Optimiser is the ability to see how accurately a Pantone colour will be printed before actually printing. This quality control tool provides assurance that a specific Pantone colour on a chosen media can be printed accurately within a specific Delta E variance, or in rare cases will indicate a specific Pantone colour is outside the gamut of the Jet Press 750S. This means decisions about printing a specific job can be made up front, and no time is wasted trying to achieve what is not possible.

Depending on the media used for printing, up to 90% of the Pantone library of 1872 colours can typically be printed with a Delta E of 3 or less providing an exceptional colour match on a four colour press.

Versatile

The Jet Press 750S is able to print on a wide range of substrates. As well as coated and uncoated offset paper, the press can print on carton board, photo canvas and some plastic materials. As a result, the opportunity to use the Jet Press 750S to diversify and open up new markets makes it an exciting proposition.



















BAS GRAVESTEIJN Director, Impressed Druk en Print

Print on standard coated & uncoated offset paper

The Jet Press 750S is unlike most other digital presses in that it can use standard offset paper, removing the need to use specialised coated digital paper. This means, for example, that a printer can take advantage of current paper stocks, simplifying inventory and reducing costs. But it also means that jobs printed on the Jet Press are potentially more cost-effective than those printed on other digital presses, as the paper is less expensive.

The use of offset paper also makes the Jet Press 750S much more versatile as it can take advantage of a multitude of different paper types and effects. In particular, the result on uncoated paper is stunning, with the effect of vibrant VIVIDIA inks on uncoated paper producing print with much greater impact than offset, with the additional benefit of the sheets being completely dry.

The Jet Press 750S achieves benchmark quality independent of paper type thanks to its integrated Rapid Coagulation Primer (RCP) system. This system coats the sheet with an ultra-thin, invisible film, providing a consistent environment for the coagulation of ink droplets and guaranteeing the highest print quality whatever the paper type.



A wide range of application possibilities



Coffee table books

The quality, format size and ability to print on standard offset paper make the Jet Press 750S ideal for the production of short run coffee table books.



Photography portfolios

High quality photography portfolios and photobooks are perfect for the Jet Press 750S, with the wider colour gamut able to deliver breathtaking images.



Brochures

Short run brochures are perfect for the Jet Press 750S, with the ability to personalise and print multiple language versions quickly and easily adding extra value.



Posters

High quality art posters are ideal for the Jet Press 750S, with the wide paper choice (coated and uncoated) and superb quality delivering perfect results time after time.



Variable data direct mail

The Jet Press 750S features a barcode system and high powered data servers to print every page on the fly, guaranteeing front and back page matching every time.



Book covers

The Jet Press 750S is perfect for single sided book jackets, with the consistent high quality and wide colour gamut helping books stand out from the crowd.



Calendars

With the ability to print on a wide variety of paper, high quality calendars up to B2 in size can be created quickly and easily, with personalisation an added bonus.

A large proportion of our work is photographic printing on canvas, and the Jet Press is perfect for this, delivering high quality print at a speed that simply would not have been possible for us prior to our Jet Press investment. But it doesn't stop there – we use it to produce a wide range of products, including our famous retro photos, premium photo books and personalised calendars. We have found it to be such a versatile machine that we can send almost any job to it."

MARIO PERL

Vice president of production and supply chain management, posterXXL



Printing on canvas

Thanks to improvements in the vacuum drum and ink chemistry, the Jet Press 750S can be used to print on canvas substrates, with the quality of results stunning. This adds another versatile option that allows owners of the Jet Press to explore new applications and revenue streams.



Suitable for offset post-press enhancements

A sheet printed by the Jet Press 750S can be dropped into existing finishing equipment and treated with the type of post-press enhancements that can be applied to an offset sheet. As a result, digital print can be treated like offset print more than ever before.



Print on 90 micron light-weight stock

The Jet Press 750S can print on 90 micron standard offset paper, and so is ideal for applications like light-weight foldout maps or leaflets.



Print on 340 micron heavy-weight stock

The Jet Press 750S can print on 340 micron stock, and so is ideal for applications like folders and even promotional packaging boxes. For heavier-duty folding carton applications, the press can be modified to take board up to 600 microns thick.




to

The ability to handle variable data is a fundamental advantage of a digital press, and the Jet Press 750S is no different.

One of the major advantages of the Jet Press 750S is its ability to handle variable data, with the press using a barcode system to guarantee front and back page matching. The barcode is printed in the non-image area of every sheet immediately after the paper leaves the input sheet stacker. Once the first side has been printed, the sheets are turned over and loaded into the sheet stacker once again. The press reads the barcode on every sheet as it leaves the stacker and downloads the correct page information before it prints the second side (in 2.2 seconds to be exact), guaranteeing front and back page matching.

The benefits of this capability extend beyond the obvious application of variable data personalisation. Jobs can also be printed 'collated' in page order to simplify and speed up the finishing process or improve the logistics for job distribution, making the production of versioned print jobs simple and straightforward.



Perfect for packaging



The packaging market is seeing a growing increase in the number of brand owners and specifiers who are looking to achieve greater shelf stand-out and differentiate their products from their competitors. At the same time they are also looking to reduce stockholdings, optimise supply chains and find digital press solutions that will allow them to more profitably print offset quality, customised packaging in much shorter and more frequent runs.

Delivering exceptionally consistent, high quality output ready for finishing on carton board or synthetic media, the Jet Press 750S already satisfies these requirements fully. In fact, around one third of all current European Jet Press customers already produce some form of packaging on the press. Capable of speeds up to 3600 B2 sheets per hour and variable data printing at full speed, the new Jet Press 750S is ideally suited to print versioned, short run packaging material to coincide with specific events, localities or store promotions.

Support for heavier weight folding carton stock

As an option, the Jet Press 750S can be modified to accommodate heavier weight folding carton stock from 0.2-0.6mm in thickness. This makes it ideal to print short run packaging applications.

Finishing solutions

Jet Press 750S printed sheets have been tested and found to be compatible with a wide range of analogue and digital coating, foiling, lamination and cutting solutions. An automatic bridge is also available to connect to online coating solutions.

Traditionally, clients in the packaging industry have doubted the ability of a digital press to match the quality of litho or flexo printing. However, our customers have been hugely impressed with the quality of what we have produced for them using the Jet Press. The Jet Press is now the benchmark platform in this sector."

MOHAMED TOUAL CEO, Packaging for Professionals







Fujifilm is now also able to offer a food safe ink, making the Jet Press 750S the first B2 digital press approved to print primary food packaging. This new, low migration, aqueous food safe ink complies with stringent primary food contact regulations, including Swiss Ordinance 817.023.21 and European Commission Regulation 1935/2004, and has been specially formulated to work with inline (via a bridge) and nearline UV or aqueous coatings.

"Packaging buyers want consistency and solid and bright colours, and the Jet Press delivers all of this. We believe packaging will grow in tandem with our commercial printing operation over the next few years, and the Fujifilm machines are essential to our success in this sector."

FRANCISCO MARTINEZ
CEO. Straub Druck & Medien AG

A powerful press requires a powerful workflow

Phoenix imposition and planning software

For companies looking to diversify into packaging, the Jet Press folding carton solution can also incorporate Phoenix imposition and planning software from tilia Labs. This software optimises the way jobs are planned, or 'ganged', for printing and can automate this process based on various priorities such as maximising the speed of production throughput or minimising substrate waste. The support for true shape nesting and any angle rotation, combined with the automated Al planning engine, means Phoenix planning is both quick and efficient.



Spot colour capability and XMF ColorPath Brand Color Optimiser

One of the key advantages of the Jet Press 750S is its enhanced colour gamut that allows more spot colours to be printed with just four CMYK inks, without the expense of special inks or toners to boost the colour. This makes it ideal for the production of folding carton packaging. In addition, via a simple calibration process within Fujifilm's XMF ColorPath Brand Colour Optimiser module, it is possible to profile the entire Pantone library for any chosen media type to ensure that every Pantone colour will be printed as accurately as possible.

What is unique to Brand Color Optimiser is the ability to see how accurately a Pantone colour will be printed within a specific delta E variance, before actually printing. This means decisions about printing a specific job can be made up front, and no time is wasted trying to achieve what is not possible.

A third generation press engineered to produce high quality print all day, every day

The Jet Press 750S has been built to produce high quality print all day, every day. The benefits of an offset paper handling system are obvious, and take advantage of technology that has evolved over many years to be ultra-reliable. But there are also many

improvements in the Jet Press 750S detailed on this page that improve quality even further, improve variable data handling, speed up job downloads, reduce the necessity for system downtime and minimise breaks in production due to press maintenance.





Sheet stacking

The final printed sheet emerges in the delivery area in the same way as a traditional offset press.



Paper cooling

Before the sheets leave the press, they pass under a bank of fans designed to optimise the sheet temperature and ink drying performance.



New drying system

A new drying system features a transport belt heated via rollers, with a vacuum applied to the sheet as it passes through this section. Drying is carried out via the heated belt and hot air applied from above. The vacuum ensures the heat is applied uniformly, keeping the sheet stable, and optimising the drying process.



Ultra-high capacity data servers

The servers are capable of transmitting variable data alongside printed output, facilitating efficient variable data production at the full press speed of 3600 sheets per hour.



5

Nozzle correction

Every sheet is scanned by the In-Line Sensor (ILS) with the system making any necessary alterations in real time. The system is mounted just after printing to ensure any adjustments are applied dynamically throughout the run.



New Samba printheads

The paper is fed onto the imaging cylinder where it is held by grippers and a vacuum, and four Samba print bars deposit the CMYK inks in a single pass. The unique vacuum system significantly enhances print quality and consistency.




Paper feed

Traditional sheet-fed paper feed mechanism ensures high registration accuracy and reliable operation.



Variable data scanning

To handle double sided variable data applications, a barcode is printed in the non-image area of every sheet. When the sheet is backed up, the barcode is read and the press downloads the right data for that sheet before printing.



Paper priming

The primer unit applies an ultra-thin film Rapid Coagulation Primer onto the paper via an anilox roller mechanism. The reaction of the primer and the water-based ink produces incredibly sharp dots and vibrant images on standard B2 coated paper.



Exceptional environmental performance

There are a number of significant environmental benefits with the Jet Press 750S. These include a reduction in raw materials, hazardous pressroom consumables and paper waste, along with the complete elimination of the plate production process. All these benefits mean that the Jet Press 750S has a much lower carbon footprint than an equivalent offset press.

Reduction in raw materials and paper waste

The advantage of digital print in terms of optimising the number of printed copies produced and minimising the overruns is a key benefit of the Jet Press 750S. In addition, the number of make readies is also considerably reduced. On some short-run jobs on older traditional sheet-fed presses, the number of make ready sheets can represent a significant percentage of the total run, up to 25% in some cases. This problem is eliminated with the Jet Press 750S as the make ready waste is virtually zero.

Elimination of plate production, water and waste

The Jet Press 750S eliminates all the elements involved in the production of plates. This includes the plates, platesetters, processors and associated chemistry, water and waste. Each one of these elements of a plate production system has a significant carbon footprint in terms of its life cycle, from design, manufacture, transport and use to eventual disposal.

Reduced power consumption

Thanks to the brand new drying system introduced in the Jet Press 750S, power consumption compared to the existing Jet Press 720S has been reduced by 23% from 428A to 330A.

Reduction of hazardous pressroom consumables

The Jet Press 750S also removes the need for a number of the pressroom consumables used on a typical offset press, for example founts, sprays and potentially harmful VOC washes, and of course significantly reduces the requirement for water. The Jet Press 750S requires only two consumables in addition to the water-based ink: a wash for the inkjet printheads and the Rapid Coagulation Primer solution applied to the paper prior to printing.


Lower carbon footprint


Fujifilm carries out a life cycle carbon footprint analysis for all the products it manufactures, a process which takes into account product design, manufacture, transport, use and eventual disposal. As a result, the company estimates that the carbon footprint of the Jet Press 750S compared to an equivalent B2 sheet-fed press (internal estimate) is approximately 25% less.

Recyclability of Jet Press print

Sheets can be easily recycled

The environmental performance of the Jet Press 750S is further enhanced by the ability of sheets printed by the press to be easily recycled. With normal water-based inks with no primer, the ink pigments sink into the structure of the paper, making them much more difficult to deink. With the Jet Press 750S, the use of the Rapid Coagulation Primer not only carefully controls the rapid coagulation of ink droplets on the surface, ensuring a much higher quality on a wide range of substrates, it also prevents the ink pigments from sinking into the structure of the paper, making them much easier to remove during the deinking and recycling process.





Normal water based inks

Fujifilm Jet Press technology

Score	Evaluation of deinkability
71 to 100 points	Good deinkability
51 to 70 points	Fair deinkability
0 to 50 points	Poor deinkability
Negative: failed to meet at least one threshold	Not suitable for deinking
0 to 50 points Negative: failed to meet at least one	Poor deinkability

The results of trials carried out by the International Association of the Deinking Industry (INGEDE) on sheets printed by the Jet Press 750S on coated paper indicate levels of deinking on a par with offset inks, with 85 out of a possible 100 points. These results represent a milestone in the ability to remove the ink from an inkjet printed sheet.

Technical specifications

Jet Press 750S		
Printing		
Printheads	Next generation Samba printheads	
Colours	4 colour, CMYK, extended gamut	
Resolution	1200 x 1200 dpi, VersaDrop technology with 4 level greyscale	
Productivity	Up to 3600 B2 sheets per hour (static and variable jobs)	
Workflow	XMF Workflow V6.x or later, or a third party workflow with XMF Processor	
Varable data capability	Yes, thanks to barcode system and high capacity data transfer	
Substrate		
Maximum sheet size	750 mm x 585 mm	
Printable area	733 mm x 567 mm	
Thickness	0.09 mm - 0.34 mm When configured for heavier, folding carton stocks: 0.2 mm – 0.6 mm	
Туре	Standard offset coated and uncoated paper Canvas Heavier duty folding carton board Some plastics	
Physical		
Dimensions	7.35m (L) x 2.65m (W) x 2.05m (H)* * The height when cover is open is 2293 mm	
Space requirements	10m x 5.2m x 3m including space for ancillary equipment	
Required weight bearing load	More than 2.2 tonnes/square metre	
Power requirements	330A/ 200-230VAC	
Operating environment	20 – 28°C, 40 – 60% RH	
Options		
Full sheet scanning		
Remote tablet operation		
Heavier duty stock capability (0.2 - 0.6mm)		
Paper conditioning unit		

Jet Press 750S	
Inks, Primer and Wash	
Inks, Primer, Wash	VIVIDIA CMYK inks Rapid Coagulation Primer (RCP) Nozzle cleaning wash
Ink light fastness	The inks have been tested for light fastness to the blue wool scale, achieving a very good blue wool step 6 rating with respect to ISO 12040
Shelf life	2 years under recommended warehouse conditions
Packaging	Inks, RCP and Wash in 10 litre packs

Fujifilm's food safe ink is compliant with the following regulations and standards:

Compliant with Food Contact Materials - Regulation (EC) 1935/2004

Compliant with Swiss Ordinance on Materials and Articles in Contact with Food (SR 817.023.21) as listed in annex 2 and 10 (lists A and B) - 01.05.2017 edition

Independently tested and certified as compliant with Commission Regulation (EU) No. 10/2011 on plastic materials and articles i ntended to come into contact with food

GMP (Good Manufacturing Practice) is installed and implemented as part of Fujifilm's ISO 9001 Standardintended to come into contact with food


(EC) No. 1907/2006 (REACH) - no with more than 0,1 weight from appendixes XIV and XVII acc. (Reference date: July 2017)

Independently tested and certified to be compliant with EN 71-3

Compliant with Regulation (EU) 528/2012 (Biocide Regulation)



Please contact your local Fujifilm partner or visit www.fujifilm.eu/print



For further information:

Web www.fujifilm.eu/print

www.imagineinkjet.com

YouTube Fujifilm Print
Twitter @FujifilmPrint

