

10x70 MTR-SX Specifications

Model	10x70 MTR-SX
Magnification	10 x
Objective diameter	70 mm
Coating	EBC Multi Coating
Field of view	5.3 °
Apparent field of view ^{*1}	49.7 °
Field of view at 1000m	93 m
Exit pupil	7 mm
Brightness	49
Eye relief	12 mm
Minimum focus distance ^{*2}	20 m
Adjustment rang for interpupillary distance	56 - 74 mm
Dioptric adjustment range	±5 m ⁻¹
Focus type	IF
Length	269 mm
Width ^{*3}	238 mm
Height	88.5 mm
Weight	1,880 g
Waterproof ^{*4}	2 m – 5 min
Operation temperature	-20 °C ~ +50 °C
Accessory	Objectif/Eyepiece lens caps, Soft case, Strap

Specifications are subject to change without notice

*1 Apparent field of view based on ISO14132-1:2002

*2 Varies depending on the observer's visual acuity

*3 When expanded

*4 Not usable underwater

10x70 MTR-SX 仕様

型番	10x70 MTR-SX
倍率	10 倍
対物レンズ有効径	70 mm
コーティング	EBC マルチコーティング
実視界	5.3 °
見かけ視界 *1	49.7 °
1000mにおける視界	93 m
射出瞳径	7 mm
明るさ	49
アイレリーフ	12 mm
最短合焦距離 *2	20 m
眼幅調整範囲	56 - 74 mm
視度調整範囲	± 5 m ⁻¹
フォーカス方式	IF 方式
長さ	269 mm
幅 *3	238 mm
高さ	88.5 mm
重さ	1,880 g
防水機能 *4	2 m - 5 分
使用温度範囲	-20 °C ~ +50 °C
付属品	対物／接眼レンズキャップ、ソフトケース、ストラップ

仕様は予告なく変更されることがあります

*1 ISO14132-1:2002 に基づいた見かけ視界の表記数値

*2 観察者の視力により変化します

*3 拡張時

*4 水中では使用できません