

# TECHNO-STABI TS 12x28WP Specifications

Model	TECHNO-STABI TS 12x28WP
Magnification	12 x
Objective diameter	28 mm
Coating	Super EBC FUJINON
Field of view	4.2 °
Apparent field of view *1	47.5 °
Field of view at 1000m	73 m
Exit pupil	2.9 mm
Brightness	5.4
Eye relief	16.5 mm
Minimum focus distance	3.5 m
Adjustment rang for interpupillary distance	56 - 70 mm
Dioptric adjustment range	±2 mm
Focus type	Center focus (CF)
Image stabilizer	Electronic gyro stabilizing system with Gimbal
Image stabilize range	± 3°
Length	148 mm
Width *2	109 mm
Height	74 mm
Weight	485 g (without batteries)
Waterproof	IPX7
Battery	Lithium (CR2) x 1
Continuous usable time	Approx. 30 hours *3
Operation temperature	-10 °C ~ +50 °C
Accessory	Objectif/Eyepiece lens caps, Soft case, Strap, Lithium (CR2) x 1

Specifications are subject to change without notice

\*1 Apparent field of view based on ISO14132-1:2002

\*2 When expanded

\*3 Depends on the type of battery used and operating environment

## テクノスタビ TS 12x28WP 仕様

型番	テクノスタビ TS 12x28WP
倍率	12 倍
対物レンズ有効径	28 mm
コーティング	Super EBC FUJINON
実視界	4.2 °
見かけ視界 *1	47.5 °
1000mにおける視界	73 m
射出瞳径	2.3 mm
明るさ	5.4
アイレリーフ	16.5 mm
最短合焦距離	3.5 m
眼幅調整範囲	56 - 70 mm
視度調整範囲	±2 mm
フォーカス方式	センターフォーカス (CF) 方式
防振方式	ジンバル構造による電子ジャイロ防振方式
防振制御角	± 3°
長さ	148 mm
幅 *2	109 mm
高さ	74 mm
重さ	485 g (電池含まず)
防水機能	IPX7
電池	Lithium(CR2) 1 本
連続使用可能時間	約 30 時間 *3
使用温度範囲	-10 °C ~ +50 °C
付属品	対物/接眼レンズキャップ、ソフトケース、ストラップ、Lithium(CR2)

仕様は予告なく変更されることがあります

\*1 ISO14132-1:2002 に基づいた見かけ視界の表記数値

\*2 拡張時

\*3 使用する電池の種類や使用環境により前後します