

A3 Colour Multifunction Printer

Apeos C3061 / C2561 / C2061

Functions & Specifications

Basic Specifications / Copy Function

Item	Description			
	C3061	C2561	C2061	
Type	Desktop / Console			
Memory Capacity	4 GB (Max: 4 GB)			
CPU	Dual Core 1.3 GHz			
Storage Device Capacity ^{*1}	256 GB			
Colour Capability	Full Colour			
Scan Resolution	600 x 600 dpi			
Printing Resolution	1,200 x 2,400 dpi			
Warm-up Time ^{*2}	[Embedded Plug-ins / Custom Services] ^{*3} When enabled: 26 seconds or less (23 degrees Celsius room temperature) When disabled: 22 seconds or less (23 degrees Celsius room temperature)			
Recovery Time (Recovery Time from Sleep Mode)	13.6 seconds or less (23 degrees Celsius room temperature)	11.0 seconds or less (23 degrees Celsius room temperature)		
Original Size	Maximum of A3, 11 x 17", 297 x 432 mm for both Sheet and Book			
Paper Size	Tray 1 ^{*4}	Max: A3, 11 x 17", Min: A5 SEF, Envelope ^{*5} , Postcard (100 x 148 mm) Custom Size: 90 x 98 mm to 297 x 432 mm		
	Tray 2, 3, 4	Max: A3, 11 x 17", Min: A5 SEF Custom Size: 140 x 182 mm to 297 x 432 mm		
	Bypass Tray	Max: A3, 11 x 17", Min: A5 SEF, Envelope ^{*6} , Postcard (100 x 148 mm) Custom Size: 89 x 98 mm to 297 x 432 mm		
	Image loss width ^{*7}	Lead edge 4.0 mm, Trail edge 2.0 mm, Right/Left edge 2.0 mm		
Paper Weight ^{*8,9}	Paper Tray	52 to 300 gsm / 14 lb. bond to 166 lb. index		
	Bypass Tray	52 to 300 gsm / 14 lb. bond to 166 lb. index		
First Copy Output Time	B/W ^{*10}	4.6 sec. (A4 LEF)	5.9 sec. (A4 LEF)	
	Colour ^{*11}	6.0 sec. (A4 LEF)	7.9 sec. (A4 LEF)	
Reduce / Enlarge	Size-to-Size	1: 1 +/- 0.7 %		
	Preset	50 %, 70 %, 81 %, 86 %, 115 %, 122 %, 141 %, 200 %		
	Variable	25 to 400 % (in 1 % increments)		
Continuous Copy Speed ^{*12}	A4 LEF / JIS B5 LEF / Letter LEF	B/W: 30 ppm, Colour: 30 ppm	B/W: 25 ppm, Colour: 25 ppm	B/W: 20 ppm, Colour: 20 ppm
	A4	B/W: 23 ppm, Colour: 23 ppm	B/W: 19 ppm, Colour: 19 ppm	B/W: 16 ppm, Colour: 16 ppm
	JIS B5	B/W: 17 ppm, Colour: 17 ppm	B/W: 14 ppm, Colour: 14 ppm	B/W: 11 ppm, Colour: 11 ppm
	JIS B4 / Legal	B/W: 20 ppm, Colour: 20 ppm	B/W: 16 ppm, Colour: 16 ppm	B/W: 13 ppm, Colour: 13 ppm
	A3	B/W: 17 ppm, Colour: 17 ppm	B/W: 14 ppm, Colour: 14 ppm	B/W: 11 ppm, Colour: 11 ppm
Paper Tray Capacity ^{*13}	Standard	520 sheets x 1-tray + Bypass Tray 96 sheets		
	Optional	1 Tray Module / 1 Tray Module with Cabinet: 520 sheets x 1-tray 3 Tray Module: 520 sheets x 3-tray		
	Max	2,176 sheets [Standard + 3 Tray Module]		
Continuous Copy ^{*14}	999 sheets			
Output Tray Capacity ^{*15}	Upper Center: 250 sheets (A4 LEF), Lower Center: 250 sheets (A4 LEF)			
Power Supply	AC220-240 V +/- 10 %, 8 A, 50/60 Hz common			
Maximum Power Consumption	1.76 kW (AC220 V +/- 10 %), 1.92 kW (AC240 V +/- 10 %) Sleep Mode: 0.4 W (AC230 V +/- 10 %) Low Power Mode: 43 W (AC230 V +/- 10 %) Ready Mode: 80 W (AC230 V +/- 10 %)			
TEC Value	0.33 kWh	0.25 kWh	0.21 kWh	

Item	Description		
	C3061	C2561	C2061
Dimensions	W 577 x D 659 x H 775 mm / W 22.8 x D 26.0 x H 30.6" W 577 x D 659 x H 878 mm / W 22.8 x D 26.0 x H 34.6" (when optional 1 Tray Module is installed.) W 587 x D 659 x H 1,126 mm / W 23.2 x D 26.0 x H 44.4" (when optional 1 Tray Module with Cabinet is installed.) W 587 x D 659 x H 1,126 mm / W 23.2 x D 26.0 x H 44.4" (when optional 3 Tray Module is installed.)		
Weight ^{*16}	63 kg / 139 lb. 75 kg / 166 lb. (when optional 1 Tray Module is installed.) 85 kg / 188 lb. (when optional 1 Tray Module with Cabinet is installed.) 87 kg / 192 lb. (when optional 3 Tray Module is installed.)		
Space Requirement ^{*17}	W 935 x D 659 mm / W 36.9 x D 26.0"		

*1: Storage Device Capacity is not totally available for customers.

*2: It may change depending on usage conditions.

*3: Embedded Plug-ins / Custom Services are enabled as factory default.

*4: 90 x 98 mm to 241 x 372 mm is available when the Envelope Feeder is on.

*5: Supported standard envelope sizes are Commercial#10, Monarch 7 3/4, DL, ISO-C4, etc.

*6: Supported standard envelope sizes are ISO-C4 and ISO-C5.

*7: Up to A3 size.

*8: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.

*9: 106 to 300 gsm, when the Envelope Feeder is on.

*10: A4 LEF / Monochrome priority mode.

*11: A4 LEF / Colour priority mode.

*12: The speed may be reduced due to the image quality adjustment.

*13: 80 gsm paper.

*14: Copy process may stop temporarily for stabilization of image quality.

*15: 70 gsm paper.

*16: Excluding Toner Cartridge.

*17: When the Bypass Tray is fully extended and the stopper of DADF is turned on. The maintenance space is not included.

Print Function

Item		Description
Type		Built-in type
Print Size	Tray 1	Same as the Basic Specifications / Copy Function
	Tray 2, 3, 4	Same as the Basic Specifications / Copy Function
	Bypass Tray	Max: A3, 11 x 17"; Min: A5 SEF, Envelope ^{*1} , Postcard (100 x 148 mm) Custom Size: 89 x 98 mm to 297 x 1,200 mm ^{*2}
	Image loss width ^{*3}	Same as the Basic Specifications / Copy Function
Continuous Print Speed ^{*4}		Same as the Basic Specifications / Copy Function
Printing Resolution	Standard	[PCL Driver] Standard: 1,200 x 2,400 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution: 1,200 x 1,200 dpi
	Optional	[Adobe® PostScript® 3™ Driver] High Speed (Standard): 600 x 600 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution: 1,200 x 1,200 dpi
Page Description Language	Standard	PCL5 / PCL6
	Optional	Adobe® PostScript® 3™
Network Protocol	Ethernet (Standard)	TCP/IP (lpd, IPP, Port9100, WSD, ThinPrint®)
Supported Operating System ^{*5}	Standard	[PCL Driver] Windows 11 (64 bit), Windows Server 2025 (64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit) [Mac OS Driver] macOS 26 / 15 / 14 / 13 / 12
	Optional	[Adobe® PostScript® 3™ Driver] Windows 11 (64 bit), Windows Server 2025 (64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit) macOS 26 / 15 / 14 / 13 / 12
Fonts	Standard	2 Japanese fonts (Heisei Mincho W3, Heisei Kaku Goshic W5), 19 European fonts, 1 Chinese font (Monotype Sung Light) PCL: 96 European fonts, 1 Chinese font (Monotype Sung Light), 4 multi language fonts (Andale Mono WT J, Andale Mono WT K, Andale Mono WT T, Andale Mono WT S) HP-GL: 1 stroke font
	Optional	Adobe® PostScript® 3™ Kit: 136 European fonts
Emulation (Standard)		TIFF, PDF, HP-GL (HP7586B), HP-GL2 / RTL (HP Design Jet 750C Plus), PCL5c / 6 (HP Color Laser-Jet 5500), XPS
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0,
	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)

Note: WSD stands for Web Services on Devices.

Note: XPS stands for XML Paper Specification.

*1: Supported standard envelope sizes are Commercial#10, Monarch 7 3/4, DL, ISO-C4, etc.

*2: Long paper of 106 to 220 gsm (Extra Heavyweight) is available. The printed papers are delivered to the Side Tray when Finisher-A3 is attached.

*3: Up to A3 size.

*4: The speed may be reduced due to the image quality adjustment. The printing speed may be reduced depending on the document.

*5: Please refer to our official website for the latest supported OS.

Scan Function

Item	Description	
Type	Colour Scanner	
Original Size	Same as the Basic Specifications / Copy Function	
Scan Resolution	600 x 600 dpi, 400 x 400 dpi, 300 x 300 dpi, 200 x 200 dpi	
Scan Speed	Same as the Scan Speed for the Duplex Automatic Document Feeder	
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T
	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)
Scan to Folder	Network Protocol	TCP/IP (WebDAV, HTTP)
	File Format	Monochrome binary: TIFF, PDF ^{*1} Grayscale: TIFF, JPEG ^{*2} , PDF ^{*1} Full colour: TIFF, JPEG, PDF ^{*1} , Highly compressed PDF ^{*1}
	Driver	TWAIN Interface support
	Operating System ^{*3}	Windows 11 (64 bit), Windows Server 2025 (64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit)
Scan to PC	Network Protocol	TCP/IP (SMB, FTP, SFTP)
	Operating System	Windows 11 (64 bit), Windows Server 2025 (64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit) ^{*4} macOS 26 ^{*5} / 15 ^{*5} / 14 ^{*5} / 13 ^{*5} / 12 ^{*5}
	File Format	Monochrome binary: TIFF, PDF Grayscale / Full colour: TIFF, JPEG, PDF, Highly compressed PDF
Scan to e-mail	Network Protocol	TCP/IP (SMTP)
	File Format	Monochrome binary: TIFF, PDF Grayscale / Full colour: TIFF, JPEG, PDF, Highly compressed PDF

*1: When CentreWare Internet Services is used.

*2: When Network Scanner Utility 3 is used.

*3: Please refer to our official website for the latest supported OS.

*4: SFTP is not supported.

*5: FTP is not supported.

Fax Function (Optional)

Item	Description	
Original Size	Max: A3, 11 x 17", Long document (Longest 600 mm ^{*1})	
Recording Paper Size	Max: A3, 11 x 17"; Min: A5	
Transmission Time	2 seconds and more but fewer than 3 seconds ^{*2}	
Transmission Mode	ITU-T G3	
Scanning Resolution	Standard	8 x 3.85 line/mm, 200 x 100 dpi
	Fine	8 x 7.7 line/mm, 200 x 200 dpi
	Super Fine (400 dpi)	16 x 15.4 line/mm, 400 x 400 dpi
	Super Fine (600 dpi)	600 x 600 dpi
Coding Method	MH, MR, MMR, JBIG	
Transmission Speed	G3: 33.6 / 31.2 / 28.8 / 26.4 / 24.0 / 21.6 / 19.2 / 16.8 / 14.4 / 12.0 / 9.6 / 7.2 / 4.8 / 2.4 kbps	
Applicable Lines	Public Switched Telephone Network (PSTN), PBX, Maximum 3 ports ^{*3} (G3-3 ports)	

*1: When Duplex Automatic Document Feeder is used.

*2: When A4 size document with approximately 700 characters is transmitted in standard image-quality (8 x 3.85 lines/mm) and in high-speed mode (28.8 kbps or faster, JBIG). Only indicates the time for transmitting the image information and does not include the communication control time. The total communication time will vary depending on the contents of the document, the type of machine receiving the fax, and line condition.

*3: No. of FAX lines is up to 3 ports. Port refers to number of channels for FAX.

Direct Fax Function (Optional)

Item	Description
Original Size	A3, JIS B4, A4
Resolution	Same as image quality indicated in Scanning Resolution for Fax Function
Transmission Speed	Same as the Fax Function
Applicable Lines	Same as the Fax Function
Supported Operating System*	[PCL Driver] Windows 11 (64 bit), Windows Server 2025 (64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit)
	[Mac OS Driver] macOS 26 / 15 / 14 / 13 / 12

* Please refer to our official website for the latest supported OS.

Internet Fax Function (Optional)

Item	Description
Original Size	A3, JIS B4, A4
Scanning Resolution	Same as the Fax Function
File Format	Format: TIFF-FX; Compression method: MH, MMR, JBIG
Profile	TIFF-S, TIFF-F, TIFF-J
Network Protocol	Transmission SMTP
	Reception SMTP, POP3
Interface	Standard Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T

IP Fax (SIP) Function (Optional)

Item	Description
Original Size	Same as the Fax Function
Scanning Resolution	Same as the Fax Function
Supported Protocol	SIP, JT-T.38
Coding Method	Same as the Fax Function
Interface	Standard Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T

Duplex Function

Item	Description
Paper Size	Max: A3, 11 x 17"; Min: A5 SEF Custom Size: 128 x 140 mm to 297 x 432 mm
Paper Weight†	52 to 256 gsm / 14 lb. bond to 142 lb. index

* It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.

Duplex Automatic Document Feeder B4-PC

Item	Description			
	C3061	C2561	C2061	
Type	1 pass, 2 sided scanning Duplex Automatic Document Feeder			
Original Size*1 / Paper Weight	Max: A3, 11 x 17"; Min: A6 38 to 128 gsm / 11 lb. bond to 34 lb. bond (In Duplex: 50 to 128 gsm / 14 lb. bond to 34 lb. bond)*2			
Capacity*3	130 sheets			
Scan Speed*4	Copy (A4 LEF, Simplex)	B/W: 30 ppm Colour: 30 ppm	B/W: 25 ppm Colour: 25 ppm	B/W: 20 ppm Colour: 20 ppm
	Scan	B/W: 80 ppm, Colour: 80 ppm (1 pass, 2 sided scanning: B/W 80 ppm, Colour 80 ppm) [Standard Document (A4 LEF / Letter LEF), 200 dpi, to Folder.]		

*1: Custom Size is 49 x 85 mm to 297 x 432 mm.

*2: Custom Sizes from 49 x 85 mm to 55 x 91 mm are available from 38 to 209 gsm.

*3: 70 gsm paper.

*4: The scanning speed varies depending on the documents.

Finisher-A3 (Optional)

Item		Description
Type	Center Tray	Stack
	Finishing Tray	Sort (Offset available ^{*1,2}) / Stack (Offset available ^{*1,2})
Paper Size	Center Tray	A4, A3
	Finishing Tray	Max: A3, 11 x 17"; Min: A6, Postcard (100 x 148 mm) Custom Size: 89 x 98 mm to 297 x 432 mm
Paper Weight	Center Tray	52 to 300 gsm
	Finishing Tray	52 to 256 gsm
Paper Capacity ^{*3}	Center Tray	A4 LEF: 125 sheets A4 SEF, A3: 50 sheets
	Finishing Tray	[Without Stapling] A4 LEF: 500 sheets, JIS B4: 250 sheets, A3 or larger: 200 sheets, Mixed Size Stacking ^{*4} : 250 sheets [With Stapling] 30 sets, or A4 LEF: 500 sheets, JIS B4: 250 sheets, A3 or larger: 200 sheets, Mixed Size Stacking ^{*4} : 250 sheets
Staple	Capacity	A4: 50 sheets (90 gsm or less), JIS B4 or larger: 30 sheets (90 gsm or less)
	Paper Size	Max: A3, 11 x 17"; Min: JIS B5 LEF Custom Size: 203 x 182 mm to 297 x 432 mm
	Paper Weight	52 to 256 gsm / 14 lb. bond to 142 lb. index
	Position	Single stapling, Dual stapling
Dimensions / Weight		W 465 x D 484 x H 248 mm / W 18.4 x D 19.1 x H 9.8" 11 kg / 25 lb.
Space Requirement (When connected to the main unit) ^{*5}		W 1,103 x D 659 mm / W 43.5 x D 26.0"

*1: [No Offset] is selected by factory default.

*2: Outputs less than 190 mm width are delivered without offset stacking.

*3: 70 gsm paper.

*4: When larger size sheets are stacked on top of smaller size sheets: 250 sheets (when large size sheets are smaller than A3) / 200 sheets (when large size sheets are A3 or larger). The same applies to when staple-free and stapled bindings are mixed or different stapling positions are mixed.

*5: Main Unit + Finisher-A3; when the paper support is pulled out and the Bypass Tray is fully extended.

Finisher-B5 (Optional)

Item		Description
Type	Center Tray	Stack
	Finishing Tray	Sort (Offset available ^{*1,2}) / Stack (Offset available ^{*1,2})
Paper Size ^{*3}	Center Tray	Max: A3, 11 x 17"; Min: A5 Custom Size: 148 x 148 mm to 297 x 432 mm
	Finishing Tray	Max: A3, 11 x 17"; Min: A5 Custom Size: 148 x 148 mm to 297 x 432 mm
Paper Weight ^{*4}	Center Tray	52 to 300 gsm / 14 lb. bond to 166 lb. index
	Finishing Tray	52 to 300 gsm / 14 lb. bond to 166 lb. index
Paper Capacity ^{*5}	Center Tray	200 sheets (80 gsm or less)
	Finishing Tray	[Without Stapling] A4: 2,000 sheets, JIS B4 or larger: 1,000 sheets, Mixed Size Stacking ^{*6} : 300 sheets [With Stapling] A4: 100 sets or 1,000 sheets ^{*7} , JIS B4 or larger: 75 sets or 750 sheets [With Booklet Finishing ^{*8}] 50 sets or 600 sheets [With Fold ^{*9}] 500 sheets
Staple	Capacity	Staple: 50 sheets (90 gsm or less) Staple-free Staple ^{*9} : 10 sheets (80 gsm or less)
	Paper Size	Max: A3, 11 x 17"; Min: A5 LEF Custom Size: 210 x 148 mm to 297 x 432 mm
	Paper Weight	Staple: 52 to 256 gsm / 14 lb. bond to 142 lb. index Staple-free Staple ^{*9} : 64 to 105 gsm / 18 lb. bond to 28 lb. bond
	Position	Single stapling, Dual stapling
Punch ^{*10}	Paper Size ^{*11}	Max: A3, 11 x 17"; Min: A5 LEF Custom Size: 210 x 148 mm to 297 x 432 mm
	Paper Weight	52 to 220 gsm / 14 lb. bond to 122 lb. index
	Number of Holes	2-hole / 4-hole punch
Booklet Finishing ^{*8}	Paper Size	Max: A3, 11 x 17", Min: A4, Letter Custom Size: 210 x 279 mm to 297 x 432 mm
	Capacity	Saddle Staple: 15 sheets; Single Fold: 5 sheets
	Paper Weight	Saddle Staple: 64 to 80 gsm / 18 lb. bond to 21 lb. bond ^{*12} Single Fold: 64 to 105 gsm / 18 lb. bond to 28 lb. bond
Dimensions ^{*13,14}		W 618 x D 653 x H 1,047 mm / W 24.4 x D 25.8 x H 41.3" With Booklet Maker Unit: W 618 x D 673 x H 1,076 mm / W 24.4 x D 25.8 x H 42.4"
Weight		28 kg / 62 lb. Punch Module: + 2 kg / 5 lb. Booklet Maker Unit: +10kg / 23 lb.
Space Requirement (When connected to the main unit) ^{*15}		W 1,522 x D 665 mm / W 60.0 x D 26.2" With Booklet Maker Unit: W 1,522 x D 671 mm / W 60.0 x D 26.5"

Note: Finisher-B5 is available only when an optional 1 Tray Module with Cabinet or an optional 3 Tray Module is attached to Main Unit.

Note: Kit Finisher-B4/B5 INST is required.

*1: The offset feature is set to disabled by factory default.

*2: Outputs whose weight is 257 gsm and more or width is less than 210 mm are delivered without offset stacking.

*3: Paper in the sizes larger than A3 or 11 x 17" or smaller than A5 are delivered to the Centre Tray.

*4: Documents may not be printed correctly depending on usage conditions. (52 to 55 gsm, 257 gsm and more)

*5: 70 gsm paper.

*6: When larger size sheets are stacked on top of smaller size sheets.

*7: 75 sets or 750 sheets with dual stapling.

*8: The Booklet Finishing function requires the optional Booklet Maker Unit for Finisher-B. Make a crease allows you to fold easily. After a job with the Booklet Finishing function specified has been output, the next job may not be delivered until the sheets are removed from the output tray. Also, if larger size sheets are stacked on top of smaller size sheets after a job with the Booklet Finishing function specified has been run, the next job may not be delivered until the sheets are removed from the output tray.

*9: Staple-free stapling does not have binding force equal to stapled stapling. Bound part may be easily separated depending on the paper, temperature, humidity, and how the page is turned over.

*10: The Punch function requires the optional 2/4 Hole Punch Module for Finisher-B.

*11: Available number of punch holes varies depending on the paper size.

*12: Covers can be up to 220 gsm (Extra Heavyweight).

*13: Inner connector within the body is excluded.

*14: When the Extension Tray is pulled out.

*15: Main Unit +Finisher-B5; When the paper support is pulled out and the Bypass Tray is fully extended.

Side Tray (Optional)

Item	Description
Paper Size / Paper Weight	Max: A3, 11 x 17", Min: A5 SEF, Envelope* ¹ , Postcard (100 x 148 mm) Custom Size: 89 x 98 mm to 297 x 1,200 mm 52 to 300 gsm / 14 lb. bond to 166 lb. index
Paper Capacity ²	100 sheets
Dimensions / Weight	W 328 x D 540 x H 198 mm / W 13.0 x D 21.3 x H 7.8" 3 kg / 7 lb.
Space Requirement (When connected to the main unit) ³	W 935 x D 659 mm / W 36.9 x D 26.0"

*1: Supported standard envelope sizes are Commercial#10, Monarch 7 3/4, DL, ISO-C4, etc.

*2: 70 gsm paper.

*3: Main Unit + Side Tray; When the Bypass Tray is fully extended and the stopper of DADF is turned on.

1 Tray Module (Optional)

Item	Description
Paper Size / Paper Weight	Max: A3, 11 x 17"; Min: A5 SEF Custom Size: 140 x 182 mm to 297 x 432 mm 52 to 300 gsm / 14 lb. bond to 166 lb. index
Feeding Capacity ¹ / Number of Tray ²	520 sheets x 1 tray
Dimensions / Weight	W 565 x D 650 x H 109 mm / W 22.3 x D 25.6 x H 4.3" ³ 15 kg / 34 lb.
Space Requirement (When connected to the main unit) ⁴	W 935 x D 659 mm / W 36.9 x D 26.0"

*1: 80 gsm paper.

*2: Up to 1 tray can be added.

*3: When excluding installing connections.

*4: When the Bypass Tray is fully extended and the stopper of DADF is turned on.

1 Tray Module with Cabinet (Optional)

Item	Description
Paper Size/Paper Weight	Max: A3, 11 x 17"; Min: A5 SEF Custom Size: 140 x 182 mm to 297 x 432 mm 52 to 300 gsm / 14 lb. bond to 166 lb. index
Feeding Capacity ¹ / Number of Tray	520 sheets x 1-tray
Dimensions ² / Weight	W 587 x D 650 x H 351 mm / W 23.2 x D 25.6 x H 13.9" ³ (Inside Dimension: W 437 x D 474 x H 147 mm / W 17.3 x D 18.7 x H 5.8") 23 kg / 51 lb.
Space Requirement (When connected to the main unit) ⁴	W 935 x D 659 mm / W 36.9 x D 26.0" ⁵

*1: 80 gsm paper.

*2: Including the foot part.

*3: When excluding installing connections.

*4: When the Bypass Tray is fully extended and the stopper of DADF is turned on.

*5: Excluding the space required for when the door opens completely.

3 Tray Module (Optional)

Item	Description
Paper Size (Tray2, 3, 4) / Paper Weight	Max: A3, 11 x 17"; Min: A5 SEF Custom Size: 140 x 182 mm to 297 x 432 mm 52 to 300 gsm / 14 lb. bond to 166 lb. index
Feeding Capacity ¹ / Number of Tray	520 sheets x 3-tray
Dimensions ² / Weight	W 587 x D 650 x H 351 mm / W 23.2 x D 25.6 x H 13.9" ³ 25 kg / 56 lb.
Space Requirement (When connected to the main unit) ⁴	W 935 x D 659 mm / W 36.9 x D 26.0"

*1: 80 gsm paper.

*2: Including the foot part.

*3: When excluding installing connections.

*4: When the Bypass Tray is fully extended and the stopper of DADF is turned on.

Exit 2 Tray

Item	Description
Paper Size / Paper Weight	Max: A3, 11 x 17"; Min: A5 SEF Custom Size: 140 x 182 mm to 297 x 432 mm 52 to 300 gsm / 14 lb. bond to 166 lb. index
Paper Capacity ¹	250 sheets ²
Paper output method	Stack

*1: 70 gsm paper.

*2: When installing the Exit 2 Tray, the Center Tray capacity is 250 sheets.

Notes

- 1) If the storage media of the base unit fail, loss of received data, accumulated data, registered setting data, etc. may occur. In no event shall "the company" be liable for any damages whatsoever arising from loss of data.
- 2) Functional spare parts will be available for at least 7 years after the product is no longer manufactured.

FUJIFILM

FUJIFILM Business Innovation Corp.

9-7-3, Akasaka Minato-ku, Tokyo
107-0052

fujifilm.com/fbglobal

FUJIFILM Business Innovation aims to address environmental issues through climate change mitigation and resource circulation efforts.

The available model varies depending on the country/region. Please ask the sales representatives for details.

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law : •Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. •Unused postage stamps, post cards, etc. •Certificate stamps stipulated by law. •Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

Trademarks •FUJIFILM, FUJIFILM logo and FUJIFILM iWpro are registered trademarks or trademarks of FUJIFILM Corporation.

•Apeos, DocuWorks and Working Folder are registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Microsoft, Active Directory, Azure, Microsoft Entra, Microsoft Edge, Excel, OneDrive, PowerPoint, SharePoint, Microsoft Teams, Windows, and Windows Server are registered trademarks of US Microsoft Corporation in the U.S. and other countries. •Apple, Mac, macOS, AirPrint, and AirPrint logo are trademarks of Apple Inc. registered in the U.S. and other countries and regions. •Adobe, Adobe logo, PostScript, and PostScript logo are either registered trademarks or trademarks of Adobe in the United States and/or other countries.

•Mopria, the Mopria Logo, and the Mopria Alliance word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. •QR Code is a registered trademark of DENSO WAVE INCORPORATED. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise, electronic shock may result in the case of a failure or short circuit.