

FUJIFILM

FUJINON

HYPER-CLARITY HC8x42 / HC10x42



LOOK TO THE CLEAR VIEW AHEAD

Discover what is yet to be seen with a hyper-clear field of view




Bright and clear field of view optimized for wildlife and nature observation

These high-quality binoculars are constructed of nine lens elements in seven groups that have been optimally placed to control distortion across the frame. The ED lens elements control chromatic aberration and Fujifilm's unique SUPER EBC FUJINON multi-coating has been applied to all light-transmitting surfaces, including the prism, for superior image resolution. This results in a bright field of view with minimal distortion and outstanding clarity to ensure total precision when you need it most.



Contrast-rich image



Advanced operability and premium design

Designed to be your trusted companion, the ergonomically engineered, easy grip body shape features high-quality metal texturing and slip-resistant elastomeric material to ensure excellent hand-held stability. With the addition of long eye relief for easy use even when wearing glasses, the the result is absolute user confidence.



Excellent reliability that withstands outdoor use in harsh conditions

A robust magnesium body that is both fog-proof and water-resistant is complemented by a water-repellent coating on objective lenses and eyepieces. Add PL and nebula filter compatibility* into the mix and you're ready for a wide range of conditions.

*M46x0.75

HC 8x42
UPC: 3126770613

HC 10x42
UPC: 3126770625

Specifications	HC8x42	HC10x42
Magnification	8x	10x
Objective Lens Diameter	1.6in (42mm)	1.6in (42mm)
Twilight Factor	28.1	17.6
Eye Relief	0.70in (18mm)	0.63in (16mm)
Real View	8°	6.5°
FOV@1000m	446ft (136m)	374ft (114m)
Minimum Objective Distance	7ft (2m)	7ft (2m)
Exit Pupil	0.20in (5.3mm)	0.16in (4.2mm)
Eye Width Adjustment Range	2-3in (57-76mm)	2-3in (57-76mm)
Eye Cup	Twist-up/Down type	Twist-up/Down type
Dimensions	5.4x5x2in (139x130x54mm)	5.3x5x2in (137x130x54mm)
Weight	Approx 28oz (786g)	Approx 27oz (778g)
Water-resistant	Up to 1m for 5 mins	Up to 1m for 5 mins
Filter Diameter	M46x0.75	M46x0.75



CF (Center Focus)
The focus on both the left and right can be adjusted by turning one dial.



ED lenses
These lenses have special glass with a low refractive index, reducing chromatic aberration for a clear view.



Water-resistant
These binoculars are airtight and nitrogen purged.



SUPER EBC FUJINON
This multi-coating increases light transmittance for bright, natural color reproduction.



Wide aperture
These binoculars have a large angle to capture a wider apparent field of view.



Bundled with
Objective lens caps.
Eyepiece caps.
Carrying case and neck strap.

PLEASE NOTE: 1) Due to Fujifilm's continuous product improvement process, specifications are subject to change without notice. 2) For safety, please read the instructions manual before use. 3) Never look directly at the sun as loss of vision can result. (4) HC binoculars are water-resistant but are not designed for underwater use.

Learn more about FUJIFILM Binoculars with FUJINON Optics. Visit: fujifilmbinoculars.com | Call: 800.659.3854 X533888 | Email: contactfuji@fujifilm.com

FUJIFILM North America Corporation, 200 Summit Lake Drive, Valhalla NY 10595. FUJIFILM, FUJINON and SUPER EBC FUJINON are trademarks of FUJIFILM Corporation and its affiliates. ©2020 FUJIFILM North America Corporation and its affiliates. All rights reserved.