

型番	Product Name	HF12.5HA-1S
焦点距離 [mm]	Focal length [mm] (design value)	12.5 (12.88)
絞り範囲 (F値)	Iris range (Fnumber)	F1.4-F16
画角 (H × V)	Angle of view	39.2° × 29.4° (2/3")
フォーカス範囲 (レンズメカ先端より) [mm] ※	Working distance (from front of lens barrel) [mm] ※	∞ - 20
操作方法:フォーカス	Operation of focus	Manual
操作方法:アイリス	Operation of iris	Manual
フィルタ径 [mm]	Filter thread [mm]	M25.5 × 0.5
マウント	Mount	C-mount
質量 (約) [g]	Weight (approx.) [g]	40
適合センサーサイズ (標準)	Sensor size (std.)	2/3" (6.2μm)
適合センサーサイズ (最大)	Sensor size (max.)	2/3" (6.2μm)
バックフォーカス (空気換算長) [mm]	Back focal length (in air) [mm]	15.09
フランジバック [mm]	Flange back [mm]	17.526
入射瞳位置 (マウント面から) [mm]	Entrance pupil position (from Mount) [mm]	-9.86
射出瞳位置 (結像面より) [mm]	Exit pupil position (from image plane) [mm]	-31.33
前側主点 (マウント面から) [mm]	Front principal point (from Mount) [mm]	-2.85
後側主点 (マウント面から) [mm]	Rear principal point (from Mount) [mm]	4.65
主点間隔 [mm]	Distance between the principal points [mm]	7.49
TV歪み [%]	TV distortion [%]	-1.95
外形寸法 [mm]	Dimension [mm]	φ29.5 × 29.5
主光線入射角度 [°]	Chief Ray Angle [°]	9.50
周辺光量比 (F4.0・対角端) [%]	Relative illumination [%] (Aperture: F4.0, Image height : at diagonal)	98
周辺光量比 (開放・対角端) [%]	Relative illumination [%] (Aperture: at full open, Image height : at diagonal)	36
使用温度範囲	Operation Temperature Range	-10°C ~ +50°C
保存温度範囲	Storage Temperature Range	-30°C ~ +60°C

※フォーカス範囲の定義をピント調整が可能な範囲に変更しました。(2020年3月)

05-Mar-20

Changed the definition of working distance to a range where focus adjustment is possible.(Mar. 2020)  
These specifications are subject to change without notice.