


## Faster printing. Compact footprint. Lighter weight.

Everything about the Frontier DX400W has been updated with the sole purpose being able to make the biggest impact possible on your business. It prints a 4" x 6" photo in standard mode in just 9.4 seconds, compared with its predecessor at 10 seconds. For high-volume applications, that time savings adds up. With space at retail and other markets at a premium these days, the Frontier DX400W has a footprint of just 1.83 ft<sup>2</sup> so it fits nearly anywhere. And it goes anywhere. Weighing in at about 38 lbs., it is easier to carry and bring to events.

<b>Print modes</b>	Standard mode High Quality mode Draft mode	<b>Ink supply units</b>	6 colors (C, M, Y, K, SB, P) Dye-based ink 250 ml volume per color
<b>Print size</b>	89 x 50 mm - 210 x 1000 mm	<b>Footprint</b>	1.83 ft <sup>2</sup>
<b>Print speed</b>	9.4 sec/sheet (4" x 6", Standard mode)	<b>Power supply</b>	AC100V-120V (50/60Hz) 7.0A AC220V-240V (50/60Hz) 3.5A
<b>Print resolution</b>	720 x 360 dpi / Draft mode 720 x 720 dpi / Standard mode 1440 x 720 dpi / High Quality mode	<b>Power consumption</b>	38
<b>Paper loading</b>	1 roll	<b>Dimensions (WxDxH)</b>	18.1" x 14.7" x 13.4"
<b>Paper types</b>	Glossy + Luster	<b>Weight (lbs.)</b>	38 (excluding paper, ink supply unit)

## Dimensions



**FUJIFILM**  
Value from Innovation



**FUJIFILM**

**FUJIFILM North America Corporation**  
200 Summit Lake Drive  
Valhalla, NY 10595

<http://www.fujifilm.com/us/en>



\*Requires options sheet feeder. \*\*As compared with the DX100. Specifications subject to change without notice. FUJIFILM and FRONTIER are trademarks of FUJIFILM Corporation and its affiliates. © 2024 Fujifilm North America Corporation and its affiliates. All rights reserved.

◀ The Frontier DX400W with optional sheet feeder

Produce a vast array of photo products



**The Frontier DX400W is faster, lighter and smaller.\*\***  
Produce a vast array of high-quality photo prints and products using both roll and flat sheet\* substrates in a printer that is more compact, lighter and prints faster.\*\*

## Premium photo quality.

The Frontier DX400W is purpose-built to print premium, high-quality images with a true-to-life representation of the photographed image. Fujifilm leverages its rich knowledge as a global photographic leader, to ensure every print has rich gradations and outstanding color reproduction. This is owed, in part, to our 6-color ink system, which adds sky blue and pink to the CMYK gamut. And, in part, to Fujifilm's superior image processing technology: ImageIntelligence™. This proprietary technology is built into every Frontier DX400W to automatically adjust for challenging conditions such as poor lighting, excessive backlight, high contrast, underexposure and overexposure.

## Go beyond the roll, with flat sheets.

Another significant distinguishing characteristic of the Frontier DX400W is its ability to print not just on roll paper, but also on flat sheets. The Frontier DX400W supports single-sided printing for tremendous versatility. Use the manual feed unit for smaller print runs or the optional sheet feeder to load up to 100 sheets for higher volume environments. Please note that the optional sheet feeder is sold separately and does not come in the package with the Frontier DX400W.



Sheet feeder (optional)



Manual feed unit

## Print Versatility.

The Frontier DX400W is versatile because it produces a wide range of photo prints using both roll paper and flat sheets.

With roll paper ranging from 5" to 8" wide, dozens of different prints can be created including square format, panoramic photos, party banners, and many other products that captivate customers.

## Easy Maintenance.

Maintaining the Frontier DX400W is easy because all tasks are accomplished from the front of the printer, such as scrap paper removal, replacing roll paper and changing ink cartridges. You no longer have to move the printer or awkwardly reach around to the back.

## Eco-friendly design.

Compared with the DX100, the power consumption of the DX400W has been reduced by half (53%). And by adopting a cartridge-free ink system, waste has also been cut in half (49%).

## 6-color ink system.

The Frontier DX400W uses a proprietary Fujifilm 250ml high-capacity, cartridge-free, 6-ink system. This helps reduce waste when compared to traditional cartridge systems.



6-ink system  
C M Y K +  
SB (Sky Blue) +  
P (Pink)