

型番	Product Name	HF25XA-5M
焦点距離 [mm]	Focal length [mm] (design value)	25 (25.07)
絞り範囲 (F値)	Iris range (Fnumber)	F1.6-F16
画角 (H x V)	Angle of view	20.0° x 15.0° (2/3")
フォーカス範囲 (レンズメカ先端より) [mm]	Working distance (from front of lens barrel) [mm]	∞ - 100
操作方法:フォーカス	Operation of focus	Manual
操作方法:アイリス	Operation of iris	Manual
フィルタ径 [mm]	Filter thread [mm]	M25.5 x 0.5
マウント	Mount	C-mount
質量 (約) [g]	Weight (approx.) [g]	72
適合センサーサイズ (標準)	Sensor size (std.)	2/3" (3.45μm)
適合センサーサイズ (最大)	Sensor size (max.)	1/1.2" (4.5μm)
バックフォーカス (空気換算長) [mm]	Back focal length (in air) [mm]	13.60
フランジバック [mm]	Flange back [mm]	17.526
入射瞳位置 (マウント面から) [mm]	Entrance pupil position (from Mount) [mm]	-22.15
射出瞳位置 (結像面より) [mm]	Exit pupil position (from image plane) [mm]	-79.47
前側主点 (マウント面から) [mm]	Front principal point (from Mount) [mm]	-5.38
後側主点 (マウント面から) [mm]	Rear principal point (from Mount) [mm]	-7.54
主点間隔 [mm]	Distance between the principal points [mm]	-2.16
TV歪み [%]	TV distortion [%]	-0.07
外形寸法 [mm]	Dimension [mm]	φ29.5 x 46.5
主光線入射角度 [°]	Chief Ray Angle [°]	3.73
周辺光量比 (F4.0・対角端) [%]	Relative illumination [%] (Aperture: F4.0, Image height : at diagonal)	95
周辺光量比 (開放・対角端) [%]	Relative illumination [%] (Aperture: at full open, Image height : at diagonal)	47
使用温度範囲	Operation Temperature	-10℃ ~ +50℃

These specifications are subject to change without notice.

10-May-19